


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200651555](#)
Status: **Active**
Overview: [Brad® Micro-Change® \(M12\) Connectors](#)
Description: Micro-Change® (M12) Single-Ended Cordset, 4 Poles, Female (90°) to Pigtail, 22 AWG, PVC Cable, 4.0m (13.12') Length



Series image - Reference only

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [120065](#)
Connector End A Micro-Change® (M12)
Connector End B Pigtail
IP Rating IP67
Overview [Brad® Micro-Change® \(M12\) Connectors](#)
Product Name Micro-Change® (M12)
Protocol N/A
Region America
Type Single Ended
UPC 78678875971

Physical

Cable Diameter 5.33mm (.210")
Cable Length 4.0m (13.12')
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Female-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PUR
Material - Contact Copper Alloy
Material - Coupling Nut Nickel-plated Brass
Material - O-Ring Fluoro-elastomer
Material - Plating Mating Gold over Nickel
Orientation 90° to Straight
Poles 4
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 22
Wire/Cable Type E152210

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 250V AC/DC

Material Info

Old Part Number 804001A09M040

Reference - Drawing Numbers

Sales Drawing SD-120065-027

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant/Exempted

REACH SVHC

Contained Per -
ED/79/2015 (17
December 2015)
2,4-Di-tert-butyl-6-(5-
chlorobenzotriazol-2-
yl)p

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS 50 Image
ELV Not Relevant

Search Parts in this Series

[120065](#) Series

This document was generated on 07/05/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION