



# 1339 Electrical Tape

## Polyester Film/Glass Filament Reinforced with Acrylic, Pressure-Sensitive Adhesive

### Data Sheet

- Excellent conformability
- High tensile strength
- High dielectric strength
- Class B (130°C)
- UL recognition

3M™ Electrical Tape 1339 is a polyester film/glass filament tape coated with a pressure-sensitive acrylic adhesive system. The polyester film/glass backing has excellent physical and electrical characteristics. The back side of the tape has a special coating which allows for an even, controlled unwind. It also promotes permanent anchoring in application. Typical applications for 1339 include lead anchoring, banding of coils, lead tape anchoring and other uses where tensile strength is needed.

#### UL Component Recognition

- Temperatures not exceeding 130°C

UL File Number E17385 A and B, Guide OANZ2. Underwriters Laboratories (UL) recognized products have been evaluated for use as components of end-product equipment that is listed or classified by UL. To achieve Underwriters Laboratories recognition, component construction must meet UL specifications and conditions of acceptability for proper and safe use of the component or product.

Properties	Typical Value*
Thickness <sup>1</sup>	6.5 mils (0,165 mm)
Breaking Strength <sup>1</sup>	275 lb./in (481 N/10 mm)
Elongation	5%
Adhesion to Steel <sup>1</sup>	35 oz/in (3,81 N/10 mm)
Dielectric Strength <sup>1</sup>	5,500V
Temperature Class	130°C
Insulation Resistance <sup>1</sup>	1x10 <sup>5</sup> megohms
Electrolytic Corrosion Factor <sup>2</sup>	1.0

\*Not recommended for specification purposes. Product specifications will be provided upon request.

<sup>1</sup>ASTM D-1000 Test Method

<sup>2</sup>3M Test Method

#### Important Notice

Technical information provided by 3M is based on experience and/or tests believed to be reliable, but their accuracy is not guaranteed and the results may not be relevant to every user's application. For this reason 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence. All questions of liability relating to 3M products are governed by the seller's terms of sale subject where applicable to the prevailing law

If any goods supplied or processed by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same or refund to the Buyer the price paid for the goods or services. Except as set out above, all warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.

3M and Scotchcast are trademarks of the 3M Company. Printed in the UK.

© 3M United Kingdom PLC, 1999

**3M United Kingdom PLC**  
**Electrical Products Group**  
**Hudson Road**  
**Bedford MK41 0HR**  
**Tel: 01234 268868**  
**Fax: 01234 229433**

**3M Ireland**  
**Electrical products Group**  
**3M House, Adelphi Centre**  
**Dun Loaghaire, CO. Dublin, Ireland**  
**Tel: (01) 2803555**  
**Fax: (01) 2803509**

**3M Innovation**

Jan. 2000