


CAMBLOCK PLUS

PCB
TERMINAL
BLOCKS

5mm Pitch Inline Screw PCB Terminal Blocks



- 1 to 12 pole terminals in 5mm pitch
- Available in horizontal or vertical orientations
- System provides same-side access as wire entry
- Useful in applications with restricted vertical access, e.g. covered enclosures
- Moulded in green UL94-V0 flame retardant PA66
- 2.5mm² (24-12AWG)
- Double row pins for enhanced board stability
-  approved

SPECIFICATION

Rating	20A/300V
Insulation resistance	500MΩ/500V
Withstand Voltage	AC2000V/1min
Contact Resistance	20mΩ (max)
Working Temperature	-40°C to 105+°C
Mouldings	UL94-V0 Flame retardant PA66
Pin/Terminal	Brass, tin plated
Cage Clamp	Steel, zinc plated
Screw/Torque	M2.5 Steel, zinc plated 0.4Nm
Recommended PCB hole size	ø1.4mm

Vertical

TYPE NO.	POLES	LENGTH
CTBP90VG/2	2	12.5mm
CTBP90VG/3	3	17.5mm
CTBP90VG/4	4	22.5mm
CTBP90VG/5	5	27.5mm
CTBP90VG/6	6	32.5mm
CTBP90VG/7	7	37.5mm
CTBP90VG/8	8	42.5mm
CTBP90VG/9	9	47.5mm
CTBP90VG/10	10	52.5mm
CTBP90VG/11	11	57.5mm
CTBP90VG/12	12	62.5mm





CTBP90VG



Horizontal

TYPE NO.	POLES	LENGTH
CTBP90HG/2	2	12.5mm
CTBP90HG/3	3	17.5mm
CTBP90HG/4	4	22.5mm
CTBP90HG/5	5	27.5mm
CTBP90HG/6	6	32.5mm
CTBP90HG/7	7	37.5mm
CTBP90HG/8	8	42.5mm
CTBP90HG/9	9	47.5mm
CTBP90HG/10	10	52.5mm
CTBP90HG/11	11	57.5mm
CTBP90HG/12	12	62.5mm



CTBP90HG

