


**Product Description:**

The all new designed IP66 Orbital™ bulkhead range are simple yet perfect for bulkhead applications. Engineered with a tough IK10 polycarbonate body and opal diffuser for even light output with no LED hot spots, all versions and accessories are impact resistant and designed to last. Available in two wattages, white and black housing, interchangeable eyelid bezels, emergency and microwave options. This range ticks all the boxes for any installation. Life not affected by frequent switching e.g. when used with occupancy controls.

**Product Image:****Product Features:**

- IP66 LED bulkhead not affected by frequent switching
- IK10 polycarbonate body and diffuser for maximum vandal resistance
- Rear entry access wiring compartment allows for easy installation
- Interchangeable eyelid bezel accessory available
- Separate 20mm conduit side entries
- Wall or ceiling mounted - accessories included
- Emergency and microwave options available
- Adjustable hold time and lux detector
- 1.5kV surge protection
- 3 year warranty

25W Polycarbonate IP66 Round LED Bulkhead

**Line Drawing Image****Product Specs:**

<b>Technology</b>	LED	<b>Number of LEDs</b>	136
<b>Lifetime L70 (hrs)</b>	25000	<b>Input Voltage</b>	180~240V AC
<b>Input Frequency</b>	50/60HZ	<b>Surge Protection (kV)</b>	1.5
<b>Power Factor</b>	0.9	<b>Dimmable</b>	No
<b>IP Rating</b>	IP66	<b>IK Rating</b>	IK10
<b>Operating Temp. (Max) °C</b>	40	<b>Optic Material</b>	PC
<b>Height (mm)</b>	105	<b>Overall Diameter (mm)</b>	360
<b>Recess Depth (mm)</b>	105		

## SKU Table and Ordering

Cat No.(SKU Code)	Wattage	Lumens	Lumens/Watt	Colour	Ra	Beam Angle	SDCM
EN-BH25W/40	25W	1800lm	72	4000K	80	120°	5
EN-BH25W/40MS	25W	1800lm	72	4000K	80	120°	5
EN-BH25W/40EM	27W	1800lm	66.67	4000K	80	120°	5
EN-BH25BLK/40	25W	1800lm	72	4000K	80	120°	5
EN-BH25BLK/40MS	25W	1800lm	72	4000K	80	120°	5
EN-BH25BLK/40EM	27W	1800lm	66.67	4000K	80	120°	5

## Compliance & Approvals:



## Warranty

Please contact Aurora for specifics concerning warranty on this product. The warranty is invalid in the case of improper use, installation, tampering, and removal of the Q.C. date label; installation in an improper working environment or installation not according to the current edition of the National Electric Code. Should this product fail during the warranty period it will be replaced free of charge, subject to the correct installation of the original product and subsequent return of the faulty unit. Aurora does not accept responsibility for any installation costs associated with the replacement of this product and Aurora reserves the right to alter specifications without prior notice.

### UK Enlite Sales

16 Alban Park Hatfield Road St. Albans  
AL4 0JJ

United Kingdom

Tel : +44 (0) 1727 83 66 11

Fax : +44 (0) 1727 83 66 22

### UK Enlite Distribution

Apex Park 6 Little Burrow Welwyn  
Garden City AL7 4SW

United Kingdom

Tel : +44 (0) 1707 35 18 20

Fax : +44 (0) 1727 35 18 21