



**Power supply unit, 1-phase, 100-240VAC/24VDC, 5A**

**Part no. PSG120E24RM**  
**Article no. 172892**  
**Catalog No. PSG120E24RM**

## Delivery program

Product range			Power supplies PSG
Subrange			power supply unit
Description			Power Boost via 1.5-fold rated operational current for 5 s PELV (EN 60204), SELV (EN 60950)
Phases			Single-phase
Input voltage range			85 - 264 V AC (120 - 375 V DC)
Nominal input voltage			100 - 240 V AC 125 - 250 V DC
Rated output voltage			24 V DC ( $\pm 2\%$ )
Rated output current		A	5
Setting range for the output voltage			24 - 28 V DC
Rated output power		W	120

## Technical data

### Input characteristics

Nominal input voltage			100 - 240 V AC 125 - 250 V DC
Input voltage range		V	85 - 264 V AC 120 - 375 V DC
Supply frequency			
Rated value		Hz	50/60
Range		Hz	47 - 63
Nominal current	$I_n$	A	< 2.2 bei 115 V AC < 1.1 bei 230 V AC
Inrush current limitation $I^2t$ (+25 °C)		A	< 35 A at 115 V AC < 35 A at 230 V AC
Mains buffering at nominal load		ms	
Mains failure bridging		ms	> 20 at 115 V AC > 125 at 230 V AC
Run-up time after mains voltage applied		ms	< 1000
Internal input fuse (device protection, not accessible)			T4 AH/250 V
Back-up fuse			6, 10, 16 A (recommended)
Tripping characteristic			B
Leakage Current			< 1 mA at 240 V AC
Short-term interruption			100% voltage dip, 1 cycle (20 ms at 50 Hz), automatic start

### Output characteristics

Rated output power		W	120
Rated output voltage			24 V DC ( $\pm 2\%$ )
Tolerance			$\pm 2\%$
Setting range for the output voltage			24 - 28 V DC
Nominal current		A	5
Derating from $T_{amb} > +50$ °C			> 50 °C (2.5% / °C)
Capacitive load starting			Max 10000 $\mu$ F
Heat dissipation		W	14.8
Efficiency		%	> 89 with 115 V AC > 90 with 230 V AC
Residual ripple and switching peaks			< 50 mVpp / < 150 mVpp
Can be switched in parallel			for redundancy, with 0 ring diode (PSG480R24RM/PSG960R24RM)

General characteristics

Housing			Aluminium
Status indication			green LED for "DC OK"
MTBF (mean time between failures)			> 800,000 h
Height		mm	121
Width		mm	50
Depth		mm	123.1
Weight		kg	0.72
Terminations			Screw terminal, pluggable
Stripping length		mm	7
Terminal capacity			
flexible with ferrules/solid		mm <sup>2</sup>	0.52 - 3.3 mm <sup>2</sup> (AWG 20 - 12)
Tightening torque		Nm	0.5
Ambient air temperature range		°C	
Operation		°C	-20 - +80 (> 50 °C derating)
Storage, transport	θ	°C	
Storage	θ	°C	-25 - +85
damp heat			< 95 % relative humidity at +25 °C, no condensation
Vibrations (IEC/EN 60068-2-6)			10 - 500 Hz at 30 m/s <sup>2</sup> (3 G max ) for 60 min. in X-axis, Y-axis, Z-axis directions
Mechanical shock resistance (IEC 60068-2-27)			30 g (300 m/s <sup>2</sup> ) in all directions
Pollution degree			2
Climatic class (IEC)			3K3 according to EN 60721

Safety and safety features

Transient overvoltage protection			Varistor
Current limitation at short-circuit			I <sub>Überstrom</sub> = 150 % der max. Ausgangsleistung
Overvoltage protection			Yes, against internal overvoltage
Insulation voltage			
Input/Output			4 kV AC (type test), 3 kV AC (routine test)
Input/PE			1.5 kV AC (type test), 1.5 kV AC (routine test)
Output/PE			1.5 kV AC (type test), 500 V AC (routine test)
Degree of Protection			IP20
Protection class			Class I with PE connection

Standards

			Electrical equipment of machines: IEC60204-1 (Overvoltage category III) Equipping power installations with electronic apparatus: EN 50178/IEC 62103 Safety extra-low voltage: PELV (EN 60204), SELV (EN 60950) Protection against electric shock: DIN 57100-410 CE: according to EMC Directive 2014/30/EU and Low Voltage Directive 2014/35/EU RoHS-compliant: RoHS Directive 2011/65/EU ITE: EN 55022, EN 61000-3-2, EN 61000-3-3, EN 55024 Industrial: EN 55011 Mains harmonics limitation: EN 601000-3-2 Electrical Safety (of IT equipment) : SIQ to EN60950-1, UL/c-UL recognized to UL 60950-1, CSA C22.2 No. 60950-1, CB scheme to IEC 60950-1 UL508 Class2: UL/c-UL recognized to UL1310 and CSA C22.2 No. 223   Component power supply unit for general use: EN61204-3
--	--	--	---

Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	I <sub>n</sub>	A	0
Heat dissipation per pole, current-dependent	P <sub>vid</sub>	W	0
Equipment heat dissipation, current-dependent	P <sub>vid</sub>	W	0
Static heat dissipation, non-current-dependent	P <sub>vs</sub>	W	14.8
Heat dissipation capacity	P <sub>diss</sub>	W	0
Operating ambient temperature min.		°C	-20
Operating ambient temperature max.		°C	80
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			Meets the product standard's requirements.


10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES		Meets the product standard's requirements.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9 Insulation properties		
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## Technical data ETIM 6.0

Low-voltage industrial components (EG000017) / DC-power supply (EC002540)			
Electric engineering, automation, process control engineering / Power supply / Power supply (other) / DC-power supply (ecl@ss8.1-27-04-90-02 [AFZ644012])			
Voltage type of supply voltage			AC
1st secondary output voltage	V		24 - 28
2nd secondary output voltage	V		0 - 0
3rd secondary output voltage	V		0 - 0
Max. output current 1	A		5
Max. output current 2	A		0
Max. output current 3	A		0
Secondary voltage adjustable			Yes
Nominal value output voltage 1	V		24
Nominal value output voltage 2	V		0
Nominal value output voltage 3	V		0
Nominal value output current 1	A		5
Nominal value output current 2	A		0
Nominal value output current 3	A		0
Short-circuit-proof			Yes
Rated supply voltage at AC 50 Hz	V		85 - 264
Rated supply voltage at AC 60 Hz	V		85 - 264
Rated supply voltage at DC	V		0 - 0
Output voltage stabilized			Yes
Power consumption	VA		253
Power output	W		120
Stabilized			Yes
Type of electric connection			Screw connection
Rail mounting possible			Yes
Wall mounting possible			No
Modular version			Yes
Width in number of modular spacings			0
Built-in width	mm		50
Built-in height	mm		121

Direct mounting possible		No
Width	mm	50
Height	mm	121
Depth	mm	1231
Suitable for safety functions		No
SIL according to IEC 61508		None
Performance level acc. to EN ISO 13849-1		None
Degree of protection (IP)		IP20

Dimensions



Additional product information (links)

IL125015EN Installation Instructions for PSG120E24RM POWER SUPPLY	
IL125015EN Installation Instructions for PSG120E24RM POWER SUPPLY	<a href="ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL125015EN2014_06.pdf">ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL125015EN2014_06.pdf</a>