

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1553219007](#)
Status: **Active**
Overview: [Flamar Standard Cables for Industrial Automation](#)
Description: Flamar Feedback Cable, WSOR Jacket, Braided Shielding Overall, 12 Circuits, 4x(2x22 AWG) + 4x(21 AWG), 9.50mm Diameter, 200.0m Length, Green

Documents:

[Product Specification 1553219001-P1E \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	155321
Bending Radius - Minimum	> 10xOD
Color - Cable Jacket	Green
Crimp Quality Equipment	Yes
Geographic Area	Global
Material - Outer Jacket	WSOR
Outer Jacket Diameter	9.50mm (.374")
Overview	Flamar Standard Cables for Industrial Automation
Product Literature Order No	987651-3992
Product Name	Flamar
UPC	889056461153

Physical

Cable Length	200.0m
Circuits (Loaded)	12 (8+4)
Insulation	TPE
Net Weight	0.010/g
Packaging Type	Reel
Temperature Range - Operating	-25°C to +80°C
Wire Size AWG	21, 22
Wire Size mm ²	0.34, 0.50
Wire/Cable Type	Servo Motor, UL AWM 21215 / CSA

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V

Material Info

Engineering Number	1X200M
--------------------	--------

Reference - Drawing Numbers

Product Specification	1553219001-P1E
-----------------------	----------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[155321](#) Series

Use With

Brad® M23 [120230](#) , [120233](#)