



Made in the  
United States of America

## Description

Conductive Drum Liners 2014 do not hold static charge when grounded. Commonly used as waste container liners.

## Specifications

Type	Test Method	Value
Thickness		4.0 mil (0.0040", 0.1016mm)
Tensile Strength	ASTM D882	
MD		2,500 psi (1,724 N/cm <sup>2</sup> )
CD		2,000 psi (1,379 N/cm <sup>2</sup> )
Puncture	Fed Std 101	8lbs
Electrical Properties		
Volume Resistivity	ASTM D991	<500 ohm-cm
Chemical Susceptibility		
Dilute Acids and Alkalies	ASTM D543	Resistant
Alcohols (Isopropanol)		Resistant
Hydrocarbons (Acetone)		Moderate attack
Ketones (Acetone)		Slight attack
Gasoline		Moderate attack
Aromatic Hydrocarbons (Toluene)		Severe attack

Item	Size	Gallon Size	Quantity
<a href="#">2014 18X24</a>	18" x 24"	5	100 / Box
<a href="#">2014 38X58</a>	38" x 58"	55	50 / Box

Unless specified tolerance is  $\pm 10\%$

Specifications and procedures subject to change without notice.

## VELOSTAT™ DISSIPATIVE DRUM LINER

# PROTEKTIVE PAK

**PROTEKTIVE PAK**  
13520 MONTE VISTA AVENUE, CHINO, CA 91710  
PHONE (909) 627-2578  
[ProtektivePak.com](http://ProtektivePak.com)

**DRAWING  
NUMBER**  
2014 18X24

**DATE**  
April  
2016