



HOLDER FOR 3 MODULES, PLASTIC, 1NO, LED MODULE, WHITE, 6-24V AC/DC, SCREW TERMINAL

Figure similar

|                                                                                |                                    |
|--------------------------------------------------------------------------------|------------------------------------|
| <b>product brand name</b>                                                      | SIRIUS ACT                         |
| <b>Product designation</b>                                                     | Commanding and signaling devices   |
| <b>Design of the product</b>                                                   | Holder                             |
| <b>Manufacturer article number</b>                                             |                                    |
| <ul style="list-style-type: none"> <li>• of supplied contact module</li> </ul> | <a href="#">3SU1400-1AA10-1BA0</a> |
| <ul style="list-style-type: none"> <li>• of supplied LED module</li> </ul>     | <a href="#">3SU1401-1BG60-1AA0</a> |
| <ul style="list-style-type: none"> <li>• of the supplied holder</li> </ul>     | <a href="#">3SU1500-0AA10-0AA0</a> |
| <b>Actuator:</b>                                                               |                                    |
| <b>Design of the operating mechanism</b>                                       | 3-way with module                  |
| <b>Number of contact modules</b>                                               | 1                                  |
| <b>Holder:</b>                                                                 |                                    |
| <b>Material of the holder</b>                                                  | Plastic                            |
| <b>Display:</b>                                                                |                                    |
| <b>Number of LED modules</b>                                                   | 1                                  |
| <b>General technical data:</b>                                                 |                                    |
| <b>Product function</b>                                                        |                                    |
| <ul style="list-style-type: none"> <li>• positive opening</li> </ul>           | No                                 |
| <b>Product component</b>                                                       |                                    |
| <ul style="list-style-type: none"> <li>• diode</li> </ul>                      | Yes                                |
| <ul style="list-style-type: none"> <li>• lamp transformer</li> </ul>           | No                                 |
| <ul style="list-style-type: none"> <li>• Light source</li> </ul>               | Yes                                |
| <ul style="list-style-type: none"> <li>• series resistor</li> </ul>            | No                                 |
| <b>Insulation voltage</b>                                                      |                                    |
| <ul style="list-style-type: none"> <li>• Rated value</li> </ul>                | 320 V                              |

|                                                                                                                                             |                                         |
|---------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------|
| <b>Degree of pollution</b>                                                                                                                  | 3                                       |
| <b>Shock resistance</b><br>• acc. to IEC 60068-2-27                                                                                         | Sinusoidal half-wave 50 g / 11 ms       |
| <b>Vibration resistance</b><br>• acc. to IEC 60068-2-6                                                                                      | 10 ... 500 Hz: 5g                       |
| <b>Surge voltage resistance Rated value</b>                                                                                                 | 4 kV                                    |
| <b>Operating frequency maximum</b>                                                                                                          | 3 600 1/h                               |
| <b>Mechanical service life (switching cycles)</b><br>• typical                                                                              | 10                                      |
| <b>Thermal current</b>                                                                                                                      | 10 A                                    |
| <b>Protection class IP</b><br>• of the terminal                                                                                             | IP20                                    |
| <b>Equipment marking</b><br>• acc. to DIN EN 61346-2<br>• acc. to DIN EN 81346-2                                                            | U<br>U                                  |
| <b>Design of the fuse link for short-circuit protection of the auxiliary switch with type of assignment 1 required</b>                      | gG / Dz 10 A, quick-acting / Dz 10 A    |
| <b>Continuous current of the C characteristic MCB</b>                                                                                       | 10 A                                    |
| <b>Operating voltage</b><br>• with AC<br>— at 50 Hz Rated value<br>— at 60 Hz Rated value<br>• for DC Rated value<br>— maximum<br>— minimum | 6 ... 24 V<br>6 ... 24 V<br>24 V<br>6 V |

#### Power Electronics:

|                            |                                                                                            |
|----------------------------|--------------------------------------------------------------------------------------------|
| <b>Contact reliability</b> | One maloperation per 100 million (17 V, 5 mA), one maloperation per 10 million (5 V, 1 mA) |
|----------------------------|--------------------------------------------------------------------------------------------|

#### Auxiliary circuit:

|                                                             |              |
|-------------------------------------------------------------|--------------|
| <b>Number of NC contacts</b><br>• for auxiliary contacts    | 0            |
| <b>Number of NO contacts</b><br>• for auxiliary contacts    | 1            |
| <b>Number of CO contacts</b><br>• for auxiliary contacts    | 0            |
| <b>Design of the contact of the auxiliary contacts</b>      | Silver alloy |
| <b>Operating current at AC-15</b><br>• at 230 V Rated value | 6 A          |

#### Connections/ Terminals:

|                                                                      |                     |
|----------------------------------------------------------------------|---------------------|
| <b>Type of electrical connection</b><br>• of modules and accessories | Screw-type terminal |
|----------------------------------------------------------------------|---------------------|

|                                                                                                                                                                                                                                                                          |                                                                                                                                                                                    |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Type of connectable conductor cross-section</b>                                                                                                                                                                                                                       |                                                                                                                                                                                    |
| <ul style="list-style-type: none"> <li>• solid with core end processing</li> <li>• solid without core end processing</li> <li>• finely stranded with core end processing</li> <li>• finely stranded without core end processing</li> <li>• for AWG conductors</li> </ul> | <p>2x (0.5 ... 0.75 mm<sup>2</sup>)</p> <p>2x (1.0 ... 1.5 mm<sup>2</sup>)</p> <p>2x (0.5 ... 1.5 mm<sup>2</sup>)</p> <p>2x (1,0 ... 1,5 mm<sup>2</sup>)</p> <p>2x (18 ... 14)</p> |
| <b>Tightening torque</b>                                                                                                                                                                                                                                                 |                                                                                                                                                                                    |
| <ul style="list-style-type: none"> <li>• with screw-type terminals</li> </ul>                                                                                                                                                                                            | 0.8 ... 0.9 N·m                                                                                                                                                                    |

|                                  |       |
|----------------------------------|-------|
| <b>Lamp:</b>                     |       |
| <b>Type of light source</b>      | LED   |
| <b>Color of the light source</b> | white |

|                                                                                                |                                             |
|------------------------------------------------------------------------------------------------|---------------------------------------------|
| <b>Ambient conditions:</b>                                                                     |                                             |
| <b>Ambient temperature</b>                                                                     |                                             |
| <ul style="list-style-type: none"> <li>• during operation</li> <li>• during storage</li> </ul> | <p>-25 ... +70 °C</p> <p>-40 ... +80 °C</p> |

|                                                                                |                      |
|--------------------------------------------------------------------------------|----------------------|
| <b>Installation/ mounting/ dimensions:</b>                                     |                      |
| <b>Mounting type</b>                                                           |                      |
| <ul style="list-style-type: none"> <li>• of modules and accessories</li> </ul> | Front plate mounting |
| <b>Height</b>                                                                  | 40 mm                |
| <b>Width</b>                                                                   | 30 mm                |
| <b>Shape of the installation opening</b>                                       | round                |

**Certificates/ approvals:**

**Further information**

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU15011AG601BA0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**


<https://support.industry.siemens.com/cs/ww/en/ps/3SU15011AG601BA0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU15011AG601BA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU15011AG601BA0&lang=en)



**-P**  
6-24 V AC/DC



last modified:

27.04.2015