

### HSK-INOX Hygienic-Design



Cope with all hygienic requirements




#### Cable Glands for special applications

#### Tested quality: EHEDG certified

Enclosures of Hygienic Cable Glands are without corners and edges as well as exposed external threads. Additional the surface roughness is smaller than Ra  $0.8\,\mu m$ . All in all this is leading to a very easy cleaning of the Cable Glands and avoids deposits of bacteria and microorganisms. The enclosure made of stainless steel (EN 1.4404/AISI~316L) and the silicone sealing are EHEDG certified and FDA conform.

#### **HSK-INOX-HD-Pro: One without corners and edges**



Easy cleaning, because of missing corners and edges.

Resistant enclosure made of stainless steel (AISI 316L)

High-quality silicone sealing





free of halogens and phosphate


high-pressure tested (IP 69K)

operating temperature

(-40 °F to +248 °F)

#### Perfection down to details creates even more security


The Hygienic-Design-Series have all approved HUMMEL advantages. HUMMEL-Cable Glands are characterized by an extremely high strain relief, provide a 360° connection of the cable shielding and protect the sealing insert from twisting during assembly. The Hygienic-Cable Glands are made of high-quality stainless steel (1.4404/AISI 316L) and with a membrane sealing made of silicone.





#### **HSK-INOX HYGIENIC-DESIGN**

**HSK-INOX-HD Pro** Metr.



Material HD-enclosure 1.4404/AISI 316 L VMQ (Silicone), blue (similar RAL 5017) Sealing HD-enclosure Protection IP 66, IP 68 to 10 bar, IP 69K

**Operating Temperature** 

-40 °F to +248 °F





ideal for high-pressure


cleaning

Advice:

- EMC connection integrated
- VDMA Riboflavin cleaning test passed
- EHEDG 01 cleaning test passed EHEDG certificate EL class I AUX approved


Upon request:

- elongated threads, further sizes, other temperature range



AG	⊘  k   mm	GL mm	H mm	D mm	₩ mm	Number
M 12 x 1,5	5 – 6,5	6	19	21	14	1.740.1203.50
M 16 x 1,5	<i>7,</i> 5 – 10	6	20	27	19/21	1.740.1603.50
M 16 x 1,5	6 – 7,5	6	20	27	19/21	1.740.1603.51
M 20 x 1,5	11 – 13,5	6	22,5	33	24/27	1.740.2003.50
$M 20 \times 1,5$	9 – 12	6	22,5	33	24/27	1.740.2003.51
M 25 x 1,5	15 – 18	7	23,5	38	30	1.740.2503.50
$M 25 \times 1,5$	14 – 16	7	23,5	38	30	1.740.2503.52
M 32 x 1,5	21 – 25	8	26,5	45	36	1.740.3203.50
$M32 \times 1,5$	18 – 21	8	26,5	45	36	1.740.3203.51

**HSK-INOX-HD** Metr.



1.4404/AISI 316 L Material HD-enclosure Sealing HD-enclosure VMQ (Silicone), blue (similar RAL 5017) IP 68 Protection -40 °F to +248 °F **Operating Temperature** 

**EMC** 



#### Advice:

- Advice:
   EMC integrated
   elongated threads on request
   other sizes upon request
   temperature range -31 °F to +302 °F (PVDF Version) on request
   ideal for foam-cleaning



AG	<b>⊘</b>  k   mm	GL mm	H mm	D mm	₩ mm	Number
M 12 x 1,5	3,5 – 6,5	6	30	21	14	1.740.1202.50
M 16 x 1,5	5 – 10	6	34	27	18/20	1.740.1602.50
M 20 x 1,5	10 – 14	6	34,5	33	24	1.740.2002.50
M 25 x 1,5	13 – 18	7	41,5	38	27/30	1.740.2502.50



#### **HSK-INOX Hygienic-Design**

# Cope with all hygienic requirements

The hygienic design Cable Glands of HUMMEL AG have been developed for applications with special requirements. They are used in areas where high hygienic standards for cleaning are demanded. These are areas where deposits of bacteria and microorganisms need to be avoided.

#### Fields of application

- Food industry
- Beverage industry
- Pharma industry
- Packaging machinery
- Biotechnical plants
- Chemical industry

# HSK-INOX-HD-Pro Ideal for high-pressure Cleaning

Recommended in all areas, which are cleaned by high-pressure cleaning: HSK-INOX-HD-Pro



Excellent solution for applications, which are cared with foam-cleaning: HSK-INOX-HD

## Product range electric components

#### **CABLE GLANDS**

Polyamide-, Brass- and Stainless steel, EMC-connections, Ex e-, Ex d-, Ex ta-Cable Glands



#### CIRCULAR CONNECTORS

M 8 to M 40, INOX, TWILOCK, Industrial Ethernet, Power, Signal, Hybrid-Connector, Moulded Cordsets



#### **INDUSTRIAL ENCLOSURES**

Enclosures made of PC, Polyester, Aluminium and Stainless Steel, Customized Systems, Enclosure-Configurator



#### **CONDUIT SYSTEMS**

Corrugated Conduit Systems, Conduit Cable Glands, Angled Systems, combined Cable Glands, Accessories



#### **CABLE ASSEMBLY**

Moulded Signal- and Power Circular Connectors, Servo Cables, Cable Sets



www.hummel.com

HUMMFL AG

Lise-Meitner-Straße 2 79211 Denzlingen

www.hummel.com

Tel. +49 (0) 76 66 / 9 11 10-0 Fax +49 (0) 76 66 / 9 11 10-20

