This document was generated on 08/03/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0459703185
Status: Active
Overview: SEARAY* Plugs, Receptacles and Copper Flex Assemblies
Description: SEARAY* Plug, 240 Circuits, 2.00mm Unmated Height, 8 Rows, with Pegs, Solder Charge™ Lead-Free



Series image - Reference only

Documents:

3D Model	Packaging Specification PK-45970-001 (PDF)
Drawing (PDF)	Packaging Specification PK-45970-002 (PDF)
Product Specification PS-45970-001 (PDF)	Test Summary TS-45970-0007 (PDF)
Product Specification PS-45970-002 (PDF)	Test Summary TS-45970-001 (PDF)
Application Specification AS-45970-002 (PDF)	Test Summary TS-45970-002 (PDF)
Application Specification AS-45970-990 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	45970
Application	Board-to-Board, Signal
Electrical Model	Yes
Overview	SEARAY* Plugs, Receptacles and Copper Flex Assemblies
Product Name	SEARAY*
UPC	883906606930

Physical

Breakaway	No
Circuits (Loaded)	240
Circuits (maximum)	240
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.163/g
Number of Rows	8
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes

EU ELV
Not Relevant

EU RoHS | **China RoHS**
Compliant

REACH SVHC
Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant

Search Parts in this Series
45970 Series

Mates With
45971 SEARAY* Receptacle

Robotic Placement	Pick and Place Cap
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	Surface Mount
Unmated Height	2.00mm

Electrical

Current - Maximum per Contact	2.7A
Voltage - Maximum	240V AC

Solder Process Data

Duration at Max. Process Temperature (seconds)	003
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	AS-45970-002, AS-45970-990
Electrical Model Document	EE-45970-007, EE-45970-010, EE-45970-015
Packaging Specification	PK-45970-001, PK-45970-002
Product Specification	PS-45970-001, PS-45970-002
S-Parameter Model	SP-45970-007, SP-45970-010, SP-45970-015
Sales Drawing	SD-45970-001
Symbol/Footprint Data	SYM-45970-3185
Test Summary	TS-45970-0007, TS-45970-001, TS-45970-002

*SEARAY is a trademark of Samtec, Inc.