


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348260200](#)
Status: **Active**
Overview: [Mini50™ Connection Systems](#)
Description: Mini50™ Unsealed Right Angle Header, Dual Row, 20 Circuit, Polarization Option A, Black, Tray

Documents:

| | |
|--|---|
| 3D Model | Application Specification AS-34791-020-CH (PDF) |
| Drawing (PDF) | Application Specification AS-34791-020-FR (PDF) |
| Product Specification PS-34791-020 (PDF) | Packaging Specification PK-31301-440 (PDF) |
| Application Specification AS-34791-020 (PDF) | RoHS Certificate of Compliance (PDF) |



Series image - Reference only

General

| | |
|----------------|--|
| Product Family | PCB Headers |
| Series | 34826 |
| Application | Power, Signal, Wire-to-Board |
| Overview | Mini50™ Connection Systems |
| Product Name | Mini50™ |
| UPC | 887191402611 |

Physical

| | |
|--------------------------------|--------------------------------|
| Breakaway | No |
| Circuits (Loaded) | 20 |
| Circuits (maximum) | 20 |
| Color - Resin | Black |
| Durability (mating cycles max) | 10 |
| First Mate / Last Break | No |
| Glow-Wire Compliant | No |
| Guide to Mating Part | No |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Tin over Nickel |
| Material - Plating Termination | Tin over Nickel |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 3.415/g |
| Number of Rows | 2 |
| Orientation | Right Angle |
| PC Tail Length | 2.80mm |
| PCB Locator | Yes |
| Packaging Type | Tray |
| Pitch - Mating Interface | 2.00mm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Temperature Range - Operating | -40°C to +105°C |
| Termination Interface: Style | Through Hole |

Electrical

| | |
|-------------------------------|---------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 500V DC |

Solder Process Data

| | |
|--|----------|
| Duration at Max. Process Temperature (seconds) | 040 |
| Lead-free Process Capability | SMC&WAVE |
| Max. Cycles at Max. Process Temperature | 003 |
| Process Temperature max. C | 260 |

Material Info

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

China RoHS

Not Relevant

Compliant

Search Parts in this Series

[34826 Series](#)

Mates With

[34824 Mini50™ Unsealed Dual Row Receptacle](#)

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

AS-34791-020, AS-34791-020-CH, AS-34791-020-FR

PK-31301-440

PS-34791-020

SD-34826-001

This document was generated on 06/13/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION