

## Desktop 2-Post Rack *RRTT Series*

350 lbs Weight Capacity



### Features

- Constructed in 14-gauge steel.
- EIA-310-D compliant 19 inch mounting rails with punched round holes for use with clip nuts.
- Includes large base for freestanding support of equipment.
- Finished in textured black powder paint.
- Knockdown design ships unassembled for easy handling and shipping protection.
- Tested to nearly double the suggested load rating of 350 lbs (113 kg).
- RoHS Compliant.
- Manufactured in North America.

Learn about our new and improved Hammond Desktop Rack (HDR Series).

### Accessories

- Universal Rack Shelf
- Two Post Mounting Clamping Shelf
- Two Post Mounting Deep Channel Battery Shelf
- Two Post Mounting Deep Channel Shelf
- 10-32 Mounting Hardware
- Cable Management
- Grounding
- Rack Unit Label
- Two Post Mounting Adjustable Shelf
- Two Post Centered Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- Adjustable Depth DIN Rail Panel
- Outlet Strips
- Hinged Acrylic Door Panel Cover
- Rack Panels

| Part No.           | Overall Dimensions |       |            | Rack Units | Mounting Dimensions |       |
|--------------------|--------------------|-------|------------|------------|---------------------|-------|
|                    | Height             | Width | Base Depth |            | Height              | Width |
| <b>RRTT1921BK1</b> | 24.00              | 20.38 | 12.00      | 12U        | 21.00               | 19.00 |
| <b>RRTT1928BK1</b> | 31.00              | 20.38 | 12.00      | 16U        | 28.00               | 19.00 |

Tags: **Relay Rack, H-Frame, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack, Two-Post Rack** *Data subject to change without notice*

