

ZXMN2F30FH 20V SOT23 N-channel enhancement mode MOSFET

Summary

V _{(BR)DSS}	$R_{DS(on)}(\Omega)$	I _D (A)
20	0.045 @ V _{GS} = 4.5V	4.9
	0.065 @ V _{GS} = 2.5V	4.1




Description

This new generation Trench MOSFET from Zetex features low onresistance achievable with low (2.5V) gate drive.

Features

- · Low on-resistance
- · 2.5V gate drive capability
- SOT23 package




Applications

- Buck/Boost DC-DC Converters
- · Load switching and SMPS
- · Charging applications in portable equipment
- Motor Control
- · LED Lighting

Ordering information

DEVICE	Reel size (inches)	Tape width (mm)	Quantity per reel
ZXMN2F30FHTA	7	8	3000



Device marking

KNC

Absolute maximum ratings

Parameter	Symbol	Limit	Unit
Drain source voltage	V_{DSS}	20	V
Gate source voltage	V_{GS}	±12	V
Continous Drain Current @ V _{GS} =4.5; T _A =25°C ^(b)	I _D	4.9	Α
@ V _{GS} =4.5; T _A =70°C ^(b)		4.0	Α
@ V _{GS} =4.5; T _A =25°C ^(a)		4.1	Α
Pulsed drain current ^(c)	I _{DM}	22.6	Α
Continuous source current (body diode)(b)	I _S	1.6	Α
Pulsed source current (body diode)(c)	I _{SM}	22.6	Α
Power dissipation at T _A =25°C ^(a)	P_{D}	0.96	W
Linear derating factor		7.6	mW/°C
Power dissipation at T _A =25°C ^(b)	P_{D}	1.4	W
Linear derating factor		11.2	mW/°C
Operating and storage temperature range	T _j , T _{stg}	-55 to 150	°C

Thermal resistance

Parameter	Symbol	Limit	Unit	
Junction to ambient ^(a)	$R_{\Theta JA}$	131	°C/W	
Junction to ambient ^(b)	$R_{\Theta JA}$	89	°C/W	
Junction to Lead ^(d)	$R_{\Theta JL}$	68	°C/W	

NOTES:


⁽a) For a device surface mounted on 25mm x 25mm FR4 PCB with high coverage of single sided 1oz copper, in still air conditions.

⁽b) For a device surface mounted on FR4 PCB measured at t $\! \leq \! 5$ sec.

⁽c) Repetitive rating - $25mm \times 25mm \text{ FR4 PCB}$, D=0.02, pulse width $300\mu\text{s}$ - pulse width limited by maximum junction temperature.

⁽d) Thermal resistance from junction to solder-point (at the end of the drain lead).

Thermal characteristics



Electrical characteristics (at T_{amb} = 25°C unless otherwise stated)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions
Static				•		
Drain-Source Breakdown Voltage	V _{(BR)DSS}	20			V	I _D = 250μA, V _{GS} =0V
Zero Gate Voltage Drain Current	I _{DSS}			1	μΑ	V _{DS} = 20V, V _{GS} =0V
Gate-Body Leakage	I _{GSS}			100	nA	V _{GS} =±12V, V _{DS} =0V
Gate-Source Threshold Voltage	V _{GS(th)}	0.6	0.9	1.5	V	$I_D=250\mu A, V_{DS}=V_{GS}$
Static Drain-Source On-State Resistance (*)	R _{DS(on)}			0.045 0.065	Ω Ω	V _{GS} = 4.5V, I _D = 2.5A V _{GS} = 2.5V, I _D = 2.0A
Forward Transconductance ^{(*)(†)}	9 _{fs}		8.6		S	V _{DS} = 10V, I _D = 3A
Dynamic (†)						
Input Capacitance	C _{iss}		452		pF	
Output Capacitance	C _{oss}		102		pF	V _{DS} = 10V, V _{GS} =0V f=1MHz
Reverse Transfer Capacitance	C _{rss}		58		pF	- 1- 11/11/2
Switching (‡)(†)						
Turn-On-Delay Time	t _{d(on)}		2.9		ns	
Rise Time	t _r		5.6		ns	V _{DD} = 10V, V _{GS} = 4.5V I _D = 1A
Turn-Off Delay Time	t _{d(off)}		19.4		ns	$R_{\rm G} \approx 6.0\Omega$
Fall Time	t _f		10.2		ns	- -
Total Gate Charge	O_g		4.8		nC	V _{DS} = 10V, V _{GS} = 4.5V
Gate-Source Charge	Q _{gs}		1		nC	I _D = 3.5A
Gate Drain Charge	Q _{gd}		1.2		nC	
Source-drain diode			ı			1
Diode Forward Voltage(*)	V_{SD}		0.75	1.2	V	I _S = 1.25A, V _{GS} =0V

NOTES


^(*) Measured under pulsed conditions. Pulse width $\leq 300 \mu s;$ duty cycle $\leq\!\!2\%.$


^(†) For design aid only, not subject to production testing.


^(‡) Switching characteristics are independent of operating junction temperature.


ZXMN2F30FH


Typical characteristics















ZXMN2F30FH

Test circuits




Current regulator


12V 0.2µF 50k D.U.T

Vos

Basic gate charge waveform

Gate charge test circuit






Switching time waveforms

Switching time test circuit

ZXMN2F30FH

Package outline - SOT23



Dim.	Millin	neters	Inc	hes	Dim.	Millimeters		Inches	
	Min.	Max.	Min.	Max.		Min.	Max.	Min.	Max.
Α	-	1.12	-	0.044	e1	1.90	NOM	0.075	NOM
A1	0.01	0.10	0.0004	0.004	Е	2.10	2.64	0.083	0.104
b	0.30	0.50	0.012	0.020	E1	1.20	1.40	0.047	0.055
С	0.085	0.20	0.003	0.008	L	0.25	0.60	0.0098	0.0236
D	2.80	3.04	0.110	0.120	L1	0.45	0.62	0.018	0.024
е	0.95	NOM	0.037	NOM	-	-	-	-	-

Note: Controlling dimensions are in millimeters. Approximate dimensions are provided in inches

Definitions

Product change

Zetex Semiconductors reserves the right to alter, without notice, specifications, design, price or conditions of supply of any product or service. Customers are solely responsible for obtaining the latest relevant information before placing orders.

Applications disclaimer

The circuits in this design/application note are offered as design ideas. It is the responsibility of the user to ensure that the circuit is fit for the user's application and meets with the user's requirements. No representation or warranty is given and no liability whatsoever is assumed by Zetex with respect to the accuracy or use of such information, or infringement of patents or other intellectual property rights arising from such use or otherwise. Zetex does not assume any legal responsibility or will not be held legally liable (whether in contract, tort (including negligence), breach of statutory duty, restriction or otherwise) for any damages, loss of profit, business, contract, opportunity or consequential loss in the use of these circuit applications, under any circumstances.

Zetex products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Zetex Semiconductors plc. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body

- 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

The product specifications contained in this publication are issued to provide outline information only which (unless agreed by the company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contract or be regarded as a representation relating to the products or services concerned.

Terms and Conditions

All products are sold subjects to Zetex' terms and conditions of sale, and this disclaimer (save in the event of a conflict between the two when the terms of the contract shall prevail) according to region, supplied at the time of order acknowledgement,

For the latest information on technology, delivery terms and conditions and prices, please contact your nearest Zetex sales office.

Quality of product

Zetex is an ISO 9001 and TS16949 certified semiconductor manufacturer.

To ensure quality of service and products we strongly advise the purchase of parts directly from Zetex Semiconductors or one of our regionally authorized distributors. For a complete listing of authorized distributors please visit: www.zetex.com/salesnetwork

Zetex Semiconductors does not warrant or accept any liability whatsoever in respect of any parts purchased through unauthorized sales channels.

ESD (Electrostatic discharge)

Semiconductor devices are susceptible to damage by ESD. Suitable precautions should be taken when handling and transporting devices. The possible damage to devices depends on the circumstances of the handling and transporting, and the nature of the device. The extent of damage can vary from immediate functional or parametric malfunction to degradation of function or performance in use over time. Devices suspected of being affected should be replaced.

Green compliance

Zetex Semiconductors is committed to environmental excellence in all aspects of its operations which includes meeting or exceeding regulatory requirements with respect to the use of hazardous substances. Numerous successful programs have been implemented to reduce the use of hazardous substances and/or emissions.

All Zetex components are compliant with the RoHS directive, and through this it is supporting its customers in their compliance with WEEE and ELV directives.

Product status key:	
"Preview"	Future device intended for production at some point. Samples may be available
"Active"	Product status recommended for new designs
"Last time buy (LTB)"	Device will be discontinued and last time buy period and delivery is in effect
"Not recommended for new designs"	Device is still in production to support existing designs and production
"Obsolete"	Production has been discontinued
Datasheet status key:	
"Draft version"	This term denotes a very early datasheet version and contains highly provisional information, which may change in any manner without notice.
"Provisional version"	This term denotes a pre-release datasheet. It provides a clear indication of anticipated performance. However, changes to the test conditions and specifications may occur, at any time and without notice.
"Issue"	This term denotes an issued datasheet containing finalized specifications. However, changes to specifications may occur, at any time and without notice.

Zetex sales offices

Europe	Americas	Asia Pacific	Corporate Headquarters
Zetex GmbH	Zetex Inc	Zetex (Asia Ltd)	Zetex Semiconductors plc
Kustermann-park	700 Veterans Memorial Highway	3701-04 Metroplaza Tower 1	Zetex Technology Park, Chadderton
Balanstraße 59	Hauppauge, NY 11788	Hing Fong Road, Kwai Fong	Oldham, OL9 9LL
D-81541 München	USA	Hong Kong	United Kingdom
Germany			
Telefon: (49) 89 45 49 49 0	Telephone: (1) 631 360 2222	Telephone: (852) 26100 611	Telephone: (44) 161 622 4444
Fax: (49) 89 45 49 49 49	Fax: (1) 631 360 8222	Fax: (852) 24250 494	Fax: (44) 161 622 4446
europe.sales@zetex.com	usa.sales@zetex.com	asia.sales@zetex.com	hq@zetex.com

© 2008 Published by Zetex Semiconductors plc