

## Heavy Duty Welded Steel 2-Post Rack *DNRRHDW Series*

UL 2416 Rated 1,500 lbs Weight Capacity



When strength and reliability is the highest priority, be sure to choose the Data/Networking Robust Rack (DNRR) from Hammond Manufacturing. Designed to support your rack mount infrastructure, regardless of the application, the DNRR includes premium features not found on most other racks.

### Features

- Weighing in at just over 75 lbs, the DNRR Heavy Duty Welded Rack Series boasts a 10-Gauge welded steel frame which is the thickest steel rack on the market.
- Our automated tapping process provides EIA compliant tapped rails on both the front and back to ensure flexibility when mounting equipment.
- Don't forget to order your **Mounting Hardware**.
- When connecting multiple racks together, Hammond provided a 1.25" cable pass-thru. In addition we added numerous tapped and non-tapped holes for mounting power distribution, cable management and other accessories.
- Bonding is a breeze with two (2) pairs of integrated 10-32 ground studs, spaced 5/8" apart. Stud pairs are conveniently located across from each other inside the rail channel. For added convenience, a pair is located near the top of the rack, while the other at lower side.
- To keep it looking great, the DNRR undergoes a three-stage paint process which includes a coat of premium smooth black powder paint.
- Before sending the DNRR on it's way we cover the rails and base with a thick layer of cardboard to prevent any damage that may occur during transportation.

### Specifications

- Heavy duty, 10-gauge steel construction.
- UL Listed 2416 rated for up to 1,500 lbs (680 kg) static load rating.
- RoHS Compliant.
- Manufactured in North America.

**When you just need the basics, you may also consider the RB-2P 2-Post Rack Series.**

### Accessories

- Universal Rack Shelf
- Two Post Mounting Adjustable Shelf
- Rack Panels
- Two Post Centered Shelf
- Two Post Mounting Deep Channel
- Vertical Rack Cable Manager with Door
- Vertical Fingered Rack Cable Manager with Door
- Top Wire Management
- Top Cable Chimney
- Two Post Equipment Rail Depth

#### Battery Shelf

- Two Post Mounting Keyboard & Equipment Shelf
- 10-32 Mounting Hardware
- Outlet Strips
- Light Duty Caster Set for Open Frame Rack

- Rack and Cabinet

Baying/Ganging/Joining Kit

#### Adapter

- Horizontal Ring Cable Manager
- Horizontal Finger Cable Manager
- Grounding
- Rack Isolation Kit
- Bolt Down Kit

### 19" Rack Mounting 10-32 Double Tapped Rails

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions			Rail Tapping
	Height	Width	Depth		Height	Width	Rail Depth	
<b>DNRR42HDW</b>	48.13	20.56	15.00	24U	42.00	19.00	3.00	10-32
<b>DNRR63HDW</b>	69.13	20.56	15.00	36U	63.00	19.00	3.00	10-32
<b>DNRR70HDW</b>	76.13	20.56	15.00	40U	70.00	19.00	3.00	10-32
<b>DNRR77HDW</b>	83.13	20.56	15.00	44U	77.00	19.00	3.00	10-32
<b>DNRR84HDW</b>	90.13	20.56	15.00	48U	84.00	19.00	3.00	10-32

### 23" Rack Mounting 12-24 Double Tapped Rails

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions			Rail Tapping
	Height	Width	Depth		Height	Width	Rail Depth	
<b>DNRR2377HDWB</b>	83.13	24.56	15.00	44U	77.00	23.00	3.00	12-24
<b>DNRR2384HDWB</b>	90.13	24.56	15.00	48U	84.00	23.00	3.00	12-24

Tags: **Relay Rack, H-Frame, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack, Two-Post Rack** *Data subject to change without notice*

© 2016. Hammond Manufacturing Ltd. All rights reserved.