TH-MG 135 E

Grinding and Engraving Tool

Art.-No. 44.191.69

Features

- Tool-support (1)
- Locking button for tool change (2)
- Speed regulation (3)
- Hook (4) for fixation on the telescopic stand rod
- On / Off switch (5)
- Soft grip (6)

Standard accessories

- Transport and storage case (7)
- Flexible shaft 1 m (8)
- Telescopic stand rod (9)
- 12 mounted points made of special corundum
- 6 milling pins
- 22 sanding tools (14 x small/ 8 x tall)
- 34 adapters for sanding tool (20 x small/ 14 x tall)
- 3 adapters for miniature grinding & cutting discs
- 4 miniature grinding discs made of special corundum
- 40 miniature cutting discs
- 14 miniature felt polishing discs (11 x flat/ 3 x longish)
- 46 round sanding papers
- 6 HSS drill bits
- 3 holders for felt polishing disc
- 4 clamping sleeves Ø 0.5/ 1.6/ 2.4/ 3.2 mm
- 1 key for tool change
- 1 brush insert

Technical Data

Mains:	230 V ~ 50 Hz
Power:	135 W
Idle speed:	10,000 – 35,000 rpm
Clamping sleeves:	Ø 0.5/ 1.6/ 2.4/ 3.2 mm
Product weight:	0.7 kg

Logistic Data

Net weight:	2.25 kg
Gross weight:	2.5 kg
Packing dimensions:	340 x 218 x 125 mm
Bar code:	4006825 585315
Sales Unit:	6 pcs



Abbildungen können nicht im Serien-Lieferumfang enthaltenes Zubehör darstellen / Illustrations can contain accessories, which are not included in standard extent of delivery.
Abbildungen ähnlich, produktionsbedingte Abweichung vorbehalten / Illustration similar (in design), production-wise modifications reserved.
File: C:\Users\smulla\Documents\Digtal Images\Digital Images 2016\EINHELL\TL18807 TECH.doc
Erstelldatum/create date: 20.07.2016 15:02:00Aktualisiert/up dated: 01.08.2016