
Vishay Siliconix



## **Power MOSFET**

PRODUCT SUMMARY				
V <sub>DS</sub> (V)	-50			
R <sub>DS(on)</sub> (Ω)	$V_{GS} = -10 V$	0.28		
Q <sub>g</sub> max. (nC)	26			
Q <sub>gs</sub> (nC)	6.2			
Q <sub>gd</sub> (nC)	8.6			
Configuration	Single			



### **FEATURES**

- · P-channel versatility
- Compact plastic package
- Fast switching
- Low drive current
- Ease of paralleling
- Excellent temperature stability
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

### DESCRIPTION

The power MOSFET technology is the key to Vishay's advanced line of power MOSFET transistors. The efficient geometry and unique processing of the power MOSFET design achieve very low on-state resistance combined with high transconductance and extreme device ruggedness.

The P-channel power MOSFETs are designed for application which require the convenience of reverse polarity operation. They retain all of the features of the more common N-channel power MOSFETs such as voltage control, very fast switching, ease of paralleling, and excellent temperature stability.

P-channel power MOSFETs are intended for use in power stages where complementary symmetry with N-channel devices offers circuit simplification. They are also very useful in drive stages because of the circuit versatility offered by the reverse polarity connection. Applications include motor control, audio amplifiers, switched mode converters, control circuits and pulse amplifiers.

ORDERING INFORMATION			
Package	TO-220AB		
Lead (Pb)-free	IRF9Z20PbF		

<b>ABSOLUTE MAXIMUM RATINGS</b> ( $T_c = 25 \degree C$ , unless otherwise noted)						
PARAMETER	SYMBOL	LIMIT	UNIT			
Drain-Source Voltage	V <sub>DS</sub>	-50	N			
Gate-Source Voltage	V <sub>GS</sub>	± 20	V			
Continuous Drain Current	$V_{GS}$ at - 10 V $\frac{T_C = 25 \degree C}{T_C = 100 \degree C}$	I <sub>D</sub>	-9.7	А		
	$T_{\rm C} = 100 ^{\circ}{\rm C}$		-6.1			
Pulsed Drain Current <sup>a</sup>	I <sub>DM</sub>	-39	1			
Linear Derating Factor		0.32	W/°C			
Inductive Current, Clamped	L = 100 µH	I <sub>LM</sub>	-39	A		
Unclamped Inductive Current (Avalanche current)	١L	-2.2	A			
Maximum Power Dissipation	T <sub>C</sub> = 25 °C	PD	40	W		
Operating Junction and Storage Temperature Range		T <sub>J</sub> , T <sub>stg</sub>	-55 to +150	°C		
Soldering Recommendations (Peak temperature) <sup>c</sup>	for 10 s		300	U		

#### Notes

a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 14).

b.  $V_{DD}$  = - 25 V, starting T<sub>J</sub> = 25 °C, L =100 µH, R<sub>g</sub> = 25  $\Omega$ 

c. 0.063" (1.6 mm) from case.

S16-0015-Rev. C, 18-Jan-16



COMPLIANT



SHAY

Vishay Siliconix

THERMAL RESISTANCE RATINGS				
PARAMETER	SYMBOL	TYP.	MAX.	UNIT
Maximum Junction-to-Ambient	R <sub>thJA</sub>	-	80	
Case-to-Sink, Flat, Greased Surface	R <sub>thCS</sub>	1.0	-	°C/W
Maximum Junction-to-Case (Drain)	R <sub>thJC</sub>	-	3.1	

PARAMETER	SYMBOL	TE	ST CONDITIONS	MIN.	TYP.	MAX.	UNIT
Static							
Drain-Source Breakdown Voltage	V <sub>DS</sub>	V <sub>GS</sub>	V <sub>GS</sub> = 0 V, I <sub>D</sub> = -250 μA		-	-	V
Gate-Source Threshold Voltage	V <sub>GS(th)</sub>	V <sub>DS</sub>	= V <sub>GS</sub> , I <sub>D</sub> = -250 μΑ	-2.0	-	-4.0	V
Gate-Source Leakage	I <sub>GSS</sub>		$V_{GS} = \pm 20 \text{ V}$	-	-	± 500	nA
		V <sub>DS</sub> =	$V_{DS}$ = max. rating, $V_{GS}$ = 0 V $V_{DS}$ = max. rating x 0,8, $V_{GS}$ = 0 V, $T_J$ =125°C		-	-250	μA
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> = max. rati			-	-1000	
Drain-Source On-State Resistance	R <sub>DS(on)</sub>	$V_{GS} = -10 \text{ V}$	I <sub>D</sub> = -5.6 A <sup>b</sup>	-	0.20	0.28	Ω
Forward Transconductance	9 <sub>fs</sub>	V <sub>DS</sub> =	2 x V <sub>GS</sub> , I <sub>DS</sub> = -5.6 A <sup>b</sup>	2.3	3.5	-	S
Dynamic							
Input Capacitance	Ciss		V <sub>GS</sub> = 0 V, V <sub>DS</sub> = -25 V,		480	-	
Output Capacitance	C <sub>oss</sub>	1			320	-	pF
Reverse Transfer Capacitance	C <sub>rss</sub>	f = 1.0 MHz, see fig. 9		-	58	-	
Total Gate Charge	Qg			-	17	26	nC
Gate-Source Charge	Q <sub>gs</sub>	V <sub>GS</sub> = -10 V	$I_D = -9.7 \text{ A}, V_{DS} = -0.8 \text{ max}.$ rating. see fig. 17	-	4.1	6.2	
Gate-Drain Charge	Q <sub>gd</sub>			-	5.7	8.6	
Turn-On Delay Time	t <sub>d(on)</sub>	¥	$V_{DD}$ = -25 V, I <sub>D</sub> = -9.7 A, R <sub>g</sub> = 18 $\Omega$ , R <sub>D</sub> = 2.4 $\Omega$ , see fig. 16 (MOSFET switching times are essentially independent		8.2	12	ns
Rise Time	t <sub>r</sub>				57	86	
Turn-Off Delay Time	t <sub>d(off)</sub>	switching time			12	18	
Fall Time	t <sub>f</sub>	of operating temperature)		-	25	38	
Internal Drain Inductance	L <sub>D</sub>	Between lead, 6 mm (0.25") from package and center of die contact		-	4.5	-	nH
Internal Source Inductance	L <sub>S</sub>			-	7.5	-	
Drain-Source Body Diode Characterist	ics						
Continuous Source-Drain Diode Current	I <sub>S</sub>	MOSFET sym	bol	-	-	-9.7	
Pulsed Diode Forward Current <sup>a</sup>	I <sub>SM</sub>	showing the integral reverse p - n junction diode		-	-	-39	A
Body Diode Voltage	V <sub>SD</sub>	$T_{J} = 25 \ ^{\circ}C, I_{S} = -9.7 \ A, V_{GS} = 0 \ V \ ^{b}$		-	-	-6.3	V
Body Diode Reverse Recovery Time	t <sub>rr</sub>	$T_J = 25 \text{ °C}, I_F = -9.7 \text{ A}, dl/dt = 100 \text{ A/}\mu\text{s}^{\text{b}}$		56	110	280	ns
Body Diode Reverse Recovery Charge	Q <sub>rr</sub>			0.17	0.34	0.85	μC
Forward Turn-On Time	t <sub>on</sub>	Intrinsic t	urn-on time is negligible (turn-o	n is domi	nated by	L <sub>s</sub> and L	-n)

Notes

a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 14).

b. Pulse width  $\leq$  300 µs; duty cycle  $\leq$  2 %.

2



**Vishay Siliconix** 

### TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Fig. 1 - Typical Output Characteristics





Fig. 2 - Typical Transfer Characteristics








Fig. 4 - Maximum Safe Operating Area




Fig. 5 - Typical Transconductance vs. Drain Current




Fig. 6 - Typical Source-Drain Diode Forward Voltage

S16-0015-Rev. C, 18-Jan-16

**3** For technical questions, contact: <u>hvm@vishay.com</u> Document Number: 90121

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000






Fig. 7 - Breakdown Voltage vs. Temperature




Fig. 8 - Normalized On-Resistance vs. Temperature




Fig. 9 - Typical Capacitance vs. Drain-to-Source Voltage

IRF9Z20, SiHF9Z20

**Vishay Siliconix** 




Fig. 10 - Typical Gate Charge vs. Gate-to-Source Voltage




Fig. 11 - Typical On-Resistance vs. Drain Current




Fig. 12 - Maximum Drain Current vs. Case Temperature

S16-0015-Rev. C, 18-Jan-16

4

Document Number: 90121

For technical questions, contact: <u>hvm@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



**Vishay Siliconix** 




Fig. 13a - Unclamped Inductive Test Circuit




Fig. 13b - Unclamped Inductive Load Test Waveforms




Fig. 14 - Maximum Effective Transient Thermal Impedance, Junction-to-Case vs. Pulse Duration





Fig. 15 - Switching Time Test Circuit







**Vishay Siliconix** 




Fig. 17 - Typical Time to Accumulated 1 % Gate Failure




Fig. 18 - Typical High Temperature Reverse Bias (HTRB) Failure Rate

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <a href="http://www.vishay.com/ppg?90121">www.vishay.com/ppg?90121</a>.



Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.