

Safety data sheet

SECTION 1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name **AS1700**

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use **Adhesive sealant.**

1.3. Details of the supplier of the safety data sheet

Name **ACC Silicones LTD**
Full address **Amber House Showground Road**
District and Country **TA6 6AJ Bridgwater (Somerset)**
England
Tel. **+44(0)1278411400**
Fax **+44(0)1278411444**

e-mail address of the competent person responsible for the Safety Data Sheet **sean.stoodley@acc-silicones.com**

1.4. Emergency telephone number

For urgent inquiries refer to **For all enquiries except Sweden: +44(0)1278411400****Sweden: Ring 112 vid inträffade förgiftningstillbud och begär giftinformation - dygnet runt.****Ring 08-331231 i mindre brådskande fall - dygnet runt. Allmänna och förebyggande frågor om akuta förgiftningar besvaras vardagar kl 9-17.**

SECTION 2. Hazards identification.

2.1. Classification of the substance or mixture.

The product is classified as hazardous pursuant to the provisions set forth in EC Regulation 1272/2008 (CLP) (and subsequent amendments and supplements). The product thus requires a safety datasheet that complies with the provisions of EC Regulation 1907/2006 and subsequent amendments.

Any additional information concerning the risks for health and/or the environment are given in sections 11 and 12 of this sheet.

Hazard classification and indication:

Skin sensitization, category 1

H317

May cause an allergic skin reaction.

2.2. Label elements.

Hazard labelling pursuant to EC Regulation 1272/2008 (CLP) and subsequent amendments and supplements.

Hazard pictograms:

Signal words: **Warning**Hazard statements:
H317 May cause an allergic skin reaction.

Precautionary statements:

P280 Wear protective gloves.
P302+P352 IF ON SKIN: wash with plenty of water / . . .
P333+P313 If skin irritation or rash occurs: Get medical advice / attention.



ACC Silicones LTD

AS1700

Revision nr.11
Dated 25/11/2015
Printed on 25/11/2015
Page n. 2 / 9

EN

SECTION 2. Hazards identification. ... / >>

Contains: TRIMETHOXY (METHYL) SILANE

2.3. Other hazards.

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

SECTION 3. Composition/information on ingredients.

3.1. Substances.

Information not relevant.

3.2. Mixtures.

Contains:

Identification. Conc. %. Classification 1272/2008 (CLP).

TRIMETHOXY (METHYL) SILANE

CAS. 1185-55-3 1 - 5 Flam. Liq. 2 H225, Skin Sens. 1 H317

EC. 214-685-0

INDEX.

TETRA-ISOPROPYLTITANATE

CAS. 546-68-9 1 - 5 Flam. Liq. 3 H226, Eye Irrit. 2 H319

EC. 208-909-6

INDEX.

VINYLTRIMETHOXYSILANE

CAS. 2768-02-7 1 - 5 Flam. Liq. 3 H226, Acute Tox. 4 H332

EC. 220-449-8

INDEX.

METHANOL

CAS. 67-56-1 0 - 0.1 Flam. Liq. 2 H225, Acute Tox. 3 H301, Acute Tox. 3 H311, Acute Tox. 3 H331, STOT SE 1 H370

EC. 200-659-6

INDEX. 603-001-00-X

Note: Upper limit is not included into the range.

The full wording of hazard (H) phrases is given in section 16 of the sheet.

SECTION 4. First aid measures.

4.1. Description of first aid measures.

EYES: Remove contact lenses, if present. Wash immediately with plenty of water for at least 15 minutes, opening the eyelids fully. If problem persists, seek medical advice.

SKIN: Remove contaminated clothing. Wash immediately with plenty of water. If irritation persists, get medical advice/attention. Wash contaminated clothing before using it again.

INHALATION: Remove to open air. In the event of breathing difficulties, get medical advice/attention immediately.

INGESTION: Get medical advice/attention. Induce vomiting only if indicated by the doctor. Never give anything by mouth to an unconscious person, unless authorised by a doctor.

4.2. Most important symptoms and effects, both acute and delayed.

For symptoms and effects caused by the contained substances, see chap. 11.

4.3. Indication of any immediate medical attention and special treatment needed.

Information not available.

SECTION 5. Firefighting measures.

5.1. Extinguishing media.

SUITABLE EXTINGUISHING EQUIPMENT

Extinguishing substances are: carbon dioxide, foam, chemical powder. For product loss or leakage that has not caught fire, water spray can be used to disperse flammable vapours and protect those trying to stem the leak.

UNSUITABLE EXTINGUISHING EQUIPMENT

Do not use jets of water. Water is not effective for putting out fires but can be used to cool containers exposed to flames to prevent explosions.

5.2. Special hazards arising from the substance or mixture.

HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE

SECTION 5. Firefighting measures. ... / >>

Excess pressure may form in containers exposed to fire at a risk of explosion. Do not breathe combustion products.

5.3. Advice for firefighters.

GENERAL INFORMATION

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

SECTION 6. Accidental release measures.

6.1. Personal precautions, protective equipment and emergency procedures.

Block the leakage if there is no hazard.

Wear suitable protective equipment (including personal protective equipment referred to under Section 8 of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.

6.2. Environmental precautions.

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

6.3. Methods and material for containment and cleaning up.

Collect the leaked product into a suitable container. Evaluate the compatibility of the container to be used, by checking section 10.

Absorb the remainder with inert absorbent material.

Make sure the leakage site is well aired. Check incompatibility for container material in section 7. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

6.4. Reference to other sections.

Any information on personal protection and disposal is given in sections 8 and 13.

SECTION 7. Handling and storage.

7.1. Precautions for safe handling.

Keep away from heat, sparks and naked flames; do not smoke or use matches or lighters. Without adequate ventilation, vapours may accumulate at ground level and, if ignited, catch fire even at a distance, with the danger of backfire. Avoid bunching of electrostatic charges. Do not eat, drink or smoke during use. Remove any contaminated clothes and personal protective equipment before entering places in which people eat. Avoid leakage of the product into the environment.

7.2. Conditions for safe storage, including any incompatibilities.

Store only in the original container. Store in a well ventilated place, keep far away from sources of heat, naked flames and sparks and other sources of ignition. Keep containers away from any incompatible materials, see section 10 for details.

7.3. Specific end use(s).

Information not available.

SECTION 8. Exposure controls/personal protection.

8.1. Control parameters.

Regulatory References:

AUS	Österreich	Grenzwerteverordnung 2011 - GKV 2011
BEL	Belgique	AR du 11/3/2002. La liste est mise à jour pour 2010
CZE	Česká Republika	Nařízení vlády č. 361/2007 Sb. kterým se stanoví podmínky ochrany zdraví při práci
DEU	Deutschland	MAK-und BAT-Werte-Liste 2012
DNK	Danmark	Graensevaerdier per stoffer og materialer
ESP	España	INSHT - Límites de exposición profesional para agentes químicos en España 2015
FIN	Suomi	HTP-arvot 2012. Haitallisiksi tunnetut pitoisuudet - Sosiaali- ja terveystieteiden tutkimuskeskus julkaisu 2012:5
FRA	France	JORF n°0109 du 10 mai 2012 page 8773 texte n° 102
GRB	United Kingdom	EH40/2005 Workplace exposure limits
HUN	Magyarország	50/2011. (XII. 22.) NGM rendelet a munkahelyek kémiai biztonságáról
IRL	Éire	Code of Practice Chemical Agent Regulations 2011
ITA	Italia	Decreto Legislativo 9 Aprile 2008, n.81
NLD	Nederland	Databank of the social and Economic Council of Netherlands (SER) Values, AF 2011:18

SECTION 8. Exposure controls/personal protection. ... / >>

NOR	Norge	Veiledning om Administrative normer for forurensning i arbeidsatmosfære
POL	Poliska	ROZPORZĄDZENIE MINISTRA PRACY I POLITYKI SPOŁECZNEJ z dnia 16 grudnia 2011r
SVK	Slovensko	NARIADENIE VLÁDY Slovenskej republiky z 20. júna 2007
SWE	Sverige	Occupational Exposure Limit Values, AF 2011:18
EU	OEL EU	Directive 2009/161/EU; Directive 2006/15/EC; Directive 2004/37/EC; Directive 2000/39/EC.
	TLV-ACGIH	ACGIH 2014

METHANOL

Threshold Limit Value.

Type	Country	TWA/8h		STEL/15min		
		mg/m ³	ppm	mg/m ³	ppm	
MAK	AUS	260	200	1040	800	SKIN.
VLEP	BEL	266	200	333	250	SKIN.
TLV	CZE	250		1000		SKIN.
AGW	DEU	270	200	1080	800	SKIN.
MAK	DEU	270	200	1080	800	SKIN.
TLV	DNK	260	200			
VLA	ESP	266	200			SKIN.
HTP	FIN	270	200	330	250	SKIN.
VLEP	FRA	260	200	1300	1000	SKIN.
WEL	GRB	266	200	333	250	SKIN.
AK	HUN	260		1040		
OEL	IRL	260	200			SKIN.
TLV	ITA	260	200			SKIN.
OEL	NLD	133	100			SKIN.
TLV	NOR	130	100			SKIN.
NDS	POL	100		300		
NPHV	SVK	260	200			SKIN.
MAK	SWE	250	200	350	250	SKIN.
OEL	EU	260	200			SKIN.
TLV-ACGIH		262	200	328	250	

Legend:

(C) = CEILING ; INHAL = Inhalable Fraction ; RESP = Respirable Fraction ; THORA = Thoracic Fraction.

8.2. Exposure controls.

As the use of adequate technical equipment must always take priority over personal protective equipment, make sure that the workplace is well aired through effective local aspiration. Personal protective equipment must be CE marked, showing that it complies with applicable standards.

Provide an emergency shower with face and eye wash station.

HAND PROTECTION

Protect hands with category III work gloves (see standard EN 374).

The following should be considered when choosing work glove material: compatibility, degradation, failure time and permeability.

The work gloves' resistance to chemical agents should be checked before use, as it can be unpredictable. The gloves' wear time depends on the duration and type of use.

SKIN PROTECTION

Wear category II professional long-sleeved overalls and safety footwear (see Directive 89/686/EEC and standard EN ISO 20344). Wash body with soap and water after removing protective clothing.

EYE PROTECTION

Wear airtight protective goggles (see standard EN 166).

RESPIRATORY PROTECTION

If the threshold value (e.g. TLV-TWA) is exceeded for the substance or one of the substances present in the product, use a mask with a type B filter whose class (1, 2 or 3) must be chosen according to the limit of use concentration. (see standard EN 14387). In the presence of gases or vapours of various kinds and/or gases or vapours containing particulate (aerosol sprays, fumes, mists, etc.) combined filters are required.

Respiratory protection devices must be used if the technical measures adopted are not suitable for restricting the worker's exposure to the threshold values considered. The protection provided by masks is in any case limited.

If the substance considered is odourless or its olfactory threshold is higher than the corresponding TLV-TWA and in the case of an emergency, wear open-circuit compressed air breathing apparatus (in compliance with standard EN 137) or external air-intake breathing apparatus (in compliance with standard EN 138). For a correct choice of respiratory protection device, see standard EN 529.

ENVIRONMENTAL EXPOSURE CONTROLS.

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

SECTION 9. Physical and chemical properties.

9.1. Information on basic physical and chemical properties.

Appearance	paste
Colour	colourless
Odour	characteristic
Odour threshold.	Not available.
pH.	Not available.
Melting point / freezing point.	Not available.
Initial boiling point.	Not available.
Boiling range.	Not available.
Flash point.	> 150 °C.
Evaporation Rate	Not available.
Flammability of solids and gases	Not available.
Lower inflammability limit.	Not available.
Upper inflammability limit.	Not available.
Lower explosive limit.	Not available.
Upper explosive limit.	Not available.
Vapour pressure.	Not available.
Vapour density	Not available.
Relative density.	Not available.
Solubility	immiscible with water
Partition coefficient: n-octanol/water	Not available.
Auto-ignition temperature.	> 400 °C.
Decomposition temperature.	Not available.
Viscosity	Not available.
Explosive properties	Not available.
Oxidising properties	Not available.

9.2. Other information.

Information not available.

SECTION 10. Stability and reactivity.

10.1. Reactivity.

There are no particular risks of reaction with other substances in normal conditions of use.

10.2. Chemical stability.

The product is stable in normal conditions of use and storage.

10.3. Possibility of hazardous reactions.

The vapours may also form explosive mixtures with the air.

10.4. Conditions to avoid.

Avoid overheating. Avoid bunching of electrostatic charges. Avoid all sources of ignition.

10.5. Incompatible materials.

Information not available.

10.6. Hazardous decomposition products.

In the event of thermal decomposition or fire, gases and vapours that are potentially dangerous to health may be released.

SECTION 11. Toxicological information.

11.1. Information on toxicological effects.

In the absence of experimental data for the product itself, health hazards are evaluated according to the properties of the substances it contains, using the criteria specified in the applicable regulation for classification.

It is therefore necessary to take into account the concentration of the individual hazardous substances indicated in section 3, to evaluate the toxicological effects of exposure to the product.

Upon contact with skin, this product causes sensitization (dermatitis). Dermatitis derives from skin irritation on the areas which repeatedly come into contact with the sensitizing agent. Cutaneous lesions may include: erythemas, edemas, papules, vesicles, pustules, scurries, ulcerations and exudative phenomena, whose intensity varies according to illness seriousness and affected areas. Erythemas, edemas and exudative phenomena prevail during the acute phase. Scurfy skin, dryness, ulcerations and skin thickening prevail during the chronic phase.

SECTION 11. Toxicological information. ... / >>

METHANOL: The minimal lethal dose following ingestion is considered to be in the range of 300-1000 mg/kg. Ingestion of as little as 4-10 ml methanol in adults may cause permanent blindness (IPCS).

VINYLTRIMETHOXYSILANE
LD50 (Oral). 7.46 mg/kg

TRIMETHOXY (METHYL) SILANE
LD50 (Oral). 7000 mg/kg

SECTION 12. Ecological information.

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or contaminate soil or vegetation.

12.1. Toxicity.

VINYLTRIMETHOXYSILANE
LC50 - for Fish. 100 mg/l/96h

TRIMETHOXY (METHYL) SILANE
LC50 - for Fish. 42.1 mg/l/96h

12.2. Persistence and degradability.

METHANOL
Solubility in water. mg/l 1000 - 10000
Rapidly biodegradable.

12.3. Bioaccumulative potential.

METHANOL
Partition coefficient: n-octanol/water. -0.77
BCF. 0.2

12.4. Mobility in soil.

Information not available.

12.5. Results of PBT and vPvB assessment.

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

12.6. Other adverse effects.

Information not available.

SECTION 13. Disposal considerations.

13.1. Waste treatment methods.

Reuse, when possible. Product residues should be considered special hazardous waste. The hazard level of waste containing this product should be evaluated according to applicable regulations.

Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.

CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

SECTION 14. Transport information.

14.1. UN number.

Not applicable.

14.2. UN proper shipping name.

Not applicable.



ACC Silicones LTD

AS1700

Revision nr.11
Dated 25/11/2015
Printed on 25/11/2015
Page n. 7 / 9

EN

SECTION 14. Transport information. ... / >>

14.3. Transport hazard class(es).

Not applicable.

14.4. Packing group.

Not applicable.

14.5. Environmental hazards.

Not applicable.

14.6. Special precautions for user.

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code.

Information not relevant.

SECTION 15. Regulatory information.

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture.

Seveso category. None.

Restrictions relating to the product or contained substances pursuant to Annex XVII to EC Regulation 1907/2006.

Product.
Point. 3

Substances in Candidate List (Art. 59 REACH).

None.

Substances subject to authorisation (Annex XIV REACH).

None.

Substances subject to exportation reporting pursuant to (EC) Reg. 649/2012:

None.

Substances subject to the Rotterdam Convention:

None.

Substances subject to the Stockholm Convention:

None.

Healthcare controls.

Workers exposed to this chemical agent must not undergo health checks, provided that available risk-assessment data prove that the risks related to the workers' health and safety are modest and that the 98/24/EC directive is respected.

15.2. Chemical safety assessment.

No chemical safety assessment has been processed for the mixture and the substances it contains.

SECTION 16. Other information.

Text of hazard (H) indications mentioned in section 2-3 of the sheet:

Flam. Liq. 2	Flammable liquid, category 2
Flam. Liq. 3	Flammable liquid, category 3
Acute Tox. 3	Acute toxicity, category 3
STOT SE 1	Specific target organ toxicity - single exposure, category 1
Acute Tox. 4	Acute toxicity, category 4
Eye Irrit. 2	Eye irritation, category 2
Skin Sens. 1	Skin sensitization, category 1
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H301	Toxic if swallowed.
H311	Toxic in contact with skin.
H331	Toxic if inhaled.



ACC Silicones LTD

AS1700

Revision nr.11
Dated 25/11/2015
Printed on 25/11/2015
Page n. 8 / 9

EN

SECTION 16. Other information. ... / >>

H370	Causes damage to organs.
H332	Harmful if inhaled.
H319	Causes serious eye irritation.
H317	May cause an allergic skin reaction.

LEGEND:

- ADR: European Agreement concerning the carriage of Dangerous goods by Road
- CAS NUMBER: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CE NUMBER: Identifier in ESIS (European archive of existing substances)
- CLP: EC Regulation 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals
- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX NUMBER: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
- PNEC: Predicted no effect concentration
- REACH: EC Regulation 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA STEL: Short-term exposure limit
- TWA: Time-weighted average exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation
- WGK: Water hazard classes (German).

GENERAL BIBLIOGRAPHY

1. Regulation (EU) 1907/2006 (REACH) of the European Parliament
2. Regulation (EU) 1272/2008 (CLP) of the European Parliament
3. Regulation (EU) 790/2009 (I Atp. CLP) of the European Parliament
4. Regulation (EU) 2015/830 of the European Parliament
5. Regulation (EU) 286/2011 (II Atp. CLP) of the European Parliament
6. Regulation (EU) 618/2012 (III Atp. CLP) of the European Parliament
7. Regulation (EU) 487/2013 (IV Atp. CLP) of the European Parliament
8. Regulation (EU) 944/2013 (V Atp. CLP) of the European Parliament
9. Regulation (EU) 605/2014 (VI Atp. CLP) of the European Parliament

- The Merck Index. - 10th Edition
- Handling Chemical Safety
- INRS - Fiche Toxicologique (toxicological sheet)
- Patty - Industrial Hygiene and Toxicology
- N.I. Sax - Dangerous properties of Industrial Materials-7, 1989 Edition
- ECHA website

Note for users:

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.



ACC Silicones LTD
AS1700

Revision nr.11
Dated 25/11/2015
Printed on 25/11/2015
Page n. 9 / 9

EN

SECTION 16. Other information. ... / >>

Changes to previous review:
The following sections were modified:
07.