









65W AC-DC IEC 2 Pin (C8) Inlet Desktop Power Supplies

-  FR4 PCB
-  100% ATE Tested
-  High Reliability
-  Built in OVP, OCP & SCP
-  100% smart burn-in test for 4 hours
-  Level VI Efficiency Regulations Compliant
-  Universal Input 90~260V AC 47~63Hz



DIMENSIONS



15DYS602

SPECIFICATIONS

| | | |
|---------------------------------|------------------------------|--|
| Input | Input Range | 100~240VAC (Full Range), 50/60Hz |
| | Input Current (RMS) | 1.5A@90VAC 0.75A@264VAC |
| Output | Voltage Range | 12~30VDC |
| | Voltage Regulation | +/- 5% At Constant Voltage Mode |
| | Current Range | 0.1~5A |
| | Max Power | 65W |
| Energy Saving | | NRCAN, DOE, ERP, GEMS, Efficiency Level VI |
| Environmental Protection | | RoHS, REACH, PAHS |
| Environmental | Operating Temperature | 0°C ~45°C Ambient |
| | Storage Temperature | -20°C ~+80°C |
| | Operating Humidity | 10~90% (Non-condensing) |
| | Relative Humidity | 5~95% (Non-condensing) |
| | MTBF | >25,000 hours at 80% load and 25°C ambient temperature |
| Approvals | | cULus, TUV-GS, RCM (C-Tick), PSE, CCC, CB, FCC, CE, RoHS & REACH up to 5000m |