

FO PCB terminal block - FOPT 2,2-R - 1907924


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




PCB terminal block, Pitch: 10.16 mm, Number of positions: 1, Connection method: Push-in spring connection, Mounting: Wave soldering, Conductor/PCB connection direction: 0 °, Color: black, Black, shielded housing with receive diode / optic fibers can be connected: Polymer fiber (in acc. with IEC 60793-2 type A4a, diameter outer sheath 2.2 mm) / data rate: 5 Mbps / transmission distance max. 50 m / detailed data sheet available on request

Why buy this product

- Connection of fiber optics without fiber pretreatment
- Time saving push-in connection, tools not required
- Defined contact force ensures that contact remains stable over the long term
- Intuitive use through colour coded actuation lever



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 017918 606572 |
| Weight per Piece (excluding packing) | 3.94 g |
| Custom tariff number | 85369010 |
| Country of origin | Poland |

Technical data

Dimensions

| | |
|-----------------------|----------|
| Pitch | 10.16 mm |
| Constructional height | 11 mm |

General

| | |
|--|-------------------|
| Range of articles | FOPT |
| Connection in acc. with standard | EN-VDE |
| Nominal cross section | 0 mm ² |
| Solder pin surface | Sn |
| Flammability rating according to UL 94 | HB |
| Number of positions | 1 |

FO PCB terminal block - FOPT 2,2-R - 1907924

Technical data

Standards and Regulations

| | |
|--|--------|
| Connection in acc. with standard | EN-VDE |
| Flammability rating according to UL 94 | HB |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440401 |
| eCl@ss 9.0 | 27440401 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002637 |
| ETIM 5.0 | EC002643 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211832 |
| UNSPSC 7.0901 | 39121429 |
| UNSPSC 11 | 39121429 |
| UNSPSC 12.01 | 39121429 |
| UNSPSC 13.2 | 39121429 |

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details


FO PCB terminal block - FOPT 2,2-R - 1907924

Approvals


EAC

Drawings


Drilling diagram



Dimensional drawing



Circuit diagram



FO PCB terminal block - FOPT 2,2-R - 1907924

Block diagram

