



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/17/06	MCCORMICK



PART #	LENGTH FEET [METERS]
FODLCMIL-01	3.28 [1.00]
FODLCMIL-02	6.56 [2.00]
FODLCMIL-03	9.84 [3.00]
FODLCMIL-05	16.40 [5.00]
FODLCMIL-10	32.81 [10.00]



OUTLINE DRAWING

INSERTION LOSS: ≥ 0.5 dB

INSTALLATION:
 MAX. TENSILE LOAD: 1000 N
 MIN. BEND RADIUS: 5.0 cm

OPERATING:
 MAX. TENSILE LOAD: 500 N
 Min. BEND RADIUS: 3.0 cm


IMPACT RESISTANCE: 200 IMPACTS (TIA/EIA-455-25, MILITARY REQ.)

CRUSH RESISTANCE: 440 N/cm (TIA/EIA-455-41, MILITARY REQ.)

OPERATING TEMPERATURE: -55°C to +75°C

DIMENSIONS ARE IN INCHES (mm)
 UNLESS OTHERWISE SPECIFIED,
 TOLERANCES TO BE:
 .X ± .1 (2.5) ANGLES ± 2°
 .XX ± .05 (1.3)
 .XXX ± .005 (.13)

OVERALL CABLE LENGTH TOL:
 ≤ 60 (1524) +3 (76.2) / - 0
 > 60 (1524) +5% / -0%



APPROVALS	DATE
DRAWN BY C.MCCORMICK	10/17/2006
CHECKED BY R.EVANS	10/17/2006
APPROVED BY J.ROBERTS	10/17/2006

CONFIGURATION DETAILS OF
 UNDIMENSIONED FEATURES
 MAY VARY

L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY FIBER OPTICS			
PRODUCT DESCRIPTION 62.5/125 LC/LC MIL ASSEMBLY			
SIZE A	FSCM NO. 43321	DWG. NO. FODLCMIL	REV. A
SCALE: NONE CAD FILE: FODLCMILSLDDRW			SHEET 1 OF 1