



SPECIFICATION CONTROL DRAWING

TECC0014C5

Issue 7
3-May-16
Page 1 of 2


COMMUNICATION CABLE - FOUR PAIR 24AWG U/FTP FRNC CAT5e

The complete requirements for procuring the wire described herein shall consist of this document and the issue in effect of the referenced specifications. This document takes precedence over documents referenced herein.


PRODUCT DETAILS

DESCRIPTION		PHYSICAL CHARACTERISTICS			
Application: 100BASE-T4, 100BASE-TX, 100VG-AnyLAN, 1000Base-T, 1000Base-TX 155Mbps ATM, 622Mbps ATM, 1 Gb Ethernet Rated temperature: 80°C Reference Standard: ANSI/TIA 568C-2.1, EN 50173-6, IEC 11801 Flammability Rating: IEC 60332-2-1 Halogen Free: IEC 60754-2 UV Resistance: EN 50289-4-17 Low Smoke: IEC 61034 Stranded Tinned Copper Conductor Colour-coded Insulation LSZH FRNC Jacket Packaging: Per customer request	Structure	Construction Number of Pairs	U/FTP 4 Pairs		
	Conductor	AWG Conductor material Conductor dimension(mm)	24 AWG Stranded Annealed Cooper 7 / 0.20mm		
	Insulation	Insulation material Insulation dimension(mm) Nom. Thickness (mm)	Polyolefin 1.32 ± 0.05 mm 0.24 mm		
	Cabling	Twisting lay length Cabling lay length	≤ 30 mm ≤ 200 mm		
	Filler	Material	N/A		
	Binder	Material	N/A		
	Shield	Individual shield & material Primary overall shield & material Shield nom. Coverage Drainwire	AL-Foil Polyester Tape N/A 7 / 0.20 mm		
	Outer Jacket	Outer Jacket material Outer Jacket Thickness (mm) Overall Nom Dimension (mm) Outer Jacket Rip cord Outer Jacket Colour	LSZH FRNC 0.80 mm Nom. 7.4 ±0.3 mm N/A Per Customer Request		
	MECHANICAL CHARACTERISTICS		Outer Jacket	Storage Temp Range Operating Temp Range Cable weight Max. recommended pulling tension Min. bend radius (Install) Heat Ageing UV Resistance Cold Bend Heat Shock	-40°C to +80°C -20°C to +80°C 59kg/km 100 N 10 x O.D. IEC 60811-502 EN 50289-4-17 IEC 60811-504 IEC 60811-509
	ELECTRICAL CHARACTERISTICS		Finished Cable	Nom. mutual capacitance Conductor DCR Max. operating voltage - UL	≤24.6 pF/m (@1kHz) ≤ 9.38Ω/100m 300 V
JACKET MARK		"TE CONNECTIVITY - TECC0014C5 - 4PR 24AWG STRANDED CAT 5e ANSI/TIA 568C-2.1, EN 50173-6, ISO/IEC 11801 80°C CABLE - YEAR OF MANUFACTURE - BATCH NUMBER-<metre mark>"			

CROSS SECTION



INSULATION COLOURS



Tyco Electronics UK Ltd
Faraday Road
Dorcan
SWINDON
SN3 5HH
Tel: +44 (0)1793 528171
Fax: +44 (0)1793 572516

TE Connectivity is a trading name of Tyco Electronics UK Ltd, which is registered in England and Wales, number 559926.
Registered office: Faraday Road, Dorcan, Swindon, SN3 5HH
Website: www.te.com

This drawing and the information set forth hereon are the property of Tyco Electronics UK Ltd, and are to be held in trust and confidence. Publication, duplication, disclosure or use for any purpose not expressly authorised in writing by Tyco Electronics UK Ltd is prohibited.

This specification sheet takes precedence over documents referenced herein. As Tyco Electronics UK Ltd, reserve the right to make changes in construction without notice please contact Tyco Electronics UK Ltd to ensure that this document is the latest issue.



COMMUNICATION CABLE - FOUR PAIR 24AWG U/FTP FRNC CAT5e

The complete requirements for procuring the wire described herein shall consist of this document and the issue in effect of the referenced specifications. This document takes precedence over documents referenced herein.

ELECTRICAL CHARACTERISTICS CONTINUED

Frequency	Impedance	ATT	RL	PSNEXT	PSELFEXT	PSACR
(MHz)	(Ω)	(dB/100m)	(dB Min)	(dB Min)	(dB Min)	(dB Min)
1	100±15	2.5	20.0	62.3	60.8	59.8
4	100±15	4.9	23.0	53.3	48.7	48.4
8	100±15	6.9	24.5	48.8	42.7	41.9
10	100±15	7.8	25.0	47.3	40.8	39.5
16	100±15	9.9	25.0	44.3	36.7	34.4
20	100±15	11.1	25.0	42.8	34.7	31.7
25	100±15	12.5	24.3	41.3	32.8	28.8
31.25	100±15	14.1	23.6	39.9	30.9	25.8
62.5	100±15	20.4	21.5	35.4	24.8	15.0
100	100±15	26.4	20.1	32.3	20.8	5.9

Note 1: Cable that meet the requirements of the template are not required to be measured for return loss ; alternately cables that meet the return loss requirements are not required to be measured for characteristic impedance.

Note 2: If FEXT loss is greater than 70dB, ACR-F loss may not be measured.