

CAMBLOCK PLUS

PCB
TERMINAL
BLOCKS

9.5mm Pitch High Power Rising Clamp Terminal Blocks

- 2 & 3 pole double interlocking mechanism for increased strength
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 4mm² (26-10AWG)
- Guided pin alignment
- Captive screws
-  us &  approved

CTBP04VZ



TYPE NO.	POLES	LENGTH
CTBP04VZ/2	2	19.04mm
CTBP04VZ/3	3	28.56mm
CTBP04VZ/4	4	38.08mm
CTBP04VZ/5	5	47.6mm
CTBP04VZ/6	6	57.12mm
CTBP04VZ/7	7	66.64mm
CTBP04VZ/8	8	76.16mm
CTBP04VZ/9	9	85.68mm
CTBP04VZ/10	10	95.2mm
CTBP04VZ/11	11	104.72mm
CTBP04VZ/12	12	114.24mm

SPECIFICATION

Rating	30A/300V
Insulation resistance	500MΩ/500V
Withstand Voltage	AC2000V/1min
Contact Resistance	20mΩ (max)
Working Temperature	-40°C to 105+°C
Mouldings	UL94-V0 Flame retardant PA66
Pin/Terminal	Tin plated brass
Rising Clamp	Brass, nickel plated
Screw/Torque	M3 Steel, zinc plated 0.5Nm
Recommended PCB hole size	ø1.6mm

