

## OPERATIONAL AREAS

- tube microphones


## ORDERING DATA

Colours grey (RAL 7024)  
 Reels at 200m H327  
 Weight/reel 12,50kg  
 Weight/metre 0,058kg  
 Conductors 'A' red & blue  
 Conductors 'B' black, green, grey,  
 white & yellow

## TECHNICAL SPECIFICATION

Conductor 'A' resistance < 40 Ohm/km  
 Conductor 'B' resistance < 145 Ohm/km  
 Shielding resistance < 15 Ohm/km  
 Capacitance cond to cond: 90 pF/m  
 cond to shield: 160 pF/m  
 Insulation resistance > 15 GigaOhm/km  
 Test Voltage cond to cond: 500 Veff  
 cond to shield: 2000 Veff

## Dimensions



- 1 - JACKET Grey PVC, Ø 6,2mm (RAL 7024)
- 2 - FLEECE LINING Polyester
- 3 - SHIELD 1 (Reussen shield) stranded lapped copper wire, 0,1mm
- 4 - SHIELD 2 (Reussen shield) stranded lapped copper wire, 0,1mm
- 5 - INSULATION Polyethylene, Ø 1,5mm
- 6 - INSULATION Polyethylene, Ø 1,1mm
- 7 - CONDUCTOR 'A' 252 x 0,05mm (0,50mm<sup>2</sup>) copper wires
- 8 - CONDUCTOR 'B' 72 x 0,05mm (0,14mm<sup>2</sup>) copper wires

CONVERTED FROM PS0739 ISS1 (06.09.94) IN JAN 2003

DrgNo 441-0900

TITLE AUDIO CABLE - GAC-7 'TUBE'

ALL DIMENSIONS IN MM  
 ANGLES IN DECIMAL DEGREES



**DELTRON** Components

ISSUE 1

GENERAL SPECIFICATION  
 FOR 441-0900

CUSTOMER

FILTER REF

Aprvd Date 10/02/03

Aprvd By MC

Drwn by BFS

Scale: NTS

Sheet 1 / 1