

Product Description:

Drum bulkhead fittings are the trusted workhorse commonly found in many installations. For years this traditional bulkhead has been fitted globally with energy consuming fluorescent lamps. With the new range, you can now upgrade to maintenance free, high efficiency LED alternatives without worrying about changing the look of existing installation. Available in round or square in both black and white with emergency and microwave versions.

Product Image:




Product Features:

- IP65 polycarbonate LED bulkhead
- Life not affected by frequent switching e.g. when used with occupancy controls
- Tough IK10 polycarbonate body and diffuser for maximum impact resistance
- Opal diffuser evenly diffuses light and eliminates LED hot spots
- Wall or ceiling mounting - accessories included
- 20mm conduit side entries
- Emergency and microwave options available
- Adjustable hold time, detection sensitivity and lux sensor for microwave version
- 1.5kV surge protection
- 3 year warranty

18W Polycarbonate IP65 Square Drum LED Bulkhead

Line Drawing Image



Product Specs:

Technology	LED	Number of LEDs	88
Luminaire Distribution	Ambient	Lifetime L70 (hrs)	25000
Input Voltage	180~240V AC	Input Frequency	50/60HZ
Surge Protection (kV)	1.5	Power Factor	0.9
Dimmable	No	IP Rating	IP65
IK Rating	IK10	Operating Temp. (Max) °C	40
Optic Material	PC	Length (mm)	255
Width (mm)	255	Height (mm)	95

SKU Table and Ordering

Cat No.(SKU Code)	Wattage	Lumens	Lumens/Watt	Colour	Ra	Beam Angle	SDCM
EN-BH18SW/40	18W	1300lm	72.22	4000K	80	120°	5
EN-BH18SBLK/40	18W	1300lm	72.22	4000K	80	120°	5
EN-BH18SW/40MS	18W	1300lm	72.22	4000K	80	120°	5
EN-BH18SBLK/40MS	18W	1300lm	72.22	4000K	80	120°	5
EN-BH18SW/40EM	20W	1300lm	65	4000K	80	120°	5
EN-BH18SBLK/40EM	20W	1300lm	65	4000K	80	120°	5

Compliance & Approvals:



Warranty

Please contact Aurora for specifics concerning warranty on this product. The warranty is invalid in the case of improper use, installation, tampering, and removal of the Q.C. date label; installation in an improper working environment or installation not according to the current edition of the National Electric Code. Should this product fail during the warranty period it will be replaced free of charge, subject to the correct installation of the original product and subsequent return of the faulty unit. Aurora does not accept responsibility for any installation costs associated with the replacement of this product and Aurora reserves the right to alter specifications without prior notice.

UK Enlite Sales

16 Alban Park Hatfield Road St. Albans
AL4 0JJ

United Kingdom

Tel : +44 (0) 1727 83 66 11

Fax : +44 (0) 1727 83 66 22

UK Enlite Distribution

Apex Park 6 Little Burrow Welwyn
Garden City AL7 4SW

United Kingdom

Tel : +44 (0) 1707 35 18 20

Fax : +44 (0) 1727 35 18 21