

TECHNICAL DATA SHEET



Models: CB19341

RoHS
Compliant

CROSSWEAVE REINFORCED TAPE

Specifications:

PP + fiberglass
Adhesive: hot melt
Tape Length: 50m
Tape Type: Sealing
Tape Width: 50mm
Tape Thickness: 0.12±0.01mm
Colour: Clear



Applications:

A 50m long roll of adhesive cross weave glass fibre reinforced tape, 50mm width. The tape is very heavy duty with strong resistance to tearing or ripping, even under the most adverse conditions. It is ideal for closing and reinforcing shipping cartons.

Storage and shelf life:

Clean and dry in a well-ventilated area, preferably at a temperature between 10°C and 30°C. Stored under these conditions shelf life will be a minimum of 6 months.

<u>Code</u>	<u>Description</u>
ACRT50X50	CROSSWEAVE REINFORCED TAPE

Important Notice : This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

