

Aluminum Electrolytic, 85C, ALS70, 1600 uF, 20%, 450 V, -40/+85C



General Information	
Dielectric:	Aluminum Electrolytic
Series:	ALS70
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Sleevling. MS (MxH) = M12x 16

Dimensions	
D	51mm +/-1mm
L	82mm +/-2mm
T	5.5mm +/-0.5mm
S	22.2mm +/-0.5mm
DT	13mm +/-0.5mm
LT	86.5mm +/-1mm
TD	10mm MIN
V	13.7mm NOM
Z	10mm NOM

Specifications	
Capacitance:	1600 uF
Capacitance Tolerance:	20%
Voltage DC:	450 VDC, 495 VDC (Surge), 550 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	2000 Hrs
Resistance:	117 mOhms (100Hz 20C), 76 mOhms (10kHz 20C)
Current:	7 Amps (100Hz 85C), 12.5 Amps (10 kHz 85C)
Leakage:	4320 uAmps (5min 20C)

Packaging Specifications	
Weight:	220 g
Sleevling:	Yes
Packaging:	T&R

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.