


**76-005**

Designation : Male BNC Adapter w/ two 4 mm Banana (female) Jacks (sockets), two Radial 4 mm Banana (female) Jacks (sockets) and two Quick Radial Wire Attachments (2 mm diameter Hole).

Applications : connecting a function generator or oscilloscope to wires, 4 mm banana leads, ...




- Male BNC.
- « GND » (ground) marking. The red-colored contacts are connected to the « signal » central contact of the BNC. The « GND » black-colored contacts are connected to the « ground » outer contact of the BNC.
- Two radial 4 mm banana (female) jacks. Their spacing complies with the 19 mm (3/4 inch) spacing. The jacks comply with non-shrouded (or retracting shroud) 4 mm banana plugs.
- Two quick radial wire attachments. Two Ø2 mm holes and two buttons.
- Two 4 mm banana (female) jacks. Their spacing complies with the 19 mm (3/4 inch) spacing. The jacks comply with non-shrouded (or retracting shroud) 4 mm banana plugs. 4 mm banana plugs can be connected while there are wires in the radial Ø2 mm holes.



How to implement : attaching a wire to one of the two quick radial attachments.

➔ Step 1 of 3. Strip the end of the wire as below depending on the outer diameter of the wire.



- ➔ Step 2 of 3. Unscrew the button and slip the end of the wire into the Ø2 mm hole.
- ➔ Step 3 of 3. Screw the button until it tightens well the wire (2.3 N.m maximum torque).
- ➔ The product is ready to use.

76-005

Designation : Male BNC Adapter w/ two 4 mm Banana (female) Jacks (sockets), two Radial 4 mm Banana (female) Jacks (sockets) and two Quick Radial Wire Attachments (2 mm diameter Hole).



|                             |  |
|-----------------------------|--|
| Electrical safety           | Very low voltages only :<br>33 V AC / 70 V DC,<br>3 A.   |
| Operating temperature range | -20 °C mini., +80 °C maxi..  |
| Conformity                  | <ul style="list-style-type: none"> <li>• European Directive "RoHS" 2011/65/EU.</li> <li>• European REACH regulation n°1907 / 2006.</li> </ul>  |
| Environment                 | <ul style="list-style-type: none"> <li>• "RoHS" compliant, Pb ≤ 4 % in conductor, Pb ≤ 0.1 % in insulator, Hg ≤ 0.1 %, Cr VI ≤ 0.1 %, Cd ≤ 0.01 %, PBB ≤ 0.1 %, and PBDE ≤ 0.1 %.</li> <li>• REACH compliant, no substances from the candidate list of SVHC for authorisation at mass concentrations greater than 0.1 %</li> </ul> |
| Materials                   | Conductors : nickel-coated brass and gold-coated brass. Insulators, please contact us.   |
| Colors                      | <b>Black</b>   |
| Weight                      | 0.030 kg.  |
| Reliability benchmark       | Year of 1st placing on the market 1992.  |
| Packaging                   | One piece per bag.   |

**GLOSSARY :**

ACCESSIBLE. Able to be touched with a standard test finger or test pin.

BASIC INSULATION. Insulation of hazardous live parts which provides basic protection.

CAT II. Measurement or overvoltage category II. For measurement performed on / equipment connected to the building wiring.

CAT III. Measurement or overvoltage category III. For measurement performed on / equipment connected to part of a building wiring installation.

CAT IV. Measurement or overvoltage category IV. For measurement performed on / equipment connected to the origin of the electrical supply to a building.

CLEARANCE. Shortest distance in air between two conductive parts.

CREEPAGE DISTANCE. Shortest distance along the surface of a solid insulating material between two conductive parts.

DOUBLE INSULATION. Insulation comprising both BASIC INSULATION and SUPPLEMENTARY INSULATION.

EN / IEC 60529:2001. The 2001 version of the European / international standard regarding the degrees of protection provided by enclosures.

EN / IEC 61010-031:2008. The latest version (in February 2012) of the European / international standard regarding the safety requirements for electrical equipment for measurement, control and laboratory use – Part 031: Safety requirements for hand-held probe assemblies for electrical measurement and test. Version year 2008.

IP2X. Solid protection to prevent finger touch according to the European / international standard EN / IEC 60529.

"LVD". European Directive 2006/95/EC on the harmonisation of the laws of Member States relating to electrical equipment designed for use within certain voltage limits. (Usually called the Low Voltage Directive.)

NF C 93-440:1986. French standard regarding one pole plugs, sockets and safety assemblies diameter 4 mm and specially the interchangeability dimensions of plugs and sockets.\*

OVERVOLTAGE CATEGORY. Numeral defining a TRANSIENT OVERVOLTAGE condition.

POLLUTION. Addition of foreign matter, solid, liquid or gaseous (ionized gases), that may produce a reduction of dielectric strength or surface resistivity.

POLLUTION DEGREE. Numeral indicating the level of POLLUTION that may be present in the environment.

POLLUTION DEGREE 1. No POLLUTION or only dry, non-conductive POLLUTION occurs, which has no influence.

POLLUTION DEGREE 2. Only non-conductive POLLUTION occurs except that occasionally a temporary conductivity caused by condensation is expected.

POLLUTION DEGREE 3. Conductive POLLUTION occurs, or dry, non-conductive pollution occurs which becomes conductive due to condensation which is expected.

REINFORCED INSULATION. Insulation which provides protection against electric shock not less than that provided by DOUBLE INSULATION.

"RoHS". European Directive 2002/95/EC on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

SOLID INSULATION. Insulating materials.

SUPPLEMENTARY INSULATION. Independent insulation applied in addition to BASIC INSULATION in order to provide protection against electric shock in the event of a failure of BASIC INSULATION.

TRANSIENT OVERVOLTAGE. Short duration overvoltage of a few milliseconds or less, oscillatory or non-oscillatory, usually highly damped.