Data Sheet




SUCOTEST_18A_Stock Assembly

Description

Sucotest 18A armoured test assemblies offer excellent electrical performance (low insertion loss combined with unique stability and excellent return loss) for heavy duty, outdoor and harsh environment measurements up to 18 GHz.

Product description Item number ST18A/Nm/Nf/3000mm

84013032



Product Configuration

Cable type SUCOTEST_18A

Ruggedisation Steel wire spring, steel braid, TPU jacket blue

3'000 mm N straight male N straight female

Technical Data

Length of assembly

Connector A

Connector B

Mechanical Data

Diameter: 10.3 mm
Min. bending radius static 30 mm
Min. bending radius repeated 50 mm
Recommended mating torque (*) 1.0 Nm
Waterproof IP 68

Flex life 100'000 cycles

Weight 300 g

Environmental Data

 $\begin{array}{lll} \text{Operating temperature} & -40^{\circ}\text{C to} + 85^{\circ}\text{C} \\ \text{Storage temperature} & -40^{\circ}\text{C to} + 85^{\circ}\text{C} \\ \text{RoHS, REACH} & \text{Compliant} \end{array}$

Electrical Data

Return Loss min. 19.0 dB (up to 18 GHz)
Insertion loss (assembly) max. 5.30 dB (18 GHz, 25°C)
Power handling min. 120 W (18 GHz, sea level, 25°C)
Screening effectiveness > 90 dB (up to 18 GHz)

Screening effectiveness > 90 dB (up to 18 GHz)
Insertion loss stability vs. bending (**) +/- 0.2 dB (up to 18 GHz)
Phase stability vs. bending (**) < 0.7° (el/GHz)

General Information

(*) H+S torque wrench H+S description: 74_Z-0-0-193 // material/item number: 22645085

(**) Stability test 360°, diameter 55 mm

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.