


KEMET Part Number: C1206J154K1RACTU
(C1206J154K1RAC7800)

Ceramic, Open Mode, OpenModeFlexTerm-(CxxxxJ), 0.15 uF, 10%, 100 V, 1206, X7R, SMD, MLCC, Open Mode, Temperature Stable



CeramicChipSolutions
© 2011 KEMET Electronics Inc.
All rights reserved

Dimensions

L	3.3mm +/-0.4mm
W	1.6mm +/-0.35mm
T	1.6mm +/-0.25mm
B	0.6mm +/-0.25mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	2000

General Information

Style:	SMD Chip
Series:	OpenModeFlexTerm-(CxxxxJ)
Chip Size:	1206
Description:	SMD, MLCC, Open Mode, Temperature Stable
Features:	Open Mode, Temperature Stable
RoHS:	Yes
Termination:	Flexible Termination
Marking:	No
Failure Rate:	N/A
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours

Specifications

Capacitance:	0.15 uF
Capacitance Tolerance:	10%
Voltage DC:	100 VDC
Dielectric Withstanding Voltage:	250 V
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	667 MOhms