


Setting Standards

Cable Glands Cable Protection



2013



Setting Standards

www.hummel.com

HUMMEL AG





Online Catalog

- Product Pictures and Product Information
- Product and Assembly Videos
- Assembly and Operations Manual
- Technical drawings
- 3D data
- Certificates



Download-Center

- Catalog and Flyer
- Assembly instructions and installation instructions
- Press releases
- Certificates and approvals
- ...



Searching Products

- Part Number search
- Searching Details



Enclosure-Configurator

- Individual Enclosures
- Enclosure Solutions
- Online configuration, requesting and ordering



Technology Center

- Technical Information (Protection, thread, material, ...)
- Diagrams and evaluation
- Product description
- Assembly Video and Operations Manual



News of the HUMMEL AG

- Trade fairs and exhibitions
- Press releases
- New Products
- Job vacancies
- Studies, training and vocational practical training



Solutions all from one source



Touch




Cable Glands,
Circular Connectors



Solutions



Industrial Enclosures



Electronic

Table of Contents

Industrial cable glands

HSK-standard cable glands

► 13



Metr. PG NPT Metr. PG NPT Metr. PG NPT

HSK-EMC cable glands

► 29



PG NPT PG NPT Metr. PG NPT

HSK cable glands for special applications

► 37



Metr. PG NPT Metr. PG NPT Metr. PG NPT

METRICA cable glands

► 57



Metr. Metr. Metr. Metr. Metr. Metr. Metr.

Miscellaneous cable glands

► 63



WADI DIN 46320 WADI DIN 46320 WADI

Accessories

► 73



Limited Liability

Products, design, colors and dimensions are subject to change without prior notice. We reserve the right to make technical improvements on all our products, currently ordered or for future orders. It is the user's responsibility to verify all dimensions and technical data. HUMMEL AG will assume no liability regarding information provided to the user by published literature or inside technical staff, its distributors and outside sales personnel. Errors in the catalog can occur and shall not create any liability whatsoever for HUMMEL. All information provided by HUMMEL is without guarantee and must be verified by the user.

Special Products

► 6

New Products

► 7

Index

► 8

Technical Information

► 176

Assembly Instructions

► 179

Created & Printed by

Graphic & Layout: intermedia marketing gmbh, Mozartstraße 2, 79183 Waldkirch, Germany, Tel. +49 (0) 76 81 / 47 78 99-0, Fax +49 (0) 76 81 / 47 78 99-27, kontakt@intermedia-marketing.de
Printer: Druckerei Furtwängler GmbH, 79211 Denzlingen, Germany, Telefon +49 (0) 76 66 / 1331. Printed on recycled paper in March 2013. English 2013

Cable glands for hazardous areas

EXIOS Standard, Barrier

► 103



EXIOS A2F

► 108



Industrial cable glands for hazardous areas

HSK-Ex-e Standard cable glands

► 111



HSK-EMC-Ex-e cable glands

► 123



HSK-Ex-e cable glands for special applications

► 131



HSK-Ex-d standard cable glands

► 139



Ex accessories

► 143



Table of Contents

Corrugated conduit systems

Snapflex Industry standard metric


► 155



Metr. PG NPT Metr. PG NPT Metr. PG NPT

Snapflex-Ex metric


► 167



ATEX ATEX ATEX ATEX ATEX ATEX ATEX

DN conduits

► 171




Special Products

HUMMEL is your partner for special projects in strain relief, conduit systems, circular connectors, thermoplastic, aluminium, metal and stainless steel enclosures.

Challenge us – we find a solution.

Please contact our sales department or engineering department (see back side of catalog).



New Products

- + **EXIOS Barrier** high end cable gland for armoured cables in hazardous areas
M16 x 1,5 to M75 x 1,5
NPT 3/8" to NPT 3"

► Product on page 106

EXIOS
+ BARRIER



- + **EXIOS A2F** Ex-e and Ex-d cable gland for non-armoured cables for hazardous areas
in the sizes M16 x 1,5 to M75 x 1,5

► Product on page 108

EXIOS
+ A2F



- + **Snapturn-elbow** for Snapflex conduits with 90° and 135° elbow with brass or plastic thread sizes M16 x 1,5 to M50 x 1,5

► Product on page 160



Product Number	Description	Page	Product Number	Description	Page	Product Number	Description	Page
1.022.	Earthtag	110	1.291.	HSK-K-Ex	112 – 116	1.634.	HSK-M-PVDF-Ex-d	140
1.033.	E-Ms	96	1.293.	HSK-K-Flex	42, 43	1.636.	HSK-M-EMV-D-Ex	124, 125
1.039.	RE-Ms	95	1.294.	HSK-K-Flex	42	1.637.	HSK-M-EMV-D-Ex	124, 125
1.052.	V-N-Ms	91	1.295.	HSK-K-Ex	112, 113	1.640.	HSK-M-Ex	117 – 120
1.052.	V-N-Ms-SD	91	1.296.	HSK-V-Ex	146	1.641.	HSK-MZ-Ex	137, 138
1.071.	R-H	93	1.296.	HSK-V-Ex MZ version	146	1.642.	HSK-INOX-Ex	121, 122
1.076.	R-H	93	1.297.	V-Ex	144, 145	1.646.	HSK-M-EMV-Ex	126, 127
1.077.	RSD-Ms	94	1.299.	HSK-K-PVDF	20, 21	1.647.	HSK-MZ-EMV-Ex	128 – 130
1.078.	RSD-Ms-Ex	148	1.306.	FW-T	85	1.660.	HSK-M-PVDF-Ex	117 – 120
1.079.	RSD-Ms-Ex	148	1.306.	FW-ZN	98	1.661.	HSK-MZ-PVDF-Ex	137, 138
1.089.	HSK-ME	86	1.309.	HSK-M-W	56	1.662.	HSK-INOX-PVDF-Ex	121, 122
1.091.	HSK-FLAKA	87	1.312.	KF-G	84, 175	1.666.	HSK-M-EMV-PVDF-Ex	127
1.094.	RS-INOX	101, 102	1.313.	HSK-W	44, 45	1.667.	HSK-MZ-EMV-PVDF-Ex	129, 130
1.097.	RSD-INOX	101, 102	1.314.	HSK-W-Flex	46	1.669.	HSK-MZ-PVDF	54, 55
1.098.	RSD-INOX-Ex	152	1.315.	90° Snap Elbow	82	1.675.	HSK-INOX	27, 28
1.099.	RSD-INOX-Ex	152	1.316.	90° Snap Elbow	82	1.676.	HSK-INOX-PVDF	27, 28
1.101.	DIN 46320-C4-Ms	69	1.317.	HSK-W rotating version	45	1.680.	SE	72
1.105.	Z	70, 71	1.318.	Snapform	166	1.681.	ZSE	72
1.106.	GM-Ms	90	1.321.	O-Ring	88	1.683.	METRICA-M-EMV	62
1.106.	HSK-MINI	51	1.325.	Thread Seal Ring	89	1.687.	HSK-M-Multi-Ex	135
1.106.	HSK-XL	52, 53	1.326.	Thread Seal Ring	109	1.688.	HSK-M-FLAKA	48
1.106.	WADI-A	64, 65	1.329.	Serrated Washer	110	1.689.	HSK-M-FLAKA-Ex	136
1.106.	WADI-A-FPM	66, 67	1.510.	Snapflex	156	1.690.	HSK-MZ	54, 55
1.112.	HSK-MINI	51	1.510.	SM-WS-PA	172	1.691.	HSK-M-EMV	32, 33
1.119.	HSK-MINI-EMV	51	1.511.	SM-N	173	1.692.	HSK-MZ-EMV	38
1.129.	HSK-MINI-INOX	51	1.513.	SM-W	174	1.695.	HSK-INOX	29, 30
1.143.	KLE	97	1.514.	SM-N	158	1.696.	HSK-INOX-PVDF	29, 30
1.152.	VINOX-NBR	100	1.515.	Snapturn	159	1.697.	HSK-M-Multi	47
1.153.	VINOX-FPM	100	1.518.	Snapsplit	157	1.699.	HSK-M-PVDF	22 – 26
1.154.	VINOX-VMQ	100	1.519.	Snapsplit	157	1.730.	Snapclip	166
1.155.	VNE-Ms	92	1.525.	Snapturn 90°	160	1.731.	Snapclip-Ex	168
1.156.	VNE-Ms-SD	92	1.526.	Snapturn 135°	161	1.740.	HSK-INOX-HD	39
1.157.	VNE-Ms-SD-FPM	92	1.542.	Snapclie-DUO-PA	162	1.802.	PVC Shroud	109
1.161.	GM-Ms	90	1.543.	Snapclie-DUO-PA	162	1.875.	V-Ms-Ex-d	149
1.161.	GM-INOX	99	1.547.	Snapclie-DUO-Ms	163	1.876.	V-Ms-Ex-d	149
1.167.	GM-EMV	90	1.548.	Snapclie-DUO-Ms	163	1.877.	V-Ms-Ex-d	149
1.171.	RE-Ms	95	1.552.	Snapclie-PA-W	164	1.878.	RSD-Ms-Ex-d	150
1.192.	VINOX-Ex	151	1.553.	Snapclie-DUO-PA-W	165	1.879.	RSD-Ms-Ex-d	150
1.193.	VINOX-Ex	151	1.554.	Snapclie-DUO-PA-W	165	1.895.	VINOX-Ex-d	153
1.194.	VINOX-Ex	151	1.560.	Snapflex-Ex	168	1.896.	VINOX-Ex-d	153
1.197.	V-Ms-Ex	147	1.566.	Snapclie-DUO-Ms-Ex	169	1.897.	VINOX-Ex-d	153
1.198.	V-Ms-FPM-Ex	147	1.567.	Snapclie-DUO-Ms-Ex	170	1.898.	RSD-INOX-Ex-d	154
1.199.	V-Ms-VMQ-Ex	147	1.587.	HSK-K-FLAKA	41	1.899.	RSD-INOX-Ex-d	154
1.201.	DIN 46320-A-FS	68	1.589.	HSK-K-FLAKA-Ex	133			
1.202.	DIN 46320-A-FS	68	1.590.	HSK-KE	18			
1.209.	HSK-K	14, 15, 16, 17, 19	1.591.	HSK-KR	18			
1.213.	KS	83	1.597.	HSK-K-Multi	40			
1.215.	HSK-K-MZ-Ex	134	1.599.	HSK-K-Multi-Ex	132			
1.218.	METRICA-P	58, 59	1.605.	EXIOS Standard	104, 105			
1.219.	HSK-K	14, 15	1.606.	EXIOS Barrier	106, 107			
1.233.	K-FS	81	1.607.	METRICA-M-EMV-E	61			
1.235.	R-FS	79	1.608.	EXIOS A2F	108			
1.236.	R-FS	79	1.609.	HSK-M	22 – 26			
1.238.	METRICA-P-Flex	58, 59	1.610.	HSK-M-Ex	117 – 120			
1.239.	E-M-PA	81	1.611.	HSK-MZ-Ex	137, 138			
1.250.	DS	77	1.612.	HSK-INOX-Ex	121, 122			
1.251.	VN-FS	75	1.616.	HSK-M-EMV-Ex	126, 127			
1.255.	VNE	76	1.617.	HSK-MZ-EMV-Ex	128 – 130			
1.256.	VNE-SD	76	1.618.	METRICA-M	60			
1.262.	GM-FS	74	1.622.	HSK-M-Ex-d	140			
1.263.	GM-KS	83	1.623.	HSK-M-Flex	49, 50			
1.271.	R-FS	79	1.624.	HSK-M-Flex-EMV	34, 35			
1.272.	R-FS	79	1.628.	HSK-MZ-Ex-d	141			
1.273.	R-M-PA	80	1.631.	HSK-M-EMV-D	30, 31			
1.280.	HSK-V	78	1.632.	HSK-INOX-Ex-d	142			
1.282.	WN	77	1.633.	HSK-INOX-PVDF-Ex-d	142			

Product Number	Description	Page	Product Number	Description	Page	Product Number	Description	Page
1.315.	90° Snap Elbow	82	1.089.	HSK-ME	86	1.553.	Snapcllic-DUO-PA-W	165
1.316.	90° Snap Elbow	82	1.106.	HSK-MINI	51	1.554.	Snapcllic-DUO-PA-W	165
1.201.	DIN 46320-A-FS	68	1.112.	HSK-MINI	51	1.731.	Snapcllic-Ex	168
1.202.	DIN 46320-A-FS	68	1.119.	HSK-MINI-EMV	51	1.552.	Snapcllic-PA-W	164
1.101.	DIN 46320-C4-Ms	69	1.129.	HSK-MINI-INOX	51	1.730.	Snapcllic	166
1.250.	DS	77	1.690.	HSK-MZ	54, 55	1.510.	Snapflex	156
1.022.	Earthtag	110	1.692.	HSK-MZ-EMV	36	1.560.	Snapflex-Ex	168
1.239.	E-M-PA	81	1.617.	HSK-MZ-EMV-Ex	128 – 129	1.318.	Snapform	166
1.033.	E-Ms	96	1.647.	HSK-MZ-EMV-Ex	128 – 130	1.518.	Snapsplit	157
1.608.	EXIOS A2F	108	1.667.	HSK-MZ-EMV-PVDF-Ex	129, 130	1.519.	Snapsplit	157
1.606.	EXIOS Barrier	106, 107	1.611.	HSK-MZ-Ex	137, 138	1.515.	Snapturn	159
1.605.	EXIOS Standard	104, 105	1.641.	HSK-MZ-Ex	137, 138	1.525.	Snapturn 90°	160
1.306.	FW-T	85	1.628.	HSK-MZ-Ex-d	141	1.526.	Snapturn 135°	161
1.306.	FW-ZN	98	1.669.	HSK-MZ-PVDF	54, 55	1.325.	Thread Seal Ring	89
1.167.	GM-EMV	90	1.661.	HSK-MZ-PVDF-Ex	137, 138	1.297.	V-Ex	144, 145
1.262.	GM-FS	74	1.280.	HSK-V	78	1.192.	V-INOX-Ex	151
1.161.	GM-INOX	99	1.296.	HSK-V-Ex	146	1.193.	V-INOX-Ex	151
1.263.	GM-KS	83	1.296.	HSK-V-Ex MZ version	146	1.194.	V-INOX-Ex	151
1.106.	GM-Ms	90	1.313.	HSK-W	44, 45	1.895.	V-INOX-Ex-d	153
1.161.	GM-Ms	90	1.314.	HSK-W-Flex	46	1.896.	V-INOX-Ex-d	153
1.091.	HSK-FLAKA	87	1.317.	HSK-W rotating version	45	1.897.	V-INOX-Ex-d	153
1.695.	HSK-INOX	27, 28	1.106.	HSK-XL	52, 53	1.153.	V-INOX-FPM	100
1.675.	HSK-INOX	27, 28	1.233.	K-FS	81	1.152.	V-INOX-NBR	100
1.612.	HSK-INOX-Ex	121, 122	1.312.	K-FG	84, 175	1.154.	V-INOX-VMQ	100
1.642.	HSK-INOX-Ex	121, 122	1.143.	KLE	97	1.197.	V-Ms-Ex	147
1.632.	HSK-INOX-Ex-d	142	1.213.	KS	83	1.875.	V-Ms-Ex-d	149
1.740.	HSK-INOX-HD	39	1.218.	METRICA-P	58, 59	1.876.	V-Ms-Ex-d	149
1.696.	HSK-INOX-PVDF	27, 28	1.238.	METRICA-P-Flex	58, 59	1.877.	V-Ms-Ex-d	149
1.676.	HSK-INOX-PVDF	27, 28	1.618.	METRICA-M	60	1.198.	V-Ms-FPM-Ex	147
1.662.	HSK-INOX-PVDF-Ex	121, 122	1.683.	METRICA-M-EMV	62	1.199.	V-Ms-VMQ-Ex	147
1.633.	HSK-INOX-PVDF-Ex-d	142	1.607.	METRICA-M-EMVE	61	1.251.	V-N-FS	75
1.209.	HSK-K	14, 15, 16, 17, 19	1.321.	O-Ring	88	1.052.	V-N-Ms	91
1.219.	HSK-K	14, 15	1.802.	PVC Shroud	109	1.052.	V-N-Ms-SD	19
1.291.	HSK-K-Ex	112 – 113	1.326.	Red Fibre Washer	109	1.255.	V-NE	76
1.295.	HSK-K-Ex	112, 113	1.235.	R-FS	79	1.155.	V-NE-Ms	92
1.587.	HSK-K-FLAKA	41	1.236.	R-FS	79	1.156.	V-NE-Ms-SD	92
1.589.	HSK-K-FLAKA-Ex	133	1.271.	R-FS	79	1.157.	V-NE-Ms-SD-FPM	92
1.293.	HSK-K-Flex	42, 43	1.272.	R-FS	79	1.256.	V-NE-SD	76
1.294.	HSK-K-Flex	42	1.071.	R-H	93	1.106.	WADI-A	64, 65
1.597.	HSK-K-Multi	40	1.076.	R-H	93	1.106.	WADI-A-FPM	66, 67
1.599.	HSK-K-Multi-Ex	132	1.273.	R-M-PA	80	1.282.	WN	77
1.215.	HSK-K-MZ-Ex	134	1.039.	RE-Ms	95	1.105.	Z	70, 71
1.299.	HSK-K-PVDF	20, 21	1.171.	RE-Ms	95	1.681.	ZSE	72
1.590.	HSK-KE	18	1.094.	RS-INOX	101, 102			
1.591.	HSK-KR	18	1.097.	RSD-INOX	101, 102			
1.609.	HSK-M	22 – 26	1.098.	RSD-INOX-Ex	152			
1.691.	HSK-M-EMV	32, 33	1.099.	RSD-INOX-Ex	152			
1.631.	HSK-M-EMVD	30, 31	1.898.	RSD-INOX-Ex-d	154			
1.636.	HSK-M-EMVD-Ex	124, 125	1.899.	RSD-INOX-Ex-d	154			
1.637.	HSK-M-EMVD-Ex	124, 125	1.077.	RSD-Ms	94			
1.616.	HSK-M-EMV-Ex	126, 127	1.078.	RSD-Ms-Ex	148			
1.646.	HSK-M-EMV-Ex	126, 127	1.079.	RSD-Ms-Ex	148			
1.666.	HSK-M-EMV-PVDF-Ex	127	1.878.	RSD-Ms-Ex-d	150			
1.610.	HSK-M-Ex	117 – 120	1.879.	RSD-Ms-Ex-d	150			
1.640.	HSK-M-Ex	117 – 120	1.680.	SE	72			
1.622.	HSK-M-Ex-d	140	1.329.	Serrated Washer	110			
1.688.	HSK-M-FLAKA	48	1.511.	SM-N	173			
1.689.	HSK-M-FLAKA-Ex	136	1.514.	SM-N	158			
1.623.	HSK-M-Flex	49, 50	1.513.	SM-W	174			
1.624.	HSK-M-Flex-EMV	34, 35	1.510.	SM-WS-PA	172			
1.697.	HSK-M-Multi	47	1.547.	Snapcllic-DUO-Ms	163			
1.687.	HSK-M-Multi-Ex	135	1.548.	Snapcllic-DUO-Ms	163			
1.699.	HSK-M-PVDF	22 – 26	1.566.	Snapcllic-DUO-Ms-Ex	169			
1.660.	HSK-M-PVDF-Ex	117 – 120	1.567.	Snapcllic-DUO-Ms-Ex	170			
1.634.	HSK-M-PVDF-Ex-d	140	1.542.	Snapcllic-DUO-PA	162			
1.309.	HSK-M-W	56	1.543.	Snapcllic-DUO-PA	162			

HSK-Industry Standard



also in



IP 69 K

- + Halogen- and phosphorous-free
- + Fire protection class V0 according to UL 94
- + ULf1 UV-stable HSK Black Nylon
- + Liquid tight per NEMA 4x & 6 to 150 PSIG (IP 68 to 10 bar) according to DIN EN 60529
- + Patented ratchet and spline secures the dome nut on the body


HSK-K

Flexible overlapping clamping splines prevent the form seal from being pulled out of the fitting

The form seal allows for an IP 68 (10 bar) rating

The rugged lead screw results in a dependable transmission of force between nut and body

The concentric seal ridge and molded groove for an optional O-Ring results in a liquid tight seal between body and housing



HSK-M

Flexible overlapping clamping splines prevent the form seal from being pulled out of the fitting

The internal sealing edge results in a superior seal between the splined Nylon clamping insert and the nickel plated brass body

The form seal allows for an IP 68 (10 bar) rating

Rotation of the cable during installation is prevented due to the internal splines



HSK-EMC-Industry Standard



also in



IP 69K


- + Halogen- and phosphorous-free
- + Fire protection class V0 according to UL 94
- + Liquid tight per NEMA 4x & 6 to 150 PSIG (IP 68 to 10 bar) according to DIN EN 60529
- + Quick assembly and reliable grounding of shielded cables

HSK-M-EMV

Flexible overlapping clamping splines prevent the form seal from being pulled out of the fitting

The internal sealing edge results in a superior seal between the splined Nylon clamping insert and the nickel plated brass body

Patented 360° grounding due to the internal O-Ring, which results in a perfect contact between braided shield of cable and fitting



HSK-M-EMV-D

Flexible overlapping clamping splines prevent the form seal from being pulled out of the fitting

Metalised spline insert provides electrical conductivity

Flexible contact points allow contact with variable braid diameters



Snapclic-DUO



- + Conduit fitting and cable gland in one article
- + Halogen- and phosphorous-free
- + Quick assembly
- + IP 68 degree of protection on cable gland according to DIN EN 60529
- + EMC version available



screw in



tighten
nut



push
into hole



finished



Snapclic-DUO

Corrugated conduit
mounting with
integrated cable gland

Industrial cable glands

HSK-standard cable glands

Cable glands of the HSK-series fulfil the highest demands of quality and security.
Outstanding high-grade materials are used together with innovative technology to offer premium products.



You can find in this chapter:

HSK standard cable glands, made of

- polyamide
- PVDF
- nickel plated brass
- various grades of stainless steel

We provide variable clamping ranges, thread lengths, thread types plus different sealing materials and temperature ranges.
Our range is completed by global certifications.

If there are still open requests from your side, please contact us. We are looking forward to developing solutions together.
You profit from our vast knowledge in development, engineering and production technology.

Contact us:

E-Mail: info.et@hummel.com

Tel.: +49 (0) 76 66/9 11 10-0

Advice:

- ➔ HSK EMC cable glands can be found in the next chapter from page 29
- ➔ Cable glands with smaller threads than M12 and larger threads than M63, multi hole fittings and much more can be found in the chapter "HSK cable glands for special applications" from page 37

HSK-standard cable glands

HSK-K

Metr.



Material Polyamide V0 according to UL 94

Seal Buna-N


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005),
blue (RAL 5012) for the intrinsic safety "i"

Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material e.g. Silicone upon request
- Other colors on request



AG	mm	GL	H	mm	Number grey	Number black	Number blue
M 12 x 1,5	3-6,5	8	21	15	1.209.1200.50	1.209.1201.50	1.209.1202.50
M 12 x 1,5	2-5	8	21	15	1.209.1200.51	1.209.1201.51	1.209.1202.51
M 16 x 1,5	4-8	8	22	19	1.209.1600.50	1.209.1601.50	1.209.1602.50
M 16 x 1,5	2-6	8	22	19	1.209.1600.51	1.209.1601.51	1.209.1602.51
M 16 x 1,5	5-10	8	25	22	1.219.1600.50	1.219.1601.50	1.219.1602.50
M 20 x 1,5	6-12	9	27	24	1.209.2000.50	1.209.2001.50	1.209.2002.50
M 20 x 1,5	5-9	9	27	24	1.209.2000.51	1.209.2001.51	1.209.2002.51
M 20 x 1,5	10-14	9	28	27	1.219.2000.50	1.219.2001.50	1.219.2002.50
M 25 x 1,5	13-18	11	31	30	1.219.2500.50	1.219.2501.50	1.219.2502.50
M 25 x 1,5	13-18	11	31	33	1.209.2500.50	1.209.2501.50	1.209.2502.50
M 25 x 1,5	9-16	11	31	33	1.209.2500.51	1.209.2501.51	1.209.2502.51
M 32 x 1,5	15-21	11	39	36	1.219.3200.50	1.219.3201.50	1.219.3202.50
M 32 x 1,5	18-25	11	39	42	1.209.3200.50	1.209.3201.50	1.209.3202.50
M 32 x 1,5	13-20	11	39	42	1.209.3200.51	1.209.3201.51	1.209.3202.51
M 40 x 1,5	19-27	13	47	46	1.219.4000.50	1.219.4001.50	1.219.4002.50
M 40 x 1,5	22-32	13	48	53	1.209.4000.50	1.209.4001.50	1.209.4002.50
M 40 x 1,5	20-26	13	48	53	1.209.4000.51	1.209.4001.51	1.209.4002.51
M 50 x 1,5	32-38	13	49	60	1.209.5000.50	1.209.5001.50	1.209.5002.50
M 50 x 1,5	25-31	13	49	60	1.209.5000.51	1.209.5001.51	1.209.5002.51
M 63 x 1,5	37-44	14	49	65/68	1.209.6300.50	1.209.6301.50	1.209.6302.50
M 63 x 1,5	29-35	14	49	65/68	1.209.6300.51	1.209.6301.51	1.209.6302.51

Accessories see page 73

HSK-standard cable glands

HSK-K

Metr.-elongated



Material Polyamide V0 according to UL 94

Seal Buna-N


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005),
blue (RAL 5012) for the intrinsic safety "i"

Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material e.g. Silicone upon request
- Other colors on request



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number grey	Number black	Number blue
M 12 x 1,5	3–6,5	15	21	15	1.209.1200.30	1.209.1201.30	1.209.1202.30
M 12 x 1,5	2–5	15	21	15	1.209.1200.31	1.209.1201.31	1.209.1202.31
M 16 x 1,5	4–8	15	22	19	1.209.1600.30	1.209.1601.30	1.209.1602.30
M 16 x 1,5	2–6	15	22	19	1.209.1600.31	1.209.1601.31	1.209.1602.31
M 16 x 1,5	5–10	15	25	22	1.219.1600.30	1.219.1601.30	1.219.1602.30
M 20 x 1,5	6–12	15	27	24	1.209.2000.30	1.209.2001.30	1.209.2002.30
M 20 x 1,5	5–9	15	27	24	1.209.2000.31	1.209.2001.31	1.209.2002.31
M 20 x 1,5	10–14	15	28	27	1.219.2000.30	1.219.2001.30	1.219.2002.30
M 25 x 1,5	13–18	15	31	33	1.209.2500.30	1.209.2501.30	1.209.2502.30
M 25 x 1,5	9–16	15	31	33	1.209.2500.31	1.209.2501.31	1.209.2502.31
M 32 x 1,5	18–25	15	39	42	1.209.3200.30	1.209.3201.30	1.209.3202.30
M 32 x 1,5	13–20	15	39	42	1.209.3200.31	1.209.3201.31	1.209.3202.31
M 40 x 1,5	22–32	18	48	53	1.209.4000.30	1.209.4001.30	1.209.4002.30
M 40 x 1,5	20–26	18	48	53	1.209.4000.31	1.209.4001.31	1.209.4002.31
M 50 x 1,5	32–38	18	49	60	1.209.5000.30	1.209.5001.30	1.209.5002.30
M 50 x 1,5	25–31	18	49	60	1.209.5000.31	1.209.5001.31	1.209.5002.31
M 63 x 1,5	37–44	18	49	65/68	1.209.6300.30	1.209.6301.30	1.209.6302.30
M 63 x 1,5	29–35	18	49	65/68	1.209.6300.31	1.209.6301.31	1.209.6302.31

HSK-standard cable glands

HSK-K

PG



Material Polyamide V0 according to UL 94



Seal Buna-N



Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring


Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005),
blue (RAL 5012) for the intrinsic safety "i"



Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material e.g. Silicone upon request
- Other colors on request



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number grey	Number black	Number blue
PG 7	3–6,5	8	21	15	1.209.0700.14	1.209.0701.14	1.209.0702.14
PG 7	2–5	8	21	15	1.209.0700.15	1.209.0701.15	1.209.0702.15
PG 9	4–8	8	22	19	1.209.0900.14	1.209.0901.14	1.209.0902.14
PG 9	2–6	8	22	19	1.209.0900.15	1.209.0901.15	1.209.0902.15
PG 11	5–10	8	25	22	1.209.1100.14	1.209.1101.14	1.209.1102.14
PG 11	3–7	8	25	22	1.209.1100.15	1.209.1101.15	1.209.1102.15
PG 13,5	6–12	9	27	24	1.209.1300.14	1.209.1301.14	1.209.1302.14
PG 13,5	5–9	9	27	24	1.209.1300.15	1.209.1301.15	1.209.1302.15
PG 16	10–14	10	28	27	1.209.1600.14	1.209.1601.14	1.209.1602.14
PG 16	7–12	10	28	27	1.209.1600.15	1.209.1601.15	1.209.1602.15
PG 21	13–18	11	31	33	1.209.2100.14	1.209.2101.14	1.209.2102.14
PG 21	9–16	11	31	33	1.209.2100.15	1.209.2101.15	1.209.2102.15
PG 29	18–25	11	39	42	1.209.2900.14	1.209.2901.14	1.209.2902.14
PG 29	13–20	11	39	42	1.209.2900.15	1.209.2901.15	1.209.2902.15
PG 36	22–32	13	48	53	1.209.3600.14	1.209.3601.14	1.209.3602.14
PG 36	20–26	13	48	53	1.209.3600.15	1.209.3601.15	1.209.3602.15
PG 42	32–38	13	49	60	1.209.4200.14	1.209.4201.14	1.209.4202.14
PG 42	25–31	13	49	60	1.209.4200.15	1.209.4201.15	1.209.4202.15
PG 48	37–44	14	49	65	1.209.4800.14	1.209.4801.14	1.209.4802.14
PG 48	29–35	14	49	65	1.209.4800.15	1.209.4801.15	1.209.4802.15

Advice: see page 18 for further polyamide cable glands with special clamping ranges in PG threads

➔ Accessories see page 73

HSK-standard cable glands

HSK-K

PG-elongated

RoHS



Material Polyamide V0 according to UL 94

Seal Buna-N


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005),
blue (RAL 5012) for the intrinsic safety "i"

Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material e.g. Silicone upon request
- Other colors on request



AG	Øk mm	GL mm	H mm	Ø mm	Number grey	Number black	Number blue
PG 7	3 – 6,5	15	21	15	1.209.0700.60	1.209.0701.60	1.209.0702.60
PG 7	2 – 5	15	21	15	1.209.0700.61	1.209.0701.61	1.209.0702.61
PG 9	4 – 8	15	22	19	1.209.0900.60	1.209.0901.60	1.209.0902.60
PG 9	2 – 6	15	22	19	1.209.0900.61	1.209.0901.61	1.209.0902.61
PG 11	5 – 10	15	25	22	1.209.1100.60	1.209.1101.60	1.209.1102.60
PG 11	3 – 7	15	25	22	1.209.1100.61	1.209.1101.61	1.209.1102.61
PG 13,5	6 – 12	15	27	24	1.209.1300.60	1.209.1301.60	1.209.1302.60
PG 13,5	5 – 9	15	27	24	1.209.1300.61	1.209.1301.61	1.209.1302.61
PG 16	10 – 14	15	28	27	1.209.1600.60	1.209.1601.60	1.209.1602.60
PG 16	7 – 12	15	28	27	1.209.1600.61	1.209.1601.61	1.209.1602.61
PG 21	13 – 18	15	31	33	1.209.2100.60	1.209.2101.60	1.209.2102.60
PG 21	9 – 16	15	31	33	1.209.2100.61	1.209.2101.61	1.209.2102.61
PG 29	18 – 25	15	39	42	1.209.2900.60	1.209.2901.60	1.209.2902.60
PG 29	13 – 20	15	39	42	1.209.2900.61	1.209.2901.61	1.209.2902.61
PG 36	22 – 32	18	48	53	1.209.3600.60	1.209.3601.60	1.209.3602.60
PG 36	20 – 26	18	48	53	1.209.3600.61	1.209.3601.61	1.209.3602.61
PG 42	32 – 38	18	49	60	1.209.4200.60	1.209.4201.60	1.209.4202.60
PG 42	25 – 31	18	49	60	1.209.4200.61	1.209.4201.61	1.209.4202.61
PG 48	37 – 44	18	49	65	1.209.4800.60	1.209.4801.60	1.209.4802.60
PG 48	29 – 35	18	49	65	1.209.4800.61	1.209.4801.61	1.209.4802.61

➔ Accessories see page 73

HSK-standard cable glands

HSK-KE

PG



Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material and colors upon request


Material Polyamide V0 according to UL 94

Seal Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005)



AG	$\varnothing$ mm	d mm	GL mm	H mm	 mm	Number grey	Number black
PG 7	4 – 8	7	8	22	19	1.590.0700.14	1.590.0701.14
PG 7	2 – 6	7	8	22	19	1.590.0700.15	1.590.0701.15
PG 9	5 – 10	9	8	25	22	1.590.0900.14	1.590.0901.14
PG 9	3 – 7	9	8	25	22	1.590.0900.15	1.590.0901.15
PG 11	6 – 12	10,5	8	24	24	1.590.1100.14	1.590.1101.14
PG 11	5 – 9	10,5	8	24	24	1.590.1100.15	1.590.1101.15
PG 13,5	10 – 14	12,5	9	28	27	1.590.1300.14	1.590.1301.14
PG 13,5	7 – 12	12,5	9	28	27	1.590.1300.15	1.590.1301.15
PG 16	13 – 18	15	10	31	33	1.590.1600.14	1.590.1601.14
PG 16	9 – 16	15	10	31	33	1.590.1600.15	1.590.1601.15

➔ Accessories see page 71

HSK-KR

PG



Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material and colors upon request


Material Polyamide V0 according to UL 94

Seal Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005)



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number grey	Number black
PG 9	3 – 6,5	8	21	19	1.591.0900.14	1.591.0901.14
PG 9	2 – 5	8	21	19	1.591.0900.15	1.591.0901.15
PG 11	4 – 8	8	22	22	1.591.1100.14	1.591.1101.14
PG 11	2 – 6	8	22	22	1.591.1100.15	1.591.1101.15
PG 13,5	5 – 10	9	25	24	1.591.1300.14	1.591.1301.14
PG 13,5	3 – 7	9	25	24	1.591.1300.15	1.591.1301.15
PG 16	6 – 12	10	27	27	1.591.1600.14	1.591.1601.14
PG 16	5 – 9	10	27	27	1.591.1600.15	1.591.1601.15
PG 21	10 – 14	11	28	33	1.591.2100.14	1.591.2101.14
PG 21	7 – 12	11	28	33	1.591.2100.15	1.591.2101.15

➔ Accessories see page 73

HSK-standard cable glands

HSK-K

NPT

RoHS



Material Polyamide V0 according to UL 94

Seal Buna-N


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005),
blue (RAL 5012) for the intrinsic safety "i"

Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material e.g. Silicone upon request
- Other colors on request



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number grey	Number black	Number blue
NPT 3/8"	4 – 8	15	22	19/22	1.209.3800.70	1.209.3801.70	1.209.3802.70
NPT 3/8"	2 – 6	15	22	19/22	1.209.3800.71	1.209.3801.71	1.209.3802.71
NPT 1/2"	6 – 12	13	27	24	1.209.1200.70	1.209.1201.70	1.209.1202.70
NPT 1/2"	5 – 9	13	27	24	1.209.1200.71	1.209.1201.71	1.209.1202.71
NPT 1/2" (16)	10 – 14	13	28	27	1.209.1216.70	1.209.1217.70	1.209.1218.70
NPT 1/2" (16)	7 – 12	13	28	27	1.209.1216.71	1.209.1217.71	1.209.1218.71
NPT 3/4"	13 – 18	14	31	33	1.209.3400.70	1.209.3401.70	1.209.3402.70
NPT 3/4"	9 – 16	14	31	33	1.209.3400.71	1.209.3401.71	1.209.3402.71
NPT 1"	18 – 25	19	39	42	1.209.1000.70	1.209.1001.70	1.209.1002.70
NPT 1"	13 – 20	19	39	42	1.209.1000.71	1.209.1001.71	1.209.1002.71
NPT 1 1/4"	18 – 25	16	39	42/46	1.209.5400.70	1.209.5401.70	1.209.5402.70
NPT 1 1/4"	13 – 20	16	39	42/46	1.209.5400.71	1.209.5401.71	1.209.5402.71
NPT 1 1/2"	22 – 32	20	48	53	1.209.6400.70	1.209.6401.70	1.209.6402.70
NPT 1 1/2"	20 – 26	20	48	53	1.209.6400.71	1.209.6401.71	1.209.6402.71

➔ Accessories see page 73

HSK-standard cable glands

HSK-K-PVDF

Metr.



Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material and colors upon request


Material PVDF V0 according to UL 94

Seal FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -35 °C – 150 °C (-31 °F – 302 °F)

Colors nature



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number
M 12 x 1,5	3 – 6,5	8	21	15	1.299.1200.50
M 12 x 1,5	2 – 5	8	21	15	1.299.1200.51
M 16 x 1,5	4 – 8	8	22	19	1.299.1600.50
M 16 x 1,5	2 – 6	8	22	19	1.299.1600.51
M 20 x 1,5	6 – 12	9	27	24	1.299.2000.50
M 20 x 1,5	5 – 9	9	27	24	1.299.2000.51
M 25 x 1,5	13 – 18	11	31	33	1.299.2500.50
M 25 x 1,5	9 – 16	11	31	33	1.299.2500.51
M 32 x 1,5	18 – 25	11	39	42	1.299.3200.50
M 32 x 1,5	13 – 20	11	39	42	1.299.3200.51

➔ Accessories see page 73

HSK-K-PVDF

NPT



Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material and colors upon request


Material PVDF V0 according to UL 94

Seal FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -35 °C – 150 °C (-31 °F – 302 °F)

Colors nature



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number
NPT 3/8"	4 – 8	15	22	19 / 22	1.299.3800.70
NPT 3/8"	2 – 6	15	22	19 / 22	1.299.3800.71
NPT 1/2"	6 – 12	13	27	24	1.299.1200.70
NPT 1/2"	5 – 9	13	27	24	1.299.1200.71
NPT 1/2" (16)	10 – 14	13	28	27	1.299.1216.70
NPT 1/2" (16)	7 – 12	13	28	27	1.299.1216.71
NPT 3/4"	13 – 18	14	31	33	1.299.3400.70
NPT 3/4"	9 – 16	14	31	33	1.299.3400.71

➔ Accessories see page 73

HSK-standard cable glands

HSK-K-PVDF

PG

RoHS



Material PVDF V0 according to UL 94

Seal FPM


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -35 °C – 150 °C (-31 °F – 302 °F)

Colors nature

Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material e.g. Silicone upon request
- Other colors on request



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number
PG 7	3 – 6,5	8	21	15	1.299.0700.14
PG 7	2 – 5	8	21	15	1.299.0700.15
PG 9	4 – 8	8	22	19	1.299.0900.14
PG 9	2 – 6	8	22	19	1.299.0900.15
PG 11	5 – 10	8	25	22	1.299.1100.14
PG 11	3 – 7	8	25	22	1.299.1100.15
PG 13,5	6 – 12	9	27	24	1.299.1300.14
PG 13,5	5 – 9	9	27	24	1.299.1300.15
PG 16	10 – 14	10	28	27	1.299.1600.14
PG 16	7 – 12	10	28	27	1.299.1600.15
PG 21	13 – 18	11	31	33	1.299.2100.14
PG 21	9 – 16	11	31	33	1.299.2100.15
PG 29	18 – 25	11	39	42	1.299.2900.14
PG 29	13 – 20	11	39	42	1.299.2900.15
PG 36	22 – 32	13	48	53	1.299.3600.14
PG 36	20 – 26	13	48	53	1.299.3600.15
PG 42	32 – 38	13	49	60	1.299.4200.14
PG 42	25 – 31	13	49	60	1.299.4200.15
PG 48	37 – 44	14	49	65	1.299.4800.14
PG 48	29 – 35	14	49	65	1.299.4800.15

Accessories see page 73

HSK-standard cable glands

HSK-M / HSK-M-PVDF

Metr.



Material Nickel plated brass

Clamping insert Polyamide / PVDF

Seal Buna-N / FPM


O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F) (PA)
-35 °C – 150 °C (-31 °F – 302 °F) (PVDF)

Advice:

- Other sealing material e.g. Silicone upon request
- Please see page 51 for size < M12 and > M63



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number HSK-M -40 °C – 100 °C -40 °F – 212 °F	Number HSK-M-PVDF -35 °C – 150 °C -31 °F – 302 °F
M 12 x 1,5	3 – 6,5	6,5	19	14	1.609.1200.50	1.699.1200.50
M 12 x 1,5	2 – 5	6,5	19	14	1.609.1200.51	1.699.1200.51
M 16 x 1,5	4 – 8	6	21	17 / 19	1.609.1600.50	1.699.1600.50
M 16 x 1,5	2 – 6	6	21	17 / 19	1.609.1600.51	1.699.1600.51
M 16 x 1,5	5 – 10	6	22	20	1.609.1611.50	1.699.1611.50
M 20 x 1,5	6 – 12	6	23	22	1.609.2000.50	1.699.2000.50
M 20 x 1,5	5 – 9	6	23	22	1.609.2000.51	1.699.2000.51
M 20 x 1,5	10 – 14	6	24	24	1.609.2016.50	1.699.2016.50
M 25 x 1,5	13 – 18	7	26	30	1.609.2500.50	1.699.2500.50
M 25 x 1,5	9 – 16	7	26	30	1.609.2500.51	1.699.2500.51
M 32 x 1,5	18 – 25	8	31	40	1.609.3200.50	1.699.3200.50
M 32 x 1,5	13 – 20	8	31	40	1.609.3200.51	1.699.3200.51
M 32 x 1,5	15 – 21	8	33	36	1.609.3200.52	
M 40 x 1,5	22 – 32	8	37	50	1.609.4000.50	1.699.4000.50
M 40 x 1,5	20 – 26	8	37	50	1.609.4000.51	1.699.4000.51
M 40 x 1,5	19 – 27	8	33	46	1.609.4000.52	
M 50 x 1,5	32 – 38	9	37	57	1.609.5000.50	
M 50 x 1,5	25 – 31	9	37	57	1.609.5000.51	
M 63 x 1,5	37 – 44	10	38	64 / 68	1.609.6300.50	
M 63 x 1,5	29 – 35	10	38	64 / 68	1.609.6300.51	

➔ Accessories see page 73

HSK-standard cable glands

HSK-M / HSK-M-PVDF

Metr.-elongated



Material Nickel plated brass

Clamping insert Polyamide / PVDF

Seal Buna-N / FPM


O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F) (PA)
-35 °C – 150 °C (-31 °F – 302 °F) (PVDF)

Advice:

- Other sealing material e.g. Silicone upon request
- Please see page 51 for size < M12 and > M63



AG mm	Ø mm	GL mm	H mm	Ø mm	Number HSK-M -40 °C – 100 °C -40 °F – 212 °F	Number HSK-M-PVDF -35 °C – 150 °C -31 °F – 302 °F
M 12 x 1,5	3 – 6,5	10	19	14	1.609.1200.30	1.699.1200.30
M 12 x 1,5	2 – 5	10	19	14	1.609.1200.31	1.699.1200.31
M 16 x 1,5	4 – 8	10	21	17 / 19	1.609.1600.30	1.699.1600.30
M 16 x 1,5	2 – 6	10	21	17 / 19	1.609.1600.31	1.699.1600.31
M 16 x 1,5	5 – 10	10	22	20	1.609.1611.30	1.699.1611.30
M 20 x 1,5	6 – 12	10	23	22	1.609.2000.30	1.699.2000.30
M 20 x 1,5	5 – 9	10	23	22	1.609.2000.31	1.699.2000.31
M 20 x 1,5	10 – 14	10	24	24	1.609.2016.30	1.699.2016.30
M 25 x 1,5	13 – 18	12	26	30	1.609.2500.30	1.699.2500.30
M 25 x 1,5	9 – 16	12	26	30	1.609.2500.31	1.699.2500.31
M 32 x 1,5	18 – 25	12	31	40	1.609.3200.30	1.699.3200.30
M 32 x 1,5	13 – 20	12	31	40	1.609.3200.31	1.699.3200.31
M 32 x 1,5	15 – 21	12	37	36	1.609.3200.32	
M 40 x 1,5	22 – 32	15	37	50	1.609.4000.30	1.699.4000.30
M 40 x 1,5	20 – 26	15	37	50	1.609.4000.31	1.699.4000.31
M 40 x 1,5	19 – 27	15	37	46	1.609.4000.32	
M 50 x 1,5	32 – 38	15	37	57	1.609.5000.30	
M 50 x 1,5	25 – 31	15	37	57	1.609.5000.31	
M 63 x 1,5	37 – 44	15	38	64 / 68	1.609.6300.30	
M 63 x 1,5	29 – 35	15	38	64 / 68	1.609.6300.31	

➔ Accessories see page 73

HSK-standard cable glands

HSK-M / HSK-M-PVDF

PG



Material Nickel plated brass



RoHS

Clamping insert Polyamide / PVDF



Seal Buna-N / FPM


O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F) (PA)
-35 °C – 150 °C (-31 °F – 302 °F) (PVDF)

Advice:

- Other sealing material e.g. Silicone upon request



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number HSK-M -40 °C – 100 °C -40 °F – 212 °F	Number HSK-M-PVDF -35 °C – 150 °C -31 °F – 302 °F
PG 7	3 – 6,5	5	19	14	1.609.0700.01	1.699.0700.01
PG 7	2 – 5	5	19	14	1.609.0700.15	1.699.0700.15
PG 9	4 – 8	6	21	17	1.609.0900.01	1.699.0900.01
PG 9	2 – 6	6	21	17	1.609.0900.15	1.699.0900.15
PG 11	5 – 10	6	22	20	1.609.1100.01	1.699.1100.01
PG 11	3 – 7	6	22	20	1.609.1100.15	1.699.1100.15
PG 13,5	6 – 12	6,5	24	22	1.609.1300.01	1.699.1300.01
PG 13,5	5 – 9	6,5	24	22	1.609.1300.15	1.699.1300.15
PG 16	10 – 14	6,5	23	24	1.609.1600.01	1.699.1600.01
PG 16	7 – 12	6,5	23	24	1.609.1600.15	1.699.1600.15
PG 21	13 – 18	7	24	30	1.609.2100.01	1.699.2100.01
PG 21	9 – 16	7	24	30	1.609.2100.15	1.699.2100.15
PG 29	18 – 25	8	29	40	1.609.2900.01	1.699.2900.01
PG 29	13 – 20	8	29	40	1.609.2900.15	1.699.2900.15
PG 36	22 – 32	8	35	50	1.609.3600.01	1.699.3600.01
PG 36	20 – 26	8	35	50	1.609.3600.15	1.699.3600.15
PG 42	32 – 38	9	37	57	1.609.4200.01	1.699.4200.01
PG 42	25 – 31	9	37	57	1.609.4200.15	1.699.4200.15
PG 48	37 – 44	10	38	64	1.609.4800.01	1.699.4800.01
PG 48	29 – 35	10	38	64	1.609.4800.15	1.699.4800.15



Accessories see page 73

HSK-standard cable glands

HSK-M / HSK-M-PVDF

PG-elongated

RoHS



Material Nickel plated brass

Clamping insert Polyamide / PVDF

Seal Buna-N / FPM


O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F) (PA)
-35 °C – 150 °C (-31 °F – 302 °F) (PVDF)

Advice:

- Other sealing material e.g. Silicone upon request



AG	mm	GL mm	H mm	mm	Number HSK-M -40 °C – 100 °C -40 °F – 212 °F	Number HSK-M-PVDF -35 °C – 150 °C -31 °F – 302 °F
PG 7	3 – 6,5	10	19	14	1.609.0700.60	1.699.0700.60
PG 7	2 – 5	10	19	14	1.609.0700.61	1.699.0700.61
PG 9	4 – 8	10	21	17	1.609.0900.60	1.699.0900.60
PG 9	2 – 6	10	21	17	1.609.0900.61	1.699.0900.61
PG 11	5 – 10	10	22	20	1.609.1100.60	1.699.1100.60
PG 11	3 – 7	10	22	20	1.609.1100.61	1.699.1100.61
PG 13,5	6 – 12	10	24	22	1.609.1300.60	1.699.1300.60
PG 13,5	5 – 9	10	24	22	1.609.1300.61	1.699.1300.61
PG 16	10 – 14	10	23	24	1.609.1600.60	1.699.1600.60
PG 16	7 – 12	10	23	24	1.609.1600.61	1.699.1600.61
PG 21	13 – 18	12	24	30	1.609.2100.60	1.699.2100.60
PG 21	9 – 16	12	24	30	1.609.2100.61	1.699.2100.61
PG 29	18 – 25	12	29	40	1.609.2900.60	1.699.2900.60
PG 29	13 – 20	12	29	40	1.609.2900.61	1.699.2900.61
PG 36	22 – 32	15	35	50	1.609.3600.60	1.699.3600.60
PG 36	20 – 26	15	35	50	1.609.3600.61	1.699.3600.61
PG 42	32 – 38	15	37	57	1.609.4200.60	1.699.4200.60
PG 42	25 – 31	15	37	57	1.609.4200.61	1.699.4200.61
PG 48	37 – 44	15	38	64	1.609.4800.60	1.699.4800.60
PG 48	29 – 35	15	38	64	1.609.4800.61	1.699.4800.61

➔ Accessories see page 73

HSK-standard cable glands

HSK-M / HSK-M-PVDF

NPT



Material Nickel plated brass

Clamping insert Polyamide / PVDF

Seal Buna-N / FPM


O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F) (PA)
-35 °C – 150 °C (-31 °F – 302 °F) (PVDF)

Advice:

- Other sealing material e.g. Silicone upon request



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number HSK-M -40 °C – 100 °C -40 °F – 212 °F	Number HSK-M-PVDF -35 °C – 150 °C -31 °F – 302 °F
NPT 3/8"	4 – 8	15	21	17 / 19	1.609.3800.70	1.699.3800.70
NPT 3/8"	2 – 6	15	21	17 / 19	1.609.3800.71	1.699.3800.71
NPT 1/2"	6 – 12	13	24	22 / 24	1.609.1200.70	1.699.1200.70
NPT 1/2"	5 – 9	13	24	22 / 24	1.609.1200.71	1.699.1200.71
NPT 3/4"	13 – 18	13	25	30	1.609.3400.70	1.699.3400.70
NPT 3/4"	9 – 16	13	25	30	1.609.3400.71	1.699.3400.71
NPT 1"	18 – 25	19	29	40	1.609.1000.70	
NPT 1"	13 – 20	19	29	40	1.609.1000.71	

➔ Accessories see page 73

HSK-standard cable glands

HSK-INOX / HSK-INOX-PVDF

Metr.



Material INOX 1.4305 / 1.4404

Clamping insert Polyamide / PVDF

Seal Buna-N / FPM


O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F) (PA)
-35 °C – 150 °C (-31 °F – 302 °F) (PVDF)

Advice:

- Other sealing material e.g. Silicone upon request
- Other sizes upon request



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-INOX 1.4305 -40 °C – 100 °C	Number HSK-INOX-PVDF 1.4305 -35 °C – 150 °C	Number HSK-INOX 1.4404 -40 °C – 100 °C	Number HSK-INOX-PVDF 1.4404 -35 °C – 150 °C
M 12 x 1,5	3 – 6,5	6,5	19	14	1.695.1200.50	1.696.1200.50	1.675.1200.50	1.676.1200.50
M 12 x 1,5	2 – 5	6,5	19	14	1.695.1200.51	1.696.1200.51	1.675.1200.51	1.676.1200.51
M 16 x 1,5	5 – 10	6	22	22	1.695.1600.50	1.696.1600.50	1.675.1600.50	1.676.1600.50
M 16 x 1,5	3 – 7	6	22	22	1.695.1600.51	1.696.1600.51	1.675.1600.51	1.676.1600.51
M 20 x 1,5	10 – 14	6	23	24	1.695.2000.50	1.696.2000.50	1.675.2000.50	1.676.2000.50
M 20 x 1,5	7 – 12	6	23	24	1.695.2000.51	1.696.2000.51	1.675.2000.51	1.676.2000.51
M 25 x 1,5	13 – 18	7	24	30	1.695.2500.50	1.696.2500.50	1.675.2500.50	1.676.2500.50
M 25 x 1,5	9 – 16	7	24	30	1.695.2500.51	1.696.2500.51	1.675.2500.51	1.676.2500.51
M 32 x 1,5	18 – 25	8	31	41	1.695.3200.50	1.696.3200.50	1.675.3200.50	1.676.3200.50
M 32 x 1,5	13 – 20	8	31	41	1.695.3200.51	1.696.3200.51	1.675.3200.51	1.676.3200.51
M 40 x 1,5	22 – 32	8	37	50	1.695.4000.50	1.696.4000.50	1.675.4000.50	1.676.4000.50
M 40 x 1,5	20 – 26	8	37	50	1.695.4000.51	1.696.4000.51	1.675.4000.51	1.676.4000.51
M 50 x 1,5	32 – 38	9	37	60	1.695.5000.50		1.675.5000.50	
M 50 x 1,5	25 – 31	9	37	60	1.695.5000.51		1.675.5000.51	
M 63 x 1,5	37 – 44	10	38	64/68	1.695.6300.50		1.675.6300.50	
M 63 x 1,5	29 – 35	10	38	64/68	1.695.6300.51		1.675.6300.51	

➔ Accessories see page 73

HSK-standard cable glands

HSK-INOX / HSK-INOX-PVDF

PG, NPT



Material INOX 1.4305 / 1.4404

Clamping insert Polyamide / PVDF

Seal Buna-N / FPM


O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F) (PA)
-35 °C – 150 °C (-31 °F – 302 °F) (PVDF)

Advice:

- Other sealing material e.g. Silicone upon request



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-INOX 1.4305 -40 °C – 100 °C	Number HSK-INOX-PVDF 1.4305 -35 °C – 150 °C	Number HSK-INOX 1.4404 -40 °C – 100 °C	Number HSK-INOX-PVDF 1.4404 -35 °C – 150 °C
PG 7	3 – 6,5	5	19	14	1.695.0700.01	1.696.0700.01	1.675.0700.01	1.676.0700.01
PG 7	2 – 5	5	19	14	1.695.0700.15	1.696.0700.15	1.675.0700.15	1.676.0700.15
PG 9	4 – 8	6	21	17	1.695.0900.01	1.696.0900.01	1.675.0900.01	1.676.0900.01
PG 9	2 – 6	6	21	17	1.695.0900.15	1.696.0900.15	1.675.0900.15	1.676.0900.15
PG 11	5 – 10	6	22	22	1.695.1100.01	1.696.1100.01	1.675.1100.01	1.676.1100.01
PG 11	3 – 7	6	22	22	1.695.1100.15	1.696.1100.15	1.675.1100.15	1.676.1100.15
PG 13,5	6 – 12	6,5	24	22	1.695.1300.01	1.696.1300.01	1.675.1300.01	1.676.1300.01
PG 13,5	5 – 9	6,5	24	22	1.695.1300.15	1.696.1300.15	1.675.1300.15	1.676.1300.15
PG 16	10 – 14	6,5	23	24	1.695.1600.01	1.696.1600.01	1.675.1600.01	1.676.1600.01
PG 16	7 – 12	6,5	23	24	1.695.1600.15	1.696.1600.15	1.675.1600.15	1.676.1600.15
PG 21	13 – 18	7	24	30	1.695.2100.01	1.696.2100.01	1.675.2100.01	1.676.2100.01
PG 21	9 – 16	7	24	30	1.695.2100.15	1.696.2100.15	1.675.2100.15	1.676.2100.15
PG 29	18 – 25	8	29	41	1.695.2900.01	1.696.2900.01	1.675.2900.01	1.676.2900.01
PG 29	13 – 20	8	29	41	1.695.2900.15	1.696.2900.15	1.675.2900.15	1.676.2900.15
PG 36	22 – 32	8	35	50	1.695.3600.01	1.696.3600.01	1.675.3600.01	1.676.3600.01
PG 36	20 – 26	8	35	50	1.695.3600.15	1.696.3600.15	1.675.3600.15	1.676.3600.15
PG 42	32 – 38	9	37	57	1.695.4200.01	1.696.4200.01	1.675.4200.01	1.676.4200.01
PG 42	25 – 31	9	37	57	1.695.4200.15	1.696.4200.15	1.675.4200.15	1.676.4200.15
PG 48	37 – 44	10	38	64	1.695.4800.01	1.696.4800.01	1.675.4800.01	1.676.4800.01
PG 48	29 – 35	10	38	64	1.695.4800.15	1.696.4800.15	1.675.4800.15	1.676.4800.15
NPT 3/8"	4 – 8	15	21	17 / 19	1.695.3800.70		1.675.3800.70	
NPT 3/8"	2 – 6	15	21	17 / 19	1.695.3800.71		1.675.3800.71	
NPT 1/2"	6 – 12	13	24	22 / 24	1.695.1200.70		1.675.1200.70	
NPT 1/2"	5 – 9	13	24	22 / 24	1.695.1200.71		1.675.1200.71	
NPT 3/4"	13 – 18	13	25	30	1.695.3400.70		1.675.3400.70	
NPT 3/4"	9 – 16	13	25	30	1.695.3400.71		1.675.3400.71	
NPT 1"	18 – 25	19	29	41	1.695.1000.70		1.675.1000.70	
NPT 1"	13 – 20	19	29	41	1.695.1000.71		1.675.1000.71	

➔ Accessories see page 73

Industrial cable glands

HSK-EMC cable glands

Cable glands of the HSK-series fulfil the highest demands of quality and security. Outstanding high-grade materials are used together with innovative technology to offer premium products.



You can find in this chapter:

HSK EMC cable glands

- EMC-D version with Best EMI attenuation and easy installation
- EMC standard version
- with additional bending protection
- with additional strain relief

We provide variable clamping ranges, thread lengths, thread types plus different sealing materials and temperature ranges. Our range is completed by global certifications.

For any further question please do not hesitate to contact us. We look forward to develop solutions together with you. You profit from our vast knowledge in development, engineering and production technology.

Contact us:

E-Mail: info.et@hummel.com

Tel.: +49 (0) 76 66/9 11 10-0

Advice:

- ➔ Do you need EMC boxes or EMC connectors? You can find suitable solutions in our catalogs „Enclosure Solutions“ and „Circular Connectors“

HSK-M-EMV-D

Metr., Metr.-elongated



Material Nickel plated brass

Clamping insert Metalised polyamide

Seal Buna-N


O-Ring Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range


Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Advice:

- Other sealing material e.g. Silicone upon request



AG	Øk mm	GL mm	H mm	Ø mm	Number	GL mm	Number long
M 12 x 1,5	3 – 6,5	6,5	25	14	1.631.1200.50	10	1.631.1200.30
M 16 x 1,5	4 – 8	6	29	17 / 19	1.631.1609.50	10	1.631.1609.30
M 16 x 1,5	5 – 10	6	32	20	1.631.1600.50	10	1.631.1600.30
M 20 x 1,5	6 – 12	6	32,5	22	1.631.2013.50	10	1.631.2013.30
M 20 x 1,5	10 – 14	6	33	24	1.631.2000.50	10	1.631.2000.30
M 25 x 1,5	13 – 18	7	39	30	1.631.2500.50	12	1.631.2500.30
M 32 x 1,5	18 – 25	8	45	40	1.631.3200.50	12	1.631.3200.30
M 40 x 1,5	24 – 32	8	51	50	1.631.4000.50	15	1.631.4000.30
M 50 x 1,5	32 – 38	9	57,5	57	1.631.5000.50	15	1.631.5000.30
M 63 x 1,5	37 – 44	10	52	64 / 68	1.631.6300.50	15	1.631.6300.30



Accessories see page 73

HSK-EMC cable glands

HSK-M-EMV-D
PG

Material	Nickel plated brass
Clamping insert	Metalised polyamide
Seal	Buna-N
O-Ring	Buna-N
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F)

Advice:
- Other sealing material e.g. Silicone upon request
- Elongated threads on request

AG	Ø mm	GL mm	H mm	W mm	Number
PG 7	3 – 6,5	5	24	14	1.631.0700.01
PG 9	4 – 8	6	28	17	1.631.0900.01
PG 11	5 – 10	6	29	20	1.631.1100.01
PG 13,5	6 – 12	6,5	31	22	1.631.1300.01
PG 16	10 – 14	6,5	32	24	1.631.1600.01
PG 21	13 – 18	7	38	30	1.631.2100.01
PG 29	18 – 25	8	43	40	1.631.2900.01
PG 36	24 – 32	8	48	50	1.631.3600.01
PG 42	32 – 38	9	45	57	1.631.4200.01
PG 48	37 – 44	10	46	64	1.631.4800.01

➔ Accessories see page 73

HSK-M-EMV-D
NPT

Material	Nickel plated brass
Clamping insert	Metalised polyamide
Seal	Buna-N
O-Ring	Buna-N
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F)

Advice:
- Other sealing material e.g. Silicone upon request

AG	Ø mm	GL mm	H mm	W mm	Number
NPT 3/8"	4 – 8	15	29	17 / 19	1.631.3800.70
NPT 1/2"	6 – 12	13	32,5	22 / 24	1.631.1200.70
NPT 3/4"	13 – 18	13	39	30	1.631.3400.70

➔ Accessories see page 73

HSK-M-EMV

Metr., Metr.-elongated



Material Nickel plated brass

Clamping insert Polyamide

Seal Buna-N

O-Ring Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range


Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Advice:

- Other sealing material e.g. Silicone upon request
- Stainless steel on request



See our homepage www.hummel.com
for assembling advices for maximum
cable diameters



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number	GL mm	Number elongated
M 12 x 1,5	3 – 6,5	6,5	19	14	1.691.1200.50	10	1.691.1200.30
M 12 x 1,5	2 – 5	6,5	19	14	1.691.1200.51	10	1.691.1200.31
M 16 x 1,5	5 – 10	6	22	20	1.691.1600.50	10	1.691.1600.30
M 16 x 1,5	3 – 7	6	22	20	1.691.1600.51	10	1.691.1600.31
M 20 x 1,5	10 – 14	6	24	24	1.691.2000.50	10	1.691.2000.30
M 20 x 1,5	7 – 12	6	24	24	1.691.2000.51	10	1.691.2000.31
M 25 x 1,5	13 – 18	7	26	30	1.691.2500.50	12	1.691.2500.30
M 25 x 1,5	9 – 16	7	26	30	1.691.2500.51	12	1.691.2500.31
M 32 x 1,5	18 – 25	8	31	40	1.691.3200.50	12	1.691.3200.30
M 32 x 1,5	13 – 20	8	31	40	1.691.3200.51	12	1.691.3200.31
M 32 x 1,5	15 – 21	8	33	36	1.691.3200.52	12	1.691.3200.32
M 40 x 1,5	22 – 32	8	37	50	1.691.4000.50	15	1.691.4000.30
M 40 x 1,5	20 – 26	8	37	50	1.691.4000.51	15	1.691.4000.31
M 40 x 1,5	19 – 27	8	33	46	1.691.4000.52	15	1.691.4000.32
M 50 x 1,5	32 – 38	9	37	57	1.691.5000.50	15	1.691.5000.30
M 50 x 1,5	25 – 31	9	37	57	1.691.5000.51	15	1.691.5000.31
M 63 x 1,5	37 – 44	10	38	64 / 68	1.691.6300.50	15	1.691.6300.30
M 63 x 1,5	29 – 35	10	38	64 / 68	1.691.6300.51	15	1.691.6300.31



Accessories see page 73

HSK-EMC cable glands

HSK-M-EMV

PG, PG-elongated, NPT

RoHS



Material Nickel plated brass

Clamping insert Polyamide

Seal Buna-N


O-Ring Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Advice:

- Also available in PVDF
- Other sealing material e.g. Silicone upon request
- Stainless steel on request



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number	GL mm	Number elongated
PG 7	3 – 6,5	5	19	14	1.691.0700.01	10	1.691.0700.60
PG 7	2 – 5	5	19	14	1.691.0700.15	10	1.691.0700.61
PG 9	4 – 8	6	21	17	1.691.0900.01	10	1.691.0900.60
PG 9	2 – 6	6	21	17	1.691.0900.15	10	1.691.0900.61
PG 11	5 – 10	6	22	20	1.691.1100.01	10	1.691.1100.60
PG 11	3 – 7	6	22	20	1.691.1100.15	10	1.691.1100.61
PG 13,5	6 – 12	6,5	24	22	1.691.1300.01	10	1.691.1300.60
PG 13,5	5 – 9	6,5	24	22	1.691.1300.15	10	1.691.1300.61
PG 16	10 – 14	6,5	23	24	1.691.1600.01	10	1.691.1600.60
PG 16	7 – 12	6,5	23	24	1.691.1600.15	10	1.691.1600.61
PG 21	13 – 18	7	24	30	1.691.2100.01	12	1.691.2100.60
PG 21	9 – 16	7	24	30	1.691.2100.15	12	1.691.2100.61
PG 29	18 – 25	8	29	40	1.691.2900.01	12	1.691.2900.60
PG 29	13 – 20	8	29	40	1.691.2900.15	12	1.691.2900.61
PG 36	22 – 32	8	35	50	1.691.3600.01	15	1.691.3600.60
PG 36	20 – 26	8	35	50	1.691.3600.15	15	1.691.3600.61
PG 42	32 – 38	9	37	57	1.691.4200.01	15	1.691.4200.60
PG 42	25 – 31	9	37	57	1.691.4200.15	15	1.691.4200.61
PG 48	37 – 44	10	38	64	1.691.4800.01	15	1.691.4800.60
PG 48	29 – 35	10	38	64	1.691.4800.15	15	1.691.4800.61
NPT 3/8"	4 – 8	15	21	17 / 19	1.691.3800.70		
NPT 3/8"	2 – 6	15	21	17 / 19	1.691.3800.71		
NPT 1/2"	6 – 12	13	24	22 / 24	1.691.1200.70		
NPT 1/2"	5 – 9	13	24	22 / 24	1.691.1200.71		
NPT 3/4"	13 – 18	13	25	30	1.691.3400.70		
NPT 3/4"	9 – 16	13	25	30	1.691.3400.71		

➔ Accessories see page 73

HSK-M-Flex-EMV

Metr., Metr.-elongated




Material	Nickel plated brass
Steel spring	INOX 1.4310
Clamping insert	Polyamide
Seal	Buna-N
O-Ring	Buna-N
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F)



Advice:
- Other sealing material e.g. Silicone upon request

See our homepage www.hummel.com
for assembling advices for maximum
cable diameters



AG	$\varnothing$ mm	GL mm	H mm	d mm	$\varnothing$ mm	Number	GL mm	Number elongated
M 12 x 1,5	3 – 6,5	6,5	55	6,8	14	1.624.1200.50	10	1.624.1200.30
M 12 x 1,5	2 – 5	6,5	55	6,8	14	1.624.1200.51	10	1.624.1200.31
M 16 x 1,5	5 – 10	6	77	10,3	20	1.624.1600.50	10	1.624.1600.30
M 16 x 1,5	3 – 7	6	77	10,3	20	1.624.1600.51	10	1.624.1600.31
M 20 x 1,5	10 – 14	6	98	14,3	24	1.624.2000.50	10	1.624.2000.30
M 20 x 1,5	7 – 12	6	98	14,3	24	1.624.2000.51	10	1.624.2000.31
M 25 x 1,5	13 – 18	7	111	18,4	30	1.624.2500.50	12	1.624.2500.30
M 25 x 1,5	9 – 16	7	111	18,4	30	1.624.2500.51	12	1.624.2500.31



HSK-M-Flex-EMV

PG, PG-elongated, NPT

RoHS



Material Nickel plated brass

Steel spring INOX 1.4310

Clamping insert Polyamide

Seal Buna-N



O-Ring Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Advice:

- Also available in PVDF
- Other sealing material e.g. Silicone upon request



AG	$\varnothing$ mm	GL mm	H mm	d mm	 mm	Number	GL mm	Number elongated
PG 7	3 – 6,5	5	55	6,8	14	1.624.0700.01	10	1.624.0700.60
PG 7	2 – 5	5	55	6,8	14	1.624.0700.15	10	1.624.0700.61
PG 9	4 – 8	6	66	8,2	17	1.624.0900.01	10	1.624.0900.60
PG 9	2 – 6	6	66	8,2	17	1.624.0900.15	10	1.624.0900.61
PG 11	5 – 10	6	77	10,3	20	1.624.1100.01	10	1.624.1100.60
PG 11	3 – 7	6	77	10,3	20	1.624.1100.15	10	1.624.1100.61
PG 13,5	6 – 12	6,5	88	12,3	22	1.624.1300.01	10	1.624.1300.60
PG 13,5	5 – 9	6,5	88	12,3	22	1.624.1300.15	10	1.624.1300.61
PG 16	10 – 14	6,5	98	14,3	24	1.624.1600.01	10	1.624.1600.60
PG 16	7 – 12	6,5	98	14,3	24	1.624.1600.15	10	1.624.1600.61
PG 21	13 – 18	7	111	18,4	30	1.624.2100.01	12	1.624.2100.60
PG 21	9 – 16	7	111	18,4	30	1.624.2100.15	12	1.624.2100.61
NPT 3/8"	4 – 8	15	66	8,2	17 / 19	1.624.3800.70		
NPT 3/8" NPT	2 – 6	15	66	8,2	17 / 19	1.624.3800.71		
NPT 1/2" NPT	6 – 12	13	88	12,3	22 / 24	1.624.1200.70		
NPT 1/2" NPT	5 – 9	13	88	12,3	22 / 24	1.624.1200.71		
NPT 3/4" NPT	13 – 18	13	111	18,4	30	1.624.3400.70		
NPT 3/4" NPT	9 – 16	13	111	18,4	30	1.624.3400.71		

➔ Accessories see page 73

HSK-MZ-EMV

Metr., Metr.-elongated, PG, PG-elongated, NPT




Material	Nickel plated brass
Clamping insert	Polyamide
Seal	Buna-N
O-Ring	Buna-N
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F)



Advice:
- Also available in PVDF*
- Other sealing material e.g. Silicone upon request

See our homepage www.hummel.com
for assembling advices for maximum
cable diameters



AG	mm	GL	H	mm	Number	GL	Number elongated
M 12 x 1,5	3 – 6,5	6,5	26	14	1.692.1200.50	10	1.692.1200.30
M 16 x 1,5	6 – 10	6	29	20	1.692.1600.50	10	1.692.1600.30
M 20 x 1,5	10 – 14	6	32	24	1.692.2000.50	10	1.692.2000.30
M 25 x 1,5	13 – 18	7	35	30	1.692.2500.50	12	1.692.2500.30
M 32 x 1,5	18 – 25	8	41	40	1.692.3200.50	12	1.692.3200.30
M 40 x 1,5	22 – 32	8	48	50	1.692.4000.50	15	1.692.4000.30
M 50 x 1,5	32 – 38	9	51	57	1.692.5000.50	15	1.692.5000.30
M 50 x 1,5	25 – 31	9	51	57	1.692.5000.51	15	1.692.5000.31
M 63 x 1,5	37 – 44	10	52	64 / 68	1.692.6300.50	15	1.692.6300.30
M 63 x 1,5	29 – 35	10	52	64 / 68	1.692.6300.51	15	1.692.6300.31
PG 7*	3 – 6,5	5	26	14	1.692.0700.01	10	1.692.0700.60
PG 9*	4 – 8	6	28	17	1.692.0900.01	10	1.692.0900.60
PG 11*	6 – 10	6	29	20	1.692.1100.01	10	1.692.1100.60
PG 13,5*	6 – 12	6,5	33	22	1.692.1300.01	10	1.692.1300.60
PG 16*	10 – 14	6,5	32	24	1.692.1600.01	10	1.692.1600.60
PG 21*	13 – 18	7	35	30	1.692.2100.01	12	1.692.2100.60
PG 29*	18 – 25	8	41	40	1.692.2900.01	12	1.692.2900.60
PG 36*	22 – 32	8	48	50	1.692.3600.01	15	1.692.3600.60
PG 42*	32 – 38	9	51	57	1.692.4200.01	15	1.692.4200.60
PG 42*	25 – 31	9	51	57	1.692.4200.15	15	1.692.4200.61
PG 48*	37 – 44	10	51	64	1.692.4800.01	15	1.692.4800.60
PG 48*	29 – 35	10	51	64	1.692.4800.15	15	1.692.4800.61
NPT 3/8"	4 – 8	15	28	17 / 19	1.692.3800.70		
NPT 1/2"	6 – 12	13	29	22 / 24	1.692.1200.70		
NPT 3/4"	13 – 18	13	35	30	1.692.3400.70		



➔ Accessories see page 73

Industrial cable glands

HSK cable glands for special applications

Cable glands of the HSK-series fulfil highest demands of quality and security. Outstanding high-grade materials are used together with innovative technology to offer premium products.

NEW



You can find in this chapter:

HSK cable glands

- for hygienic areas like food production, pharmaceutical and chemical industries, biotechnology and clean room
- made of polyamide and nickel plated brass with multi hole and flat cable sealing inserts
- made of polyamide and nickel plated brass with bending protection
- snap elbows made of polyamide and nickel plated brass
- Minis in the sizes M6 to M10 and PG7
- XL in the sizes M63 with extended clamping range to M110 and XL cable glands with pipe threads from G2 1/2" to G4"
- with additional strain relief


We provide variable clamping ranges, thread lengths, thread types plus different sealing materials and temperature ranges. Our range is completed by global certifications.

For any further question please do not hesitate to contact us. We look forward to develop solutions together with you. You profit from our vast knowledge in development, engineering and production technology.

Contact us:

E-Mail: info.et@hummel.com

Tel.: +49 (0) 76 66/9 11 10-0



HSK-INOX Hygienic-Design

www.hummel.com

The HSK-INOX Hygienic Design has been developed for all areas which require the avoidance of possible bacteria and micro-organism deposits, for example in food, pharmaceutical and chemical industries, biotechnology and clean room areas.

Characteristics

- Available sizes: M 12 to M 25
- Operating Temperature:
-40 °C – 120 °C (-40 °F – 248 °F)
- Protection: IP 66, IP 68, IP 69K
- Available as EMC version

Certifications

- Approved by EHEDG regulation
(European Hygienic Engineering
& Design Group)
- FDA conforming materials

Materials HD-shell

- Made of stainless steel grade 1.4404/
AISI 316 L, surface roughness < 0,8 µm
- Silicone seals made of VMQ

Advantages

- Easy and efficient to clean
- Fast and simple installation
- High chemical and thermal resistance

NEW

HSK cable glands for special applications

HSK-INOX-HD

Metr.

Material HD-shell 1.4404 / AISI 316 L


Seal HD-shell VMQ (Silicone), blue (RAL 5017)

Protection IP 66, IP 68, IP 69K

Operating Temperature -40 °C – 120 °C (-40 °F – 248 °F)

Advice:

- Elongated threads on request
- Other sizes upon request



AG	$\varnothing$ mm	GL mm	H mm	D mm	 mm	Number
M 12 x 1,5	3 – 6,5	6	30	21	14	1.740.1200.50
M 16 x 1,5	5 – 10	6	34	27	20	1.740.1600.50
M 20 x 1,5	10 – 14	6	34,5	33	24	1.740.2000.50
M 25 x 1,5	13 – 18	6	41,5	40	30	1.740.2500.50

HSK cable glands for special applications

HSK-K-Multi

Metr., PG, NPT



Material Polyamide V0 according to UL 94

Seal Elastomer

Protection IP 65
IP 68 possible with ideal fit, only with optional O-Ring


Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005)



Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material e.g. Silicone upon request
- Elongated threads on request
- Installation instruction see page 176



AG	GL mm	H mm	mm	Number of Holes x d	Number grey	Number black	Number of Holes x d	Number grey	Number black
M 16 x 1,5	8	22	19	4 x 1,4	1.597.1600.50	1.597.1600.51	2 x 3	1.597.1601.50	1.597.1601.51
M 20 x 1,5	9	27	24	6 x 3	1.597.2001.50	1.597.2001.51	2 x 5	1.597.2003.50	1.597.2003.51
M 25 x 1,5	11	31	33	4 x 6	1.597.2500.50	1.597.2500.51	3 x 7	1.597.2501.50	1.597.2501.51
M 32 x 1,5	11	39	42	6 x 6,5	1.597.3200.50	1.597.3200.51	4 x 9	1.597.3201.50	1.597.3201.51
M 40 x 1,5	13	48	53	7 x 9	1.597.4001.50	1.597.4001.51	2 x 15	1.597.4003.50	1.597.4003.51
M 50 x 1,5	13	49	60		1.597.5099.50	1.597.5099.51			
M 63 x 1,5	14	49	65 / 68	6 x 12	1.597.6301.50	1.597.6301.51	3 x 18	1.597.6302.50	1.597.6302.51
PG 7	8	21	15		1.597.0799.00				
PG 9	8	22	19	4 x 1,4	1.597.0900.00	1.597.0900.01	2 x 3	1.597.0901.00	1.597.0901.01
PG 11	8	25	22	2 x 4	1.597.1102.00	1.597.1102.01	3 x 3	1.597.1101.00	1.597.1101.01
PG 13,5	9	27	24	3 x 4	1.597.1302.00	1.597.1302.01	2 x 5	1.597.1303.00	1.597.1303.01
PG 16	10	28	27	4 x 4	1.597.1602.00	1.597.1602.01	6 x 4	1.597.1604.00	1.597.1604.01
PG 16	10	28	27	3 x 5,6	1.597.1606.00	1.597.1606.01	2 x 6	1.597.1605.00	1.597.1605.01
PG 21	11	31	33	4 x 6	1.597.2100.00	1.597.2100.01	3 x 7	1.597.2101.00	1.597.2101.01
PG 29	11	39	42	6 x 6,5	1.597.2900.00	1.597.2900.01	4 x 9	1.597.2901.00	1.597.2901.01
PG 36	13	48	53	7 x 9	1.597.3601.00	1.597.3601.01	2 x 15	1.597.3603.00	1.597.3603.01
PG 42	13	49	60		1.597.4299.00				
PG 48	14	49	65	6 x 12	1.597.4801.00	1.597.4801.01	3 x 18	1.597.4802.00	1.597.4802.01
NPT 3/8"	15	22	19 / 22	4 x 1,4	1.597.3800.70	1.597.3800.71	2 x 3	1.597.3801.70	1.597.3801.71
NPT 1/2"	13	27	24	3 x 4	1.597.1202.70	1.597.1202.71	2 x 5	1.597.1203.70	1.597.1203.71
NPT 1/2" (16)	13	28	27	6 x 4	1.597.1220.70	1.597.1220.71	2 x 6	1.597.1221.70	1.597.1221.71
NPT 3/4"	14	31	33	4 x 6	1.597.3400.70	1.597.3400.71	3 x 7	1.597.3401.70	1.597.3401.71
NPT 1"	19	39	42	6 x 6,5	1.597.1000.70	1.597.1000.71	4 x 9	1.597.1001.70	1.597.1001.71
NPT 1 1/4"	16	39	42 / 46		1.597.5499.70	1.597.5499.71			
NPT 1 1/2"	20	48	53	5 x 9	1.597.6400.70	1.597.6400.71	7 x 9	1.597.6401.70	1.597.6401.71

Advice: The shown inserts are samples, more inserts upon request

HSK cable glands for special applications

HSK-K-FLAKA

Metr., PG, NPT



Material VO according to UL 94

Seal Elastomer


Protection IP 65
IP 68 possible with ideal fit, only with optional O-Ring

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005)

Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material e.g. Silicone upon request
- Elongated threads on request
- Installation instruction see page 176



AG	GL mm	H mm	mm	Dimensions w x h mm	Number grey	Number black	Dimensions w x h mm	Number grey	Number black
M 20 x 1,5	9	28	27	11,5 x 5	1.587.2016.50	1.587.2016.51	12 x 7	1.587.2017.50	1.587.2017.51
M 20 x 1,5	9	28	27	14 x 6	1.587.2018.50	1.587.2018.51			
M 25 x 1,5	11	31	33	14 x 6	1.587.2500.50	1.587.2500.51	14 x 7	1.587.2501.50	1.587.2501.51
M 32 x 1,5	11	39	42	22 x 8	1.587.3200.50	1.587.3200.51			
M 40 x 1,5	13	48	53	28,5 x 10	1.587.4000.50	1.587.4000.51	29 x 5,5	1.587.4001.50	1.587.4001.51
M 40 x 1,5	13	48	53	30,5 x 12	1.587.4002.50	1.587.4002.51	31 x 7,5	1.587.4003.50	1.587.4003.51
M 50 x 1,5	13	49	60	33,5 x 11,5	1.587.5000.50	1.587.5000.51			
M 63 x 1,5	14	49	65/68	38 x 12	1.587.6300.50	1.587.6301.51			
PG 16	10	28	27	11,5 x 5	1.587.1600.00	1.587.1600.01	12 x 7	1.587.1601.00	1.587.1601.01
PG 16	10	28	27	14 x 6	1.587.1602.00	1.587.1602.01			
PG 21	11	31	33	14 x 6	1.587.2100.00	1.587.2100.01	14 x 7	1.587.2101.00	1.587.2101.01
PG 29	11	39	42	22 x 8	1.587.2900.00	1.587.2900.01			
PG 36	13	48	53	28,5 x 10	1.587.3600.00	1.587.3600.01	29 x 5,5	1.587.3601.00	1.587.3601.01
PG 36	13	48	53	30,5 x 12	1.587.3602.00	1.587.3602.01	31 x 7,5	1.587.3603.00	1.587.3603.01
PG 42	13	49	60	33,5 x 11,5	1.587.4200.00	1.587.4200.01			
PG 48	14	49	65	38 x 12	1.587.4800.00	1.587.4800.01			
NPT 1/2" (16)	13	28	27	11,5 x 5,5	1.587.1216.70	1.587.1216.71	12 x 7	1.587.1217.70	1.587.1217.71
NPT 1/2" (16)	13	28	27	14 x 6	1.587.1218.70	1.587.1218.71			
NPT 3/4"	14	31	33	14 x 6	1.587.3400.70	1.587.3400.71			
NPT 1"	19	39	42	22 x 8	1.587.1000.70	1.587.1000.71			
NPT 1 1/4"	16	39	42/46	22 x 8	1.587.5400.70	1.587.5400.71			
NPT 1 1/2"	20	48	53	28,5 x 10	1.587.6400.70	1.587.6400.71	29 x 5,5	1.587.6401.70	1.587.6401.71
NPT 1 1/2"	20	48	53	30,5 x 12	1.587.6402.70	1.587.6402.71	31 x 7,5	1.587.6403.70	1.587.6403.71

Advice: The shown inserts are samples, more inserts upon request

HSK cable glands for special applications

HSK-K-Flex

Metr., Metr.-elongated



Material Polyamide

Seal Buna-N


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005)

Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material e.g. Silicone upon request
- Other colors on request



AG	mm	GL	H	d	mm	Number grey	Number black	GL	Number grey elongated	Number black elongated
M 12 x 1,5	3-6,5	8	54	7	15	1.293.1200.50	1.293.1201.50	15	1.293.1200.30	1.293.1201.30
M 12 x 1,5	2-5	8	54	7	15	1.293.1200.51	1.293.1201.51	15	1.293.1200.31	1.293.1201.31
M 16 x 1,5	4-8	8	63	8,5	19	1.293.1600.50	1.293.1601.50	15	1.293.1600.30	1.293.1601.30
M 16 x 1,5	2-6	8	63	8,5	19	1.293.1600.51	1.293.1601.51	15	1.293.1600.31	1.293.1601.31
M 16 x 1,5	5-10	8	78	10,5	22	1.294.1600.50	1.294.1601.50	15	1.294.1600.30	1.294.1601.30
M 16 x 1,5	3-7	8	78	10,5	22	1.294.1600.51	1.294.1601.51	15	1.294.1600.31	1.294.1601.31
M 20 x 1,5	6-12	9	90	13	24	1.293.2000.50	1.293.2001.50	15	1.293.2000.30	1.293.2001.30
M 20 x 1,5	5-9	9	90	13	24	1.293.2000.51	1.293.2001.51	15	1.293.2000.31	1.293.2001.31
M 20 x 1,5	10-14	9	100	15,5	27	1.294.2000.50	1.294.2001.50	15	1.294.2000.30	1.294.2001.30
M 20 x 1,5	7-12	9	100	15,5	27	1.294.2000.51	1.294.2001.51	15	1.294.2000.31	1.294.2001.31
M 25 x 1,5	13-18	11	114	20	33	1.293.2500.50	1.293.2501.50	15	1.293.2500.30	1.293.2501.30
M 25 x 1,5	9-16	11	114	20	33	1.293.2500.51	1.293.2501.51	15	1.293.2500.31	1.293.2501.31

HSK cable glands for special applications

HSK-K-Flex

PG, PG-elongated, NPT

RoHS



Material Polyamide

Seal Buna-N


Protection IP 68 – 10 bar/ IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005)

Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material e.g. Silicone upon request
- Other colors on request




AG	$\varnothing$ mm	GL mm	H mm	d mm	 mm	Number grey	Number black	GL mm	Number grey elongated	Number black elongated
PG 7*	3–6,5	8	54	7	15	1.293.0700.14	1.293.0701.14	15	1.293.0700.60	1.293.0701.60
PG 7*	2–5	8	54	7	15	1.293.0700.15	1.293.0701.15	15	1.293.0700.61	1.293.0701.61
PG 9*	4–8	8	63	8,5	19	1.293.0900.14	1.293.0901.14	15	1.293.0900.60	1.293.0901.60
PG 9*	2–6	8	63	8,5	19	1.293.0900.15	1.293.0901.15	15	1.293.0900.61	1.293.0901.61
PG 11*	5–10	8	78	10,5	22	1.293.1100.14	1.293.1101.14	15	1.293.1100.60	1.293.1101.60
PG 11*	3–7	8	78	10,5	22	1.293.1100.15	1.293.1101.15	15	1.293.1100.61	1.293.1101.61
PG 13,5*	6–12	9	90	13	24	1.293.1300.14	1.293.1301.14	15	1.293.1300.60	1.293.1301.60
PG 13,5*	5–9	9	90	13	24	1.293.1300.15	1.293.1301.15	15	1.293.1300.61	1.293.1301.61
PG 16*	10–14	10	100	15,5	27	1.293.1600.14	1.293.1601.14	15	1.293.1600.60	1.293.1601.60
PG 16*	7–12	10	100	15,5	27	1.293.1600.15	1.293.1601.15	15	1.293.1600.61	1.293.1601.61
PG 21*	13–18	11	114	20	33	1.293.2100.14	1.293.2101.14	15	1.293.2100.60	1.293.2101.60
PG 21*	9–16	11	114	20	33	1.293.2100.15	1.293.2101.15	15	1.293.2100.61	1.293.2101.61
NPT 3/8"	4–8	15	63	8,5	22/19	1.293.3800.70	1.293.3801.70			
NPT 3/8"	2–6	15	63	8,5	22/19	1.293.3800.71	1.293.3801.71			
NPT 1/2"	6–12	13	90	13	24	1.293.1200.70	1.293.1201.70			
NPT 1/2"	5–9	13	90	13	24	1.293.1200.71	1.293.1201.71			
NPT 1/2" (16)	10–14	13	100	15,5	27	1.293.1216.70	1.293.1217.70			
NPT 1/2" (16)	7–12	13	100	15,5	27	1.293.1216.71	1.293.1217.71			
NPT 3/4"	13–18	14	114	20	33	1.293.3400.70	1.293.3401.70			
NPT 3/4"	9–16	14	114	20	33	1.293.3400.71	1.293.3401.71			

* Also available as KE-Flex with enlarged clamping range and as KR-Flex with reduced clamping range, see clamping range page 18

HSK cable glands for special applications

HSK-W

Metr.


Advice:

- Other sealing material e.g. Silicone upon request
- Other colors on request

Material Polyamide




Seal Buna-N


Protection IP 68
O-Ring Buna-N

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005)



AG	$\varnothing$ mm	GL mm	H mm	L mm	R mm		Number grey	Number black
M 16 x 1,5	4-8	8	23	45	5	19	1.313.1600.50	1.313.1601.50
M 16 x 1,5	2-6	8	23	45	5	19	1.313.1600.51	1.313.1601.51
M 20 x 1,5	6-12	9	30,5	57	7	24	1.313.2000.50	1.313.2001.50
M 20 x 1,5	5-9	9	30,5	57	7	24	1.313.2000.51	1.313.2001.51
M 25 x 1,5	13-18	11	40	73	10	33	1.313.2500.50	1.313.2501.50
M 25 x 1,5	9-16	11	40	73	10	33	1.313.2500.51	1.313.2501.51
M 32 x 1,5	18-25	11	51,5	91	14	42	1.313.3200.50	1.313.3201.50
M 32 x 1,5	13-20	11	51,5	91	14	42	1.313.3200.51	1.313.3201.51

➔ Accessories see page 73

HSK-W

NPT


Advice:

- Glands not fitted with O-Rings.
- We recommend the use of thread washer seal ring (page 89)

Material Polyamide




Seal Buna-N


Protection IP 68
O-Ring Buna-N

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005)

- Other sealing material e.g. Silicone upon request
- Other colors on request



AG	$\varnothing$ mm	GL mm	H mm	L mm	R mm		Number grey	Number black
NPT 3/8"	4-8	15	23	45	5	19	1.313.3800.70	1.313.3801.70
NPT 3/8"	2-6	15	23	45	5	19	1.313.3800.71	1.313.3801.71
NPT 1/2"	6-12	13	32,5	57	7	24	1.313.1200.70	1.313.1201.70
NPT 1/2"	5-9	13	32,5	57	7	24	1.313.1200.71	1.313.1201.71
NPT 1/2" (16)	10-14	13	31,5	59	8	27	1.313.1216.70	1.313.1217.70
NPT 1/2" (16)	7-12	13	31,5	59	8	27	1.313.1216.71	1.313.1217.71
NPT 3/4"	13-18	13	40	73	10	33	1.313.3400.70	1.313.3401.70
NPT 3/4"	9-16	13	40	73	10	33	1.313.3400.71	1.313.3401.71
NPT 1"	18-25	19	51,5	91	14	42	1.313.1000.70	1.313.1001.70
NPT 1"	13-20	19	51,5	91	14	42	1.313.1000.71	1.313.1001.71

➔ Accessories see page 73

HSK cable glands for special applications

HSK-W
PG

Material	Polyamide
Seal	Buna-N
Protection O-Ring	IP 68 Buna-N
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F)
Colors	grey (RAL 7035), black (RAL 9005)

Advice:
 - Other sealing material e.g. Silicone upon request
 - Other colors on request

AG	mm	GL mm	H mm	L mm	R mm	mm	Number grey	Number black
PG 9	4-8	8	23	45	5	19	1.313.0900.14	1.313.0901.14
PG 9	2-6	8	23	45	5	19	1.313.0900.15	1.313.0901.15
PG 11	5-10	8	27	50	6	22	1.313.1100.14	1.313.1101.14
PG 11	3-7	8	27	50	6	22	1.313.1100.15	1.313.1101.15
PG 13,5	6-12	9	30,5	57	7	24	1.313.1300.14	1.313.1301.14
PG 13,5	5-9	9	30,5	57	7	24	1.313.1300.15	1.313.1301.15
PG 16	10-14	10	32,5	59	8	27	1.313.1600.14	1.313.1601.14
PG 16	7-12	10	32,5	59	8	27	1.313.1600.15	1.313.1601.15
PG 21	13-18	11	40	73	10	33	1.313.2100.14	1.313.2101.14
PG 21	9-16	11	40	73	10	33	1.313.2100.15	1.313.2101.15
PG 29	18-25	11	51,5	91	14	42	1.313.2900.14	1.313.2901.14
PG 29	13-20	11	51,5	91	14	42	1.313.2900.15	1.313.2901.15

➔ Accessories see page 73

HSK-W rotating version
PG

Material	Polyamide
Seal	Buna-N
Protection O-Ring	IP 68 Buna-N
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F)
Colors	grey (RAL 7035), black (RAL 9005)

Advice:
 - Other sealing material e.g. Silicone upon request
 - Other colors on request

AG	mm	GL mm	H mm	L mm	R mm	mm	Number grey	Number black
PG 9	4-8	8	28	45	5	19	1.317.0900.14	1.317.0901.14
PG 9	2-6	8	28	45	5	19	1.317.0900.15	1.317.0901.15
PG 11	5-10	8	32	50	6	22	1.317.1100.14	1.317.1101.14
PG 11	3-7	8	32	50	6	22	1.317.1100.15	1.317.1101.15
PG 13,5	6-12	9	35,5	57	7	24	1.317.1300.14	1.317.1301.14
PG 13,5	5-9	9	35,5	57	7	24	1.317.1300.15	1.317.1301.15
PG 16	10-14	10	38,5	59	8	27	1.317.1600.14	1.317.1601.14
PG 16	7-12	11	46	73	10	33	1.317.1600.15	1.317.1601.15
PG 21	13-18	11	46	73	10	33	1.317.2100.14	1.317.2101.14
PG 21	9-16	11	46	73	10	33	1.317.2100.15	1.317.2101.15

➔ Accessories see page 73

HSK cable glands for special applications

HSK-W-Flex

Metr., PG, NPT



Material Polyamide

Seal Buna-N


Protection IP 68

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005)

Advice:

- Other sealing material e.g. Silicone upon request
- Other colors on request



AG	$\varnothing$ mm	d mm	GL mm	H mm	L mm	R mm	mm	Number grey	Number black
M 16 x 1,5	4-8	8,5	8	23	85	5	19	1.314.1600.50	1.314.1601.50
M 16 x 1,5	2-6	8,5	8	23	85	5	19	1.314.1600.51	1.314.1601.51
M 20 x 1,5	6-12	13	9	30,5	119	7	24	1.314.2000.50	1.314.2001.50
M 20 x 1,5	5-9	13	9	30,5	119	7	24	1.314.2000.51	1.314.2001.51
M 25 x 1,5	13-18	20	11	40	156	10	33	1.314.2500.50	1.314.2501.50
M 25 x 1,5	9-16	20	11	40	156	10	33	1.314.2500.51	1.314.2501.51
PG 9	4-8	8,5	8	23	85	5	19	1.314.0900.14	1.314.0901.14
PG 9	2-6	8,5	8	23	85	5	19	1.314.0900.15	1.314.0901.15
PG 11	5-10	10,5	8	27	103	6	22	1.314.1100.14	1.314.1101.14
PG 11	3-7	10,5	8	27	103	6	22	1.314.1100.15	1.314.1101.15
PG 13,5	6-12	13	9	30,5	119	7	24	1.314.1300.14	1.314.1301.14
PG 13,5	5-9	13	9	30,5	119	7	24	1.314.1300.15	1.314.1301.15
PG 16	10-14	15,5	10	32,5	130	8	27	1.314.1600.14	1.314.1601.14
PG 16	7-12	15,5	10	32,5	130	8	27	1.314.1600.15	1.314.1601.15
PG 21	13-18	20	11	40	156	10	33	1.314.2100.14	1.314.2101.14
PG 21	9-16	20	11	40	156	10	33	1.314.2100.15	1.314.2101.15
NPT* 3/8"	4-8	8,5	15	23	85	5	19	1.314.3800.70	1.314.3801.70
NPT* 3/8"	2-6	8,5	15	23	85	5	19	1.314.3800.71	1.314.3801.71
NPT* 1/2"	6-12	13	13	30,5	119	7	24	1.314.1200.70	1.314.1201.70
NPT* 1/2"	5-9	13	13	30,5	119	7	24	1.314.1200.71	1.314.1201.71
NPT* 1/2" (16)	10-14	15,5	13	31,5	130	8	27	1.314.1216.70	1.314.1217.70
NPT* 1/2" (16)	7-12	15,5	13	31,5	130	8	27	1.314.1216.71	1.314.1217.71
NPT* 3/4"	13-18	20	13	40	156	10	33	1.314.3400.70	1.314.3401.70
NPT* 3/4"	9-16	20	13	40	156	10	33	1.314.3400.71	1.314.3401.71

* Glands not fitted with O-Rings. We recommend the use of thread washer seal ring.
Please see page 89 for suitable thread seal ring.

➔ Accessories see page 73

HSK cable glands for special applications

HSK-M-Multi

Metr., PG, NPT



Material Nickel plated brass

Clamping insert Polyamide

Seal Elastomer


O-Ring NBR

Protection IP 65
IP 68 possible with ideal fit

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Advice:

- Other sealing material e.g. Silicone upon request
- Stainless steel on request
- Elongated threads on request
- Installation instructions see page 176



AG	GL mm	H mm	mm	Number of Holes x d	Number	Number of Holes x d	Number
M 12 x 1,5	6,5	19	14		1.697.1299.50		1.697.1299.50
M 16 x 1,5	6	21	17 / 19	4 x 1,4	1.697.1600.50	2 x 3	1.697.1601.50
M 20 x 1,5	6	23	22	6 x 3	1.697.2001.50	2 x 5	1.697.2003.50
M 25 x 1,5	7	26	30	4 x 6	1.697.2500.50	3 x 7	1.697.2501.50
M 32 x 1,5	8	31	40	6 x 6,5	1.697.3200.50	4 x 9	1.697.3201.50
M 40 x 1,5	8	37	50	7 x 9	1.697.4001.50	2 x 15	1.697.4003.50
M 50 x 1,5	9	37	57		1.697.5099.50		
M 63 x 1,5	10	38	64 / 68	6 x 12	1.697.6301.50	3 x 18	1.697.6302.50
PG 7	5	19	14		1.697.0799.01		1.697.0799.01
PG 9	6	21	17	4 x 1,4	1.697.0900.01	2 x 3	1.697.0901.01
PG 11	6	22	20	2 x 4	1.697.1102.01	3 x 3	1.697.1101.01
PG 13,5	6,5	24	22	3 x 4	1.697.1302.01	2 x 5	1.697.1303.01
PG 16	6,5	23	24	4 x 4	1.697.1602.01	6 x 4	1.697.1604.01
PG 16	6,5	23	24	3 x 5,6	1.697.1606.01	2 x 6	1.697.1605.01
PG 21	7	24	30	4 x 6	1.697.2100.01	3 x 7	1.697.2101.01
PG 29	8	29	40	6 x 6,5	1.697.2900.01	4 x 9	1.697.2901.01
PG 36	8	35	50	7 x 9	1.697.3601.01	2 x 15	1.697.3603.01
PG 42	9	37	57		1.697.4299.01		1.697.4299.01
PG 48	10	38	64	6 x 12	1.697.4801.01	3 x 18	1.697.4802.01
NPT 3/8"	15	21	17 / 19	4 x 1,4	1.697.3800.70	2 x 3	1.697.3801.70
NPT 1/2"	13	24	24	3 x 4	1.697.1202.70	2 x 5	1.697.1203.70
NPT 3/4"	13	25	30	4 x 6	1.697.3400.70	3 x 7	1.697.3401.70
NPT 1"	19	29	40	6 x 6,5	1.697.1000.70	4 x 9	1.697.1001.70

Advice: The shown inserts are samples, more inserts upon request

HSK cable glands for special applications

HSK-M-FLAKA

Metr., PG, NPT



Material Nickel plated brass



Clamping insert Polyamide

Seal Elastomer


O-Ring Buna-N

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Advice:

- Other sealing material e.g. Silicone upon request
- Stainless steel on request
- Elongated threads on request
- Installation instructions see page 176

RoHS



AG	GL mm	H mm	mm	B x H mm	Number	B x H mm	Number
M 20 x 1,5	6	24	24	11,5 x 5	1.688.2016.50	12 x 7	1.688.2017.50
M 20 x 1,5	6	24	24	14 x 6	1.688.2018.50		
M 25 x 1,5	7	26	30	14 x 6	1.688.2500.50	14 x 7	1.688.2501.50
M 32 x 1,5	8	31	40	22 x 8	1.688.3200.50		
M 40 x 1,5	8	37	50	28,5 x 10	1.688.4000.50	29 x 5,5	1.688.4001.50
M 40 x 1,5	8	37	50	30,5 x 12	1.688.4002.50	31 x 7,5	1.688.4003.50
M 50 x 1,5	9	37	57	33,5 x 11,5	1.688.5000.50		
M 63 x 1,5	10	38	64/68	38 x 12	1.688.6300.50		
PG 16	6,5	23	24	11,5 x 5	1.688.1600.01	12 x 7	1.688.1601.01
PG 16	6,5	23	24	14 x 6	1.688.1602.01		
PG 21	7	24	30	14 x 6	1.688.2100.01	14 x 7	1.688.2101.01
PG 29	8	29	40	22 x 8	1.688.2900.01		
PG 36	8	35	50	28,5 x 10	1.688.3600.01	29 x 5,5	1.688.3601.01
PG 36	8	35	50	30,5 x 12	1.688.3602.01	31 x 7,5	1.688.3603.01
PG 42	9	37	57	33,5 x 11,5	1.688.4200.01		
PG 48	10	38	64	38 x 12	1.688.4802.01		
NPT 3/4"	13	25	30	14 x 6	1.688.3400.70	14 x 7	1.688.3401.70
NPT 1"	19	29	40	22 x 8	1.688.1000.70		

Advice: The shown inserts are samples, more inserts upon request

HSK cable glands for special applications

HSK-M-Flex

Metr. / Metr.-elongated



Material Nickel plated brass

Steel spring INOX 1.4310

Clamping insert Polyamide

Seal Buna-N


O-Ring Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Advice:

- Other sealing material e.g. Silicone upon request



AG	Ø mm	GL mm	H mm	d mm	mm	Number	GL mm	Number long
M 12 x 1,5	3 – 6,5	6,5	55	6,8	14	1.623.1200.50	10	1.623.1200.30
M 12 x 1,5	2 – 5	6,5	55	6,8	14	1.623.1200.51	10	1.623.1200.31
M 16 x 1,5	4 – 8	6	66	8,2	19	1.623.1600.50	10	1.623.1600.30
M 16 x 1,5	2 – 6	6	66	8,2	19	1.623.1600.51	10	1.623.1600.31
M 16 x 1,5	5 – 10	6	77	10,3	20	1.623.1611.50	10	1.623.1611.30
M 16 x 1,5	3 – 7	6	77	10,3	20	1.623.1611.51	10	1.623.1611.31
M 20 x 1,5	6 – 12	6	88	12,3	22	1.623.2000.50	10	1.623.2000.30
M 20 x 1,5	5 – 9	6	88	12,3	22	1.623.2000.51	10	1.623.2000.31
M 20 x 1,5	10 – 14	6	98	14,3	24	1.623.2016.50	10	1.623.2016.30
M 20 x 1,5	7 – 12	6	98	14,3	24	1.623.2016.51	10	1.623.2016.31
M 25 x 1,5	13 – 18	7	111	18,4	30	1.623.2500.50	12	1.623.2500.30
M 25 x 1,5	9 – 16	7	111	18,4	30	1.623.2500.51	12	1.623.2500.31

HSK cable glands for special applications

HSK-M-Flex


PG, PG-elongated



Advice:

- Other sealing material e.g. Silicone upon request

Material	Nickel plated brass
Steel spring	INOX 1.4310
Clamping insert	Polyamide
Seal	Buna-N
O-Ring	Buna-N
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F)



AG	$\varnothing$ mm	GL mm	H mm	d mm	$\varnothing$ mm	Number	GL mm	Number long
PG 7	3 – 6,5	5	55	6,8	14	1.623.0700.01	10	1.623.0700.60
PG 7	2 – 5	5	55	6,8	14	1.623.0700.15	10	1.623.0700.61
PG 9	4 – 8	6	66	8,2	17	1.623.0900.01	10	1.623.0900.60
PG 9	2 – 6	6	66	8,2	17	1.623.0900.15	10	1.623.0900.61
PG 11	5 – 10	6	77	10,3	20	1.623.1100.01	10	1.623.1100.60
PG 11	3 – 7	6	77	10,3	20	1.623.1100.15	10	1.623.1100.61
PG 13,5	6 – 12	6,5	88	12,3	22	1.623.1300.01	10	1.623.1300.60
PG 13,5	5 – 9	6,5	88	12,3	22	1.623.1300.15	10	1.623.1300.61
PG 16	10 – 14	6,5	98	14,3	24	1.623.1600.01	10	1.623.1600.60
PG 16	7 – 12	6,5	98	14,3	24	1.623.1600.15	10	1.623.1600.61
PG 21	13 – 18	7	111	18,4	30	1.623.2100.01	12	1.623.2100.60
PG 21	9 – 16	7	111	18,4	30	1.623.2100.15	12	1.623.2100.61

➔ Accessories see page 73

HSK-M-Flex


NPT



Advice:

- Other sealing material e.g. Silicone upon request

Material	Nickel plated brass
Steel spring	INOX 1.4310
Clamping insert	Polyamide
Seal	Buna-N
O-Ring	Buna-N
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F)



AG	$\varnothing$ mm	GL mm	H mm	d mm	$\varnothing$ mm	Number
NPT 3/8"	4 – 8	15	66	8,2	17/19	1.623.3800.70
NPT 3/8"	2 – 6	15	66	8,2	17/19	1.623.3800.71
NPT 1/2"	6 – 12	13	88	12,3	22/24	1.623.1200.70
NPT 1/2"	5 – 9	13	88	12,3	22/24	1.623.1200.71
NPT 3/4"	13 – 18	13	111	18,4	33	1.623.3400.70
NPT 3/4"	9 – 16	13	111	18,4	33	1.623.3400.71

➔ Accessories see page 73

HSK cable glands for special applications

HSK-MINI

Metr., PG



RoHS

Material Nickel plated brass / INOX 1.4305

Seal ring TPE / FPM

O-Ring Buna-N / FPM

Protection IP 68


Operating Temperature -20 °C – 100 °C (-4 °F – 212 °F) (Buna-N / TPE)
-25 °C – 200 °C (-13 °F – 392 °F) (FPM)

Advice:


- Other sealing material e.g. Silicone upon request
- Other thread pitches on request
- Stainless steel 1.4404 on request



HSK-Mini



HSK-Mini EMC





AG	mm	GL mm	H mm	mm	Number Buna-N / TPE	Number FPM
M 6 x 1	2-3,2	6	10	8	1.106.0601.50	1.106.0600.55
M 8 x 0,75	2-4,5	3,5	14,3	11	1.112.0801.01	
M 8 x 1,25	3-5	6	13	11	1.106.0801.50	1.106.0800.55
M 10 x 1,5	4-6	6	14	12	1.106.1001.50	
PG 7	2-4,5	3,5	14,3	11/15	1.112.0708.01	
HSK-Mini elongated						
M 8 x 1,25	3-5	10	13	11	1.106.0801.30	1.106.0800.35
M 10 x 1,5	4-6	10	14	12	1.106.1001.30	1.106.1000.35
HSK-Mini EMV						
M 8 x 1,25	3-5	6	13	11	1.119.0800.50	
M 10 x 1,5	4-6	6	14	12	1.119.1000.50	
HSK-Mini INOX						
M 8 x 1,25	3-5	6	13	11	1.129.0800.50	1.129.0800.55
M 10 x 1,5	4-6	6	14	12	1.129.1000.50	1.129.1000.55

HSK cable glands for special applications

HSK-XL

Metr.



Material Nickel plated brass

Seal Buna-N


O-Ring Buna-N

Protection IP 68

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Advice:

- Other sealing material e.g. Silicone upon request
- Stainless steel on request



AG	mm	GL	H	mm	Number
M 63 x 1,5	48-55	10	42	75	1.106.6375.50
M 75 x 1,5	48-55	15	42	80	1.106.7500.50
M 75 x 1,5	53-60	15	42	85	1.106.7500.51
M 80 x 2	58-65	15	42	90	1.106.8000.50
M 90 x 2	63-70	15	42	100	1.106.9000.50
M 90 x 2	68-75	15	52	100	1.106.9000.51
M 100 x 2	78-85	20	52	110	1.106.1000.50
M 100 x 2	73-80	20	52	110	1.106.1000.51
M 110 x 2	83-90	20	52	120	1.106.1100.51

HSK cable glands for special applications

HSK-XL

G

RoHS



Material Nickel plated brass

Seal Buna-N




O-Ring Buna-N

Protection IP 68

Operating Temperature -20 °C – 100 °C (-4 °F – 212 °F)

Advice:

- Other sealing material e.g. Silicone upon request
- Stainless steel on request



AG	Ø mm	GL mm	H mm	U mm	Number
G 2 1/2"	48–55	18	42	80	1.106.5200.01
G 2 1/2"	53–60	18	42	85	1.106.5201.01
G 3"	58–65	18	42	90 / 95	1.106.3000.01
G 3"	63–70	18	42	100	1.106.3001.01
G 4"	68–75	22	52	100 / 120	1.106.4000.01
G 4"	73–80	22	52	110 / 120	1.106.4001.01
G 4"	78–85	22	52	110 / 120	1.106.4002.01
G 4"	83–90	22	52	120	1.106.4003.01

➔ Accessories see page 73

HSK cable glands for special applications

HSK-MZ / HSK-MZ-PVDF

Metr., Metr.-elongated




Material	Nickel plated brass
Clamping insert	Polyamide / PVDF
Seal	Buna-N / FPM
O-Ring	Buna-N / FPM
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F) (PA) -35 °C – 150 °C (-31 °F – 302 °F) (PVDF)

Advice:
- Other sealing material e.g. Silicone upon request



See our homepage www.hummel.com
for assembling advices for maximum
cable diameters



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-MZ -40 °C – 100 °C -40 °F – 212 °F	Number HSK-MZ-PVDF -35 °C – 150 °C -31 °F – 302 °F	GL mm	Number HSK-MZ elongated -40 °C – 100 °C -40 °F – 212 °F
M 12 x 1,5	3 – 6,5	6,5	26	14	1.690.1200.50	1.669.1200.50	10	1.690.1200.30
M 16 x 1,5	4 – 8	6	28	17 / 19	1.690.1600.50	1.669.1600.50	10	1.690.1600.30
M 16 x 1,5	6 – 10	6	30	20	1.690.1611.50	1.669.1611.50	10	1.690.1611.30
M 20 x 1,5	6 – 12	6	33	22	1.690.2000.50	1.669.2000.50	10	1.690.2000.30
M 20 x 1,5	10 – 14	6	33	24	1.690.2016.50	1.669.2016.50	10	1.690.2016.30
M 25 x 1,5	13 – 18	7	37	30	1.690.2500.50	1.669.2500.50	12	1.690.2500.30
M 32 x 1,5	18 – 25	8	43	40	1.690.3200.50	1.669.3200.50	12	1.690.3200.30
M 40 x 1,5	22 – 32	8	50	50	1.690.4000.50	1.669.4000.50	15	1.690.4000.30
M 50 x 1,5	32 – 38	9	51	57	1.690.5000.50		15	1.690.5000.30
M 50 x 1,5	25 – 31	9	51	57	1.690.5000.51		15	1.690.5000.31
M 63 x 1,5	37 – 44	10	52	64/68	1.690.6300.50		15	1.690.6300.30
M 63 x 1,5	29 – 35	10	52	64/68	1.690.6300.51		15	1.690.6300.31

HSK cable glands for special applications

HSK-MZ / HSK-MZ-PVDF

PG, PG-elongated

RoHS



Material Nickel plated brass

Clamping insert Polyamide / PVDF

Seal Buna-N / FPM


O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F) (PA)
-35 °C – 150 °C (-31 °F – 302 °F) (PVDF)



Advice:
- Other sealing material e.g. Silicone upon request



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number HSK-MZ -40 °C – 100 °C -40 °F – 212 °F	Number HSK-MZ-PVDF -35 °C – 150 °C -31 °F – 302 °F	GL mm	Number elongated
PG 7	3 – 6,5	5	26	14	1.690.0700.01	1.669.0700.01	10	1.690.0700.60
PG 9	4 – 8	6	28	17	1.690.0900.01	1.669.0900.01	10	1.690.0900.60
PG 11	6 – 10	6	30	20	1.690.1100.01	1.669.1100.01	10	1.690.1100.60
PG 13,5	6 – 12	6,5	33	22	1.690.1300.01	1.669.1300.01	10	1.690.1300.60
PG 16	10 – 14	6,5	33	24	1.690.1600.01	1.669.1600.01	10	1.690.1600.60
PG 21	13 – 18	7	37	30	1.690.2100.01	1.669.2100.01	12	1.690.2100.60
PG 29	18 – 25	8	43	40	1.690.2900.01	1.669.2900.01	12	1.690.2900.60
PG 36	22 – 36	8	50	50	1.690.3600.01	1.669.3600.01	15	1.690.3600.60
PG 42	32 – 38	9	51	57	1.690.4200.01	1.669.4200.01	15	1.690.4200.60
PG 42	25 – 31	9	51	57	1.690.4200.15	1.669.4200.15	15	1.690.4200.61
PG 48	37 – 44	10	52	64	1.690.4800.01	1.669.4800.01	15	1.690.4800.60
PG 48	29 – 35	10	51	64	1.690.4800.15	1.669.4800.15	15	1.690.4800.61

➔ Accessories see page 73

HSK-MZ / HSK-MZ-PVDF

NPT

RoHS



Material Nickel plated brass

Clamping insert Polyamide / PVDF

Seal Buna-N / FPM


O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F) (PA)
-35 °C – 150 °C (-31 °F – 302 °F) (PVDF)



Advice:
- Other sealing material e.g. Silicone upon request



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number HSK-MZ -40 °C – 100 °C -40 °F – 212 °F	Number HSK-MZ-PVDF -35 °C – 150 °C -31 °F – 302 °F
NPT 3/8"	4 – 8	15	28	17/19	1.690.3800.70	1.669.3800.70
NPT 1/2"	7 – 12	13	33	22/24	1.690.1200.70	1.669.1200.70
NPT 3/4"	13 – 18	13	37	30	1.690.3400.70	1.669.3400.70
NPT 1"	18 – 25	19	43	40	1.690.1000.70	

➔ Accessories see page 73

HSK-M-W

Metr., PG



Material	Zinc die casting / Nickel plated brass
Clamping insert	Polyamide
Seal ring	Buna-N
O-Ring	Buna-N
Protection	IP 68
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F)


Advice:

Advice:


- Other sealing material e.g. Silicone upon request



With mounting flange



With threaded connection

[illegible]

Accessories see page 73

Industrial cable glands

METRICA cable glands

Cable glands of the METRICA series are based on metric dimensions. So these glands offer space saving with optimised clamping ranges.

Both plastic and nickel plated brass versions feature recessed grooves for O-rings on the connecting thread.

In combination with the sealing O-Ring these glands keep the protection rating IP 68 also with the high pressure of 10 bars.



You can find in this chapter:

METRICA cable glands

- made of polyamide
- made of polyamide with bending protection
- made of nickel plated brass
- made of nickel plated brass in EMC and EMC-E version.

We provide variable clamping ranges and thread lengths.

For any further question please do not hesitate to contact us. We look forward to develop solutions together with you. You profit from our vast knowledge in development, engineering and production technology.

Contact us:

E-Mail: info.et@hummel.com

Tel.: +49 (0) 76 66/9 11 10-0

METRICA-P, METRICA-P-Flex

Metr.



Material Polyamide

Seal Buna-N



Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005),
blue (RAL 5012) for the intrinsic safety "i"

Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material e.g. Silicone upon request
- Other colors on request



AG	Ø mm	GL mm	H mm	mm	d mm	Number grey	Number black	Number blue
M 12 x 1,5	4 – 7	8	22	15		1.218.1200.50	1.218.1201.50	1.218.1202.50
M 12 x 1,5	2 – 5	8	22	15		1.218.1200.51	1.218.1201.51	1.218.1202.51
M 16 x 1,5	6 – 10	8	26	19		1.218.1600.50	1.218.1601.50	1.218.1602.50
M 16 x 1,5	3 – 7	8	26	19		1.218.1600.51	1.218.1601.51	1.218.1602.51
M 20 x 1,5	8 – 13	9	29	24		1.218.2000.50	1.218.2001.50	1.218.2002.50
M 20 x 1,5	7 – 10	9	29	24		1.218.2000.51	1.218.2001.51	1.218.2002.51
M 25 x 1,5	11 – 17	10	33	30		1.218.2500.50	1.218.2501.50	1.218.2502.50
M 25 x 1,5	8 – 13	10	33	30		1.218.2500.51	1.218.2501.51	1.218.2502.51
M 32 x 1,5	11 – 21	10	41	36		1.218.3200.50	1.218.3201.50	1.218.3202.50
M 32 x 1,5	10 – 15	10	41	36		1.218.3200.51	1.218.3201.51	1.218.3202.51
M 40 x 1,5	19 – 28	12	46	46		1.218.4000.50	1.218.4001.50	1.218.4002.50
M 40 x 1,5	15 – 23	12	46	46		1.218.4000.51	1.218.4001.51	1.218.4002.51
M 50 x 1,5	27 – 35	12	52	55		1.218.5000.50	1.218.5001.50	1.218.5002.50
M 50 x 1,5	22 – 29	12	52	55		1.218.5000.51	1.218.5001.51	1.218.5002.51
M 63 x 1,5	36 – 48	12	57	68		1.218.6300.50	1.218.6301.50	1.218.6302.50
M 63 x 1,5	28 – 39	12	57	68		1.218.6300.51	1.218.6301.51	1.218.6302.51

METRICA-P-Flex

M 12 x 1,5	4 – 7	8	55,5	15	7,5	1.238.1200.50	1.238.1201.50	
M 12 x 1,5	2 – 5	8	55,5	15	7,5	1.238.1200.51	1.238.1201.51	
M 16 x 1,5	6 – 10	8	67	19	10,5	1.238.1600.50	1.238.1601.50	
M 16 x 1,5	3 – 7	8	67	19	10,5	1.238.1600.51	1.238.1601.51	
M 20 x 1,5	8 – 13	9	92,5	24	14	1.238.2000.50	1.238.2001.50	
M 20 x 1,5	7 – 10	9	92,5	24	14	1.238.2000.51	1.238.2001.51	
M 25 x 1,5	11 – 17	10	113	30	19	1.238.2500.50	1.238.2501.50	
M 25 x 1,5	8 – 13	10	113	30	19	1.238.2500.51	1.238.2501.51	

➔ Accessories see page 73

METRICA-P, METRICA-P-Flex

Metr.-elongated



Material Polyamide

Seal Buna-N



Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range, only with optional O-Ring

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005),
blue (RAL 5012) for the intrinsic safety "i"

Advice:

- With additional pre-assembled O-Ring upon request
- Please find suitable O-Ring on page 88
- Other sealing material e.g. Silicone upon request
- Other colors on request



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	d mm	Number grey	Number black	Number blue
M 12 x 1,5	4 – 7	15	22	15		1.218.1200.30	1.218.1201.30	1.218.1202.30
M 12 x 1,5	2 – 5	15	22	15		1.218.1200.31	1.218.1201.31	1.218.1202.31
M 16 x 1,5	6 – 10	15	26	19		1.218.1600.30	1.218.1601.30	1.218.1602.30
M 16 x 1,5	3 – 7	15	26	19		1.218.1600.31	1.218.1601.31	1.218.1602.31
M 20 x 1,5	8 – 13	15	29	24		1.218.2000.30	1.218.2001.30	1.218.2002.30
M 20 x 1,5	7 – 10	15	29	24		1.218.2000.31	1.218.2001.31	1.218.2002.31
M 25 x 1,5	11 – 17	15	33	30		1.218.2500.30	1.218.2501.30	1.218.2502.30
M 25 x 1,5	8 – 13	15	33	30		1.218.2500.31	1.218.2501.31	1.218.2502.31
M 32 x 1,5	11 – 21	15	41	36		1.218.3200.30	1.218.3201.30	1.218.3202.30
M 32 x 1,5	10 – 15	15	41	36		1.218.3200.31	1.218.3201.31	1.218.3202.31
M 40 x 1,5	19 – 28	18	46	46		1.218.4000.30	1.218.4001.30	1.218.4002.30
M 40 x 1,5	15 – 23	18	46	46		1.218.4000.31	1.218.4001.31	1.218.4002.31
M 50 x 1,5	27 – 35	18	52	55		1.218.5000.30	1.218.5001.30	1.218.5002.30
M 50 x 1,5	22 – 29	18	52	55		1.218.5000.31	1.218.5001.31	1.218.5002.31
M 63 x 1,5	36 – 48	18	57	68		1.218.6300.30	1.218.6301.30	1.218.6302.30
M 63 x 1,5	28 – 39	18	57	68		1.218.6300.31	1.218.6301.31	1.218.6302.31

METRICA-P-Flex

M 12 x 1,5	4 – 7	15	55,5	15	7,5	1.238.1200.30	1.238.1201.30	
M 12 x 1,5	2 – 5	15	55,5	15	7,5	1.238.1200.31	1.238.1201.31	
M 16 x 1,5	6 – 10	15	67	19	10,5	1.238.1600.30	1.238.1601.30	
M 16 x 1,5	3 – 7	15	67	19	10,5	1.238.1600.31	1.238.1601.31	
M 20 x 1,5	8 – 13	15	92,5	24	14	1.238.2000.30	1.238.2001.30	
M 20 x 1,5	7 – 10	15	92,5	24	14	1.238.2000.31	1.238.2001.31	
M 25 x 1,5	11 – 17	15	113	30	19	1.238.2500.30	1.238.2501.30	
M 25 x 1,5	8 – 13	15	113	30	19	1.238.2500.31	1.238.2501.31	

METRICA-M

Metr., Metr.-elongated



Material Nickel plated brass

Clamping insert Polyamide

Seal Buna-N

O-Ring Buna-N

Protection IP 68 – 10 bar (NEMA 6 – 150 PSIG)
within the specified clamping range


Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Advice:


- Other sealing material e.g. Silicone upon request



Metr.



Metr.-elongated





AG	$\varnothing$ mm	GL mm	H mm	 mm	Number	GL mm	Number elongated
M 12 x 1,5	4 – 7	6	20	14	1.618.1200.50	10	1.618.1200.30
M 12 x 1,5	2 – 5	6	20	14	1.618.1200.51	10	1.618.1200.31
M 16 x 1,5	6 – 10	6	25	19	1.618.1600.50	10	1.618.1600.30
M 16 x 1,5	3 – 7	6	25	19	1.618.1600.51	10	1.618.1600.31
M 20 x 1,5	8 – 13	6,5	26	24	1.618.2000.50	10	1.618.2000.30
M 20 x 1,5	7 – 10	6,5	26	24	1.618.2000.51	10	1.618.2000.31
M 25 x 1,5	11 – 17	7	29	29	1.618.2500.50	12	1.618.2500.30
M 25 x 1,5	8 – 13	7	29	29	1.618.2500.51	12	1.618.2500.31
M 32 x 1,5	11 – 21	8	37	34	1.618.3200.50	12	1.618.3200.30
M 32 x 1,5	10 – 15	8	37	34	1.618.3200.51	12	1.618.3200.31
M 40 x 1,5	19 – 28	8	40,5	44	1.618.4000.50	15	1.618.4000.30
M 40 x 1,5	15 – 23	8	40,5	44	1.618.4000.51	15	1.618.4000.31
M 50 x 1,5	27 – 35	9	49,5	55	1.618.5000.50	15	1.618.5000.30
M 50 x 1,5	22 – 29	9	49,5	55	1.618.5000.51	15	1.618.5000.31
M 63 x 1,5	34 – 48	10	49	68	1.618.6300.50	15	1.618.6300.30
M 63 x 1,5	28 – 39	10	49	68	1.618.6300.51	15	1.618.6300.31

METRICA-M-EMV-E


Metr.



Material	Nickel plated brass
Clamping insert	Polyamide
Seal	Buna-N
O-Ring	Buna-N
Protection	IP 68 – 10 bar (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F)



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number
M 12 x 1,5	3 – 6,5	6	19,4	14	1.607.1200.50
M 16 x 1,5	4,5 – 10	6	24,4	19	1.607.1600.50
M 20 x 1,5	6 – 12	6	25,4	22	1.607.2013.50
M 20 x 1,5	7,5 – 14	6	28,3	24	1.607.2000.50
M 25 x 1,5	9 – 17	7	29,3	29	1.607.2500.50
M 32 x 1,5	11 – 21	8	37,7	34	1.607.3200.50
M 40 x 1,5	19 – 28	8	40,7	44	1.607.4000.50
M 50 x 1,5	27 – 35	9	50,7	55	1.607.5000.50
M 63 x 1,5	34 – 48	10	55,7	68	1.607.6300.50



➔ Accessories see page 73

METRICA-M-EMV

Metr., Metr.-elongated



Material Nickel plated brass

Clamping insert Polyamide

Seal Buna-N


O-Ring Buna-N

Protection IP 68 – 10 bar (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Advice:

- Other sealing material e.g. Silicone upon request



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number	GL mm	Number elongated
M 12 x 1,5	4 – 7	6	20	14	1.683.1200.50	10	1.683.1200.30
M 12 x 1,5	2 – 5	6	20	14	1.683.1200.51	10	1.683.1200.31
M 16 x 1,5	6 – 10	6	25	19	1.683.1600.50	10	1.683.1600.30
M 16 x 1,5	3 – 7	6	25	19	1.683.1600.51	10	1.683.1600.31
M 20 x 1,5	8 – 13	6,5	26	24	1.683.2000.50	10	1.683.2000.30
M 20 x 1,5	7 – 10	6,5	26	24	1.683.2000.51	10	1.683.2000.31
M 25 x 1,5	11 – 17	7	29	29	1.683.2500.50	12	1.683.2500.30
M 25 x 1,5	8 – 13	7	29	29	1.683.2500.51	12	1.683.2500.31
M 32 x 1,5	11 – 21	8	37	34	1.683.3200.50	12	1.683.3200.30
M 32 x 1,5	10 – 15	8	37	34	1.683.3200.51	12	1.683.3200.31
M 40 x 1,5	19 – 28	8	40,5	44	1.683.4000.50	15	1.683.4000.30
M 40 x 1,5	15 – 23	8	40,5	44	1.683.4000.51	15	1.683.4000.31
M 50 x 1,5	27 – 35	9	49,5	55	1.683.5000.50	15	1.683.5000.30
M 50 x 1,5	22 – 29	9	49,5	55	1.683.5000.51	15	1.683.5000.31
M 63 x 1,5	34 – 48	10	49	68	1.683.6300.50	15	1.683.6300.30
M 63 x 1,5	28 – 39	10	49	68	1.683.6300.51	15	1.683.6300.31



➔ Accessories see page 73

Industrial cable glands

Miscellaneous cable glands

Cable glands in this chapter have different designs to the modern clamping finger cable glands. Some types are perfect for high temperature applications or provide special options for clamping ranges.



You can find in this chapter:

Miscellaneous cable glands

- WADI cable glands with various clamping and temperature ranges
- DIN 46320 cable glands made of plastic or nickel plated brass
- Z cable glands made of nickel plated brass. These glands meet the DIN 46320 standard made from nickel plated brass but with additional strain relief
- SE cable glands made of nickel plated brass. These glands meet the DIN 46320 standard and are made of nickel plated brass with additional EMC attenuation
- ZSE cable glands made of nickel plated brass. These glands meet the "Z standard" but with additional EMC attenuation

We provide variable clamping ranges and thread lengths.

For any further question please do not hesitate to contact us. We look forward to develop solutions together with you. You profit from our vast knowledge in development, engineering and production technology.

Contact us:

E-Mail: info.et@hummel.com

Tel.: +49 (0) 76 66/9 11 10-0

Miscellaneous cable glands

WADI-A

Metr.




Material Nickel plated brass

Seal ring Buna-N

O-Ring Buna-N

Protection IP 68 (NEMA 6)

Operating Temperature -20 °C – 100 °C (-4 °F – 212 °F)
short time exposure 130 °C (266 °F)



AG	Ø mm	GL mm	H mm	Ø mm	Number
M 12 x 1,5	4–6	5	16	14	1.106.1201.50
M 16 x 1,5	4–9	5	18	18	1.106.1601.50
M 20 x 1,5	7–13	6	22	22	1.106.2001.50
M 25 x 1,5	10–18	7	23	28	1.106.2501.50
M 32 x 1,5	20–24	8	26	35	1.106.3201.50
M 40 x 1,5	27–32	8	27	45	1.106.4001.50
M 50 x 1,5	35–40	10	28	55	1.106.5001.50
M 63 x 1,5	45–52	10	36	68	1.106.6301.50

Miscellaneous cable glands

WADI-A

PG

Material	Nickel plated brass
Seal ring	Buna-N
O-Ring	Buna-N
Protection	IP 68 (NEMA 6)
Operating Temperature	-20 °C – 100 °C (-4 °F – 212 °F) short time exposure 130 °C (266 °F)

AG	$\varnothing$ mm	GL mm	H mm	 mm	Number	$\varnothing$ mm	Number	$\varnothing$ mm	Number
PG 7	2 – 3	6	16	14	1.106.0701.01	4 – 6,5	1.106.0700.01	6,5 – 8	1.106.0702.01
PG 9	4 – 5	6	17	18	1.106.0904.01	5 – 7	1.106.0900.01	7 – 10	1.106.0902.01
PG 11	5 – 7	6	20	18	1.106.1101.01	7 – 10	1.106.1103.01	8 – 12	1.106.1100.01
PG 13,5	7 – 10	6	21	24	1.106.1303.01	9 – 12	1.106.1300.01	11 – 15	1.106.1304.01
PG 16	7 – 10	6	21	24	1.106.1603.01	9 – 12	1.106.1600.01	11 – 15	1.106.1604.01
PG 21	14 – 17	7,5	22,5	32	1.106.2102.01	16 – 20,5	1.106.2103.01	19 – 22	1.106.2101.01
PG 29	19 – 22,5	8	24	40	1.106.2901.01	20 – 27	1.106.2902.01		
PG 29	22 – 28	8	24	40	1.106.2903.01	26 – 32	1.106.2904.01		

Accessories see page 73

WADI-A two piece sealing insert

PG

RoHS

Material Nickel plated brass

Seal ring Buna-N (multi-perforated)

O-Ring Buna-N

Protection IP 68 (NEMA 6)

Operating Temperature -20 °C – 100 °C (-4 °F – 212 °F)
short time exposure 130 °C (266 °F)

AG	$\varnothing$ mm	GL mm	H mm	 mm	Number
PG 11	5 – 12	6	18	20	1.106.1104.01
PG 13,5	8 – 15	6	21	24	1.106.1301.01
PG 16	8 – 15	6	21	24	1.106.1601.01
PG 21	11 – 20,5	7,5	22,5	32	1.106.2100.01
PG 29	18 – 27	8	24	40	1.106.2900.01
PG 36	25 – 35	8	29	50	1.106.3600.01
PG 42	35 – 45	10	31	60	1.106.4200.01
PG 48	38 – 49	11	33	64	1.106.4800.01

 Accessories see page 73


Miscellaneous cable glands

WADI-A-FPM

Metr.



Material	Nickel plated brass
Seal ring	FPM
O-Ring	FPM
Protection	IP 68 (NEMA 6)
Operating Temperature	-25 °C – 200 °C (-13 °F – 392 °F)



AG	mm	GL	H	mm	Number
M 12 x 1,5	4-6	5	18	14	1.106.1200.58
M 16 x 1,5	7-9	5	19	18	1.106.1600.58
M 20 x 1,5	10-13	6	21	22	1.106.2000.58
M 25 x 1,5	15-18	7	23	28	1.106.2500.58
M 32 x 1,5	20-24	8	26	35	1.106.3200.58
M 40 x 1,5	27-32	8	27	45	1.106.4000.58
M 50 x 1,5	35-40	10	28	55	1.106.5000.58
M 63 x 1,5	45-52	10	36	68	1.106.6300.58


Accessories see page 73

WADI-A-FPM two piece sealing insert

Metr.



Material	Nickel plated brass
Seal ring	FPM (multi-perforated)
O-Ring	FPM
Protection	IP 68 (NEMA 6)
Operating Temperature	-25 °C – 200 °C (-13 °F – 392 °F)



AG	mm	GL	H	mm	Number
M 16 x 1,5	4-9	5	19	18	1.106.1601.58
M 20 x 1,5	7-13	6	21	22	1.106.2001.58
M 25 x 1,5	10-18	7	23	28	1.106.2501.58
M 32 x 1,5	16-24	8	26	35	1.106.3201.58
M 40 x 1,5	22-32	8	27	45	1.106.4001.58
M 50 x 1,5	30-40	10	28	55	1.106.5001.58
M 63 x 1,5	38-52	10	36	68	1.106.6301.58

Accessories see page 73


Miscellaneous cable glands

WADI-A-FPM

PG

RoHS





Material

Nickel plated brass

Seal ring

FPM

O-Ring

FPM

Protection

IP 68 (NEMA 6)

Operating Temperature

-25 °C – 200 °C (-13 °F – 392 °F)



AG	 mm	GL mm	H mm	 mm	Number
PG 7	5–7	6	16	14	1.106.0700.80
PG 9	6–8	6	17	18	1.106.0900.80
PG 9	7–10	6	17	18	1.106.0901.80
PG 11	6–8	6	20	18	1.106.1100.80
PG 11	7–10	6	20	18	1.106.1101.80
PG 11	8–12	6	20	18	1.106.1102.80
PG 13,5	11–15	6	21	24	1.106.1300.80
PG 16	11–15	6	21	24	1.106.1600.80
PG 21	15–20,5	7,5	22,5	32	1.106.2100.80
PG 29	20–27	8	24	40	1.106.2900.80
PG 36	30–35	8	29	50	1.106.3600.80
PG 42	40–45	10	31	60	1.106.4200.80
PG 48	42–49	11	33	64	1.106.4800.80

WADI-A-FPM two piece sealing insert

PG

RoHS

Material Nickel plated brass

Seal ring FPM (multi-perforated)

O-Ring FPM

Protection IP 68 (NEMA 6)

Operating Temperature -25 °C – 200 °C (-13 °F – 392 °F)

AG

mm

GL
mm

H
mm

mm

Number

PG 11	5–12	6	20	18	1.106.1103.80
PG 13,5	8–15	6	21	24	1.106.1301.80
PG 16	8–15	6	21	24	1.106.1601.80
PG 21	11–20,5	7,5	22,5	32	1.106.2101.80
PG 29	18–27	8	24	40	1.106.2901.80
PG 36	25–35	8	29	50	1.106.3601.80
PG 42	35–45	10	30	60	1.106.4201.80
PG 48	38–49	11	33	64	1.106.4801.80

Accessories see page 73

➔ Accessories see page 73

Miscellaneous cable glands

DIN 46320-A-FS with Seal ring No. 6

PG

Material Styrene Butadiene / Polyamide

Seal ring Soft rubber / Buna-N


Protection IP 54,
with thread seal ring IP 65

Operating Temperature -20 °C – 60 °C (-4 °F – 140 °F) (Soft rubber)
-20 °C – 80 °C (-4 °F – 176 °F) (Buna-N)

Colors grey (RAL 7035)

Advice:

- Metric thread on request
- Please see page 89 for suitable thread seal ring



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number SB / Soft rubber -20 °C – 60 °C -4 °F – 140 °F	Number PA / Buna-N -20 °C – 80 °C -4 °F – 176 °F
PG 7	3,5–6	8	20	15 / 13	1.201.0700.10	1.202.0700.11
PG 9	4,5–7	8	21	19 / 16	1.201.0900.10	1.202.0900.11
PG 11	6–9	8	22	22 / 19	1.201.1100.10	1.202.1100.11
PG 13,5	9–12	9	26	24 / 21	1.201.1300.10	1.202.1300.11
PG 16	11–14	10	28	27 / 23	1.201.1600.10	1.202.1600.11
PG 21	14–18	11	32	33 / 30	1.201.2100.10	1.202.2100.11
PG 29	18–25	11	35	42 / 40	1.201.2900.10	1.202.2900.11
PG 36	25–32	13	39	53 / 50	1.201.3600.10	1.202.3600.11
PG 42	30–38	13	44	60 / 55	1.201.4200.10	1.202.4200.11
PG 48	34–42	14	44	65 / 60	1.201.4800.10	1.202.4800.11

➔ Accessories see page 73

DIN 46320-A-FS with multiperforated seal ring No. 7

PG

Material Styrene Butadiene / Polyamide

Seal ring Soft rubber / Buna-N (multiperforated)


Protection IP 54,
with thread seal ring IP 65

Operating Temperature -20 °C – 60 °C (-4 °F – 140 °F) (Soft rubber)
-20 °C – 80 °C (-4 °F – 176 °F) (Buna-N)

Colors grey (RAL 7035)

Advice:

- Metric thread on request
- Please see page 89 for suitable thread seal ring



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number SB / Soft rubber -20 °C – 60 °C -4 °F – 140 °F	Number PA / Buna-N -20 °C – 80 °C -4 °F – 176 °F
PG 9	4–10	8	21	19 / 16	1.201.0902.10	1.202.0901.11
PG 11	6,5–12	8	22	22 / 19	1.201.1102.10	1.202.1101.11
PG 13,5	6,5–13,5	9	26	24 / 21	1.201.1302.10	1.202.1301.11
PG 16	6,5–16	10	28	27 / 23	1.201.1602.10	1.202.1601.11
PG 21	9–20	11	32	33 / 30	1.201.2102.10	1.202.2101.11
PG 29	17–28	11	35	42 / 40	1.201.2902.10	1.202.2901.11
PG 36	23–34	13	39	53 / 50	1.201.3602.10	1.202.3601.11
PG 42	29–40	13	44	60 / 55	1.201.4202.10	1.202.4201.11
PG 48	35–46	14	44	65 / 60	1.201.4802.10	1.202.4801.11

➔ Accessories see page 73

Miscellaneous cable glands

DIN 46320-C4-Ms with Seal ring No. 6

PG

RoHS



Material Nickel plated brass

Seal ring Soft rubber / Buna-N

Protection IP 54,
with thread seal ring IP 65


Operating Temperature -20 °C – 60 °C (-4 °F – 140 °F) (Soft rubber)
-20 °C – 80 °C (-4 °F – 176 °F) (Buna-N)

Advice:

- Metric thread on request
- Please see page 89 for suitable thread seal ring



- This cable gland is available with additional strain relief (see page 71) and EMC attenuation (see page 72)



AG	mm	GL mm	H mm	mm	Number Soft rubber -20 °C – 60 °C -4 °F – 140 °F	Number Buna-N -20 °C – 80 °C -4 °F – 176 °F
PG 7	6–8	5	15	14/13	1.101.0700.01	1.101.0703.01
PG 9	8–10	6	15	17/15	1.101.0900.01	1.101.0903.01
PG 11	10–12	6	17	20/18	1.101.1100.01	1.101.1103.01
PG 13,5	12–14	6,5	20	22/20	1.101.1300.01	1.101.1303.01
PG 16	14–16	6,5	22	24/22	1.101.1600.01	1.101.1603.01
PG 21	17–19	7	24	30/28	1.101.2100.01	1.101.2103.01
PG 29	26–28	8	26	40/37	1.101.2900.01	1.101.2903.01
PG 36	33–35	9	30	50/47	1.101.3600.01	1.101.3603.01
PG 42	39–41	10	34	57/54	1.101.4200.01	1.101.4203.01
PG 48	45–47	10	37	64/60	1.101.4800.01	1.101.4803.01

➔ Accessories see page 73

DIN 46320-C4-Ms with multiperforated seal ring No. 7

PG

RoHS



Material Nickel plated brass

Seal ring Buna-N (multiperforated)

Protection IP 54,
with thread seal ring IP 65


Operating Temperature -20 °C – 80 °C (-4 °F – 176 °F)

Advice:

- Metric thread on request
- Please see page 89 for suitable thread seal ring



- This cable gland is available with additional strain relief (see page 71) and EMC attenuation (see page 72)



AG	mm	GL mm	H mm	mm	Number
PG 9	4–10	6	15	17/15	1.101.0901.01
PG 11	6,5–12	6	17	20/18	1.101.1101.01
PG 13,5	6,5–13,5	6,5	20	22/20	1.101.1301.01
PG 16	6,5–16	6,5	22	24/22	1.101.1601.01
PG 21	9–20	7	24	30/28	1.101.2101.01
PG 29	17–28	8	26	40/37	1.101.2901.01
PG 36	23–34	9	30	50/47	1.101.3601.01
PG 42	29–40	10	34	57/54	1.101.4201.01
PG 48	35–46	10	37	64/60	1.101.4801.01

➔ Accessories see page 73

Miscellaneous cable glands

Z (DIN 46320-C4-Ms with Seal ring No. 6 with additional strain relief)


Metr.



Material Nickel plated brass

Seal ring Soft rubber / Buna-N

Protection IP 54,
with thread seal ring IP 65

Operating Temperature -20 °C – 60 °C (-4 °F – 140 °F) (Soft rubber)
-20 °C – 80 °C (-4 °F – 176 °F) (Buna-N)


Advice:

- Please see page 89 for suitable thread seal ring

AG	$\varnothing$ mm	GL mm	H mm	 mm	Number Soft rubber -20 °C – 60 °C -4 °F – 160 °F	Number Buna-N -20 °C – 80 °C -4 °F – 176 °F
M 12 x 1,5	6–8	5	22	14 / 16	1.105.1200.50	1.105.1200.51
M 16 x 1,5	8–10	5	25	18 / 19	1.105.1600.50	1.105.1600.51
M 20 x 1,5	10–12	6	26	22 / 22	1.105.2000.50	1.105.2000.51
M 20 x 1,5	12–14	6	27,5	22 / 24	1.105.2013.50	1.105.2013.51
M 20 x 1,5	13–15	6	28,5	24 / 26	1.105.2016.50	1.105.2016.51
M 25 x 1,5	17–19	6	33	30 / 33	1.105.2500.50	1.105.2500.51
M 32 x 1,5	26–27	6	36	39 / 42	1.105.3200.50	1.105.3200.51
M 40 x 1,5	33–35	7	41	50 / 52	1.105.4000.50	1.105.4000.51
M 50 x 1,5	39–41	8	45	57 / 59	1.105.5000.50	1.105.5000.51
M 63 x 1,5	43–45	9	48	66 / 64	1.105.6300.50	1.105.6300.51

➔ Accessories see page 73

Z (DIN 46320-C4-Ms with multiperforated seal ring No. 7 with additional strain relief)

Metr.




Material Nickel plated brass

Seal ring Buna-N (multiperforated)

Protection IP 54,
with thread seal ring IP 65

Operating Temperature -20 °C – 80 °C (-4 °F – 176 °F)



Advice:

- Please see page 89 for suitable thread seal ring

AG	$\varnothing$ mm	GL mm	H mm	 mm	Number
M 16 x 1,5	6,5–10	5	25	18 / 19	1.105.1600.52
M 20 x 1,5	7,5–12	6	26	22 / 22	1.105.2000.52
M 20 x 1,5	8,5–13,5	6	27,5	22 / 24	1.105.2013.52
M 20 x 1,5	10,5–15	6	28,5	24 / 26	1.105.2016.52
M 25 x 1,5	13–20	6	33	30 / 33	1.105.2500.52
M 32 x 1,5	19–28	6	36	39 / 42	1.105.3200.52
M 40 x 1,5	24–34	7	41	50 / 52	1.105.4000.52
M 50 x 1,5	34–40	8	45	57 / 59	1.105.5000.52
M 63 x 1,5	39–46	9	48	66 / 64	1.105.6300.52

➔ Accessories see page 73

Miscellaneous cable glands

Z (DIN 46320-C4-Ms with Seal ring No. 6 with additional strain relief)

PG

RoHS



Material Nickel plated brass

Seal ring Soft rubber / Buna-N


Protection IP 54,
with thread seal ring IP 65

Operating Temperature -20 °C – 60 °C (-4 °F – 140 °F) (Soft rubber)
-20 °C – 80 °C (-4 °F – 176 °F) (Buna-N)



Advice:

- Please see page 89 for suitable thread seal ring
- Please see page 72 for the EMC version of this gland



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number Soft rubber -20 °C – 60 °C -4 °F – 140 °F	Number Buna-N -20 °C – 80 °C -4 °F – 176 °F
PG 7	6–8	5	22	14 / 16	1.105.0700.01	1.105.0703.01
PG 9	8–10	6	25	17 / 19	1.105.0900.01	1.105.0903.01
PG 11	10–12	6	26	20 / 22	1.105.1100.01	1.105.1103.01
PG 13,5	12–14	6,5	27,5	22 / 24	1.105.1300.01	1.105.1303.01
PG 16	14–16	6,5	28,5	24 / 26	1.105.1600.01	1.105.1603.01
PG 21	17–19	7	33	30 / 33	1.105.2100.01	1.105.2103.01
PG 29	26–28	8	36	40 / 42	1.105.2900.01	1.105.2903.01
PG 36	33–35	9	41	50 / 52	1.105.3600.01	1.105.3603.01
PG 42	39–41	10	45	57 / 59	1.105.4200.01	1.105.4203.01
PG 48	43–45	10	48	64 / 64	1.105.4800.01	1.105.4803.01

➔ Accessories see page 73

Z (DIN 46320-C4-Ms with multiperforated seal ring No. 7 with additional strain relief)

PG

RoHS



Material Nickel plated brass

Seal ring Buna-N (multiperforated)


Protection IP 54,
with thread seal ring IP 65

Operating Temperature -20 °C – 80 °C (-4 °F – 176 °F)



Advice:

- Please see page 89 for suitable thread seal ring
- Please see page 72 for the EMC version of this gland



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number
PG 9	6,5–10	6	25	17 / 19	1.105.0901.01
PG 11	7,5–12	6	26	20 / 22	1.105.1101.01
PG 13,5	8,5–13,5	6,5	27,5	22 / 24	1.105.1301.01
PG 16	10,5–16	6,5	28,5	24 / 26	1.105.1601.01
PG 21	13–20	7	33	30 / 33	1.105.2101.01
PG 29	19–28	8	36	40 / 42	1.105.2901.01
PG 36	24–34	9	41	50 / 52	1.105.3601.01
PG 42	34–40	10	45	57 / 59	1.105.4201.01
PG 48	39–46	10	48	64 / 64	1.105.4801.01

➔ Accessories see page 73

Miscellaneous cable glands


SE (DIN 46320-C4-Ms with EMC attenuation)

PG


Material	Nickel plated brass
Seal ring	Buna-N
Protection	IP 54, with thread seal ring IP 65
Operating Temperature	-20 °C – 80 °C (-4 °F – 176 °F)


RoHS
Advice:

- Please see page 89 for suitable thread seal ring



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	E mm	Number
PG 9	4–10	7	17	17/15	6	1.680.0906.01
PG 11	6,5–12	7	20	20/18	8	1.680.1108.01
PG 13,5	6,5–13,5	8	21	22/20	10	1.680.1310.01
PG 13,5	6,5–13,5	8	21	22/20	12	1.680.1312.01
PG 16	6,5–16	8	24	24/22	12	1.680.1612.01
PG 16	6,5–16	8	24	24/22	14	1.680.1614.01
PG 21	9–20	10	27	30/28	15	1.680.2115.01
PG 21	9–20	10	27	30/28	18	1.680.2118.01
PG 29	17–28	10	30	40/37	20	1.680.2920.01
PG 29	17–28	10	30	40/37	24	1.680.2924.01

➔ Accessories see page 73


ZSE (DIN 46320-C4-Ms with EMC attenuation with additional strain relief)

PG


Material	Nickel plated brass
Seal ring	Buna-N
Protection	IP 54, with thread seal ring IP 65
Operating Temperature	-20 °C – 80 °C (-4 °F – 176 °F)


RoHS
Advice:

- Please see page 89 for suitable thread seal ring




AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	E mm	Number
PG 9	6,5–10	7	27	17 / 19	6	1.681.0906.01
PG 11	7,5–12	7	29	20 / 22	7	1.681.1107.01
PG 11	7,5–12	7	29	20 / 22	8	1.681.1108.01
PG 13,5	8,5–13,5	8	30	22 / 24	10	1.681.1310.01
PG 13,5	8,5–13,5	8	30	22 / 24	12	1.681.1312.01
PG 16	10,5–16	8	31	24 / 26	12	1.681.1612.01
PG 16	10,5–16	8	31	24 / 26	14	1.681.1614.01
PG 21	13–20	10	36	30 / 33	15	1.681.2115.01
PG 21	13–20	10	36	30 / 33	18	1.681.2118.01
PG 29	19–28	10	40	40 / 42	20	1.681.2920.01
PG 29	19–28	10	40	40 / 42	24	1.681.2924.01

➔ Accessories see page 73

Industrial cable glands

Accessories



You can find in this chapter accessories for all series of our industrial cable glands:

- Accessories made of plastic from page 74
- Accessories made of nickel plated brass from page 90
- Accessories made of stainless steel from page 99

For any further question please do not hesitate to contact us. We look forward to develop solutions together with you. You profit from our vast knowledge in development, engineering and production technology.

Contact us:

E-Mail: info.et@hummel.com

Tel.: +49 (0) 76 66/9 11 10-0

GM-FS

Metr., PG, NPT




Material	Polyamide V0 according to UL 94
-----------------	---------------------------------

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)


Colors grey (RAL 7035), black (RAL 9005)

Advice:
- Other colors upon request

[illegible]

V-N-FS

Metr.



Material Polyamide

Protection IP 54

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005)




Advice:
- Other colors upon request

AG	GL mm	H mm	D mm	Number PA grey	Number PA black
M 12 x 1,5	6	10	15	1.251.1200.50	1.251.1201.50
M 16 x 1,5	7	11,5	20	1.251.1600.50	1.251.1601.50
M 20 x 1,5	6	9,5	25	1.251.2000.50	1.251.2001.50
M 25 x 1,5	11	15,5	30	1.251.2500.50	1.251.2501.50
M 32 x 1,5	11	16	38	1.251.3200.50	1.251.3201.50
M 40 x 1,5	13	18	46	1.251.4000.50	1.251.4001.50
M 50 x 1,5	13	18,5	56	1.251.5000.50	1.251.5001.50
M 63 x 1,5	15	19	69	1.251.6300.50	1.251.6301.50

V-N-FS

PG



Material Polyamide

Protection IP 54

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005)



Advice:
- Other colors upon request

AG	GL mm	H mm	D mm	Number PA grey	Number PA black
PG 7	6	8	15	1.251.0700.11	1.251.0701.11
PG 9	6	9	19	1.251.0900.11	1.251.0901.11
PG 11	6	9	22	1.251.1100.11	1.251.1101.11
PG 13,5	6	9,5	25	1.251.1300.11	1.251.1301.11
PG 16	6	9,5	27	1.251.1600.11	1.251.1601.11
PG 21	8	11	33	1.251.2100.11	1.251.2101.11
PG 29	8	12	44	1.251.2900.11	1.251.2901.11
PG 36	10	15	55	1.251.3600.11	1.251.3601.11
PG 42	10	16	62	1.251.4200.11	1.251.4201.11
PG 48	12	16	69	1.251.4800.11	1.251.4801.11

V-NE / V-NE-SD

Metr.



Advice:

- Other colors upon request
- Please find more O-Rings on page 88


Material Polyamide, fiber reinforced

Operating Temperature -20 °C – 80 °C (-4 °F – 176 °F)

O-Ring Buna-N

Colors black (RAL 9005)

Protection IP 54 (V-NE)
IP 68 – 10 bar / IP 69K (V-NE-SD)



AG	GL mm	H mm	D mm	 mm	 mm	Number V-NE without O-Ring	Number V-NE-SD
M 12 x 1,5	8,5	13	16,5	15	6	1.255.1201.50	1.256.1201.50
M 16 x 1,5	8,5	13	20,5	19	8	1.255.1601.50	1.256.1601.50
M 20 x 1,5	9	14,5	25,5	24	8	1.255.2001.50	1.256.2001.50
M 25 x 1,5	10,5	16	30,5	28	8	1.255.2501.50	1.256.2501.50
M 32 x 1,5	11,5	17,5	38	36	8	1.255.3201.50	1.256.3201.50
M 40 x 1,5	11,5	18	48	46	8	1.255.4001.50	1.256.4001.50
M 50 x 1,5	13,5	20	60	55	8	1.255.5001.50	1.256.5001.50
M 63 x 1,5	14,5	21	75	70	8	1.255.6301.50	1.256.6301.50

V-NE / V-NE-SD

PG



Advice:

- Other colors upon request
- Please find more O-Rings on page 88


Material Polyamide, fiber reinforced

Operating Temperature -20 °C – 80 °C (-4 °F – 176 °F)

O-Ring Buna-N

Colors black (RAL 9005)

Protection IP 54 (V-NE)
IP 68 – 10 bar / IP 69K (V-NE-SD)



AG	GL mm	H mm	D mm	 mm	 mm	Number V-NE without O-Ring	Number V-NE-SD
PG 7	8,5	13	16,5	15	6	1.255.0701.11	1.256.0701.11
PG 9	8,5	13	20,5	19	8	1.255.0901.11	1.256.0901.11
PG 11	9	14,5	25,5	24	8	1.255.1101.11	1.256.1101.11
PG 13,5	9	14,5	25,5	24	8	1.255.1301.11	1.256.1301.11
PG 16	10,5	16	30,5	28	8	1.255.1601.11	1.256.1601.11
PG 21	11,5	17,5	38	36	8	1.255.2101.11	1.256.2101.11
PG 29	11,5	18	48	46	8	1.255.2901.11	1.256.2901.11
PG 36	13,5	20	60	55	8	1.255.3601.11	1.256.3601.11
PG 42	13,5	20	65	60	8	1.255.4201.11	1.256.4201.11
PG 48	14,5	21	75	70	8	1.255.4801.11	1.256.4801.11

HSK-V

Metr., PG, NPT




Material Polyamide

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors black (RAL 9005)



RoHS



Fits the following sizes			D mm	d mm	L mm	Number
PG 7	M 12 x 1,5		6	4,5	15	1.280.0007.00
PG 9	M 16 x 1,5	NPT 3/8"	7,5	5,5	17	1.280.0009.00
PG 11	M 16 x 1,5 / 11		9,5	6,5	19	1.280.0011.00
PG 13,5	M 20 x 1,5	NPT 1/2"	11,5	8,5	19	1.280.0013.00
PG 16	M 20 x 1,5 / 16	NPT 1/2" (16)	13,5	11,5	19,5	1.280.0016.00
PG 21	M 25 x 1,5	NPT 3/4"	17,5	15,5	23,5	1.280.0021.00
PG 29	M 32 x 1,5	NPT 1" NPT 1 1/4"	24	19	26	1.280.0029.00
PG 36	M 40 x 1,5	NPT 1 1/2"	31	25	28	1.280.0036.00
PG 42	M 50 x 1,5		37	30	28	1.280.0042.00
PG 48	M 63 x 1,5		43	34	28	1.280.0048.00

R-FS

Metr., PG




Material Styrene Butadiene / Polyamide

Operating Temperature -20 °C – 70 °C (-4 °F – 156 °F) (Styrene Butadiene)
-40 °C – 80 °C (-40 °F – 176 °F) (Polyamide)


Colors grey (RAL 7035)




Type A



Type B



Type C



AG	IG	GL mm	H mm	D mm	 mm	Type	Number SB	Number PA
M 16 x 1,5	M 12 x 1,5	9	16	24	22	A		1.272.1612.50
M 20 x 1,5	M 16 x 1,5	9	16	27	24	A		1.272.2016.50
M 25 x 1,5	M 20 x 1,5	10	17	32	29	A		1.272.2520.50
M 32 x 1,5	M 25 x 1,5	12	19	40	36	A		1.272.3225.50
M 40 x 1,5	M 32 x 1,5	12	19	51	46	A		1.272.4032.50
M 50 x 1,5	M 40 x 1,5	14	21	61	55	A		1.272.5040.50
M 63 x 1,5	M 50 x 1,5	15	22	75	65	A		1.272.6350.50
PG 13,5	PG 9	8	12	27		B	1.271.1309.10	1.272.1309.11
PG 16	PG 9	10	13	29		B	1.271.1609.10	1.272.1609.11
PG 16	PG 11	10	13	29		B	1.271.1611.10	1.272.1611.11
PG 21	PG 13,5	11	13,5	36		B	1.271.2113.10	1.272.2113.11
PG 21	PG 16	11	13,5	36		B	1.271.2116.10	1.272.2116.11
PG 29	PG 21	11	13,5	46		B	1.271.2921.10	1.272.2921.11
PG 36	PG 29	11	15	58		B	1.271.3629.10	1.272.3629.11
Reducing intermediate connector								
PG 9	PG 7	8	14	19	15	C	1.235.0907.10	1.236.0907.11
PG 11	PG 9	8	18	22,5	19	C	1.235.1109.10	1.236.1109.11
PG 13,5	PG 11	9	21	25,5	22	C	1.235.1311.10	1.236.1311.11
PG 16	PG 13,5	10	25	28,5	24	C	1.235.1613.10	1.236.1613.11

R-M-PA


Metr., PG




Material	Polyamide (Type A/Type B), Polypropylene (Type C)
Operating Temperature	-20 °C – 80 °C (-4 °F – 176 °F)
Colors	black (RAL 9005)




Type A



Type B



Type C



AG	IG	Type	GL mm	H mm	d mm	 mm	Number
M 16 x 1,5	M 12 x 1,5	B	8	6	10	20	1.273.1612.50
M 20 x 1,5	M 16 x 1,5	B	8	6	13,5	25	1.273.2016.50
M 25 x 1,5	M 20 x 1,5	B	8	6	18	29	1.273.2520.50
M 32 x 1,5	M 25 x 1,5	B	10	6	23	36	1.273.3225.50
M 40 x 1,5	M 32 x 1,5	C	15	5	30		1.273.4032.50
M 50 x 1,5	M 40 x 1,5	C	15	5	38		1.273.5040.50
M 63 x 1,5	M 50 x 1,5	C	15	5	48		1.273.6350.50
M 25 x 1,5	PG 13,5	B	8	6	18	29	1.273.2513.50
M 25 x 1,5	PG 16	A	8	14	18	29	1.273.2516.50
M 32 x 1,5	PG 21	A	10	15	25	36	1.273.3221.50
M 40 x 1,5	PG 29	A	10	15	33	45	1.273.4029.50
M 50 x 1,5	PG 36	A	12	17	43	55	1.273.5036.50
M 63 x 1,5	PG 42	C	15	5	52		1.273.6342.50
PG 9	M 12 x 1,5	C	15	19	8,5		1.273.0912.11
PG 11	M 16 x 1,5	C	15	19	11,5		1.273.1116.11
PG 13,5	M 16 x 1,5	B	8	6	14	25	1.273.1316.11
PG 16	M 20 x 1,5	A	8	13	16	27	1.273.1620.11
PG 21	M 25 x 1,5	C	15	19	20,5		1.273.2125.11
PG 29	M 32 x 1,5	C	15	19	28		1.273.2932.11
PG 36	M 40 x 1,5	C	15	5	38		1.273.3640.11
PG 42	M 40 x 1,5	C	15	5	38		1.273.4240.11
PG 48	M 50 x 1,5	C	15	5	38		1.273.4850.11

E-M-PA, K-FS


Metr., PG




Material	Polyamide (Type A/Type B), Polypropylene (Type C)
Operating Temperature	-20 °C – 80 °C (-4 °F – 176 °F)
Colors	K-FS grey (RAL 7035), E-M-PA black (RAL 9005)




Type A



Type B



Type C




AG	IG	Type	GL mm	H mm	d mm	mm	Number
M 12 x 1,5	M 16 x 1,5	A	8	12	6,5	21	1.239.1216.50
M 16 x 1,5	M 20 x 1,5	A	8	13	9	25	1.239.1620.50
M 20 x 1,5	M 25 x 1,5	A	8	15	14	30	1.239.2025.50
M 25 x 1,5	M 32 x 1,5	C	15	15	16,5		1.239.2532.50
M 32 x 1,5	M 40 x 1,5	C	15	19,5	23		1.239.3240.50
M 40 x 1,5	M 50 x 1,5	C	15	19,5	30		1.239.4050.50
M 50 x 1,5	M 63 x 1,5	C	15	20	39		1.239.5063.50
M 12 x 1,5	PG 7	A	8	12	6,5	17	1.239.1207.50
M 16 x 1,5	PG 9	C	1	19	8,5		1.239.1609.50
M 20 x 1,5	PG 13,5	A	8	13	14	25	1.239.2013.50
M 63 x 1,5	PG 48	C	15	20	51		1.239.6348.50
PG 7	M 12 x 1,5	C	15	19	6		1.239.0712.11
PG 9	M 16 x 1,5	A	8	12	9	21	1.239.0916.11
PG 11	M 20 x 1,5	C	15	19	11,5		1.239.1120.11
PG 13,5	M 20 x 1,5	A	8	13	14	25	1.239.1320.11
PG 16	M 25 x 1,5	A	8	15	16	30	1.239.1625.11
PG 21	M 32 x 1,5	A	8	15	21	37	1.239.2132.11
PG 29	M 40 x 1,5	A	10	17	30	45	1.239.2940.11
PG 36	M 50 x 1,5	C	15	19,5	37		1.239.3650.11
PG 42	M 50 x 1,5	C	15	19,5	43		1.239.4250.11
PG 48	M 63 x 1,5	C	15	20	48		1.239.4863.11
PG 11	PG 13,5	B	8	15	12,5	24	1.233.1113.11
PG 13,5	PG 16	B	9	16	15	27	1.233.1316.11
PG 16	PG 21	B	10	19	16	32	1.233.1621.11
PG 21	PG 29	B	11	21	22,5	42	1.233.2129.11

90° Snap Elbow

Metr., PG, NPT



Material	Polyamide
O-Ring	Buna-N
Protection	IP 68 (NEMA 6)
Operating Temperature	-20 °C – 80 °C (-4 °F – 176 °F)
Colors	grey (RAL 7035), black (RAL 9005)




AG	IG	GL mm	H mm	L mm	R mm		Number grey	Number black
M 16x1,5	M 16x1,5	8	23	28,5	5	19	1.316.1600.50	1.316.1601.50
M 20x1,5	M 20x1,5	9	30,5	35	7	24	1.316.2000.50	1.316.2001.50
M 25x1,5	M 25x1,5	11	40	49	10	33	1.316.2500.50	1.316.2501.50
PG 9	M 16x1,5	8	23	28,5	5	19	1.316.0900.11	1.316.0901.11
PG 13,5	M 20x1,5	9	30,5	35	7	24	1.316.1300.11	1.316.1301.11
PG 21	M 25x1,5	11	40	49	10	33	1.316.2100.11	1.316.2101.11
M 16x1,5	PG 9	8	23	28,5	5	19	1.315.1600.50	1.315.1601.50
M 20x1,5	PG 13,5	9	30,5	35	7	24	1.315.2000.50	1.315.2001.50
M 25x1,5	PG 21	11	40	49	10	33	1.315.2500.50	1.315.2501.50
M 32x1,5	PG 29	11	51,5	60	14	42	1.315.3200.50	1.315.3201.50
PG 9	PG 9	8	23	28,5	5	19	1.315.0900.11	1.315.0901.11
PG 11	PG 11	8	27	31,5	6	22	1.315.1100.11	1.315.1101.11
PG 13,5	PG 13,5	9	30,5	35	7	24	1.315.1300.11	1.315.1301.11
PG 16	PG 16	10	32,5	37,5	8	27	1.315.1600.11	1.315.1601.11
PG 21	PG 21	11	40	49	10	33	1.315.2100.11	1.315.2101.11
PG 29	PG 29	11	51,5	60	14	42	1.315.2900.11	1.315.2901.11
NPT 3/8"	PG 9	15	23	28,5	5	19	1.315.3800.70	1.315.3801.70
NPT 1/2"	PG 13,5	13	30,5	35	7	24	1.315.1200.70	1.315.1201.70
NPT 3/4"	PG 21	13	40	49	10	33	1.315.3400.70	1.315.3401.70
NPT 1"	PG 29	19	51,5	60	14	42	1.315.1000.70	1.315.1001.70

KF-G

Metr., PG




Material	Polyamide
Dichtung	Buna-N
Protection	IP 54
Operating Temperature	-40 °C – 110 °C (-40 °F – 230 °F)
Colors	grey (RAL 7011), black (RAL 9005)



Size	Flange	Ø mm	A mm	B mm	C mm	D mm	F mm	H mm	Number grey	Number black
M 16x1,5	1	4,3	49	47	37	15,5	29	35	1.312.1600.50	1.312.1601.50
M 20x1,5	1	4,5	49	47	37	15,5	29	35	1.312.2000.50	1.312.2001.50
M 25x1,5	1	6,0	69	65	51,5	21,5	41,5	44	1.312.2500.50	1.312.2501.50
M 32x1,5	2	6,5	90	78	64,5	9,5	64,5	55	1.312.3200.50	1.312.3201.50
M 40x1,5	2	6,5	99	94	79,5	10,5	79,5	66	1.312.4000.50	1.312.4001.50
M 50x1,5	2	6,5	116	101	87,5	12,5	87,5	76	1.312.5000.50	1.312.5001.50
PG 11	1	4,3	49	47	37	15,5	29	35	1.312.1100.11	1.312.1101.11
PG 16	1	4,3	49	47	37	15,5	29	35	1.312.1600.11	1.312.1601.11
PG 21	1	6,0	69	65	51,5	21,5	41,5	44	1.312.2100.11	1.312.2101.11
PG 29	2	6,5	90	78	64,5	9,5	64,5	55	1.312.2900.11	1.312.2901.11
PG 36	2	6,5	99	94	79,5	10,5	79,5	66	1.312.3600.11	1.312.3601.11
PG 48	2	6,5	116	101	87,5	12,5	87,5	76	1.312.4800.11	1.312.4801.11

PG

A 3D rendering of a grey, square-shaped metal bracket. The bracket has a central circular hole with internal threading. It features a flat base with four small circular mounting holes, one at each corner. The top surface is slightly recessed, and the sides are vertical. The object is shown against a light blue background.

Dimensions and specifications may be changed without prior notice

HSK-ME

Metr., PG, NPT



Material Elastomer




Operating Temperature -40°C – 100°C (-40°F – 212°F)

Advice:

- Installation instruction see page 176
- Other materials available upon request

! - The inserts are exclusively capable for the glands of the HSK series



Fits the following sizes		Number of Holes x d	Number	Number of Holes x d	Number	Number without holes
PG 7 / KR PG 9		1,5*	1.089.0712.19			1.089.0799.19
PG 9 / KE PG 7 / KR PG 11	M 16 x 1,5 NPT 3/8"	4 x 1,4	1.089.0900.19	2 x 3	1.089.0901.19	1.089.0999.19
		5 x 1,6	1.089.0902.19	10 x 1,4	1.089.0904.19	
		4 x 2,3	1.089.0908.19	1 x 2,2*	1.089.0916.19	
PG 11 / KE PG 9 / KR PG 13,5	M 16 x 1,5/16	2 x 3	1.089.1100.19	3 x 3	1.089.1101.19	1.089.1199.19
		2 x 4	1.089.1102.19	3 x 1,5	1.089.1103.19	
PG 13,5 / KE PG 11 / KR PG 16	M 20 x 1,5 NPT 1/2"	3 x 2	1.089.1300.19	6 x 3	1.089.1301.19	1.089.1399.19
		3 x 4	1.089.1302.19	2 x 5	1.089.1303.19	
		3 x 3	1.089.1304.19	1 x 5*	1.089.1312.19	
PG 16 / KE PG 13,5 / KR PG 21	M 16 x 1,5/16 NPT 1/2" (16)	4 x 4	1.089.1602.19	5 x 4	1.089.1603.19	1.089.1699.19
		6 x 4	1.089.1604.19	2 x 6	1.089.1605.19	
		6 x 3	1.089.1607.19	3 x 4	1.089.1601.19	
		4 x 5	1.089.1611.19	2 x 4,5	1.089.1614.19	
PG 21 / KE PG 16	M 25 x 1,5 NPT 3/4"	4 x 6	1.089.2100.19	3 x 7	1.089.2101.19	1.089.2199.19
		2 x 8	1.089.2102.19	4 x 5	1.089.2103.19	
		3 x 5,2	1.089.2106.19	1 x 5,8*	1.089.2113.19	
PG 29	M 32 x 1,5 NPT 1" / 1 1/4"	6 x 6,5	1.089.2900.19	4 x 9	1.089.2901.19	1.089.2999.19
		2 x 6	1.089.2905.19			
PG 36	M 40 x 1,5 NPT 1 1/2"	5 x 9	1.089.3600.19	7 x 9	1.089.3601.19	1.089.3699.19
		6 x 8	1.089.3602.19	2 x 15	1.089.3603.19	
PG 42	M 50 x 1,5					1.089.4299.19
PG 48	M 63 x 1,5	8 x 10	1.089.4800.19	6 x 12	1.089.4801.19	1.089.4899.19

* Slit version to accommodate terminated cable

Advice: The shown inserts are samples, more inserts upon request

HSK-FLAKA

Metr., PG, NPT

RoHS

Material

Elastomer


Operating Temperature

-40°C – 100°C (-40°F – 212°F)

Advice:

- Installation instruction see page 176
- Other materials available upon request

! - The inserts are exclusively capable for the glands of the HSK series



ASI-BUS




Fits the following sizes			w x h mm	Number	w x h mm	Number
PG 13 (ASI-BUS)	M 20 x 1,5	NPT 1/2"	10,4 x 4,2	1.091.1300.19		
PG 16/KE PG 13,5 / KR PG 21		NPT 1/2" (16)	14 x 6	1.091.1600.19	11,5 x 5	1.091.1601.19
PG 16/KE PG 13,5 / KR PG 21		NPT 1/2" (16)	12 x 7	1.091.1602.19		
PG 21/KE PG 16	M 25 x 1,5	NPT 3/4"	14 x 6	1.091.2100.19	14 x 7	1.091.2101.19
PG 29	M 32 x 1,5	NPT 1"/1 1/4"	22 x 8	1.091.2900.19		
PG 36	M 40 x 1,5	NPT 1 1/2"	28,5 x 10	1.091.3600.19	29 x 5,5	1.091.3601.19
PG 42	M 50 x 1,5		33,5 x 11,5	1.091.4200.19		
PG 48	M 63 x 1,5		38 x 12	1.091.4800.19		

Advice: The shown inserts are samples, more inserts upon request

O-Ring

Metr., PG, NPT



O-Ring Buna-N

Material Buna-N

Operating Temperature -30 °C – 120 °C (-22 °F – 248 °F)

O-Ring FPM

Material FPM

Operating Temperature -40 °C – 200 °C (-40 °F – 392 °F)

O-Ring VMQ


Material VMQ (Silicone)

Operating Temperature -60 °C – 250 °C (-76 °F – 482 °F)

RoHS



O-Ring for HSK-K



Fits the following sizes	d mm	s mm	Number Buna-N	Number FPM	Number VMQ
M 12 x 1,5	10	1,5	1.321.1200.57	1.321.1200.58	1.321.1200.59
M 16 x 1,5	12	1,5	1.321.1600.57	1.321.1600.58	1.321.1600.59
M 20 x 1,5	17	1,8	1.321.2000.57	1.321.2000.58	1.321.2000.59
M 25 x 1,5	22	2	1.321.2500.57	1.321.2500.58	1.321.2500.59
M 32 x 1,5	29	2	1.321.3200.57	1.321.3200.58	1.321.3200.59
M 40 x 1,5	35	2	1.321.4000.57	1.321.4000.58	1.321.4000.59
M 50 x 1,5	43	2	1.321.5000.57	1.321.5000.58	1.321.5000.59
M 63 x 1,5	55	2	1.321.6300.57	1.321.6300.58	1.321.6300.59
PG 7	10	1,5	1.321.0700.17	1.321.0700.21	1.321.0700.22
PG 9	12	1,5	1.321.0900.17	1.321.0900.21	1.321.0900.22
PG 11	16	1,5	1.321.1100.17	1.321.1100.21	1.321.1100.22
PG 13,5	17	1,8	1.321.1300.17	1.321.1300.21	1.321.1300.22
PG 16	18	1,5	1.321.1600.17	1.321.1600.21	1.321.1600.22
PG 21	26	2	1.321.2100.17	1.321.2100.21	1.321.2100.22
PG 29	33	2	1.321.2900.17	1.321.2900.21	1.321.2900.22
PG 36	43	2	1.321.3600.17	1.321.3600.21	1.321.3600.22
PG 42	50	2	1.321.4200.17	1.321.4200.21	1.321.4200.22
PG 48	55	2	1.321.4800.17	1.321.4800.21	1.321.4800.22
NPT 3/8"	13	2	1.321.3800.77	1.321.3800.78	1.321.3800.79
NPT 1/2"	19	1,8	1.321.1200.77	1.321.1200.78	1.321.1200.79
NPT 3/4"	22	2	1.321.3400.77	1.321.3400.78	1.321.3400.79
NPT 1"	29	2	1.321.1000.77	1.321.1000.78	1.321.1000.79
NPT 1 1/4"	38	2,5	1.321.5400.77	1.321.5400.78	1.321.5400.79
NPT 1 1/2"	45	2,5	1.321.6400.77	1.321.6400.78	1.321.6400.79

Thread Seal Ring

Metr.

RoHS

Thread Seal Ring PE


Material Polyethylene

Operating Temperature -30 °C – 70 °C (-22 °F – 158 °F)


Thread Seal Ring HD

Material Fiber-reinforced plastic

Operating Temperature -40 °C – 300 °C (-40 °F – 572 °F)



Advice:
- GFK thread seal see page 109



Size	d mm	D mm	S mm	Number Polyethylene	Number Fiber-reinforced plastic
M 12 x 1,5	12	16	2	1.325.1200.59	1.325.1200.50
M 16 x 1,5	16	20	2	1.325.1600.59	1.325.1600.50
M 20 x 1,5	20	25	2	1.325.2000.59	1.325.2000.50
M 25 x 1,5	25	31	2	1.325.2500.59	1.325.2500.50
M 32 x 1,5	32	38	2	1.325.3200.59	1.325.3200.50
M 40 x 1,5	40	48	2	1.325.4000.59	1.325.4000.50
M 50 x 1,5	50	58	2	1.325.5000.59	1.325.5000.50
M 63 x 1,5	63	72	2	1.325.6300.59	1.325.6300.50

Thread Seal Ring

PG

RoHS

Thread Seal Ring PE



Material Polyethylene

Operating Temperature -30 °C – 70 °C (-22 °F – 158 °F)

Thread Seal Ring HD

Material Fiber-reinforced plastic


Operating Temperature -40 °C – 300 °C (-40 °F – 572 °F)



Size	d mm	D mm	S Polyethylene mm	S Fiber-reinforced plastic mm	Number Polyethylene	Number Fiber-reinforced plastic
PG 7	12,5	16,5	2	1,5	1.325.0700.19	1.325.0700.20
PG 9	15,2	19	2	1,5	1.325.0900.19	1.325.0900.20
PG 11	18,6	22,5	2	1,5	1.325.1100.19	1.325.1100.20
PG 13,5	20,4	25	2	1,5	1.325.1300.19	1.325.1300.20
PG 16	22,5	27	2	1,5	1.325.1600.19	1.325.1600.20
PG 21	28,3	33,5	2	2	1.325.2100.19	1.325.2100.20
PG 29	37	43,5	2	2	1.325.2900.19	1.325.2900.20
PG 36	47	55	2	2	1.325.3600.19	1.325.3600.20
PG 42	54	63	2	2	1.325.4200.19	1.325.4200.20
PG 48	59,3	69	2	2	1.325.4800.19	1.325.4800.20


GM-Ms

Metr., PG, G



Material

Nickel plated brass



IG	H mm	 mm	Number
M 12 x 1,5	2,8	15	1.161.1200.50
M 16 x 1,5	2,8	19	1.161.1600.50
M 20 x 1,5	3,0	23	1.161.2000.50
M 25 x 1,5	3,5	29	1.161.2500.50
M 32 x 1,5	4,0	36	1.161.3200.50
M 40 x 1,5	4,5	45	1.161.4000.50
M 50 x 1,5	5,5	55	1.161.5000.50
M 63 x 1,5	6,0	70	1.161.6300.50
M 75 x 1,5	8,0	85	1.161.7500.50
M 80 x 2	8,0	90	1.161.8000.50
M 90 x 2	8,0	100	1.161.9000.50
M 100 x 2	11	115	1.161.1000.50
M 110 x 2	11	125	1.161.1100.50

IG	H mm	 mm	Number
PG 7	2,8	15	1.161.0700.01
PG 9	2,8	18	1.161.0900.01
PG 11	3,0	21	1.161.1100.01
PG 13,5	3,0	23	1.161.1300.01
PG 16	3,0	26	1.161.1600.01
PG 21	3,5	32	1.161.2100.01
PG 29	4,0	41	1.161.2900.01
PG 36	5,0	51	1.161.3600.01
PG 42	5,0	60	1.161.4200.01
PG 48	5,5	64	1.161.4800.01
G 2 1/2"	7	80	1.106.5200.99
G 3"	8	95	1.106.3000.99
G 4"	11	125	1.106.4000.99


GM-EMV

Metr., PG



Material

Nickel plated brass



IG	H mm	 mm	S mm	Number
M 12 x 1,5	2,8	15	0,7	1.167.1200.50
M 16 x 1,5	2,8	19	0,7	1.167.1600.50
M 20 x 1,5	3,0	24	0,7	1.167.2000.50
M 25 x 1,5	3,5	30	0,7	1.167.2500.50
M 32 x 1,5	4,5	36	0,7	1.167.3200.50
M 40 x 1,5	5,0	46	0,7	1.167.4000.50
M 50 x 1,5	5,0	60	0,7	1.167.5000.50
M 63 x 1,5	6,0	70	0,7	1.167.6300.50

IG	H mm	 mm	S mm	Number
PG 7	2,8	15	0,7	1.167.0700.01
PG 9	2,8	18	0,7	1.167.0900.01
PG 11	3,0	21	0,7	1.167.1100.01
PG 13,5	3,0	23	0,7	1.167.1300.01
PG 16	3,0	26	0,7	1.167.1600.01
PG 21	3,5	32	0,7	1.167.2100.01
PG 29	4,0	41	0,7	1.167.2900.01
PG 36	5,0	51	0,7	1.167.3600.01
PG 42	5,0	60	0,7	1.167.4200.01
PG 48	5,5	64	0,7	1.167.4800.01

V-N-Ms

Metr., PG

Material

Nickel plated brass

Protection

IP 54

AG	GL mm	H mm	D mm	Number
M 12 x 1,5	5	7,5	14	1.052.1200.50
M 16 x 1,5	5	9,0	18	1.052.1600.50
M 20 x 1,5	6,5	9,5	22	1.052.2000.50
M 25 x 1,5	7	11,0	28	1.052.2500.50
M 32 x 1,5	8	12,0	35	1.052.3200.50
M 40 x 1,5	8,5	13,0	44	1.052.4000.50
M 50 x 1,5	9	15,0	54	1.052.5000.50
M 63 x 1,5	10	16,0	67	1.052.6300.50

AG	GL mm	H mm	D mm	Number
PG 7	5	8	14	1.052.0700.01
PG 9	6	9	17	1.052.0900.01
PG 11	6	9	20	1.052.1100.01
PG 13,5	6,5	9,5	22	1.052.1300.01
PG 16	6,5	9,5	24	1.052.1600.01
PG 21	7	11	30	1.052.2100.01
PG 29	8	12	39	1.052.2900.01
PG 36	9	15	50	1.052.3600.01
PG 42	10	16	57	1.052.4200.01
PG 48	10	16	64	1.052.4800.01

V-N-Ms-SD

Metr., PG

Material	Nickel plated brass
O-Ring	Buna-N
Protection	IP 68 (NEMA 6)
Operating Temperature	-40 °C – 80 °C (-40 °F – 176 °F)

Advice:

- NPT thread on request
- Elongated thread on request
- Other O-Ring materials upon request


AG	GL mm	H mm	D mm	Number
M 12 x 1,5	6,5	9,5	14	1.052.1201.50
M 16 x 1,5	6	9	20	1.052.1601.50
M 20 x 1,5	6,5	9,5	24	1.052.2001.50
M 25 x 1,5	7	11	28	1.052.2501.50
M 32 x 1,5	8	12,5	35	1.052.3201.50
M 40 x 1,5	8	12	45	1.052.4001.50
M 50 x 1,5	9	15	55	1.052.5001.50
M 63 x 1,5	10	16	68	1.052.6301.50

AG	GL mm	H mm	D mm	Number
PG 7	4,8	8	14	1.052.0701.01
PG 9	5,5	9	17	1.052.0901.01
PG 11	5,5	9	20	1.052.1101.01
PG 13,5	6	9,5	22	1.052.1301.01
PG 16	6	9,5	24	1.052.1601.01
PG 21	6,5	11	30	1.052.2101.01
PG 29	7,5	12	39	1.052.2901.01
PG 36	9	15	50	1.052.3601.01
PG 42	10	16	57	1.052.4201.01
PG 48	10	16	64	1.052.4801.01

Advice:
- NPT thread on request
- Elongated thread on request
- Other O-Ring materials upon request

V-NE-Ms

Metr.



Advice:

- NPT thread on request
- Elongated thread on request
- Other O-Ring materials upon request

Material Nickel plated brass

V-NE-Ms


Protection IP 54

V-NE-Ms-SD/ V-NE-Ms-SD-FPM


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)

O-Ring / Operating Temperature Buna-N/ -20 °C – 95 °C (-4 °F – 203 °F)
FPM/-20 °C – 180 °C (-4 °F – 356 °F)


V-NE-Ms




V-NE-Ms-SD



AG	GL mm	H mm	 mm	Number V-NE-Ms without O-Ring	Number V-NE-Ms-SD -20 °C – 95 °C -4 °F – 203 °F	Number V-NE-Ms-SD-FPM -20 °C – 180 °C -4 °F – 356 °F
M 12 x 1,5	6,5	9,5	14	1.155.1200.50	1.156.1200.50	1.157.1200.50
M 16 x 1,5	6	9	19	1.155.1600.50	1.156.1600.50	1.157.1600.50
M 20 x 1,5	6	9,5	22	1.155.2000.50	1.156.2000.50	1.157.2000.50
M 25 x 1,5	7	10,5	30	1.155.2500.50	1.156.2500.50	1.157.2500.50
M 32 x 1,5	8	12,5	41	1.155.3200.50	1.156.3200.50	1.157.3200.50
M 40 x 1,5	8	13	46	1.155.4000.50	1.156.4000.50	1.157.4000.50
M 50 x 1,5	9	15	55	1.155.5000.50	1.156.5000.50	1.157.5000.50
M 63 x 1,5	10	16,5	70	1.155.6300.50	1.156.6300.50	1.157.6300.50

V-NE-Ms

PG



Advice:

- Other O-Ring materials upon request

Material Nickel plated brass

V-NE-Ms


Protection IP 54

V-NE-Ms-SD/ V-NE-Ms-SD-FPM


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)

O-Ring / Operating Temperature Buna-N/ -20 °C – 95 °C (-4 °F – 203 °F)
FPM/-20 °C – 180 °C (-4 °F – 356 °F)


V-NE-Ms



V-NE-Ms-SD



AG	GL mm	H mm	 mm	Number V-NE-Ms without O-Ring	Number V-NE-Ms-SD -20 °C – 95 °C -4 °F – 203 °F	Number V-NE-Ms-SD-FPM -20 °C – 180 °C -4 °F – 356 °F
PG 7	5	8	14	1.155.0700.01	1.156.0700.01	1.157.0700.01
PG 9	6	9	17	1.155.0900.01	1.156.0900.01	1.157.0900.01
PG 11	6	9,5	20	1.155.1100.01	1.156.1100.01	1.157.1100.01
PG 13,5	6,5	10	22	1.155.1300.01	1.156.1300.01	1.157.1300.01
PG 16	6,5	10	24	1.155.1600.01	1.156.1600.01	1.157.1600.01
PG 21	7	10,5	30	1.155.2100.01	1.156.2100.01	1.157.2100.01
PG 29	8	12,5	41	1.155.2900.01	1.156.2900.01	1.157.2900.01
PG 36	8	13	50	1.155.3600.01	1.156.3600.01	1.157.3600.01
PG 42	9	15	58	1.155.4200.01	1.156.4200.01	1.157.4200.01
PG 48	10	16,5	65	1.155.4800.01	1.156.4800.01	1.157.4800.01

R-H

Metr., PG




Material

Nickel plated brass

Advice:


- Metric threads with O-Ring thread seal available



AG	IG	GL mm	H mm	D mm	Number
M 16 x 1,5	M 12 x 1,5	6,0	8,5	18	1.076.1612.50
M 20 x 1,5	M 12 x 1,5	6,5	9,0	24	1.076.2012.50
M 20 x 1,5	M 16 x 1,5	6,5	9,0	24	1.076.2016.50
M 25 x 1,5	M 16 x 1,5	7,0	10,0	30	1.076.2516.50
M 25 x 1,5	M 20 x 1,5	7,0	10,0	30	1.076.2520.50
M 32 x 1,5	M 20 x 1,5	8,0	11,5	39	1.076.3220.50
M 32 x 1,5	M 25 x 1,5	8,0	11,5	39	1.076.3225.50
M 40 x 1,5	M 25 x 1,5	8,0	11,5	43	1.076.4025.50
M 40 x 1,5	M 32 x 1,5	9,0	12,5	43	1.076.4032.50
M 50 x 1,5	M 32 x 1,5	10,0	14,0	57	1.076.5032.50
M 50 x 1,5	M 40 x 1,5	10,0	14,0	57	1.076.5040.50
M 63 x 1,5	M 40 x 1,5	10,0	14,0	64	1.076.6340.50
M 63 x 1,5	M 50 x 1,5	10,0	14,0	64	1.076.6350.50
PG 9	PG 7	6	8,5	17	1.071.0907.01
PG 11	PG 7	6	8,5	20	1.071.1107.01
PG 11	PG 9	6	8,5	20	1.071.1109.01
PG 13,5	PG 9	6,5	9	22	1.071.1309.01
PG 13,5	PG 11	6,5	9	22	1.071.1311.01
PG 16	PG 9	6,5	9,5	24	1.071.1609.01
PG 16	PG 11	6,5	9,5	24	1.071.1611.01
PG 16	PG 13,5	6,5	9,5	24	1.071.1613.01
PG 21	PG 11	7	10	30	1.071.2111.01
PG 21	PG 13,5	7	10	30	1.071.2113.01
PG 21	PG 16	7	10	30	1.071.2116.01
PG 29	PG 16	8	11,5	39	1.071.2916.01
PG 29	PG 21	8	11,5	39	1.071.2921.01
PG 36	PG 21	9	12,5	50	1.071.3621.01
PG 36	PG 29	9	12,5	50	1.071.3629.01
PG 42	PG 29	10	14	57	1.071.4229.01
PG 42	PG 36	10	14	57	1.071.4236.01
PG 48	PG 36	10	14	64	1.071.4836.01
PG 48	PG 42	10	14	64	1.071.4842.01

RSD-MS


Metr.



Material	Nickel plated brass
O-Ring	Buna-N
Operating Temperature	-40 °C – 100 °C



Advice:
- Other O-Ring materials upon request




AG	IG mm	GL mm	H mm	 mm	Number
M 16 x 1,5	M 12 x 1,5	5	8	17	1.077.1612.50
M 20 x 1,5	M 12 x 1,5	6	9	22	1.077.2012.50
M 20 x 1,5	M 16 x 1,5	6	9	22	1.077.2016.50
M 25 x 1,5	M 16 x 1,5	7	10	29	1.077.2516.50
M 25 x 1,5	M 20 x 1,5	7	10	29	1.077.2520.50
M 32 x 1,5	M 16 x 1,5	8	11	34	1.077.3216.50
M 32 x 1,5	M 20 x 1,5	8	11	35	1.077.3220.50
M 32 x 1,5	M 25 x 1,5	8	11	34	1.077.3225.50
M 40 x 1,5	M 20 x 1,5	8	12	43	1.077.4020.50
M 40 x 1,5	M 25 x 1,5	8	12	43	1.077.4025.50
M 40 x 1,5	M 32 x 1,5	8	12	43	1.077.4032.50

AG	IG mm	GL mm	H mm	 mm	Number
M 50 x 1,5	M 25 x 1,5	9	13	55	1.077.5025.50
M 50 x 1,5	M 32 x 1,5	9	13	55	1.077.5032.50
M 50 x 1,5	M 40 x 1,5	9	13	55	1.077.5040.50
M 63 x 1,5	M 32 x 1,5	10	14	65	1.077.6332.50
M 63 x 1,5	M 40 x 1,5	10	14	65	1.077.6340.50
M 63 x 1,5	M 50 x 1,5	10	14	65	1.077.6350.50

RSD-MS


PG



Material	Nickel plated brass
O-Ring	Buna-N
Operating Temperature	-40 °C – 100 °C



Advice:
- Other O-Ring materials upon request



AG	IG mm	GL mm	H mm	 mm	Number
PG 9	PG 7	6	8,8	17	1.077.0907.01
PG 11	PG 7	6	9	20	1.077.1107.01
PG 11	PG 9	6	9	20	1.077.1109.01
PG 13,5	PG 9	6,5	9,5	22	1.077.1309.01
PG 13,5	PG 11	6,5	9,5	22	1.077.1311.01
PG 16	PG 9	6,5	9,5	24	1.077.1609.01
PG 16	PG 11	6,5	9,5	24	1.077.1611.01
PG 16	PG 13,5	6,5	9,5	24	1.077.1613.01
PG 21	PG 11	7	10,3	30	1.077.2111.01
PG 21	PG 13,5	7	10,3	30	1.077.2113.01
PG 21	PG 16	7	10,3	30	1.077.2116.01

AG	IG mm	GL mm	H mm	 mm	Number
PG 29	PG 16	8	11,5	40	1.077.2916.01
PG 29	PG 21	8	11,5	40	1.077.2921.01
PG 36	PG 21	9	12,5	50	1.077.3621.01
PG 36	PG 29	9	12,5	50	1.077.3629.01
PG 42	PG 29	10	13,5	57	1.077.4229.01
PG 42	PG 36	10	13,5	57	1.077.4236.01
PG 48	PG 36	10	13,5	64	1.077.4836.01
PG 48	PG 42	10	13,5	64	1.077.4842.01

RE-MS

Metr., PG





RoHS



Material

Nickel plated brass





AG	IG	GL mm	H mm	D mm	 mm	Number
M 16 x 1,5	PG 9	6	10,5	20		1.039.1609.01
M 20 x 1,5	PG 11	6,5	12,5	22		1.039.2011.01
M 20 x 1,5	PG 13,5	6,5	12,5	22		1.039.2013.01
M 20 x 1,5	PG 16	6,5	12,5	24		1.039.2016.01
M 25 x 1,5	PG 16	6,5	12,5	28		1.039.2516.01
M 25 x 1,5	PG 21	6,5	14,5	30		1.039.2521.01
M 32 x 1,5	PG 29	7	16	39		1.039.3229.01
PG 9	M 16 x 1,5	6	10,5	20		1.039.0916.01
PG 11	M 20 x 1,5	6,5	12,5	22		1.039.1120.01
PG 13,5	M 20 x 1,5	6,5	12,5	22		1.039.1320.01
PG 16	M 25 x 1,5	6,5	14,5	27		1.039.1625.01

RE-MS

PG

RoHS

Material

Nickel plated brass


O-Ring

NBR

AG	IG	GL mm	H mm	D mm	mm	Number
M 16 x 1,5	NPT 1/2"	6	17		24	1.171.1612.50
M 20 x 1,5	NPT 1/2"	6	17		24	1.171.2012.50
M 25 x 1,5	NPT 1/2"	7	8		30	1.171.2512.50
M 25 x 1,5	NPT 3/4"	7	19		30	1.171.2534.50
M 32 x 1,5	NPT 1"	8	25		40	1.171.3210.50
M 32 x 1,5	NPT 1 1/4"	8	25		46	1.171.3254.50
PG 11	NPT 1/2"	6	16,7		24	1.171.1112.01
PG 13,5	NPT 1/2"	6,5	17		24	1.171.1312.01
PG 16	NPT 1/2"	6,5	16,5		24	1.171.1612.01
PG 21	NPT 1/2"	7	8		30	1.171.2112.01
PG 21	NPT 3/4"	7	17		30	1.171.2134.01
PG 29	NPT 1"	8	12		40	1.171.2910.01

E-Ms

Metr.




Material

Nickel plated brass







AG	IG	GL mm	H mm	D mm	Number
M 12 x 1,5	M 16 x 1,5	5	15	18	1.033.1216.50
M 16 x 1,5	M 20 x 1,5	6	17,5	22	1.033.1620.50
M 20 x 1,5	M 25 x 1,5	6,5	19	27	1.033.2025.50
M 25 x 1,5	M 32 x 1,5	6,5	21	34	1.033.2532.50
M 32 x 1,5	M 40 x 1,5	7	23	42	1.033.3240.50
M 40 x 1,5	M 50 x 1,5	9	31	53	1.033.4050.50
M 50 x 1,5	M 63 x 1,5	9	31	66	1.033.5063.50

E-**Ms**

PG

Material

Nickel plated brass

AG	IG	GL mm	H mm	D mm	Number
PG 7	PG 9	5	15	17	1.033.0709.01
PG 9	PG 11	6	16,5	20	1.033.0911.01
PG 9	PG 13,5	6	17,5	22	1.033.0913.01
PG 11	PG 13,5	6	17,5	22	1.033.1113.01
PG 11	PG 16	6	18,5	24	1.033.1116.01
PG 11	PG 21	6	20,5	30	1.033.1121.01
PG 13,5	PG 16	6,5	19	24	1.033.1316.01
PG 13,5	PG 21	6,5	21	30	1.033.1321.01
PG 16	PG 21	6,5	21	30	1.033.1621.01
PG 16	PG 29	6,5	22,5	39	1.033.1629.01
PG 21	PG 29	7	23	39	1.033.2129.01

AG	IG	GL mm	H mm	D mm	Number
PG 29	PG 36	8	27,5	50	1.033.2936.01
PG 36	PG 42	9	31	57	1.033.3642.01
PG 42	PG 48	10	33	64	1.033.4248.01

KLE

Metr.

Material

Nickel plated brass

AG	GL	H mm	mm	mm	Number
M 12 x 1,5	5,5	15,0	16	5-7,5	1.143.1200.50
M 16 x 1,5	6,0	16,0	19	7-10	1.143.1600.50
M 20 x 1,5	6,5	18,0	24	10-14	1.143.2000.50
M 25 x 1,5	8,0	21,0	34	12-21,5	1.143.2500.50
M 32 x 1,5	8,0	22,0	42	16-27	1.143.3200.50
M 40 x 1,5	9,5	25,5	52	22-33	1.143.4000.50
M 50 x 1,5	9,5	25,5	52	25-38,5	1.143.5000.50

KLE

PG

RoHS

PG


Material

Nickel plated brass

AG	GL	H mm	mm	mm	Number
PG 7	5,5	14,8	16	5,5–8	1.143.0700.01
PG 9	6	16,6	19	6,5–10	1.143.0900.01
PG 11	6	17,3	22	7,5–12	1.143.1100.01
PG 13,5	6,5	17,8	24	8,5–14	1.143.1300.01
PG 16	6,5	18,3	26	9,5–16	1.143.1600.01
PG 21	7,5	20,8	33	12–21	1.143.2100.01
PG 29	8	21,8	42	19–30	1.143.2900.01
PG 36	9,5	25,3	52	25–37	1.143.3600.01
PG 42	10	26,3	59	31–43	1.143.4200.01
PG 48	11	27,3	64	35–48	1.143.4800.01

FW-ZN

Metr.




Material Zinc die casting

Protection IP 65

O-Ring Buna-N


Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)



A	C mm	D mm	E mm	G mm	H mm	Number
M 20 x 1,5	56	53	44	5,5	35	1.306.2000.50
M 25 x 1,5	65	63	54	5,5	42	1.306.2500.50
M 32 x 1,5	75	71	60	5,5	52	1.306.3200.50
M 50 x 1,5	93	89	72	6,5	69	1.306.5000.50
M 63 x 1,5	114	96	84	6,5	74	1.306.6300.50

FW-ZN

PG




Material Zinc die casting

Protection IP 65

O-Ring Buna-N

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)



A	C mm	D mm	E mm	G mm	H mm	Number
PG 9	50	45	37	4,3	30	1.306.0900.05
PG 11	50	45	37	4,3	30	1.306.1100.05
PG 13,5	56	53	44	5,5	35	1.306.1300.05
PG 16	56	53	44	5,5	35	1.306.1600.05
PG 21	65	63	54	5,5	42	1.306.2100.05
PG 29	74	70	60	5,5	52	1.306.2900.05
PG 36	94	89	72	6,5	69	1.306.3600.05
PG 42	114	96	84	6,5	74	1.306.4200.05
PG 48	114	96	84	6,5	74	1.306.4800.05

GM-INOX

Metr.

Material

INOX 1.4305

IG

H

Advice:

- Other sizes upon request

- Other steel upon request

IG mm	H mm	 mm	Number
M 12 x 1,5	2,8	15	1.161.1200.58
M 16 x 1,5	2,8	19	1.161.1600.58
M 20 x 1,5	3	24	1.161.2000.58
M 25 x 1,5	3,5	30	1.161.2500.58
M 32 x 1,5	3,5	36	1.161.3200.58
M 40 x 1,5	5	46	1.161.4000.58
M 50 x 1,5	5	57	1.161.5000.58
M 63 x 1,5	6	70	1.161.6300.58

GM-INOX


PG

RoHS



Material


INOX 1.4305



Advice:

- Other sizes upon request


- Other steel upon request



IG mm	H mm	 mm	Number
PG 7	2,8	17	1.161.0700.08
PG 9	2,8	22	1.161.0900.08
PG 11	3	22	1.161.1100.08
PG 13,5	3	24	1.161.1300.08
PG 16	3	27	1.161.1600.08
PG 21	3,5	32	1.161.2100.08
PG 29	4	41	1.161.2900.08
PG 36	5	50	1.161.3600.08

V-INOX

Metr.




Material INOX 1.4305



Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)

O-Ring Buna-N / FPM / VMQ

Operating Temperature -20°C – 95°C (-4°F – 203°F) (NBR), -20°C – 180°C (-4°F – 356°F) (FPM), -60°C – 180°C (-76°F – 356°F) (VMQ)




Advice:

- Elongated thread on request
- Other sizes upon request
- AISI 316L on request

AG	GL mm	H mm	 mm	Number V-INOX-Buna-N -20 °C – 95 °C -4 °F – 203 °F	Number V-INOX-FPM -20 °C – 180 °C -4 °F – 356 °F	Number V-INOX-VMQ -60 °C – 180 °C -76 °F – 356 °F
M 12 x 1,5	6,5	9,5	14	1.152.1200.50	1.153.1200.50	1.154.1200.50
M 16 x 1,5	6	9	19	1.152.1600.50	1.153.1600.50	1.154.1600.50
M 20 x 1,5	6	9,5	22	1.152.2000.50	1.153.2000.50	1.154.2000.50
M 25 x 1,5	7	10,5	30	1.152.2500.50	1.153.2500.50	1.154.2500.50
M 32 x 1,5	8	12,5	41	1.152.3200.50	1.153.3200.50	1.154.3200.50
M 40 x 1,5	8	13	46	1.152.4000.50	1.153.4000.50	1.154.4000.50

V-INOX

PG




Material INOX 1.4305



Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)

O-Ring Buna-N / FPM / VMQ

Operating Temperature -20°C – 95°C (-4°F – 203°F) (NBR), -20°C – 180°C (-4°F – 356°F) (FPM), -60°C – 180°C (-76°F – 356°F) (VMQ)



Advice:

- Elongated thread on request
- Other sizes upon request
- AISI 316L on request

AG	GL mm	H mm	 mm	Number V-INOX-Buna-N -20 °C – 95 °C -4 °F – 203 °F	Number V-INOX-FPM -20 °C – 180 °C -4 °F – 356 °F	Number V-INOX-VMQ -60 °C – 180 °C -76 °F – 356 °F
PG 7	5	8	14	1.152.0700.01	1.153.0700.01	1.154.0700.01
PG 9	6	9	17	1.152.0900.01	1.153.0900.01	1.154.0900.01
PG 11	6	9,5	20	1.152.1100.01	1.153.1100.01	1.154.1100.01
PG 13,5	6,5	10	22	1.152.1300.01	1.153.1300.01	1.154.1300.01
PG 16	6,5	10	24	1.152.1600.01	1.153.1600.01	1.154.1600.01
PG 21	7	10,5	30	1.152.2100.01	1.153.2100.01	1.154.2100.01
PG 29	8	12,5	41	1.152.2900.01	1.153.2900.01	1.154.2900.01
PG 36	8	13	50	1.152.3600.01	1.153.3600.01	1.154.3600.01

RS-INOX / RSD-INOX

Metr.






Material INOX 1.4305

O-Ring Buna-N

Operating Temperature -20°C – 95°C (-4 °F – 203 °F)

Advice:


- Other O-Ring materials upon request
- AISI 316L on request



AG	IG	GL mm	H mm	mm	Number RS-INOX without O-Ring	Number RSD-INOX
M 16 x 1,5	M 12 x 1,5	6	9	19	1.094.1612.50	1.097.1612.50
M 20 x 1,5	M 12 x 1,5	6	9,5	22	1.094.2012.50	1.097.2012.50
M 20 x 1,5	M 16 x 1,5	6	9,5	22	1.094.2016.50	1.097.2016.50
M 25 x 1,5	M 16 x 1,5	7	10,5	27	1.094.2516.50	1.097.2516.50
M 25 x 1,5	M 20 x 1,5	7	10,5	27	1.094.2520.50	1.097.2520.50
M 32 x 1,5	M 16 x 1,5	8	12,5	34	1.094.3216.50	1.097.3216.50
M 32 x 1,5	M 20 x 1,5	8	12,5	34	1.094.3220.50	1.097.3220.50
M 32 x 1,5	M 25 x 1,5	8	12,5	34	1.094.3225.50	1.097.3225.50
M 40 x 1,5	M 20 x 1,5	8	13	43	1.094.4020.50	1.097.4020.50
M 40 x 1,5	M 25 x 1,5	8	13	43	1.094.4025.50	1.097.4025.50
M 40 x 1,5	M 32 x 1,5	8	13	43	1.094.4032.50	1.097.4032.50
M 50 x 1,5	M 25 x 1,5	9	15	55	1.094.5025.50	1.097.5025.50
M 50 x 1,5	M 32 x 1,5	9	15	55	1.094.5032.50	1.097.5032.50
M 50 x 1,5	M 40 x 1,5	9	15	55	1.094.5040.50	1.097.5040.50
M 63 x 1,5	M 32 x 1,5	10	16,5	65	1.094.6332.50	1.097.6332.50
M 63 x 1,5	M 40 x 1,5	10	16,5	65	1.094.6340.50	1.097.6340.50
M 63 x 1,5	M 50 x 1,5	10	16,5	65	1.094.6350.50	1.097.6350.50

RS-INOX / RSD-INOX

PG



Material INOX 1.4305




RoHS

O-Ring Buna-N


Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)

Advice:


- Other O-Ring materials upon request
- AISI 316L on request



RS-INOX



RSD-INOX



AG	IG	GL mm	H mm	 mm	Number RS-INOX without O-Ring	Number RSD-INOX -20 °C – 95 °C -4 °F – 203 °F
PG 9	PG 7	6	8,8	17	1.094.0907.01	1.097.0907.01
PG 11	PG 7	6	9	22	1.094.1107.01	1.097.1107.01
PG 11	PG 9	6	9	22	1.094.1109.01	1.097.1109.01
PG 13,5	PG 9	6,5	9,5	22	1.094.1309.01	1.097.1309.01
PG 13,5	PG 11	6,5	9,5	22	1.094.1311.01	1.097.1311.01
PG 16	PG 9	6,5	9,5	24	1.094.1609.01	1.097.1609.01
PG 16	PG 11	6,5	9,5	24	1.094.1611.01	1.097.1611.01
PG 16	PG 13,5	6,5	9,5	24	1.094.1613.01	1.097.1613.01
PG 21	PG 11	7	10,3	30	1.094.2111.01	1.097.2111.01
PG 21	PG 13,5	7	10,3	30	1.094.2113.01	1.097.2113.01
PG 21	PG 16	7	10,3	30	1.094.2116.01	1.097.2116.01
PG 29	PG 16	8	11,5	41	1.094.2916.01	1.097.2916.01
PG 29	PG 21	8	11,5	41	1.094.2921.01	1.097.2921.01
PG 36	PG 21	9	12,5	50	1.094.3621.01	1.097.3621.01
PG 36	PG 29	9	12,5	50	1.094.3629.01	1.097.3629.01
PG 42	PG 29	10	13,5	60	1.094.4229.01	1.097.4229.01
PG 42	PG 36	10	13,5	60	1.094.4236.01	1.097.4236.01
PG 48	PG 36	10	13,5	65	1.094.4836.01	1.097.4836.01
PG 48	PG 42	10	13,5	65	1.094.4842.01	1.097.4842.01

Cable glands for hazardous areas

EXIOS⁺ STANDARD, **EXIOS⁺ BARRIER**, **EXIOS⁺ A2F**

Cable glands for all popular threads, used in electrical equipment and hazardous areas in Group I, II and III applications. The Ex-d, Ex-e and/or Ex-ta certified cable glands have been designed for all explosion proof areas which are in need of high standards, reliability, strain relief and water proof requirements, e.g. marine, offshore, gas conveying machinery, refineries and chemical industry.



You can find in this chapter

- **EXIOS⁺ STANDARD** the innovative HUMMEL high-end cable gland for armoured cables in hazardous areas including the latest IECEx and ATEX certifications, for the use in Ex-e, Ex-d and Ex-ta areas.
- **EXIOS⁺ BARRIER** High-end cable gland for armoured cables in hazardous areas uses a barrier compound sealing. Including the latest IECEx and ATEX certifications, for the use in Ex-e, Ex-d and Ex-ta areas.
- **EXIOS⁺ A2F** for non-armoured cables for the use in Ex-e and Ex-d areas
- Accessories:
 - Thread Seal Ring
 - Plugs
 - Earthtags
 - Serrated Washer

For any further question please do not hesitate to contact us. We look forward to develop solutions together with you. You profit from our vast knowledge in development, engineering and production technology.

Contact us:

E-Mail: info.et@hummel.com

Tel.: +49 (0) 76 66/9 11 10-0



Cable glands for hazardous areas

EXIOS⁺ STANDARD
Metr., NPT


Material	Brass
Seal	Silicone, VMQ
Clamping insert	PA 6
Armouring	Metallic Armour or Screen
Protection	IP 66, 67 and 68 (5 bar)
Operating Temperature	-60° C – 105° C (-76° F – 221° F)



Advice:
- INOX on request



AG	Size	Ø		GL mm	H max. mm	mm	D mm	Armouring Ø mm			Number
		A ₁ mm	A ₂ mm					Clamping ring 1	Clamping ring 2	Clamping ring optional	
M 16 x1,5	20-1	6 – 12	3 – 8,1	16	69,5	22	27	0 – 0,7	0,7 – 1,25		1.605.1600.50
M 20 x1,5	20-1	6 – 12	3 – 8,1	16	69,5	22	27	0 – 0,7	0,7 – 1,25		1.605.2000.50
M 20 x1,5	20-2	9 – 16	6 – 12	16	74,3	24	29	0 – 0,7	0,7 – 1,25		1.605.2000.51
M 20 x1,5	20-3	12,5 – 20,5	9 – 14	16	80,5	30	35	0 – 0,7	0,7 – 1,4		1.605.2000.52
M 25 x1,5	20-3	12,5 – 20,5	9 – 14	16	80,5	30	35	0 – 0,7	0,7 – 1,4		1.605.2500.51
M 25 x1,5	25	16,9 – 26	12,5 – 20,5	16	91	36	42	0 – 0,7	0,9 – 1,6	0,7 – 1,4	1.605.2500.50
M 32 x1,5	32	22 – 33	16,9 – 26	16	96	46	52	0 – 0,7	1,3 – 2,0	0,7 – 1,4	1.605.3200.50
M 40 x1,5	40	28 – 41	22 – 33	16	107	55	64	0 – 0,7	1,3 – 2,0	0,7 – 1,4	1.605.4000.50
M 50 x1,5	50	36 – 52,6	28,9 – 44,4	16	131,5	65	73	0 – 1,0	1,5 – 2,5	1,0 – 2,0	1.605.5000.50
M 63 x1,5	63	46 – 65,3	39,9 – 56,3	16	144,5	80	90	0 – 1,0	1,5 – 2,5	1,0 – 2,0	1.605.6300.50
M 75 x1,5	75	57 – 78	50,5 – 68,2	16	154	95	107	0 – 1,0	1,5 – 2,5	1,0 – 2,0	1.605.7500.50
NPT 3/8"	20 – 1	6 – 12	3 – 8,1	16	69,5	22	27	0 – 0,7	0,7 – 1,25		1.605.3800.70
NPT 1/2"	20 – 2	9 – 16	6 – 12	20	74,3	24	29	0 – 0,7	0,7 – 1,25		1.605.1200.70
NPT 1/2"	20 – 3	12,5 – 20,5	9 – 14	20	80,5	30	35	0 – 0,7	0,7 – 1,4		1.605.1200.71
NPT 3/4"	25	16,9 – 26	12,5 – 20,5	20,5	91	36	42	0 – 0,7	0,9 – 1,6	0,7 – 1,4	1.605.3400.70
NPT 1"	32	22 – 33	16,9 – 26	25	96	46	52	0 – 0,7	1,3 – 2,0	0,7 – 1,4	1.605.1000.70
NPT 1 1/4"	40	28 – 41	22 – 33	26	107	55	64	0 – 0,7	1,3 – 2,0	0,7 – 1,4	1.605.5400.70
NPT 1 1/2"	40	28 – 41	22 – 33	26,5	107	55	64	0 – 0,7	1,3 – 2,0	0,7 – 1,4	1.605.6400.70
NPT 2"	50	36 – 52,6	28,9 – 44,4	27	131,5	65	73	0 – 1,0	1,5 – 2,5	1,0 – 2,0	1.605.2000.70
NPT 2 1/2"	63	46 – 65,3	39,9 – 56,3	40	144,5	80	90	0 – 1,0	1,5 – 2,5	1,0 – 2,0	1.605.5200.70
NPT 3"	75	57 – 78	50,5 – 68,2	41,5	154	95	107	0 – 1,0	1,5 – 2,5	1,0 – 2,0	1.605.3000.70

Cable glands for hazardous areas

EXIOS⁺ STANDARD

Metr., NPT



II 2G Ex de IIC Gb
II 1D Ex ta IIIC Da



BVS-10-ATEX-E-062-X



BVS 10.0078X



POCC-RU-0001-11TB05



AEX-13499-X



Material Nickel plated brass

Seal Silicone, VMQ


Clamping insert PA 6

Armouring Metallic Armour or Screen

Protection IP 66, 67 and 68 (5 bar)

Operating Temperature -60° C – 105° C (-76° F – 221° F)

Advice:
- INOX on request



AG	Size	Ø		GL mm	H max. mm	mm	D mm	Armouring Ø mm			Number
		A1 mm	A2 mm					Clamping ring 1	Clamping ring 2	Clamping ring optional	
M 16 x1,5	20-1	6 – 12	3 – 8,1	16	69,5	22	27	0 – 0,7	0,7 – 1,25		1.605.1603.50
M 20 x1,5	20-1	6 – 12	3 – 8,1	16	69,5	22	27	0 – 0,7	0,7 – 1,25		1.605.2003.50
M 20 x1,5	20-2	9 – 16	6 – 12	16	74,3	24	29	0 – 0,7	0,7 – 1,25		1.605.2003.51
M 20 x1,5	20-3	12,5 – 20,5	9 – 14	16	80,5	30	35	0 – 0,7	0,7 – 1,4		1.605.2003.52
M 25 x1,5	20-3	12,5 – 20,5	9 – 14	16	80,5	30	35	0 – 0,7	0,7 – 1,4		1.605.2503.51
M 25 x1,5	25	16,9 – 26	12,5 – 20,5	16	91	36	42	0 – 0,7	0,9 – 1,6	0,7 – 1,4	1.605.2503.50
M 32 x1,5	32	22 – 33	16,9 – 26	16	96	46	52	0 – 0,7	1,3 – 2,0	0,7 – 1,4	1.605.3203.50
M 40 x1,5	40	28 – 41	22 – 33	16	107	55	64	0 – 0,7	1,3 – 2,0	0,7 – 1,4	1.605.4003.50
M 50 x1,5	50	36 – 52,6	28,9 – 44,4	16	131,5	65	73	0 – 1,0	1,5 – 2,5	1,0 – 2,0	1.605.5003.50
M 63 x1,5	63	46 – 65,3	39,9 – 56,3	16	144,5	80	90	0 – 1,0	1,5 – 2,5	1,0 – 2,0	1.605.6303.50
M 75 x1,5	75	57 – 78	50,5 – 68,2	16	154	95	107	0 – 1,0	1,5 – 2,5	1,0 – 2,0	1.605.7503.50
NPT 3/8"	20 – 1	6 – 12	3 – 8,1	16	69,5	22	27	0 – 0,7	0,7 – 1,25		1.605.3803.70
NPT 1/2"	20 – 2	9 – 16	6 – 12	20	74,3	24	29	0 – 0,7	0,7 – 1,25		1.605.1203.70
NPT 1/2"	20 – 3	12,5 – 20,5	9 – 14	20	80,5	30	35	0 – 0,7	0,7 – 1,4		1.605.1203.71
NPT 3/4"	25	16,9 – 26	12,5 – 20,5	20,5	91	36	42	0 – 0,7	0,9 – 1,6	0,7 – 1,4	1.605.3403.70
NPT 1"	32	22 – 33	16,9 – 26	25	96	46	52	0 – 0,7	1,3 – 2,0	0,7 – 1,4	1.605.1003.70
NPT 1 1/4"	40	28 – 41	22 – 33	26	107	55	64	0 – 0,7	1,3 – 2,0	0,7 – 1,4	1.605.5403.70
NPT 1 1/2"	40	28 – 41	22 – 33	26,5	107	55	64	0 – 0,7	1,3 – 2,0	0,7 – 1,4	1.605.6403.70
NPT 2"	50	36 – 52,6	28,9 – 44,4	27	131,5	65	73	0 – 1,0	1,5 – 2,5	1,0 – 2,0	1.605.2003.70
NPT 2 1/2"	63	46 – 65,3	39,9 – 56,3	40	144,5	80	90	0 – 1,0	1,5 – 2,5	1,0 – 2,0	1.605.5203.70
NPT 3"	75	57 – 78	50,5 – 68,2	41,5	154	95	107	0 – 1,0	1,5 – 2,5	1,0 – 2,0	1.605.3003.70


Cable glands for hazardous areas

EXIOS⁺ BARRIER
Metr., NPT


Material	Brass
Seal	Silicone, VMQ
Clamping insert	PA 6
Armouring	Metallic Armour or Screen
Compound	Two-component epoxy compound
Protection	IP 66, 67 and 68 (5 bar)
Operating Temperature	-60° C – 85 C (-76° F – 185° F)



Advice:
- INOX on request



AG	Size	Ø			GL mm	H max. mm	mm	D mm	Armouring Ø mm		Clamping ring 2	Number
		A ₁ mm	A ₂ mm	A ₃ mm					Max. No. cores	Clamping ring 1		
M 16 x1,5	20-1	6 – 12	8,2	7,9	16	68,5	22	27	8	0 – 0,7	0,7 – 1,25	1.606.1600.50
M 20 x1,5	20-1	6 – 12	8,2	7,9	16	68,5	22	27	8	0 – 0,7	0,7 – 1,25	1.606.2000.50
M 20 x1,5	20-2	9 – 16	12	8,8	16	74,3	24	29	10	0 – 0,7	0,7 – 1,25	1.606.2000.51
M 20 x1,5	20-3	12,5 – 20,5	14	11,5	16	80,5	30	35	15	0 – 0,7	0,7 – 1,4	1.606.2000.52
M 25 x1,5	20-3	12,5 – 20,5	14	11,5	16	80,5	30	35	15	0 – 0,7	0,7 – 1,4	1.606.2500.51
M 25 x1,5	25	16,9 – 26	20	16,4	16	91	36	42	25	0 – 0,7	0,9 – 1,6	1.606.2500.50
M 32 x1,5	32	22 – 33	26	21,4	16	96	46	52	45	0 – 0,7	1,3 – 2,0	1.606.3200.50
M 40 x1,5	40	28 – 41	33,2	27,6	16	107	55	64	70	0 – 0,7	1,3 – 2,0	1.606.4000.50
M 50 x1,5	50	36 – 52,6	44,2	37,5	16	131,5	65	73	85	0 – 1,0	1,5 – 2,5	1.606.5000.50
M 63 x1,5	63	46 – 65,3	56,2	47,3	16	144,5	80	90	120	0 – 1,0	1,5 – 2,5	1.606.6300.50
M 75 x1,5	75	57 – 78	68,2	58,0	16	154	95	107	150	0 – 1,0	1,5 – 2,5	1.606.7500.50
NPT 3/8"	20-1	6 – 12	8,2	7,9	16	64	22	27	8	0 – 0,7	0,7 – 1,25	1.606.3800.70
NPT 1/2"	20-2	9 – 12	12	8,8	20	68	24	29	10	0 – 0,7	0,7 – 1,25	1.606.1200.70
NPT 1/2"	20-3	12,5 – 20,5	14	11,5	20	73	30	35	15	0 – 0,7	0,7 – 1,4	1.606.1200.71
NPT 3/4"	25	16,9 – 26	20	16,4	20,5	81,3	36	42	25	0 – 0,7	0,9 – 1,6	1.606.3400.70
NPT 1"	32	22 – 33	26	21,4	25	85,5	46	52	45	0 – 0,7	1,3 – 2,0	1.606.1000.70
NPT 1 1/4"	40	28 – 41	33,2	27,6	26	94,4	55	64	70	0 – 0,7	1,3 – 2,0	1.606.5400.70
NPT 1 1/2"	40	28 – 41	33,2	27,6	26,5	94,4	55	64	70	0 – 0,7	1,3 – 2,0	1.606.6400.70
NPT 2"	50	36 – 52,6	44,2	37,5	27	116,3	65	73	85	0 – 1,0	1,5 – 2,5	1.606.2000.70
NPT 2 1/2"	63	46 – 65,3	56,2	47,3	40	127,6	80	90	120	0 – 1,0	1,5 – 2,5	1.606.5200.70
NPT 3"	75	57 – 78	68,2	58,0	41,5	136,5	95	107	150	0 – 1,0	1,5 – 2,5	1.606.3000.70

Cable glands for hazardous areas

EXIOS⁺ BARRIER

Metr., NPT



I M2 Ex de I Mb IIC Gb
I M2 Ex ta I IIC Da

ATEX Ex Sira-11-ATEX-1110-X



Sir 11.0044X



Material Nickel plated brass

Seal Silicone, VMQ

Clamping insert PA 6


Armouring Metallic Armour or Screen

Compound Two-component epoxy compound

Protection IP 66, 67 and 68 (5 bar)

Operating Temperature -60° C – 85° C (-76° F – 185° F)

Advice:
- INOX on request



AG	Size	Ø A ₁ mm	Ø A ₂ mm	Ø A ₃ mm	GL mm	H max. mm	Ø mm	D mm	Armouring Ø mm			Number
									Max. No. cores	Clamping ring 1	Clamping ring 2	
M 16 x1,5	20-1	6 – 12	8,2	7,9	16	68,5	22	27	8	0 – 0,7	0,7 – 1,25	1.606.1603.50
M 20 x1,5	20-1	6 – 12	8,2	7,9	16	68,5	22	27	8	0 – 0,7	0,7 – 1,25	1.606.2003.50
M 20 x1,5	20-2	9 – 16	12	8,8	16	74,3	24	29	10	0 – 0,7	0,7 – 1,25	1.606.2003.51
M 20 x1,5	20-3	12,5 – 20,5	14	11,5	16	80,5	30	35	15	0 – 0,7	0,7 – 1,4	1.606.2003.52
M 25 x1,5	20-3	12,5 – 20,5	14	11,5	16	80,5	30	35	15	0 – 0,7	0,7 – 1,4	1.606.2503.51
M 25 x1,5	25	16,9 – 26	20	16,4	16	91	36	42	25	0 – 0,7	0,9 – 1,6	1.606.2503.50
M 32 x1,5	32	22 – 33	26	21,4	16	96	46	52	45	0 – 0,7	1,3 – 2,0	1.606.3203.50
M 40 x1,5	40	28 – 41	33,2	27,6	16	107	55	64	70	0 – 0,7	1,3 – 2,0	1.606.4003.50
M 50 x1,5	50	36 – 52,6	44,2	37,5	16	131,5	65	73	85	0 – 1,0	1,5 – 2,5	1.606.5003.50
M 63 x1,5	63	46 – 65,3	56,2	47,3	16	144,5	80	90	120	0 – 1,0	1,5 – 2,5	1.606.6303.50
M 75 x1,5	75	57 – 78	68,2	58,0	16	154	95	107	150	0 – 1,0	1,5 – 2,5	1.606.7503.50
NPT 3/8"	20-1	6 – 12	8,2	7,9	16	64	22	27	8	0 – 0,7	0,7 – 1,25	1.606.3803.70
NPT 1/2"	20-2	9 – 12	12	8,8	20	68	24	29	10	0 – 0,7	0,7 – 1,25	1.606.1203.70
NPT 1/2"	20-3	12,5 – 20,5	14	11,5	20	73	30	35	15	0 – 0,7	0,7 – 1,4	1.606.1203.71
NPT 3/4"	25	16,9 – 26	20	16,4	20,5	81,3	36	42	25	0 – 0,7	0,9 – 1,6	1.606.3403.70
NPT 1"	32	22 – 33	26	21,4	25	85,5	46	52	45	0 – 0,7	1,3 – 2,0	1.606.1003.70
NPT 1 1/4"	40	28 – 41	33,2	27,6	26	94,4	55	64	70	0 – 0,7	1,3 – 2,0	1.606.5403.70
NPT 1 1/2"	40	28 – 41	33,2	27,6	26,5	94,4	55	64	70	0 – 0,7	1,3 – 2,0	1.606.6403.70
NPT 2"	50	36 – 52,6	44,2	37,5	27	116,3	65	73	85	0 – 1,0	1,5 – 2,5	1.606.2003.70
NPT 2 1/2"	63	46 – 65,3	56,2	47,3	40	127,6	80	90	120	0 – 1,0	1,5 – 2,5	1.606.5203.70
NPT 3"	75	57 – 78	68,2	58,0	41,5	136,5	95	107	150	0 – 1,0	1,5 – 2,5	1.606.3003.70


Cable glands for hazardous areas

EXIOS⁺ A2F
Metr.


Material	Brass
Seal	Silicone, VMQ
Clamping insert	PA 6
Protection	IP 66, 67 and 68 (5 bar)
Operating Temperature	-60° C – 105° C (-76° F – 221° F)



Advice:
- Aluminum and Stainless Steel on request



AG	Size	Ø A1 mm	GL mm	H max. mm	Ø mm	D mm	Number	Number Nickel plated brass
M 16 x 1,5	20 – 1	6 – 12	16	36,5	22	27	1.608.1600.50	1.608.1603.50
M 20 x 1,5	20 – 1	6 – 12	16	36,5	22	27	1.608.2000.50	1.608.2003.50
M 20 x 1,5	20 – 2	9 – 16	16	41	24	29	1.608.2000.51	1.608.2003.51
M 25 x 1,5	20 – 3	12,5 – 20,5	16	48	30	35	1.608.2500.50	1.608.2503.50
M 32 x 1,5	25	16,9 – 26	16	48,5	36	42	1.608.3200.50	1.608.3203.50
M 40 x 1,5	32	22 – 33	16	54	46	52	1.608.4000.50	1.608.4003.50
M 50 x 1,5	40	28 – 41	16	60	55	64	1.608.5000.50	1.608.5003.50
M 63 x 1,5	50	40 – 52,6	16	67	65	73	1.608.6300.50	1.608.6303.50
M 75 x 1,5	63	51 – 65,3	16	72	80	90	1.608.7500.50	1.608.7503.50
NPT 3/8"	20 – 1	6 – 12	16	35,6	22	27	1.608.3800.70	1.608.3803.70
NPT 1/2"	20 – 1	6 – 12	20	35,6	22/24	27	1.608.1200.70	1.608.1203.70
NPT 1/2"	20 – 2	9 – 16	20	39,7	24	29	1.608.1200.71	1.608.1203.71
NPT 3/4"	20 – 3	12,5 – 20,5	20,5	47,5	30	35	1.608.3400.70	1.608.3403.70
NPT 1"	25	16,9 – 26	25	47,8	36	42	1.608.1000.70	1.608.1003.70
NPT 1 1/4"	32	22 – 23	26	51,1	46	52	1.608.5400.70	1.608.5403.70
NPT 1 1/2"	40	28 – 41	26,5	56,8	55	64	1.608.6400.70	1.608.6403.70
NPT 2"	50	40 – 52,6	27	65,4	65	73	1.608.2000.70	1.608.2003.70
NPT 2 1/2"	63	51 – 61	40	70,3	80	90	1.608.5200.70	1.608.5203.70
NPT 3"	75	62 – 78	41,5	76,2	95	107	1.608.3000.70	1.608.3003.70

Cable glands for hazardous areas

Red Fibre Washer

Metr., NPT



GFK thread seal

Material

Fiber reinforced Nylon

Operating Temperature

-60 °C – 105 °C



Size	Number
M 16	1.326.1600.50
M 20	1.326.2000.50
M 25	1.326.2500.50
M 32	1.326.3200.50
M 40	1.326.4000.50
M 50	1.326.5000.50
M 63	1.326.6300.50
M 75	1.326.7500.50


Size	Number
1/2"	1.326.1200.70
3/4"	1.326.3400.70
1"	1.326.1000.70
1 1/4"	1.326.5400.70
1 1/2"	1.326.6400.70
2"	1.326.2000.70
2 1/2"	1.326.5200.70
3"	1.326.3000.70

PVC Shroud	
	Material
	PVC
	
Size	Number
20-1	1.802.2000.50
20-2	1.802.2000.51
20-3	1.802.2000.52
25	1.802.2500.50
32	1.802.3200.50
40	1.802.4000.50
50	1.802.5000.50
63	1.802.6300.50
75	1.802.7500.50

Cable glands for hazardous areas

Earthtag

Metr., NPT




Material

Brass




Advice

- INOX on request




Size	Number	Size	Number
M 16	1.022.1600.50	1/2"	1.022.1200.70
M 20	1.022.2000.50	3/4"	1.022.3400.70
M 25	1.022.2500.50	1"	1.022.1000.70
M 32	1.022.3200.50	1 1/4"	1.022.5400.70
M 40	1.022.4000.50	1 1/2"	1.022.6400.70
M 50	1.022.5000.50	2"	1.022.2000.70
M 63	1.022.6300.50	2 1/2"	1.022.5200.70
M 75	1.022.7500.50	3"	1.022.3000.70

Advice
- INOX on request

Serrated Washer

Metr., NPT




Material

INOX







Size	Number
M 16	1.329.1600.50
M 20	1.329.2000.50
M 25	1.329.2500.50
M 32	1.329.3200.50
M 40	1.329.4000.50
M 50	1.329.5000.50
M 63	1.329.6300.50
M 75	1.329.7500.50

Size	Number
1/2"	1.329.1200.70
3/4"	1.329.3400.70
1"	1.329.1000.70
1 1/4"	1.329.5400.70
1 1/2"	1.329.6400.70
2"	1.329.2000.70
2 1/2"	1.329.5200.70
3"	1.329.3000.70

Industrial cable glands

HSK Ex-e Standard cable glands

Cable glands of the HSK-Ex-e-series have been designed for standard applications in hazardous locations type "e" according to EN 60079-0 and EN 60079-7.



You can find in this chapter:

HSK-Ex-e standard cable glands

- made of polyamide
- nickel plated brass with different temperature ranges
- various grades of stainless steel with different temperature ranges

We provide variable clamping ranges, thread lengths, thread types plus different sealing materials and temperature ranges. Our range is completed by global certifications.

For any further question please do not hesitate to contact us. We look forward to develop solutions together with you. You profit of our vast knowledge in development, engineering and production technology

Contact us:

E-Mail: info.et@hummel.com

Tel.: +49(0) 76 66/9 11 10-0

Advice:

- ➔ you can find HSK-EMV-Ex-e cable glands in the next chapter from page 123
- ➔ you can find HSK-Ex-e Multi hole glands and much more in the chapter "HSK-Ex-e cable glands for special applications" from page 131
- ➔ you can find HSK-Ex-d standard cable glands from page 139

HSK Ex-e Standard cable glands

HSK-K-Ex

Metr.



Material Polyamide V0 according to UL 94

Seal Buna-N

O-Ring Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)


Colors grey (RAL 7035)
black (RAL 9005), blue (RAL 5012)



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com



AG	mm	GL	H	mm	Number grey	Number black	Number blue
M 12 x 1,5	3 – 6,5	8	21	15	1.291.1200.50	1.291.1201.50	1.291.1202.50
M 12 x 1,5	2 – 5	8	21	15	1.291.1200.51	1.291.1201.51	1.291.1202.51
M 16 x 1,5	4 – 8	8	22	19	1.291.1600.50	1.291.1601.50	1.291.1602.50
M 16 x 1,5	3 – 6	8	22	19	1.291.1600.51	1.291.1601.51	1.291.1602.51
M 16 x 1,5	5 – 10	8	25	22	1.295.1600.50	1.295.1601.50	1.295.1602.50
M 16 x 1,5	3 – 7	8	25	22	1.295.1600.51	1.295.1601.51	1.295.1602.51
M 20 x 1,5	6,5 – 12	9	27	24	1.291.2000.50	1.291.2001.50	1.291.2002.50
M 20 x 1,5	5 – 9	9	27	24	1.291.2000.51	1.291.2001.51	1.291.2002.51
M 20 x 1,5	10 – 14	9	28	27	1.295.2000.50	1.295.2001.50	1.295.2002.50
M 20 x 1,5	7 – 12	9	28	27	1.295.2000.51	1.295.2001.51	1.295.2002.51
M 25 x 1,5	13 – 18	11	31	33	1.291.2500.50	1.291.2501.50	1.291.2502.50
M 25 x 1,5	9 – 16	11	31	33	1.291.2500.51	1.291.2501.51	1.291.2502.51
M 32 x 1,5	18 – 25	11	39	42	1.291.3200.50	1.291.3201.50	1.291.3202.50
M 32 x 1,5	13 – 20	11	39	42	1.291.3200.51	1.291.3201.51	1.291.3202.51
M 40 x 1,5	22 – 32	13	48	53	1.291.4000.50	1.291.4001.50	1.291.4002.50
M 40 x 1,5	20 – 26	13	48	53	1.291.4000.51	1.291.4001.51	1.291.4002.51
M 50 x 1,5	32 – 38	13	49	60	1.291.5000.50	1.291.5001.50	1.291.5002.50
M 50 x 1,5	25 – 31	13	49	60	1.291.5000.51	1.291.5001.51	1.291.5002.51
M 63 x 1,5	37 – 44	14	49	65/68	1.291.6300.50	1.291.6301.50	1.291.6302.50
M 63 x 1,5	29 – 35	14	49	65/68	1.291.6300.51	1.291.6301.51	1.291.6302.51

Accessories see page 73 and 143

HSK Ex-e Standard cable glands

HSK-K-Ex

Metr.-elongated



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material Polyamide V0 according to UL 94


Seal Buna-N

O-Ring Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)

Colors grey (RAL 7035)
black (RAL 9005), blue (RAL 5012)



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number grey	Number black	Number blue
M 12 x 1,5	3 – 6,5	15	21	15	1.291.1200.30	1.291.1201.30	1.291.1202.30
M 12 x 1,5	2 – 5	15	21	15	1.291.1200.31	1.291.1201.31	1.291.1202.31
M 16 x 1,5	4 – 8	15	22	19	1.291.1600.30	1.291.1601.30	1.291.1602.30
M 16 x 1,5	3 – 6	15	22	19	1.291.1600.31	1.291.1601.31	1.291.1602.31
M 16 x 1,5	5 – 10	15	25	22	1.295.1600.30	1.295.1601.30	1.295.1602.30
M 16 x 1,5	3 – 7	15	25	22	1.295.1600.31	1.295.1601.31	1.295.1602.31
M 20 x 1,5	6,5 – 12	15	27	24	1.291.2000.30	1.291.2001.30	1.291.2002.30
M 20 x 1,5	5 – 9	15	27	24	1.291.2000.31	1.291.2001.31	1.291.2002.31
M 20 x 1,5	10 – 14	15	28	27	1.295.2000.30	1.295.2001.30	1.295.2002.30
M 20 x 1,5	7 – 12	15	28	27	1.295.2000.31	1.295.2001.31	1.295.2002.31
M 25 x 1,5	13 – 18	15	31	33	1.291.2500.30	1.291.2501.30	1.291.2502.30
M 25 x 1,5	9 – 16	15	31	33	1.291.2500.31	1.291.2501.31	1.291.2502.31
M 32 x 1,5	18 – 25	15	39	42	1.291.3200.30	1.291.3201.30	1.291.3202.30
M 32 x 1,5	13 – 20	15	39	42	1.291.3200.31	1.291.3201.31	1.291.3202.31
M 40 x 1,5	22 – 32	18	48	53	1.291.4000.30	1.291.4001.30	1.291.4002.30
M 40 x 1,5	20 – 26	18	48	53	1.291.4000.31	1.291.4001.31	1.291.4002.31
M 50 x 1,5	32 – 38	18	49	60	1.291.5000.30	1.291.5001.30	1.291.5002.30
M 50 x 1,5	25 – 31	18	49	60	1.291.5000.31	1.291.5001.31	1.291.5002.31
M 63 x 1,5	37 – 44	18	49	65/68	1.291.6300.30	1.291.6301.30	1.291.6302.30
M 63 x 1,5	29 – 35	18	49	65/68	1.291.6300.31	1.291.6301.31	1.291.6302.31



Accessories see page 73 and 143

HSK Ex-e Standard cable glands

HSK-K-Ex

PG



Material Polyamide V0 according to UL 94

Seal Buna-N

O-Ring Buna-N


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)

Colors grey (RAL 7035)
black (RAL 9005), blue (RAL 5012)



For the international certificates
please see page 176 or our homepage
www.hummel.com



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number grey	Number black	Number blue
PG 7	3 – 6,5	8	21	15	1.291.0700.14	1.291.0701.14	1.291.0702.14
PG 7	2 – 5	8	21	15	1.291.0700.15	1.291.0701.15	1.291.0702.15
PG 9	4 – 8	8	22	19	1.291.0900.14	1.291.0901.14	1.291.0902.14
PG 9	3 – 6	8	22	19	1.291.0900.15	1.291.0901.15	1.291.0902.15
PG 11	5 – 10	8	25	22	1.291.1100.14	1.291.1101.14	1.291.1102.14
PG 11	3 – 7	8	25	22	1.291.1100.15	1.291.1101.15	1.291.1102.15
PG 13,5	6,5 – 12	9	27	24	1.291.1300.14	1.291.1301.14	1.291.1302.14
PG 13,5	5 – 9	9	27	24	1.291.1300.15	1.291.1301.15	1.291.1302.15
PG 16	10 – 14	10	28	27	1.291.1600.14	1.291.1601.14	1.291.1602.14
PG 16	7 – 12	10	28	27	1.291.1600.15	1.291.1601.15	1.291.1602.15
PG 21	13 – 18	11	31	33	1.291.2100.14	1.291.2101.14	1.291.2102.14
PG 21	9 – 16	11	31	33	1.291.2100.15	1.291.2101.15	1.291.2102.15
PG 29	18 – 25	11	39	42	1.291.2900.14	1.291.2901.14	1.291.2902.14
PG 29	13 – 20	11	39	42	1.291.2900.15	1.291.2901.15	1.291.2902.15
PG 36	22 – 32	13	48	53	1.291.3600.14	1.291.3601.14	1.291.3602.14
PG 36	20 – 26	13	48	53	1.291.3600.15	1.291.3601.15	1.291.3602.15
PG 42	32 – 38	13	49	60	1.291.4200.14	1.291.4201.14	1.291.4202.14
PG 42	25 – 31	13	49	60	1.291.4200.15	1.291.4201.15	1.291.4202.15
PG 48	37 – 44	14	49	65	1.291.4800.14	1.291.4801.14	1.291.4802.14
PG 48	29 – 35	14	49	65	1.291.4800.15	1.291.4801.15	1.291.4802.15

➔ Accessories see page 73 and 143

HSK Ex-e Standard cable glands

HSK-K-Ex

PG-elongated

RoHS



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material Polyamide V0 according to UL 94


Seal Buna-N

O-Ring Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)

Colors grey (RAL 7035)
black (RAL 9005), blue (RAL 5012)



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number grey	Number black	Number blue
PG 7	3–6,5	15	21	15	1.291.0700.60	1.291.0701.60	1.291.0702.60
PG 7	2–5	15	21	15	1.291.0700.61	1.291.0701.61	1.291.0702.61
PG 9	4–8	15	22	19	1.291.0900.60	1.291.0901.60	1.291.0902.60
PG 9	3–6	15	22	19	1.291.0900.61	1.291.0901.61	1.291.0902.61
PG 11	5–10	15	25	22	1.291.1100.60	1.291.1101.60	1.291.1102.60
PG 11	3–7	15	25	22	1.291.1100.61	1.291.1101.61	1.291.1102.61
PG 13,5	6,5–12	15	27	24	1.291.1300.60	1.291.1301.60	1.291.1302.60
PG 13,5	5–9	15	27	24	1.291.1300.61	1.291.1301.61	1.291.1302.61
PG 16	10–14	15	28	27	1.291.1600.60	1.291.1601.60	1.291.1602.60
PG 16	7–12	15	28	27	1.291.1600.61	1.291.1601.61	1.291.1602.61
PG 21	13–18	15	31	33	1.291.2100.60	1.291.2101.60	1.291.2102.60
PG 21	9–16	15	31	33	1.291.2100.61	1.291.2101.61	1.291.2102.61
PG 29	18–25	15	39	42	1.291.2900.60	1.291.2901.60	1.291.2902.60
PG 29	13–20	15	39	42	1.291.2900.61	1.291.2901.61	1.291.2902.61
PG 36	22–32	18	48	53	1.291.3600.60	1.291.3601.60	1.291.3602.60
PG 36	20–26	18	48	53	1.291.3600.61	1.291.3601.61	1.291.3602.61
PG 42	32–38	18	49	60	1.291.4200.60	1.291.4201.60	1.291.4202.60
PG 42	25–31	18	49	60	1.291.4200.61	1.291.4201.61	1.291.4202.61
PG 48	37–44	18	49	65	1.291.4800.60	1.291.4801.60	1.291.4802.60
PG 48	29–35	18	49	65	1.291.4800.61	1.291.4801.61	1.291.4802.61

➔ Accessories see page 73 and 143

HSK Ex-e Standard cable glands

HSK-K-Ex

NPT



Material Polyamide V0 according to UL 94

Seal Buna-N

O-Ring Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range


Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)

Colors grey (RAL 7035)
black (RAL 9005), blue (RAL 5012)



II 2G 1D

For the international certificates
please see page 176 or our homepage
www.hummel.com



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number grey	Number black	Number blue
NPT 3/8"	4 – 8	15	22	19/22	1.291.3800.70	1.291.3801.70	1.291.3802.70
NPT 3/8"	2 – 6	15	22	19/22	1.291.3800.71	1.291.3801.71	1.291.3802.71
NPT 1/2"	6,5 – 12	13	27	24	1.291.1200.70	1.291.1201.70	1.291.1202.70
NPT 1/2"	5 – 9	13	27	24	1.291.1200.71	1.291.1201.71	1.291.1202.71
NPT 1/2" (16)	10 – 14	13	28	27	1.291.1216.70	1.291.1217.70	1.291.1218.70
NPT 1/2" (16)	7 – 12	13	28	27	1.291.1216.71	1.291.1217.71	1.291.1218.71
NPT 3/4"	13 – 18	14	31	33	1.291.3400.70	1.291.3401.70	1.291.3402.70
NPT 3/4"	9 – 16	14	31	33	1.291.3400.71	1.291.3401.71	1.291.3402.71
NPT 1"	18 – 25	19	39	42	1.291.1000.70	1.291.1001.70	1.291.1002.70
NPT 1"	13 – 20	19	39	42	1.291.1000.71	1.291.1001.71	1.291.1002.71
NPT 1 1/4"	18 – 25	16	39	42/46	1.291.5400.70	1.291.5401.70	1.291.5402.70
NPT 1 1/4"	13 – 20	16	39	42/46	1.291.5400.71	1.291.5401.71	1.291.5402.71
NPT 1 1/2"	22 – 32	20	48	53	1.291.6400.70	1.291.6401.70	1.291.6402.70
NPT 1 1/2"	20 – 26	20	48	53	1.291.6400.71	1.291.6401.71	1.291.6402.71

➔ Accessories see page 73 and 143

HSK Ex-e Standard cable glands

HSK-M-Ex / HSK-M-PVDF-Ex

Metr.



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material Nickel plated brass


Clamping insert Polyamide / PVDF

Seal Buna-N / FPM

O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C
(-76 °F – 203 °F) / -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-M-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-M-Ex -60 °C – 95 °C (-76 °F – 203 °F)	Number HSK-M-PVDF-Ex -20 °C – 130 °C (-4 °F – 266 °F)
M 12 x 1,5	3 – 6,5	6,5	19	14	1.610.1200.50	1.640.1200.50	1.660.1200.50
M 12 x 1,5	2 – 5	6,5	19	14	1.610.1200.51	1.640.1200.51	1.660.1200.51
M 16 x 1,5	4 – 8	6	21	17 / 19	1.610.1600.50	1.640.1600.50	1.660.1600.50
M 16 x 1,5	2 – 6	6	21	17 / 19	1.610.1600.51	1.640.1600.51	1.660.1600.51
M 16 x 1,5	6 – 10	6	22	20	1.610.1611.50	1.640.1611.50	1.660.1611.50
M 16 x 1,5	3 – 7	6	22	20	1.610.1611.51	1.640.1611.51	1.660.1611.51
M 20 x 1,5	6 – 12	6	23	22	1.610.2000.50	1.640.2000.50	1.660.2000.50
M 20 x 1,5	5 – 9	6	23	22	1.610.2000.51	1.640.2000.51	1.660.2000.51
M 20 x 1,5	10 – 14	6	24	24	1.610.2016.50	1.640.2016.50	1.660.2016.50
M 20 x 1,5	7 – 12	6	24	24	1.610.2016.51	1.640.2016.51	1.660.2016.51
M 25 x 1,5	14 – 18	7	26	30	1.610.2500.50	1.640.2500.50	1.660.2500.50
M 25 x 1,5	10 – 16	7	26	30	1.610.2500.51	1.640.2500.51	1.660.2500.51
M 32 x 1,5	20 – 25	8	31	40	1.610.3200.50	1.640.3200.50	1.660.3200.50
M 32 x 1,5	13 – 20	8	31	40	1.610.3200.51	1.640.3200.51	1.660.3200.51
M 40 x 1,5	22 – 32	8	37	50	1.610.4000.50	1.640.4000.50	1.660.4000.50
M 40 x 1,5	20 – 26	8	37	50	1.610.4000.51	1.640.4000.51	1.660.4000.51
M 50 x 1,5	32 – 38	9	37	57	1.610.5000.50	1.640.5000.50	
M 50 x 1,5	25 – 31	9	37	57	1.610.5000.51	1.640.5000.51	
M 63 x 1,5	37 – 44	10	38	64 / 68	1.610.6300.50	1.640.6300.50	
M 63 x 1,5	29 – 35	10	38	64 / 68	1.610.6300.51	1.640.6300.51	

➔ Accessories see page 73 and 143

HSK Ex-e Standard cable glands

HSK-M-Ex / HSK-M-PVDF-Ex


Metr.-elongated



Material	Nickel plated brass
Clamping insert	Polyamide / PVDF
Seal	Buna-N / FPM
O-Ring	Buna-N / FPM
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C (-76 °F – 203 °F) / -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)



For the international certificates
please see page 176 or our homepage
www.hummel.com



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number HSK-M-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-M-Ex -60 °C – 95 °C (-76 °F – 203 °F)	Number HSK-M-PVDF-Ex -20 °C – 130 °C (-4 °F – 266 °F)
M 12 x 1,5	3 – 6,5	10	19	14	1.610.1200.30	1.640.1200.30	1.660.1200.30
M 12 x 1,5	2 – 5	10	19	14	1.610.1200.31	1.640.1200.31	1.660.1200.31
M 16 x 1,5	4 – 8	10	21	17 / 19	1.610.1600.30	1.640.1600.30	1.660.1600.30
M 16 x 1,5	2 – 6	10	21	17 / 19	1.610.1600.31	1.640.1600.31	1.660.1600.31
M 16 x 1,5	6 – 10	10	22	20	1.610.1611.30	1.640.1611.30	1.660.1611.30
M 16 x 1,5	3 – 7	10	22	20	1.610.1611.31	1.640.1611.31	1.660.1611.31
M 20 x 1,5	6 – 12	10	23	22	1.610.2000.30	1.640.2000.30	1.660.2000.30
M 20 x 1,5	5 – 9	10	23	22	1.610.2000.31	1.640.2000.31	1.660.2000.31
M 20 x 1,5	10 – 14	10	24	24	1.610.2016.30	1.640.2016.30	1.660.2016.30
M 20 x 1,5	7 – 12	10	24	24	1.610.2016.31	1.640.2016.31	1.660.2016.31
M 25 x 1,5	14 – 18	12	26	30	1.610.2500.30	1.640.2500.30	1.660.2500.30
M 25 x 1,5	10 – 16	12	26	30	1.610.2500.31	1.640.2500.31	1.660.2500.31
M 32 x 1,5	20 – 25	12	31	40	1.610.3200.30	1.640.3200.30	1.660.3200.30
M 32 x 1,5	13 – 20	12	31	40	1.610.3200.31	1.640.3200.31	1.660.3200.31
M 40 x 1,5	22 – 32	15	37	50	1.610.4000.30	1.640.4000.30	1.660.4000.30
M 40 x 1,5	20 – 26	15	37	50	1.610.4000.31	1.640.4000.31	1.660.4000.31
M 50 x 1,5	32 – 38	15	37	57	1.610.5000.30	1.640.5000.30	
M 50 x 1,5	25 – 31	15	37	57	1.610.5000.31	1.640.5000.31	
M 63 x 1,5	37 – 44	15	38	64 / 68	1.610.6300.30	1.640.6300.30	
M 63 x 1,5	29 – 35	15	38	64 / 68	1.610.6300.31	1.640.6300.31	

➔ Accessories see page 73 and 143

HSK Ex-e Standard cable glands

HSK-M-Ex / HSK-M-PVDF-Ex

PG, NPT

RoHS



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material Nickel plated brass


Clamping insert Polyamide / PVDF

Seal Buna-N / FPM

O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C
(-76 °F – 203 °F) / -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-M-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-M-Ex -60 °C – 95 °C (-76 °F – 203 °F)	Number HSK-M-PVDF-Ex -20 °C – 130 °C (-4 °F – 266 °F)
PG 7	3 – 6,5	5	19	14	1.610.0700.01	1.640.0700.01	1.660.0700.01
PG 7	2 – 5	5	19	14	1.610.0700.15	1.640.0700.15	1.660.0700.15
PG 9	4 – 8	6	21	17	1.610.0900.01	1.640.0900.01	1.660.0900.01
PG 9	2 – 6	6	21	17	1.610.0900.15	1.640.0900.15	1.660.0900.15
PG 11	6 – 10	6	22	20	1.610.1100.01	1.640.1100.01	1.660.1100.01
PG 11	3 – 7	6	22	20	1.610.1100.15	1.640.1100.15	1.660.1100.15
PG 13,5	6 – 12	6,5	24	22	1.610.1300.01	1.640.1300.01	1.660.1300.01
PG 13,5	5 – 9	6,5	24	22	1.610.1300.15	1.640.1300.15	1.660.1300.15
PG 16	10 – 14	6,5	23	24	1.610.1600.01	1.640.1600.01	1.660.1600.01
PG 16	7 – 12	6,5	23	24	1.610.1600.15	1.640.1600.15	1.660.1600.15
PG 21	14 – 18	7	24	30	1.610.2100.01	1.640.2100.01	1.660.2100.01
PG 21	10 – 16	7	24	30	1.610.2100.15	1.640.2100.15	1.660.2100.15
PG 29	20 – 25	8	29	40	1.610.2900.01	1.640.2900.01	1.660.2900.01
PG 29	13 – 20	8	29	40	1.610.2900.15	1.640.2900.15	1.660.2900.15
PG 36	22 – 32	8	35	50	1.610.3600.01	1.640.3600.01	1.660.3600.01
PG 36	20 – 26	8	35	50	1.610.3600.15	1.640.3600.15	1.660.3600.15
PG 42	32 – 38	9	37	57	1.610.4200.01	1.640.4200.01	1.660.4200.01
PG 42	25 – 31	9	37	57	1.610.4200.15	1.640.4200.15	1.660.4200.15
PG 48	37 – 44	10	38	64	1.610.4800.01	1.640.4800.01	1.660.4800.01
PG 48	29 – 35	10	38	64	1.610.4800.15	1.640.4800.15	1.660.4800.15
NPT 3/8"	4 – 8	15	21	17/19	1.610.3800.70	1.640.3800.70	1.660.3800.70
NPT 3/8"	2 – 6	15	21	17/19	1.610.3800.71	1.640.3800.71	1.660.3800.71
NPT 1/2"	6 – 12	13	24	22/24	1.610.1200.70	1.640.1200.70	1.660.1200.70
NPT 1/2"	5 – 9	13	24	22/24	1.610.1200.71	1.640.1200.71	1.660.1200.71
NPT 3/4"	14 – 18	13	25	30	1.610.3400.70	1.640.3400.70	1.660.3400.70
NPT 3/4"	10 – 16	13	25	30	1.610.3400.71	1.640.3400.71	1.660.3400.71
NPT 1"	20 – 25	19	29	40	1.610.1000.70	1.640.1000.70	
NPT 1"	13 – 20	19	29	40	1.610.1000.71	1.640.1000.71	

➔ Accessories see page 73 and 143

HSK Ex-e Standard cable glands

HSK-M-Ex / HSK-M-PVDF-Ex

PG-elongated



Material Nickel plated brass

Clamping insert Polyamide / PVDF

Seal Buna-N / FPM

O-Ring Buna-N / FPM


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C
(-76 °F – 203 °F) / -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)



II 2G 1D

For the international certificates
please see page 176 or our homepage
www.hummel.com



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number HSK-M-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-M-Ex -60 °C – 95 °C (-76 °F – 203 °F)	Number HSK-M-PVDF-Ex -20 °C – 130 °C (-4 °F – 266 °F)
PG 7	3 – 6,5	10	19	14	1.610.0700.60	1.640.0700.60	1.660.0700.60
PG 7	2 – 5	10	19	14	1.610.0700.61	1.640.0700.61	1.660.0700.61
PG 9	4 – 8	10	21	17	1.610.0900.60	1.640.0900.60	1.660.0900.60
PG 9	2 – 6	10	21	17	1.610.0900.61	1.640.0900.61	1.660.0900.61
PG 11	6 – 10	10	22	20	1.610.1100.60	1.640.1100.60	1.660.1100.60
PG 11	3 – 7	10	22	20	1.610.1100.61	1.640.1100.61	1.660.1100.61
PG 13,5	6 – 12	10	24	22	1.610.1300.60	1.640.1300.60	1.660.1300.60
PG 13,5	5 – 9	10	24	22	1.610.1300.61	1.640.1300.61	1.660.1300.61
PG 16	10 – 14	10	23	24	1.610.1600.60	1.640.1600.60	1.660.1600.60
PG 16	7 – 12	10	23	24	1.610.1600.61	1.640.1600.61	1.660.1600.61
PG 21	14 – 18	12	24	30	1.610.2100.60	1.640.2100.60	1.660.2100.60
PG 21	10 – 16	12	24	30	1.610.2100.61	1.640.2100.61	1.660.2100.61
PG 29	20 – 25	12	29	40	1.610.2900.60	1.640.2900.60	1.660.2900.60
PG 29	13 – 20	12	29	40	1.610.2900.61	1.640.2900.61	1.660.2900.61
PG 36	22 – 32	15	35	50	1.610.3600.60	1.640.3600.60	1.660.3600.60
PG 36	20 – 26	15	35	50	1.610.3600.61	1.640.3600.61	1.660.3600.61
PG 42	32 – 38	15	37	57	1.610.4200.60	1.640.4200.60	1.660.4200.60
PG 42	25 – 31	15	37	57	1.610.4200.61	1.640.4200.61	1.660.4200.61
PG 48	37 – 44	15	38	64	1.610.4800.60	1.640.4800.60	1.660.4800.60
PG 48	29 – 35	15	38	64	1.610.4800.61	1.640.4800.61	1.660.4800.61

➔ Accessories see page 73 and 143

HSK Ex-e Standard cable glands

HSK-INOX-Ex / HSK-INOX-PVDF-Ex

Metr.



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material INOX (1.4305)

Clamping insert Polyamide / PVDF



Seal Buna-N / FPM

O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C
(-76 °F – 203 °F) / -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)

Advice:
- AISI 316L on request



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number HSK-INOX-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-INOX-Ex -60 °C – 95 °C (-76 °F – 203 °F)	Number HSK-INOX-PVDF-Ex -20 °C – 130 °C (-4 °F – 266 °F)
M 12 x 1,5	3 – 6,5	6,5	19	14	1.612.1200.50	1.642.1200.50	1.662.1200.50
M 12 x 1,5	2 – 5	6,5	19	14	1.612.1200.51	1.642.1200.51	1.662.1200.51
M 16 x 1,5	5 – 10	6	22	22	1.612.1600.50	1.642.1600.50	1.662.1600.50
M 16 x 1,5	3 – 7	6	22	22	1.612.1600.51	1.642.1600.51	1.662.1600.51
M 20 x 1,5	10 – 14	6	23	24	1.612.2000.50	1.642.2000.50	1.662.2000.50
M 20 x 1,5	7 – 12	6	23	24	1.612.2000.51	1.642.2000.51	1.662.2000.51
M 25 x 1,5	13 – 18	7	24	30	1.612.2500.50	1.642.2500.50	1.662.2500.50
M 25 x 1,5	9 – 16	7	24	30	1.612.2500.51	1.642.2500.51	1.662.2500.51
M 32 x 1,5	20 – 25	8	29	41	1.612.3200.50	1.642.3200.50	1.662.3200.50
M 32 x 1,5	13 – 20	8	29	41	1.612.3200.51	1.642.3200.51	1.662.3200.51
M 40 x 1,5	22 – 32	8	35	50	1.612.4000.50	1.642.4000.50	1.662.4000.50
M 40 x 1,5	20 – 26	8	35	50	1.612.4000.51	1.642.4000.51	1.662.4000.51

➔ Accessories see page 73 and 143

HSK Ex-e Standard cable glands

HSK-INOX-Ex / HSK-INOX-PVDF-Ex

PG

Material INOX (1.4305)

Clamping insert Polyamide / PVDF

Seal Buna-N / FPM

O-Ring Buna-N / FPM


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -20°C – 95 °C (-4°F – 203°F) / -60°C – 95 °C
(-76°F – 203°F) / -20°C – 130°C (-4°F – 266°F) (PVDF)

Advice:
- AISI 316L on request

RoHS

II 2G 1D

 For the international certificates
please see page 176 or our homepage
www.hummel.com


AG	$\varnothing$ mm	GL mm	H mm	 mm	Number HSK-INOX-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-INOX-Ex -60 °C – 95 °C (-76 °F – 203 °F)	Number HSK-INOX-PVDF-Ex -20 °C – 130 °C (-4 °F – 266 °F)
PG 7	3 – 6,5	5	19	14	1.612.0700.01	1.642.0700.01	1.662.0700.01
PG 7	2 – 5	5	19	14	1.612.0700.15	1.642.0700.15	1.662.0700.15
PG 9	4 – 8	6	21	17	1.612.0900.01	1.642.0900.01	1.662.0900.01
PG 9	2 – 6	6	21	17	1.612.0900.15	1.642.0900.15	1.662.0900.15
PG 11	5 – 10	6	22	22	1.612.1100.01	1.642.1100.01	1.662.1100.01
PG 11	3 – 7	6	22	22	1.612.1100.15	1.642.1100.15	1.662.1100.15
PG 13,5	6 – 12	6	24	22	1.612.1300.01	1.642.1300.01	1.662.1300.01
PG 13,5	5 – 9	6	24	22	1.612.1300.15	1.642.1300.15	1.662.1300.15
PG 16	10 – 14	6	23	24	1.612.1600.01	1.642.1600.01	1.662.1600.01
PG 16	7 – 12	6	23	24	1.612.1600.15	1.642.1600.15	1.662.1600.15
PG 21	13 – 18	7	24	30	1.612.2100.01	1.642.2100.01	1.662.2100.01
PG 21	9 – 16	7	24	30	1.612.2100.15	1.642.2100.15	1.662.2100.15
PG 29	20 – 25	8	29	41	1.612.2900.01	1.642.2900.01	1.662.2900.01
PG 29	13 – 20	8	29	41	1.612.2900.15	1.642.2900.15	1.662.2900.15
PG 36	22 – 32	8	35	50	1.612.3600.01	1.642.3600.01	1.662.3600.01
PG 36	20 – 26	8	35	50	1.612.3600.15	1.642.3600.15	1.662.3600.15

Accessories see page 73 and 143

Industrial cable glands

HSK-EMC-Ex-e cable glands

Cable glands of the HSK-EMC-Ex-series have been designed for standard applications in hazardous locations type "e" according to EN 60079-0 and EN 60079-7.



You can find in this chapter:

HSK-EMC-Ex-e cable glands

- made of nickel plated brass with different temperature ranges
- various grades of stainless steel with different temperature ranges

We provide variable clamping ranges, thread lengths, thread types plus different sealing materials and temperature ranges. Our range is completed by global certifications.

For any further question please do not hesitate to contact us. We look forward to develop solutions together with you. You profit of our vast knowledge in development, engineering and production technology.

Contact us:

E-Mail: info.et@hummel.com

Tel.: +49 (0) 76 66/9 11 10-0

Advice:

- ➔ you can find HSK-Ex-e Multi hole glands and much more in the chapter "HSK-Ex-e cable glands for special applications" from page 131
- ➔ you can find HSK-Ex-d standard cable glands from page 139

HSK-EMC-Ex-e cable glands


HSK-M-EMV-D-Ex

Metr.



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material	Nickel plated brass
Clamping insert	Metalised Polyamide
Seal	Buna-N
O-Ring	Buna-N
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C (-76 °F – 203 °F)



AG	Ø mm	GL mm	H mm	mm	Number HSK-M-EMV-D-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-M-EMV-D-Ex -60 °C – 95 °C (-76 °F – 203 °F)
M 16 x 1,5	5–10	6	29	20	1.636.1600.50	1.637.1600.50
M 20 x 1,5	10–14	6	31	24	1.636.2000.50	1.637.2000.50
M 25 x 1,5	13–18	7	38	30	1.636.2500.50	1.637.2500.50
M 32 x 1,5	18–25	8	43	40	1.636.3200.50	1.637.3200.50
M 40 x 1,5	24–32	8	51	50	1.636.4000.50	1.637.4000.50

➔ Accessories see page 73 and 143



HSK-M-EMV-D-Ex

Metr.-elongated



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material	Nickel plated brass
Clamping insert	Metalised Polyamide
Seal	Buna-N
O-Ring	Buna-N
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C (-76 °F – 203 °F)



AG	Ø mm	GL mm	H mm	mm	Number HSK-M-EMV-D-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-M-EMV-D-Ex -60 °C – 95 °C (-76 °F – 203 °F)
M 16 x 1,5	5–10	10	29	20	1.636.1600.30	1.637.1600.30
M 20 x 1,5	10–14	10	31	24	1.636.2000.30	1.637.2000.30
M 25 x 1,5	13–18	12	38	30	1.636.2500.30	1.637.2500.30
M 32 x 1,5	18–25	12	43	40	1.636.3200.30	1.637.3200.30
M 40 x 1,5	24–32	15	51	50	1.636.4000.30	1.637.4000.30

➔ Accessories see page 73 and 143

HSK-EMC-Ex-e cable glands

HSK-M-EMV-D-Ex

PG

RoHS



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material Nickel plated brass

Clamping insert Metalised Polyamide


Seal Buna-N

O-Ring Buna-N


Protection IP 68 – 10 bar / IP 69K
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) /
-60 °C – 95 °C (-76 °F – 203 °F)

Advice:
- Elongated threads on request



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-M-EMV-D-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-M-EMV-D-Ex -60 °C – 95 °C (-76 °F – 203 °F)
PG 11	5–10	6	29	20	1.636.1100.01	1.637.1100.01
PG 13,5	6–12	6,5	31	22	1.636.1300.01	1.637.1300.01
PG 16	10–14	6,5	32	24	1.636.1600.01	1.637.1600.01
PG 21	13–18	7	38	30	1.636.2100.01	1.637.2100.01
PG 29	18–25	8	43	40	1.636.2900.01	1.637.2900.01
PG 36	22–32	8	48	50	1.636.3600.01	1.637.3600.01



➔ Accessories see page 73 and 143

HSK-EMC-Ex-e cable glands

HSK-M-EMV-Ex

Metr.



Material Nickel plated brass

Clamping insert Polyamide

Seal Buna-N

O-Ring Buna-N

 Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

 Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) /
-60 °C – 95 °C (-76 °F – 203 °F)

Advice:

- Elongated threads on request
- Stainless steel on request




II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com

See our homepage www.hummel.com
for assembling advices for maximum
cable diameters



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number HSK-M-EMV-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-M-EMV-Ex -60 °C – 95 °C (-76 °F – 203 °F)
M 12 x 1,5	3 – 6,5	6,5	19	14	1.616.1200.50	1.646.1200.50
M 12 x 1,5	2 – 5	6,5	19	14	1.616.1200.51	1.646.1200.51
M 16 x 1,5	6 – 10	6	22	20	1.616.1600.50	1.646.1600.50
M 16 x 1,5	3 – 7	6	22	20	1.616.1600.51	1.646.1600.51
M 20 x 1,5	10 – 14	6	23	24	1.616.2000.50	1.646.2000.50
M 20 x 1,5	7 – 12	6	23	24	1.616.2000.51	1.646.2000.51
M 25 x 1,5	14 – 18	7	24	30	1.616.2500.50	1.646.2500.50
M 25 x 1,5	10 – 16	7	24	30	1.616.2500.51	1.646.2500.51
M 32 x 1,5	20 – 25	8	31	40	1.616.3200.50	1.646.3200.50
M 32 x 1,5	13 – 20	8	31	40	1.616.3200.51	1.646.3200.51
M 40 x 1,5	22 – 32	8	37	50	1.616.4000.50	1.646.4000.50
M 40 x 1,5	20 – 26	8	37	50	1.616.4000.51	1.646.4000.51
M 50 x 1,5	32 – 38	9	37	57	1.616.5000.50	1.646.5000.50
M 50 x 1,5	25 – 31	9	37	57	1.616.5000.51	1.646.5000.51
M 63 x 1,5	37 – 44	10	38	64/68	1.616.6300.50	1.646.6300.50
M 63 x 1,5	29 – 35	10	38	64/68	1.616.6300.51	1.646.6300.51

➔ Accessories see page 73 and 143

HSK-EMC-Ex-e cable glands

HSK-M-EMV-Ex / HSK-M-EMV-PVDF-Ex

PG, NPT

RoHS



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material Nickel plated brass

Clamping insert Polyamide / PVDF

Seal Buna-N / FPM


O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C
(-76 °F – 203 °F) / -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)

Advice:

- Elongated threads on request



AG	mm	GL mm	H mm	mm	Number HSK-M-EMV-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-M-EMV-Ex -60 °C – 95 °C (-76 °F – 203 °F)	Number HSK-M-EMV-PVDF-Ex -20 °C – 130 °C (-4 °F – 266 °F)
PG 7	3 – 6,5	5	19	14	1.616.0700.01	1.646.0700.01	1.666.0700.01
PG 7	2 – 5	5	19	14	1.616.0700.15	1.646.0700.15	1.666.0700.15
PG 9	4 – 8	6	21	17	1.616.0900.01	1.646.0900.01	1.666.0900.01
PG 9	2 – 6	6	21	17	1.616.0900.15	1.646.0900.15	1.666.0900.15
PG 11	6 – 10	6	22	20	1.616.1100.01	1.646.1100.01	1.666.1100.01
PG 11	3 – 7	6	22	20	1.616.1100.15	1.646.1100.15	1.666.1100.15
PG 13,5	6 – 12	6,5	24	22	1.616.1300.01	1.646.1300.01	1.666.1300.01
PG 13,5	5 – 9	6,5	24	22	1.616.1300.15	1.646.1300.15	1.666.1300.15
PG 16	10 – 14	6,5	23	24	1.616.1600.01	1.646.1600.01	1.666.1600.01
PG 16	7 – 12	6,5	23	24	1.616.1600.15	1.646.1600.15	1.666.1600.15
PG 21	14 – 18	7	24	30	1.616.2100.01	1.646.2100.01	1.666.2100.01
PG 21	10 – 16	7	24	30	1.616.2100.15	1.646.2100.15	1.666.2100.15
PG 29	20 – 25	8	29	40	1.616.2900.01	1.646.2900.01	1.666.2900.01
PG 29	13 – 20	8	29	40	1.616.2900.15	1.646.2900.15	1.666.2900.15
PG 36	22 – 32	8	35	50	1.616.3600.01	1.646.3600.01	1.666.3600.01
PG 36	20 – 26	8	35	50	1.616.3600.15	1.646.3600.15	1.666.3600.15
PG 42	32 – 38	9	37	57	1.616.4200.01	1.646.4200.01	1.666.4200.01
PG 42	25 – 31	9	37	57	1.616.4200.15	1.646.4200.15	1.666.4200.15
PG 48	37 – 44	10	38	64	1.616.4800.01	1.646.4800.01	1.666.4800.01
PG 48	29 – 35	10	38	64	1.616.4800.15	1.646.4800.15	1.666.4800.15
NPT 3/8"	4 – 8	15	21	17/19	1.616.3800.70	1.646.3800.70	1.666.3800.70
NPT 3/8"	2 – 6	15	21	17/19	1.616.3800.71	1.646.3800.71	1.666.3800.71
NPT 1/2"	6 – 12	13	24	22/24	1.616.1200.70	1.646.1200.70	1.666.1200.70
NPT 1/2"	5 – 9	13	24	22/24	1.616.1200.71	1.646.1200.71	1.666.1200.71
NPT 3/4"	14 – 18	13	25	30	1.616.3400.70	1.646.3400.70	1.666.3400.70
NPT 3/4"	10 – 16	13	25	30	1.616.3400.71	1.646.3400.71	1.666.3400.71

Accessories see page 73 and 143

HSK-EMC-Ex-e cable glands

HSK-MZ-EMV-Ex

Metr.



Material Nickel plated brass

Clamping insert Polyamide

Seal Buna-N

O-Ring Buna-N


 Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

 Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) /
-60 °C – 95 °C (-76 °F – 203 °F)

 Advice:
- Elongated threads on request


II 2G 1D


 For the international certificates
please see page 176 or our homepage
www.hummel.com

 See our homepage www.hummel.com
for assembling advices for maximum
cable diameters


AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-M-EMV-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-M-EMV-Ex -60 °C – 95 °C (-76 °F – 203 °F)
M 12 x 1,5	3 – 6,5	6,5	26	14	1.617.1200.50	1.647.1200.50
M 16 x 1,5	6 – 10	6	29	20	1.617.1600.50	1.647.1600.50
M 20 x 1,5	10 – 14	6	32	24	1.617.2000.50	1.647.2000.50
M 25 x 1,5	14 – 18	7	35	30	1.617.2500.50	1.647.2500.50
M 32 x 1,5	20 – 25	8	41	40	1.617.3200.50	1.647.3200.50
M 40 x 1,5	24 – 32	8	48	50	1.617.4000.50	1.647.4000.50
M 50 x 1,5	32 – 38	9	51	57	1.617.5000.50	1.647.5000.50
M 50 x 1,5	28 – 31	9	51	57	1.617.5000.51	1.647.5000.51
M 63 x 1,5	37 – 44	10	52	68	1.617.6300.50	1.647.6300.50
M 63 x 1,5	32 – 35	10	52	68	1.617.6300.51	1.647.6300.51

HSK-EMC-Ex-e cable glands

HSK-MZ-EMV-Ex / HSK-MZ-EMV-PVDF-Ex

PG

RoHS



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material Nickel plated brass

Clamping insert Polyamide / PVDF


Seal Buna-N / FPM

O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C
(-76 °F – 203 °F) / -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)

Advice:
- Elongated threads on request



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-MZ-EMV-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-MZ-EMV-Ex -60 °C – 95 °C (-76 °F – 203 °F)	Number HSK-MZ-EMV-PVDF-Ex -20 °C – 130 °C (-4 °F – 266 °F)
PG 7	3–6,5	5	26	14	1.617.0700.01	1.647.0700.01	1.667.0700.01
PG 9	4–8	6	28	17	1.617.0900.01	1.647.0900.01	1.667.0900.01
PG 11	6–10	6	29	20	1.617.1100.01	1.647.1100.01	1.667.1100.01
PG 13,5	7–12	6,5	33	22	1.617.1300.01	1.647.1300.01	1.667.1300.01
PG 16	10–14	6,5	32	24	1.617.1600.01	1.647.1600.01	1.667.1600.01
PG 21	13–18	7	35	30	1.617.2100.01	1.647.2100.01	1.667.2100.01
PG 29	20–25	8	41	40	1.617.2900.01	1.647.2900.01	1.667.2900.01
PG 36	24–32	8	48	50	1.617.3600.01	1.647.3600.01	1.667.3600.01
PG 42	32–38	9	51	57	1.617.4200.01	1.647.4200.01	1.667.4200.01
PG 42	28–31	9	51	57	1.617.4200.15	1.647.4200.15	1.667.4200.15
PG 48	37–44	10	51	64	1.617.4800.01	1.647.4800.01	1.667.4800.01
PG 48	32–35	10	51	64	1.617.4800.15	1.647.4800.15	1.667.4800.15

➔ Accessories see page 73 and 143

HSK-EMC-Ex-e cable glands

HSK-MZ-EMV-Ex / HSK-MZ-EMV-PVDF-Ex


NPT


Material	Nickel plated brass
Clamping insert	Polyamide / PVDF
Seal	Buna-N / FPM
O-Ring	Buna-N / FPM
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C (-76 °F – 203 °F) / -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)

Advice:
- Elongated threads on request



For the international certificates
please see page 176 or our homepage
www.hummel.com



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-MZ-EMV-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-MZ-EMV-Ex -60 °C – 95 °C (-76 °F – 203 °F)	Number HSK-MZ-EMV-PVDF-Ex -20 °C – 130 °C (-4 °F – 266 °F)
NPT 3/8"	4–8	15	27	17/19	1.617.3800.70	1.647.3800.70	1.667.3800.70
NPT 1/2"	7–12	13	31	22/24	1.617.1200.70	1.647.1200.70	1.667.1200.70
NPT 3/4"	13–18	13	36	30	1.617.3400.70	1.647.3400.70	1.667.3400.70

➔ Accessories see page 73 and 143

Industrial cable glands

HSK Ex-e cable glands for special applications

Cable glands of the HSK-Ex-e-series have been designed for standard applications in hazardous locations type "e" according to EN 60079-0 and EN 60079-7.



You can find in this chapter:

HSK-Ex-e cable glands

- made of polyamide and nickel plated brass with multi hole and flat cable sealing inserts
- made of polyamide and nickel plated brass with additional stain relief

We provide variable clamping ranges, thread lengths, thread types plus different sealing materials and temperature ranges. Our range is completed by global certifications.

For any further question please do not hesitate to contact us. We look forward to develop solutions together with you. You profit of our vast knowledge in development, engineering and production technology.

Contact us:

E-Mail: info.et@hummel.com

Tel.: +49(0) 76 66/9 11 10-0

Advice:

➔ you can find HSK-Ex-d standard cable glands from page 139

HSK Ex-e cable glands for special applications

HSK-K-Multi-Ex

Metr., PG, NPT



Material Polyamide V0 according to UL 94

Seal Elastomer

Protection IP 68

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)


Colors grey (RAL 7035), black (RAL 9005)

O-Ring Buna-N

Advice:
- Installation instruction see page 176



For the international certificates
please see page 176 or our homepage
www.hummel.com



AG	GL mm	H mm	 mm	Number of Holes x d	Number grey	Number black	Number of Holes x d	Number grey	Number black
M 16 x 1,5	8	22	19	4 x 1,4	1.599.1600.50	1.599.1600.51	2 x 3	1.599.1601.50	1.599.1601.51
M 20 x 1,5	9	27	24	6 x 3	1.599.2001.50	1.599.2001.51	2 x 5	1.599.2003.50	1.599.2003.51
M 25 x 1,5	11	31	33	4 x 6	1.599.2500.50	1.599.2500.51	3 x 7	1.599.2501.50	1.599.2501.51
M 32 x 1,5	11	39	42	6 x 6,5	1.599.3200.50	1.599.3200.51	4 x 9	1.599.3201.50	1.599.3201.51
M 40 x 1,5	13	48	53	7 x 9	1.599.4001.50	1.599.4001.51	2 x 15	1.599.4003.50	1.599.4003.51
M 50 x 1,5	13	49	60		1.599.5099.50	1.599.5099.51			
M 63 x 1,5	14	49	65 / 68	6 x 12	1.599.6301.50	1.599.6301.51	3 x 18	1.599.6302.50	1.599.6302.51
PG 9	8	22	19	4 x 1,4	1.599.0900.00	1.599.0900.01	2 x 3	1.599.0901.00	1.599.0901.01
PG 11	8	25	22	2 x 4	1.599.1102.00	1.599.1102.01	3 x 3	1.599.1101.00	1.599.1101.01
PG 13,5	9	27	24	3 x 4	1.599.1302.00	1.599.1302.01	2 x 5	1.599.1303.00	1.599.1303.01
PG 16	10	28	27	4 x 4	1.599.1602.00	1.599.1602.01	6 x 4	1.599.1604.00	1.599.1604.01
PG 16	10	28	27	3 x 5,6	1.599.1606.00	1.599.1606.01	2 x 6	1.599.1605.00	1.599.1605.01
PG 21	11	31	33	4 x 6	1.599.2100.00	1.599.2100.01	3 x 7	1.599.2101.00	1.599.2101.01
PG 29	11	39	42	6 x 6,5	1.599.2900.00	1.599.2900.01	4 x 9	1.599.2901.00	1.599.2901.01
PG 36	13	48	53	7 x 9	1.599.3601.00	1.599.3601.01	2 x 15	1.599.3603.00	1.599.3603.01
PG 48	14	49	65	6 x 12	1.599.4801.00	1.599.4801.01	3 x 18	1.599.4802.00	1.599.4802.01
NPT 3/8"	15	22	19 / 22	4 x 1,4	1.599.3800.70	1.599.3800.71	2 x 3	1.599.3801.70	1.599.3801.71
NPT 1/2"	13	27	24	3 x 4	1.599.1202.70	1.599.1202.71	2 x 5	1.599.1203.70	1.599.1203.71
NPT 1/2" (16)	13	28	27	6 x 4	1.599.1220.70	1.599.1220.71	2 x 6	1.599.1221.70	1.599.1221.71
NPT 3/4"	14	31	33	4 x 6	1.599.3400.70	1.599.3400.71	3 x 7	1.599.3401.70	1.599.3401.71
NPT 1"	19	39	42	6 x 6,5	1.599.1000.70	1.599.1000.71	4 x 9	1.599.1001.70	1.599.1001.71
NPT 1 1/4"	16	39	42 / 46		1.599.5499.70	1.599.5499.71			
NPT 1 1/2"	20	48	53	5 x 9	1.599.6400.70	1.599.6400.71	7 x 9	1.599.6401.70	1.599.6401.71

Advice: The shown inserts are samples, more inserts upon request

➔ Accessories see page 73 and 143

HSK Ex-e cable glands for special applications

HSK-K-FLAKA-Ex

Metr., PG, NPT



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material Polyamide V0 according to UL 94

Seal Elastomer


Protection IP 68

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)

Colors grey (RAL 7035), black (RAL 9005)

O-Ring Buna-N

Advice:
- Installation instruction see page 176



AG	GL mm	H mm	mm	w x h mm	Number grey	Number black	w x h mm	Number grey	Number black
M 20 x 1,5	9	28	27	12 x 7	1.589.2017.50	1.589.2017.51	14 x 6	1.589.2018.50	1.589.2018.51
M 25 x 1,5	11	31	33	14 x 6	1.589.2500.50	1.589.2500.51	14 x 7	1.589.2501.50	1.589.2501.51
M 32 x 1,5	11	39	42	22 x 8	1.589.3200.50	1.589.3200.51			
M 40 x 1,5	13	48	53	28,5 x 10	1.589.4000.50	1.589.4000.51	29 x 5,5	1.589.4001.50	1.589.4001.51
M 40 x 1,5	13	48	53	30,5 x 12	1.589.4002.50	1.589.4002.51	31 x 7,5	1.589.4003.50	1.589.4003.51
M 50 x 1,5	13	49	60	33,5 x 11,5	1.589.5000.50	1.589.5000.51			
PG 16	10	28	27	12 x 7	1.589.1601.00	1.589.1601.01	14 x 6	1.589.1602.00	1.589.1602.01
PG 21	11	31	33	14 x 6	1.589.2100.00	1.589.2100.01	14 x 7	1.589.2101.00	1.589.2101.01
PG 29	11	39	42	22 x 8	1.589.2900.00	1.589.2900.01			
PG 36	13	48	53	28,5 x 10	1.589.3600.00	1.589.3600.01	29 x 5,5	1.589.3601.00	1.589.3601.01
PG 36	13	48	53	30,5 x 12	1.589.3602.00	1.589.3602.01	31 x 7,5	1.589.3603.00	1.589.3603.01
PG 42	13	49	60	33,5 x 11,5	1.589.4200.00	1.589.4200.01			
NPT 1/2" (16)	13	28	27	12 x 7	1.589.1217.70	1.589.1217.71	14 x 6	1.589.1218.70	1.589.1218.71
NPT 3/4"	14	31	33	14 x 6	1.589.3400.70	1.589.3400.71			
NPT 1"	19	39	42	22 x 8	1.589.1000.70	1.589.1000.71			
NPT 1 1/4"	16	39	42/46	22 x 8	1.589.5400.70	1.589.5400.71			
NPT 1 1/2"	20	48	53	28,5 x 10	1.589.6400.70	1.589.6400.71	29 x 5,5	1.589.6401.70	1.589.6401.71
NPT 1 1/2"	20	48	53	30,5 x 12	1.589.6402.70	1.589.6402.71	31 x 7,5	1.589.6403.70	1.589.6403.71

Advice: The shown inserts are samples, more inserts upon request

➔ Accessories see page 73 and 143

HSK Ex-e cable glands for special applications

HSK-K-MZ-Ex

Metr.



For the international certificates
please see page 176 or our homepage
www.hummel.com


Material Polyamide-AL

Seal Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

O-Ring Buna-N

Operating Temperature -20 °C – 70 °C (-4 °F – 158 °F)



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number
M 16 x 1,5	4 – 8	15	29	19	1.215.1601.50
M 20 x 1,5	6 – 12	15	35,5	24	1.215.2001.50
M 25 x 1,5	13 – 18	11	41	33	1.215.2501.50
M 32 x 1,5	18 – 25	11	49	42	1.215.3201.50
M 40 x 1,5	22 – 32	13	58	53	1.215.4001.50
M 50 x 1,5	32 – 38	13	61,5	60	1.215.5001.50
M 63 x 1,5	37 – 44	14	62	65/68	1.215.6301.50

➔ Accessories see page 73 and 143

HSK-K-MZ-Ex

PG



For the international certificates
please see page 176 or our homepage
www.hummel.com


Material Polyamide-AL

Seal Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

O-Ring Buna-N

Operating Temperature -20 °C – 70 °C (-4 °F – 158 °F)



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number
PG 9	4 – 8	15	29	19	1.215.0901.14
PG 11	6 – 10	15	32,5	22	1.215.1101.14
PG 13,5	6 – 12	15	35,5	24	1.215.1301.14
PG 16	10 – 14	10	37,5	27	1.215.1601.14
PG 21	13 – 18	11	41	33	1.215.2101.14
PG 29	18 – 25	11	49	42	1.215.2901.14
PG 36	22 – 32	13	58	53	1.215.3601.14
PG 42	32 – 38	13	61,5	60	1.215.4201.14
PG 48	37 – 44	14	62	65	1.215.4801.14

➔ Accessories see page 73 and 143

HSK Ex-e cable glands for special applications

HSK-M-Multi-Ex

Metr., PG, NPT



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material Nickel plated brass

Clamping insert Polyamide

Seal Elastomer


O-Ring Buna-N

Protection IP 68

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)

Advice:

- Stainless steel on request



AG	GL mm	H mm	mm	Number of Holes x d	Number	Number of Holes x d	Number
M 16 x 1,5	6	21	17 / 19	4 x 1,4	1.687.1600.50	2 x 3	1.687.1601.50
M 20 x 1,5	6	23	22	6 x 3	1.687.2001.50	2 x 5	1.687.2003.50
M 25 x 1,5	7	26	30	4 x 6	1.687.2500.50	3 x 7	1.687.2501.50
M 32 x 1,5	8	31	40	6 x 6,5	1.687.3200.50	4 x 9	1.687.3201.50
M 40 x 1,5	8	37	50	7 x 9	1.687.4001.50	2 x 15	1.687.4003.50
M 50 x 1,5	9	37	57				1.687.5099.50
M 63 x 1,5	10	38	64 / 68	6 x 12	1.687.6301.50	3 x 18	1.687.6302.50
PG 9	6	21	17	4 x 1,4	1.687.0900.01	2 x 3	1.687.0901.01
PG 11	6	22	20	2 x 4	1.687.1102.01	3 x 3	1.687.1101.01
PG 13,5	6,5	24	22	3 x 4	1.687.1302.01	2 x 5	1.687.1303.01
PG 16	6,5	23	24	4 x 4	1.687.1602.01	6 x 4	1.687.1604.01
PG 16	6,5	23	24	3 x 5,6	1.687.1606.01	2 x 6	1.687.1605.01
PG 21	7	24	30	4 x 6	1.687.2100.01	3 x 7	1.687.2101.01
PG 29	8	29	40	6 x 6,5	1.687.2900.01	4 x 9	1.687.2901.01
PG 36	8	35	50	7 x 9	1.687.3601.01	2 x 15	1.687.3603.01
PG 48	10	38	64	6 x 12	1.687.4801.01	3 x 18	1.687.4802.01
NPT 3/8"	15	21	17 / 19	4 x 1,4	1.687.3800.70	2 x 3	1.687.3801.70
NPT 1/2"	13	24	24	3 x 4	1.687.1220.70	2 x 5	1.687.1203.70
NPT 3/4"	13	25	30	4 x 6	1.687.3400.70	3 x 7	1.687.3401.70
NPT 1"	19	29	40	6 x 6,5	1.687.1000.70	4 x 9	1.687.1001.70

Advice: The shown inserts are samples, more inserts upon request

Accessories see page 73 and 143

HSK Ex-e cable glands for special applications

HSK-M-FLAKA-Ex

Metr.



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material Nickel plated brass

Clamping insert Polyamide

Seal Elastomer

O-Ring Buna-N


Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)

Advice:
- Stainless steel on request



ATEX Ex

II 2G 1D



AG	GL mm	H mm	mm	w x h mm	Number	w x h mm	Number
M 20 x 1,5	6	24	24	12 x 7	1.689.2017.50	14 x 6	1.689.2018.50
M 25 x 1,5	7	26	30	14 x 6	1.689.2500.50	14 x 7	1.689.2501.50
M 32 x 1,5	8	31	40	22 x 8	1.689.3200.50		
M 40 x 1,5	8	37	50	28,5 x 10	1.689.4000.50	29 x 5,5	1.689.4001.50
M 40 x 1,5	8	37	50	30,5 x 12	1.689.4002.50	31 x 7,5	1.689.4003.50
M 50 x 1,5	9	37	57	33,5 x 11,5	1.689.5000.50		
M 63 x 1,5	10	38	64/68	38 x 12	1.689.6300.50		

Advice: The shown inserts are samples, more inserts upon request

➔ Accessories see page 73 and 143

HSK-M-FLAKA-Ex

PG, NPT



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material Nickel plated brass

Clamping insert Polyamide

Seal Elastomer

O-Ring Buna-N


Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)

Advice:
- Stainless steel on request



ATEX Ex

II 2G 1D



AG	GL mm	H mm	mm	w x h mm	Number	w x h mm	Number
PG 16	6,5	23	24	12 x 7	1.689.1601.01	14 x 6	1.689.1602.01
PG 21	7	24	30	14 x 6	1.689.2100.01	14 x 7	1.689.2101.01
PG 29	8	29	40	22 x 8	1.689.2900.01		
PG 36	8	35	50	28,5 x 10	1.689.3600.01	29 x 5,5	1.689.3601.01
PG 36	8	35	50	30,5 x 12	1.689.3602.01	31 x 7,5	1.689.3603.01
PG 42	9	37	57	33,5 x 11,5	1.689.4200.01		
PG 48	10	38	64	38 x 12	1.689.4802.01		
NPT 3/4"	13	25	30	14 x 6	1.689.3400.70	14 x 7	1.689.3401.70
NPT 1"	19	29	40	22 x 8	1.689.1000.70		

Advice: The shown inserts are samples, more inserts upon request

➔ Accessories see page 73 and 143

HSK Ex-e cable glands for special applications

HSK-MZ-Ex / HSK-MZ-PVDF-Ex

Metr.



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com

Material Nickel plated brass

Clamping insert Polyamide / PVDF

Seal Buna-N / FPM


O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C
(-76 °F – 203 °F) / -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)

Advice:

- Elongated threads on request.



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-MZ-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-MZ-Ex -60 °C – 95 °C (-76 °F – 203 °F)	Number HSK-MZ-PVDF-Ex -20 °C – 130 °C (-4 °F – 266 °F)
M 12 x 1,5	3 – 6,5	6,5	26	14	1.611.1200.50	1.641.1200.50	1.661.1200.50
M 16 x 1,5	4 – 8	6	28	19	1.611.1600.50	1.641.1600.50	1.661.1600.50
M 16 x 1,5	6 – 10	6	30	20	1.611.1611.50	1.641.1611.50	1.661.1611.50
M 20 x 1,5	6 – 12	6	33	22	1.611.2000.50	1.641.2000.50	1.661.2000.50
M 20 x 1,5	10 – 14	6	33	24	1.611.2016.50	1.641.2016.50	1.661.2016.50
M 25 x 1,5	14 – 18	7	37	30	1.611.2500.50	1.641.2500.50	1.661.2500.50
M 32 x 1,5	20 – 25	8	43	40	1.611.3200.50	1.641.3200.50	1.661.3200.50
M 40 x 1,5	24 – 32	8	50	50	1.611.4000.50	1.641.4000.50	1.661.4000.50
M 50 x 1,5	32 – 38	9	51	57	1.611.5000.50	1.641.5000.50	
M 63 x 1,5	37 – 44	10	52	64/68	1.611.6300.50	1.641.6300.50	

➔ Accessories see page 73 and 143

HSK Ex-e cable glands for special applications

HSK-MZ-Ex / HSK-MZ-PVDF-Ex

PG


For the international certificates
please see page 176 or our homepage
www.hummel.com

Advice:

- Elongated threads on request.

Material Nickel plated brass

Clamping insert Polyamide / PVDF


Seal Buna-N / FPM

O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C
(-76 °F – 203 °F) / -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)


RoHS

ATEX
II 2G 1D


AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-MZ-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-MZ-Ex -60 °C – 95 °C (-76 °F – 203 °F)	Number HSK-MZ-PVDF-Ex -20 °C – 130 °C (-4 °F – 266 °F)
PG 7	3 – 6,5	5	26	14	1.611.0700.01	1.641.0700.01	1.661.0700.01
PG 9	4 – 8	6	28	17	1.611.0900.01	1.641.0900.01	1.661.0900.01
PG 11	6 – 10	6	30	20	1.611.1100.01	1.641.1100.01	1.661.1100.01
PG 13,5	7 – 12	6	33	22	1.611.1300.01	1.641.1300.01	1.661.1300.01
PG 16	10 – 14	6	33	24	1.611.1600.01	1.641.1600.01	1.661.1600.01
PG 21	13 – 18	7	37	30	1.611.2100.01	1.641.2100.01	1.661.2100.01
PG 29	20 – 25	8	43	40	1.611.2900.01	1.641.2900.01	1.661.2900.01
PG 36	24 – 32	8	50	50	1.611.3600.01	1.641.3600.01	1.661.3600.01
PG 42	32 – 38	9	51	57	1.611.4200.01	1.641.4200.01	1.661.4200.01
PG 48	37 – 44	10	52	64	1.611.4800.01	1.641.4800.01	1.661.4800.01

➔ Accessories see page 73 and 143

HSK-MZ-Ex / HSK-MZ-PVDF-Ex

NPT


For the international certificates
please see page 176 or our homepage
www.hummel.com

Advice:

- Elongated threads on request.

Material Nickel plated brass

Clamping insert Polyamide / PVDF


Seal Buna-N / FPM

O-Ring Buna-N / FPM

Protection IP 68 – 10 bar / IP 69K
within the specified clamping range

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) / -60 °C – 95 °C
(-76 °F – 203 °F) / -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)


RoHS

ATEX
II 2G 1D


AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-MZ-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number HSK-MZ-Ex -60 °C – 95 °C (-76 °F – 203 °F)	Number HSK-MZ-PVDF-Ex -20 °C – 130 °C (-4 °F – 266 °F)
NPT 3/8"	4 – 8	15	28	17 / 19	1.611.3800.70	1.641.3800.70	1.661.3800.70
NPT 1/2"	7 – 12	13	33	22 / 24	1.611.1200.70	1.641.1200.70	1.661.1200.70
NPT 3/4"	13 – 18	13	37	30	1.611.3400.70	1.641.3400.70	1.661.3400.70
NPT 1"	20 – 25	19	43	40	1.611.1000.70	1.641.1000.70	

➔ Accessories see page 73 and 143

Industrial cable glands

HSK-Ex-d standard cable glands

Cable glands of the HSK-Ex-d series have been designed for standard applications in hazardous locations type "e" and/or "d" according to EN 60079-0, EN 60079-1 and EN 60079-7



You can find in this chapter:

HSK-Ex-d cable glands

- made of nickel plated brass
- made of nickel plated brass with additional strain relief
- acid-resistant stainless steel

We provide variable clamping ranges, thread types and temperature ranges. Our range is completed by global certifications.

For any further question please do not hesitate to contact us. We look forward to develop solutions together with you. You profit of our vast knowledge in development, engineering and production technology.

Contact us:

E-Mail: info.et@hummel.com

Tel.: +49(0) 76 66/9 11 10-0

HSK-Ex-d standard cable glands

HSK-M-Ex-d / HSK-M-PVDF-Ex-d

Metr.




For the international certificates
please see page 176 or our homepage
www.hummel.com

Material	Nickel plated brass
Clamping insert	Polyamide / PVDF
Seal	FPM / FPM
O-Ring	FPM / FPM
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-60 °C – 105 °C (-76 °F – 221 °F) (PA) -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)



II 2G 1D Ex d IIC



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-M-Ex-d -60 °C – 105 °C (-76 °F – 221 °F)	Number HSK-M-PVDF-Ex-d -20 °C – 130 °C (-4 °F – 266 °F)
M 12 x 1,5	3 – 6,5	16	18,7	14	1.622.1200.50	1.634.1200.50
M 12 x 1,5	2 – 5	16	18,7	14	1.622.1200.51	1.634.1200.51
M 16 x 1,5	5 – 10	16	22	20	1.622.1600.50	1.634.1600.50
M 16 x 1,5	3 – 7	16	22	20	1.622.1600.51	1.634.1600.51
M 20 x 1,5	10 – 14	16	25	24	1.622.2000.50	1.634.2000.50
M 20 x 1,5	7 – 12	16	25	24	1.622.2000.51	1.634.2000.51
M 25 x 1,5	13 – 18	16	26,5	30	1.622.2500.50	1.634.2500.50
M 25 x 1,5	9 – 16	16	26,5	30	1.622.2500.51	1.634.2500.51
M 32 x 1,5	18 – 25	16	32	40	1.622.3200.50	1.634.3200.50
M 32 x 1,5	14 – 20	16	32	40	1.622.3200.51	1.634.3200.51
M 40 x 1,5	22 – 32	16	38,5	50	1.622.4000.50	1.634.4000.50
M 40 x 1,5	20 – 26	16	38,5	50	1.622.4000.51	1.634.4000.51

Accessories see page 73 and 143

HSK-M-Ex-d / HSK-M-PVDF-Ex-d

NPT




For the international certificates
please see page 176 or our homepage
www.hummel.com

Material	Nickel plated brass
Clamping insert	Polyamide / PVDF
Seal	FPM / FPM
O-Ring	FPM / FPM
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-60 °C – 105 °C (-76 °F – 221 °F) (PA) -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)



II 2G 1D Ex d IIC



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-M-Ex-d -60 °C – 105 °C (-76 °F – 221 °F)	Number HSK-M-PVDF-Ex-d -20 °C – 130 °C (-4 °F – 266 °F)
NPT 3/8"	5 – 10	16	22	20	1.622.3800.70	1.634.3800.70
NPT 3/8"	3 – 7	16	22	20	1.622.3800.71	1.634.3800.71
NPT 1/2"	10 – 14	20	25	24	1.622.1200.70	1.634.1200.70
NPT 1/2"	7 – 12	20	25	24	1.622.1200.71	1.634.1200.71
NPT 3/4"	13 – 18	20,5	26,5	30	1.622.3400.70	1.634.3400.70
NPT 3/4"	9 – 16	20,5	26,5	30	1.622.3400.71	1.634.3400.71
NPT 1"	18 – 25	25	32	40	1.622.1000.70	
NPT 1"	14 – 20	25	32	40	1.622.1000.71	
NPT 1 1/4"	22 – 32	26	38,5	50	1.622.5400.70	
NPT 1 1/4"	20 – 26	26	38,5	50	1.622.5400.71	
NPT 1 1/2"	22 – 32	26,5	38,5	50	1.622.6400.70	
NPT 1 1/2"	20 – 26	26,5	38,5	50	1.622.6400.71	

Accessories see page 73 and 143


HSK-Ex-d standard cable glands

HSK-MZ-Ex-d

Metr.



II 2G 1D Ex d IIC



Material	Nickel plated brass
Clamping insert	Polyamide
Seal	FPM
O-Ring	FPM
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-60 °C – 105 °C (-76 °F – 221 °F)



For the international certificates
please see page 176 or our homepage
www.hummel.com

AG	 mm	GL mm	H mm	 mm	Number HSK-MZ-Ex-d -60 °C – 105 °C (-76 °F – 221 °F)
M 12 x 1,5	3 – 6,5	16	26	14	1.628.1200.50
M 16 x 1,5	5 – 10	16	30,2	20	1.628.1600.50
M 20 x 1,5	10 – 14	16	34	24	1.628.2000.50
M 25 x 1,5	13 – 18	16	37,8	30	1.628.2500.50
M 32 x 1,5	18 – 25	16	44	40	1.628.3200.50
M 40 x 1,5	22 – 32	16	51,5	50	1.628.4000.50


➔ Accessories see page 73 and 143

HSK-MZ-Ex-d

NPT



II 2G 1D Ex d IIC



Material	Nickel plated brass
Clamping insert	Polyamide
Seal	FPM
O-Ring	FPM
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-60 °C – 105 °C (-76 °F – 221 °F)



For the international certificates
please see page 176 or our homepage
www.hummel.com

AG	 mm	GL mm	H mm	 mm	Number HSK-MZ-Ex-d -60 °C – 105 °C (-76 °F – 221 °F)
NPT 3/8"	5 – 10	16	30	20	1.628.3800.70
NPT 1/2"	10 – 14	20	33,6	24	1.628.1200.70
NPT 3/4"	13 – 18	20,5	37,8	30	1.628.3400.70
NPT 1"	18 – 25	25	44	40	1.628.1000.70
NPT 1 1/4"	22 – 32	26	51,5	50	1.628.5400.70
NPT 1 1/2"	22 – 32	26,5	51,5	50	1.628.6400.70

➔ Accessories see page 73 and 143

HSK-Ex-d standard cable glands

HSK-INOX-Ex-d / HSK-INOX-PVDF-Ex-d

Metr.




For the international certificates
please see page 176 or our homepage
www.hummel.com

Material	INOX (1.4404)
Clamping insert	Polyamide / PVDF
Seal	FPM / FPM
O-Ring	FPM / FPM
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-60 °C – 105 °C (-76 °F – 221 °F) (PA) -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)



II 2G 1D Ex d IIC



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-INOX-Ex-d -60 °C – 105 °C (-76 °F – 221 °F)	Number HSK-INOX-PVDF-Ex-d -20 °C – 130 °C (-4 °F – 266 °F)
M 12 x 1,5	3 – 6,5	16	19	14	1.632.1200.50	1.633.1200.50
M 12 x 1,5	2 – 5	16	19	14	1.632.1200.51	1.633.1200.51
M 16 x 1,5	5 – 10	16	22	20	1.632.1600.50	1.633.1600.50
M 16 x 1,5	3 – 7	16	22	20	1.632.1600.51	1.633.1600.51
M 20 x 1,5	10 – 14	16	25	24	1.632.2000.50	1.633.2000.50
M 20 x 1,5	7 – 12	16	25	24	1.632.2000.51	1.633.2000.51
M 25 x 1,5	13 – 18	16	26,5	30	1.632.2500.50	1.633.2500.50
M 25 x 1,5	9 – 16	16	26,5	30	1.632.2500.51	1.633.2500.51
M 32 x 1,5	18 – 25	16	32	40	1.632.3200.50	1.633.3200.50
M 32 x 1,5	14 – 20	16	32	40	1.632.3200.51	1.633.3200.51
M 40 x 1,5	22 – 32	16	38,5	50	1.632.4000.50	1.633.4000.50
M 40 x 1,5	20 – 26	16	38,5	50	1.632.4000.51	1.633.4000.51

Accessories see page 73 and 143

HSK-INOX-Ex-d / HSK-INOX-PVDF-Ex-d

NPT




For the international certificates
please see page 176 or our homepage
www.hummel.com

Material	INOX (1.4404)
Clamping insert	Polyamide / PVDF
Seal	FPM / FPM
O-Ring	FPM / FPM
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) within the specified clamping range
Operating Temperature	-60 °C – 105 °C (-76 °F – 221 °F) (PA) -20 °C – 130 °C (-4 °F – 266 °F) (PVDF)



II 2G 1D Ex d IIC



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number HSK-INOX-Ex-d -60 °C – 105 °C (-76 °F – 221 °F)	Number HSK-INOX-PVDF-Ex-d -20 °C – 130 °C (-4 °F – 266 °F)
NPT 3/8"	5 – 10	16	22	20	1.632.3800.70	1.633.3800.70
NPT 3/8"	3 – 7	16	22	20	1.632.3800.71	1.633.3800.71
NPT 1/2"	10 – 14	20	25	24	1.632.1200.70	1.633.1200.70
NPT 1/2"	7 – 12	20	25	24	1.632.1200.71	1.633.1200.71
NPT 3/4"	13 – 18	20,5	26,5	30	1.632.3400.70	1.633.3400.70
NPT 3/4"	9 – 16	20,5	26,5	30	1.632.3400.71	1.633.3400.71

Accessories see page 73 and 143

Industrial cable glands

Ex accessories

You can find in this chapter accessories for all series of our industrial cable glands for hazardous locations with protection "e" and/or "d":

- accessories made of plastic starting on page 144
- accessories made of nickel plated brass starting on page 147
- accessories made of stainless steel starting on page 151



V-Ex

Metr.




Material	Polyamide, fiber reinforced
O-Ring	Buna-N
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
Operating Temperature	-20 °C – 90 °C (-4 °F – 194 °F)
Colors	black (RAL 9005)



II 2G 1D

For the international certificates
please see page 176 or our homepage
www.hummel.com



AG	GL mm	H mm	D mm	mm	mm	Number
M 12 x 1,5	8,5	13	16,5	15	6	1.297.1201.50
M 16 x 1,5	8,5	13	20,5	19	8	1.297.1601.50
M 20 x 1,5	9	14,5	25,5	24	8	1.297.2001.50
M 25 x 1,5	10,5	16	30,5	28	8	1.297.2501.50
M 32 x 1,5	11,5	17,5	38	36	8	1.297.3201.50
M 40 x 1,5	11,5	18	48	46	8	1.297.4001.50
M 50 x 1,5	13,5	20	60	55	8	1.297.5001.50
M 63 x 1,5	14,5	21	75	70	8	1.297.6301.50

V-Ex

PG

RoHS

CE

PG

IECEx

ATEX

IECEx

II 2G 1D

For the international certificates
please see page 176 or our homepage
www.hummel.com


Material Polyamide, fiber reinforced

O-Ring Buna-N

Protection IP 68 – 10 bar/IP 69K (NEMA 6 – 150 PSIG)

Operating Temperature -20 °C – 90 °C (-4 °F – 194 °F)

Colors black (RAL 9005)



AG	GL mm	H mm	D mm	 mm	 mm	Number
PG 7	8,5	13	16,5	15	6	1.297.0701.11
PG 9	8,5	13	20,5	19	8	1.297.0901.11
PG 11	9	14,5	25,5	24	8	1.297.1101.11
PG 13,5	9	14,5	25,5	24	8	1.297.1301.11
PG 16	10,5	16	30,5	28	8	1.297.1601.11
PG 21	11,5	17,5	38	36	8	1.297.2101.11
PG 29	11,5	18	48	46	8	1.297.2901.11
PG 36	13,5	20	60	55	8	1.297.3601.11
PG 42	13,5	20	65	60	8	1.297.4201.11
PG 48	14,5	21	75	70	8	1.297.4801.11

HSK-V-Ex

Metr., PG, NPT




Material Elastomer

Operating Temperature -40 °C – 95 °C (-40 °F – 203 °F)

Colors black (RAL 9005)

Advice:
- Elongated threads on request



II 2G 1D

For the international certificates
please see page 176 or our homepage
www.hummel.com

Fits the Following Sizes			D mm	d mm	H mm	h mm	Number
PG 7	M 12 x 1,5		9,5	6,3	11,5	4,5	1.296.0701.11
PG 9	M 16 x 1,5	NPT 3/8"	11	7,8	13,5	5,5	1.296.0901.11
PG 11	M 16 x 1,5		13,5	9,8	14,5	5,5	1.296.1101.11
PG 13,5	M 20 x 1,5	NPT 1/2"	16	11,8	18	8	1.296.1301.11
PG 16	M 20 x 1,5	NPT 1/2"/16	18,5	13,8	19	9	1.296.1601.11
PG 21	M 25 x 1,5	NPT 3/4"	22	17,8	22	11	1.296.2101.11
PG 29	M 32 x 1,5	NPT 1" NPT 1 1/4"	29	25	25	10	1.296.2901.11
PG 36	M 40 x 1,5	NPT 1 1/2"	38	32	28	11	1.296.3601.11
PG 42	M 50 x 1,5		43	38	30	12	1.296.4201.11
PG 48	M 63 x 1,5		49	44	30	12	1.296.4801.11

HSK-V-Ex MZ variety

Metr., PG, NPT




Material Elastomer

Operating Temperature -40 °C – 95 °C (-40 °F – 203 °F)

Colors black (RAL 9005)

Advice:
- This plug is suitable in all HSK glands with additional strain relief



II 2G 1D

For the international certificates
please see page 176 or our homepage
www.hummel.com


Fits the Following Sizes			D mm	d mm	H mm	h mm	Number
PG 7	M 12 x 1,5		9,5	6,3	18	4,5	1.296.0701.61
PG 9	M 16 x 1,5	NPT 3/8"	11	7,8	20,5	5,5	1.296.0901.61
PG 11	M 16 x 1,5		13,5	9,8	22	5,5	1.296.1101.61
PG 13,5	M 20 x 1,5	NPT 1/2"	16	11,8	26,5	8	1.296.1301.61
PG 16	M 20 x 1,5	NPT 1/2"/16	18,5	13,8	28,4	9	1.296.1601.61
PG 21	M 25 x 1,5	NPT 3/4"	22	17,8	32	11	1.296.2101.61
PG 29	M 32 x 1,5	NPT 1" NPT 1 1/4"	29	25	35,5	10	1.296.2901.61
PG 36	M 40 x 1,5	NPT 1 1/2"	38	32	39	11	1.296.3601.61
PG 42	M 50 x 1,5		43	38	42,5	12	1.296.4201.61
PG 48	M 63 x 1,5		49	44	42,5	12	1.296.4801.61

V-Ms-Ex / V-Ms-FPM-Ex / V-Ms-VMQ-Ex

Metr.



II 2G 1D



Material Nickel plated brass

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)

**V-Ms-Ex
O-Ring** Buna-N

**V-Ms-FPM-Ex
O-Ring** FPM

**V-Ms-VMQ-Ex
O-Ring** VMQ

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) (Buna-N)
-20 °C – 180 °C (-4 °F – 356 °F) (FPM), -60 °C – 180 °C (-76 °F – 356 °F) (VMQ)



For the international certificates
please see page 176 or our homepage
www.hummel.com


AG	GL mm	H mm	mm	Number V-Ms-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number V-Ms-FPM-Ex -20 °C – 180 °C (-4 °F – 356 °F)	Number V-Ms-VMQ-Ex -60 °C – 180 °C (-76 °F – 356 °F)
M 12 x 1,5	6,5	9,5	14	1.197.1200.50	1.198.1200.50	1.199.1200.50
M 16 x 1,5	6	9	19	1.197.1600.50	1.198.1600.50	1.199.1600.50
M 20 x 1,5	6	9,5	22	1.197.2000.50	1.198.2000.50	1.199.2000.50
M 25 x 1,5	7	10,5	30	1.197.2500.50	1.198.2500.50	1.199.2500.50
M 32 x 1,5	8	12,5	41	1.197.3200.50	1.198.3200.50	1.199.3200.50
M 40 x 1,5	8	13	46	1.197.4000.50	1.198.4000.50	1.199.4000.50
M 50 x 1,5	9	15	55	1.197.5000.50	1.198.5000.50	1.199.5000.50
M 63 x 1,5	10	16,5	70	1.197.6300.50	1.198.6300.50	1.199.6300.50

V-Ms-Ex / V-Ms-FPM-Ex / V-Ms-VMQ-Ex

PG



II 2G 1D



Material Nickel plated brass


Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)

**V-Ms-Ex
O-Ring** Buna-N

**V-Ms-FPM-Ex
O-Ring** FPM

**V-Ms-VMQ-Ex
O-Ring** VMQ

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) (Buna-N)
-20 °C – 180 °C (-4 °F – 356 °F) (FPM), -60 °C – 180 °C (-76 °F – 356 °F) (VMQ)



For the international certificates
please see page 176 or our homepage
www.hummel.com

AG	GL mm	H mm	mm	Number V-Ms-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number V-Ms-FPM-Ex -20 °C – 180 °C (-4 °F – 356 °F)	Number V-Ms-VMQ-Ex -60 °C – 180 °C (-76 °F – 356 °F)
PG 7	5	8	14	1.197.0700.01	1.198.0700.01	1.199.0700.01
PG 9	6	9	17	1.197.0900.01	1.198.0900.01	1.199.0900.01
PG 11	6	9,5	20	1.197.1100.01	1.198.1100.01	1.199.1100.01
PG 13,5	6,5	10	22	1.197.1300.01	1.198.1300.01	1.199.1300.01
PG 16	6,5	10	24	1.197.1600.01	1.198.1600.01	1.199.1600.01
PG 21	7	10,5	30	1.197.2100.01	1.198.2100.01	1.199.2100.01
PG 29	8	12,5	41	1.197.2900.01	1.198.2900.01	1.199.2900.01
PG 36	8	13	50	1.197.3600.01	1.198.3600.01	1.199.3600.01
PG 42	9	15	58	1.197.4200.01	1.198.4200.01	1.199.4200.01
PG 48	10	16,5	65	1.197.4800.01	1.198.4800.01	1.199.4800.01

Ex accessories

RSD-MS-Ex

Metr.



Material Nickel plated brass


O-Ring Buna-N / VMQ

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)

Operating Temperature -20°C – 95°C (-4°F – 203°F) (Buna-N)
-60°C – 180°C (-76°F – 356°F) (VMQ)



II 2G 1D




For the international certificates
please see page 176 or our homepage
www.hummel.com

AG	IG	GL mm	H mm	Number Buna-N -20°C – 95°C (-4°F – 203°F)	Number VMQ -60°C – 180°C (-76°F – 356°F)
M 16 x 1,5	M 12 x 1,5	5	17	1.078.1612.50	1.079.1612.50
M 20 x 1,5	M 12 x 1,5	6	22	1.078.2012.50	1.079.2012.50
M 20 x 1,5	M 16 x 1,5	6	22	1.078.2016.50	1.079.2016.50
M 25 x 1,5	M 16 x 1,5	7	29	1.078.2516.50	1.079.2516.50
M 25 x 1,5	M 20 x 1,5	7	29	1.078.2520.50	1.079.2520.50
M 32 x 1,5	M 16 x 1,5	8	34	1.078.3216.50	1.079.3216.50
M 32 x 1,5	M 20 x 1,5	8	34	1.078.3220.50	1.079.3220.50
M 32 x 1,5	M 25 x 1,5	8	34	1.078.3225.50	1.079.3225.50
M 40 x 1,5	M 20 x 1,5	8	43	1.078.4020.50	1.079.4020.50
M 40 x 1,5	M 25 x 1,5	8	43	1.078.4025.50	1.079.4025.50
M 40 x 1,5	M 32 x 1,5	8	43	1.078.4032.50	1.079.4032.50
M 50 x 1,5	M 25 x 1,5	9	55	1.078.5025.50	1.079.5025.50

AG	IG	GL mm	H mm	Number Buna-N -20°C – 95°C (-4°F – 203°F)	Number VMQ -60°C – 180°C (-76°F – 356°F)
M 50 x 1,5	M 32 x 1,5	9	55	1.078.5032.50	1.079.5032.50
M 50 x 1,5	M 40 x 1,5	9	55	1.078.5040.50	1.079.5040.50
M 63 x 1,5	M 32 x 1,5	10	65	1.078.6332.50	1.079.6332.50
M 63 x 1,5	M 40 x 1,5	10	65	1.078.6340.50	1.079.6340.50
M 63 x 1,5	M 50 x 1,5	10	65	1.078.6350.50	1.079.6350.50

RSD-MS-Ex

PG



Material Nickel plated brass


O-Ring Buna-N / VMQ

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)

Operating Temperature -20°C – 95°C (-4°F – 203°F) (Buna-N)
-60°C – 180°C (-76°F – 356°F) (VMQ)



II 2G 1D




For the international certificates
please see page 176 or our homepage
www.hummel.com

AG	IG	GL mm	H mm	H mm	Number Buna-N -20°C – 95°C (-4°F – 203°F)	Number VMQ -60°C – 180°C (-76°F – 356°F)
PG 9	PG 7	6	8,8	17	1.078.0907.01	1.079.0907.01
PG 11	PG 7	6	9	20	1.078.1107.01	1.079.1107.01
PG 11	PG 9	6	9	20	1.078.1109.01	1.079.1109.01
PG 13,5	PG 9	6,5	9,5	22	1.078.1309.01	1.079.1309.01
PG 16	PG 9	6,5	9,5	24	1.078.1609.01	1.079.1609.01
PG 16	PG 11	6,5	9,5	24	1.078.1611.01	1.079.1611.01
PG 16	PG 13,5	6,5	9,5	24	1.078.1613.01	1.079.1613.01
PG 21	PG 11	7	10,3	30	1.078.2111.01	1.079.2111.01
PG 21	PG 13,5	7	10,3	30	1.078.2113.01	1.079.2113.01
PG 21	PG 16	7	10,3	30	1.078.2116.01	1.079.2116.01
PG 29	PG 16	8	11,5	40	1.078.2916.01	1.079.2916.01
PG 29	PG 21	8	11,5	40	1.078.2921.01	1.079.2921.01


AG	IG	GL mm	H mm	H mm	Number Buna-N -20°C – 95°C (-4°F – 203°F)	Number VMQ -60°C – 180°C (-76°F – 356°F)
PG 36	PG 21	9	12,5	50	1.078.3621.01	1.079.3621.01
PG 36	PG 29	9	12,5	50	1.078.3629.01	1.079.3629.01
PG 42	PG 29	10	13,5	57	1.078.4229.01	1.079.4229.01
PG 42	PG 36	10	13,5	57	1.078.4236.01	1.079.4236.01
PG 48	PG 36	10	13,5	64	1.078.4836.01	1.079.4836.01
PG 48	PG 42	10	13,5	64	1.078.4842.01	1.079.4842.01

Metr., NPT

[illegible]

RSD-MS-Ex-d

Metr.



Material Nickel plated brass

O-Ring Buna-N / VMQ

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)


Operating Temperature -20°C – 95°C (-4°F – 203°F) (Buna-N)
-60°C – 180°C (-76°F – 356°F) (VMQ)



II 2G 1D Ex d IIC



For the international certificates
please see page 176 or our homepage
www.hummel.com



AG	IG	GL mm	H mm	 mm	Number Buna-N -20 °C – 95 °C (-4 °F – 203 °F)	Number VMQ -60 °C – 180 °C (-76 °F – 356 °F)
M 16 x 1,5	M 12 x 1,5	16	19	19	1.878.1612.50	1.879.1612.50
M 20 x 1,5	M 12 x 1,5	16	19,5	22	1.878.2012.50	1.879.2012.50
M 20 x 1,5	M 16 x 1,5	16	19,5	22	1.878.2016.50	1.879.2016.50
M 25 x 1,5	M 16 x 1,5	16	19,5	30	1.878.2516.50	1.879.2516.50
M 25 x 1,5	M 20 x 1,5	16	19,5	30	1.878.2520.50	1.879.2520.50
M 32 x 1,5	M 16 x 1,5	16	20,5	41	1.878.3216.50	1.879.3216.50
M 32 x 1,5	M 20 x 1,5	16	20,5	41	1.878.3220.50	1.879.3220.50
M 32 x 1,5	M 25 x 1,5	16	20,5	41	1.878.3225.50	1.879.3225.50
M 40 x 1,5	M 20 x 1,5	16	21	46	1.878.4020.50	1.879.4020.50
M 40 x 1,5	M 25 x 1,5	16	21	46	1.878.4025.50	1.879.4025.50
M 40 x 1,5	M 32 x 1,5	16	21	46	1.878.4032.50	1.879.4032.50

V-INOX-Ex
Metr.

II 2G 1D

Material	INOX (1.4305)
Protection	IP 68 - 10 bar / IP 69K (NEMA 6 – 150 PSIG)
V-INOX-Ex O-Ring	Buna-N
V-INOX-FPM-Ex O-Ring	FPM
V-INOX-VMQ-Ex O-Ring	VMQ
Operating Temperature	-20 °C – 95 °C (-4 °F – 203 °F) (Buna-N) -20 °C – 180 °C (-4 °F – 356 °F) (FPM), -60 °C – 180 °C (-76 °F – 356 °F) (VMQ)

For the international certificates
please see page 176 or our homepage
www.hummel.com

AG	GL mm	H mm	mm	Number V-INOX-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number V-INOX-FPM-Ex -20 °C – 180 °C (-4 °F – 356 °F)	Number V-INOX-VMQ-Ex -60 °C – 180 °C (-76 °F – 356 °F)
M 12 x 1,5	6,5	9,5	14	1.192.1200.50	1.193.1200.50	1.194.1200.50
M 16 x 1,5	6	9	19	1.192.1600.50	1.193.1600.50	1.194.1600.50
M 20 x 1,5	6	9,5	22	1.192.2000.50	1.193.2000.50	1.194.2000.50
M 25 x 1,5	7	10,5	30	1.192.2500.50	1.193.2500.50	1.194.2500.50
M 32 x 1,5	8	12,5	41	1.192.3200.50	1.193.3200.50	1.194.3200.50
M 40 x 1,5	8	13	46	1.192.4000.50	1.193.4000.50	1.194.4000.50
M 50 x 1,5	9	15	55	1.192.5000.50	1.193.5000.50	1.194.5000.50
M 63 x 1,5	10	16,5	70	1.192.6300.50	1.193.6300.50	1.194.6300.50

V-INOX-Ex
PG

II 2G 1D

Material	INOX (1.4305)
Protection	IP 68 - 10 bar / IP 69K (NEMA 6 – 150 PSIG)
V-INOX-Ex O-Ring	Buna-N
V-INOX-FPM-Ex O-Ring	FPM
V-INOX-VMQ-Ex O-Ring	VMQ
Operating Temperature	-20 °C – 95 °C (-4 °F – 203 °F) (Buna-N) -20 °C – 180 °C (-4 °F – 356 °F) (FPM), -60 °C – 180 °C (-76 °F – 356 °F) (VMQ)

For the international certificates
please see page 176 or our homepage
www.hummel.com

AG	GL mm	H mm	mm	Number V-INOX-Ex -20 °C – 95 °C (-4 °F – 203 °F)	Number V-INOX-FPM-Ex -20 °C – 180 °C (-4 °F – 356 °F)	Number V-INOX-VMQ-Ex -60 °C – 180 °C (-76 °F – 356 °F)
PG 7	5	8	14	1.192.0700.01	1.193.0700.01	1.194.0700.01
PG 9	6	9	17	1.192.0900.01	1.193.0900.01	1.194.0900.01
PG 11	6	9,5	20	1.192.1100.01	1.193.1100.01	1.194.1100.01
PG 13,5	6,5	10	22	1.192.1300.01	1.193.1300.01	1.194.1300.01
PG 16	6,5	10	24	1.192.1600.01	1.193.1600.01	1.194.1600.01
PG 21	7	10,5	30	1.192.2100.01	1.193.2100.01	1.194.2100.01
PG 29	8	12,5	41	1.192.2900.01	1.193.2900.01	1.194.2900.01
PG 36	8	13	50	1.192.3600.01	1.193.3600.01	1.194.3600.01
PG 42	9	15	58	1.192.4200.01	1.193.4200.01	1.194.4200.01
PG 48	10	16,5	65	1.192.4800.01	1.193.4800.01	1.194.4800.01

Ex accessories

RSD-INOX-Ex

Metr.



Material INOX (1.4305)


O-Ring Buna-N / VMQ

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) (Buna-N)
-60 °C – 180 °C (-76 °F – 356 °F) (VMQ)



II 2G 1D




For the international certificates
please see page 176 or our homepage
www.hummel.com

AG	IG	GL mm		Number Buna-N -20 °C – 95 °C (-4 °F – 203 °F)	Number VMQ -60 °C – 180 °C (-76 °F – 356 °F)
M 16 x 1,5	M 12 x 1,5	5	17	1.098.1612.50	1.099.1612.50
M 20 x 1,5	M 12 x 1,5	6	22	1.098.2012.50	1.099.2012.50
M 20 x 1,5	M 16 x 1,5	6	22	1.098.2016.50	1.099.2016.50
M 25 x 1,5	M 16 x 1,5	7	27	1.098.2516.50	1.099.2516.50
M 25 x 1,5	M 20 x 1,5	7	27	1.098.2520.50	1.099.2520.50
M 32 x 1,5	M 16 x 1,5	8	34	1.098.3216.50	1.099.3216.50
M 32 x 1,5	M 20 x 1,5	8	34	1.098.3220.50	1.099.3220.50
M 32 x 1,5	M 25 x 1,5	8	34	1.098.3225.50	1.099.3225.50
M 40 x 1,5	M 20 x 1,5	8	43	1.098.4020.50	1.099.4020.50
M 40 x 1,5	M 25 x 1,5	8	43	1.098.4025.50	1.099.4025.50
M 40 x 1,5	M 32 x 1,5	8	43	1.098.4032.50	1.099.4032.50
M 50 x 1,5	M 25 x 1,5	9	55	1.098.5025.50	1.099.5025.50

AG	IG	GL mm		Number Buna-N -20 °C – 95 °C (-4 °F – 203 °F)	Number VMQ -60 °C – 180 °C (-76 °F – 356 °F)
M 50 x 1,5	M 32 x 1,5	9	55	1.098.5032.50	1.099.5032.50
M 50 x 1,5	M 40 x 1,5	9	55	1.098.5040.50	1.099.5040.50
M 63 x 1,5	M 32 x 1,5	10	65	1.098.6332.50	1.099.6332.50
M 63 x 1,5	M 40 x 1,5	10	65	1.098.6340.50	1.099.6340.50
M 63 x 1,5	M 50 x 1,5	10	65	1.098.6350.50	1.099.6350.50

RSD-INOX-Ex

PG



Material INOX (1.4305)


O-Ring Buna-N / VMQ

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) (Buna-N)
-60 °C – 180 °C (-76 °F – 356 °F) (VMQ)



II 2G 1D



For the international certificates
please see page 176 or our homepage
www.hummel.com


AG	IG	GL mm	H mm		Number Buna-N -20 °C – 95 °C (-4 °F – 203 °F)	Number VMQ -60 °C – 180 °C (-76 °F – 356 °F)
PG 9	PG 7	6	8,8	17	1.098.0907.01	1.099.0907.01
PG 11	PG 7	6	9	20	1.098.1107.01	1.099.1107.01
PG 11	PG 9	6	9	20	1.098.1109.01	1.099.1109.01
PG 13,5	PG 9	6,5	9,5	22	1.098.1309.01	1.099.1309.01
PG 13,5	PG 11	6,5	9,5	22	1.098.1311.01	1.099.1311.01
PG 16	PG 9	6,5	9,5	24	1.098.1609.01	1.099.1609.01
PG 16	PG 11	6,5	9,5	24	1.098.1611.01	1.099.1611.01
PG 16	PG 13,5	6,5	9,5	24	1.098.1613.01	1.099.1613.01
PG 21	PG 11	7	10,3	30	1.098.2111.01	1.099.2111.01
PG 21	PG 13,5	7	10,3	30	1.098.2113.01	1.099.2113.01
PG 21	PG 16	7	10,3	30	1.098.2116.01	1.099.2116.01
PG 29	PG 16	8	11,5	40	1.098.2916.01	1.099.2916.01

AG		IG mm	GL mm	 mm	Number Buna-N -20 °C – 95 °C (-4 °F – 203 °F)	Number VMQ -60 °C – 180 °C (-76 °F – 356 °F)
PG 29	PG 21	8	11,5	40	1.098.2921.01	1.099.2921.01
PG 36	PG 21	9	12,5	50	1.098.3621.01	1.099.3621.01
PG 36	PG 29	9	12,5	50	1.098.3629.01	1.099.3629.01
PG 42	PG 29	10	13,5	57	1.098.4229.01	1.099.4229.01
PG 42	PG 36	10	13,5	57	1.098.4236.01	1.099.4236.01
PG 48	PG 36	10	13,5	64	1.098.4836.01	1.099.4836.01
PG 48	PG 42	10	13,5	64	1.098.4842.01	1.099.4842.01

Metr., NPT




II 2G1D Ex d/e IIC tD A20
KEMA 06 ATEX 0024
IECEX KEM 07.0012
-20°C - +180°C
M 25 x 1.5

[illegible]

RSD-INOX-Ex-d

Metr.



Material INOX (1.4404)

O-Ring Buna-N / VMQ

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)


Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F) (Buna-N)
-60 °C – 180 °C (-76 °F – 356 °F) (VMQ)



II 2G 1D Ex d IIC



For the international certificates
please see page 176 or our homepage
www.hummel.com




AG	IG	GL mm	H mm	mm	Number Buna-N -20 °C – 95 °C (-4 °F – 203 °F)	Number VMQ -60 °C – 180 °C (-76 °F – 356 °F)
M 16 x 1,5	M 12 x 1,5	16	19	19	1.898.1612.50	1.899.1612.50
M 20 x 1,5	M 12 x 1,5	16	19,5	22	1.898.2012.50	1.899.2012.50
M 20 x 1,5	M 16 x 1,5	16	19,5	22	1.898.2016.50	1.899.2016.50
M 25 x 1,5	M 16 x 1,5	16	19,5	30	1.898.2516.50	1.899.2516.50
M 25 x 1,5	M 20 x 1,5	16	19,5	30	1.898.2520.50	1.899.2520.50
M 32 x 1,5	M 16 x 1,5	16	20,5	41	1.898.3216.50	1.899.3216.50
M 32 x 1,5	M 20 x 1,5	16	20,5	41	1.898.3220.50	1.899.3220.50
M 32 x 1,5	M 25 x 1,5	16	20,5	41	1.898.3225.50	1.899.3225.50
M 40 x 1,5	M 20 x 1,5	16	21	46	1.898.4020.50	1.899.4020.50
M 40 x 1,5	M 25 x 1,5	16	21	46	1.898.4025.50	1.899.4025.50
M 40 x 1,5	M 32 x 1,5	16	21	46	1.898.4032.50	1.899.4032.50

Corrugated conduit systems

Snapflex Industry standard metric

Conduits of the Snapflex series are based on metric dimensions and fulfil current and future requirements.



You can find in this chapter:

- metric conduits
- conduit glands
- combined conduit/cable glands
- T and Y-shaped distributors for metric conduits
- snap elbow systems for metric conduits
- Nylon mounting brackets for metric conduits

Snapflex Industry standard metric

Snapflex



Material Polyamide



RoHS

Operating Temperature -30 °C – 100 °C (-22 °F – 212 °F)

Colors grey (RAL 7035), black (RAL 9005)

Advice:
- PP on request



Size D	d mm	D mm	Number grey	Number black
16	10,7	16	1.510.1600.50	1.510.1601.50
20	14,1	20	1.510.2000.50	1.510.2001.50
25	18,3	25	1.510.2500.50	1.510.2501.50
32	24,3	32	1.510.3200.50	1.510.3201.50
40	31,2	40	1.510.4000.50	1.510.4001.50
50	39,6	50	1.510.5000.50	1.510.5001.50
63	50,6	63	1.510.6300.50	1.510.6301.50

RoHS



Polyamide



-40 °C – 100 °C (-40°F – 212°F)

IP 42

black (RAL 9005)



Y-Connector



Snapflex Industry standard metric

SM-N

Metr.




Material Polyamide

Protection IP 54, with O-Ring
with fixed conduit mounting IP 65

Operating Temperature -20 °C – 80 °C (-4 °F – 176 °F)

Colors grey (RAL 7031), black (RAL 9005)

Advice:
- International certificat under development



AG	GL mm	H mm	D mm	 mm	fits to Snapflex	Number grey	Number black
M 16 x 1,5	8	23	23	17	16	1.514.1600.50	1.514.1601.50
M 20 x 1,5	9	28	28,6	24	20	1.514.2000.50	1.514.2001.50
M 25 x 1,5	11	32	34	35	25	1.514.2500.50	1.514.2501.50
M 32 x 1,5	11	35	41	39	32	1.514.3200.50	1.514.3201.50
M 40 x 1,5	13	40	51	47	40	1.514.4000.50	1.514.4001.50
M 50 x 1,5	14	48	62	57	50	1.514.5000.50	1.514.5001.50

Snapflex Industry standard metric

Snapturn
Metr.

Material	Polyamide
Operating Temperature	-20 °C – 80 °C
Protection	IP 42
Colors	black (RAL 9005)

Advice:
- International certificat under development

AG	d mm	GL mm	D mm	H mm	 mm	fits to Snapflex	Number
M 16 x 1,5	9,5	9	25,6	29,5	25	16	1.515.1601.50
M 20 x 1,5	12,5	9	31	33	30	20	1.515.2001.50
M 25 x 1,5	17	11	40,2	36,5	39	25	1.515.2501.50
M 32 x 1,5	22,5	13	47,5	38,5	47,5	32	1.515.3201.50
M 40 x 1,5	29	13	56,5	41	55	40	1.515.4001.50
M 50 x 1,5	36,5	13,5	67	43	65	50	1.515.5001.50

Snapturn-M
Metr.

Material	Polyamide, Brass
Operating Temperature	-20 °C – 80 °C
Protection	IP 42
Colors	black (RAL 9005)

Advice:
- International certificat under development
- NPT on request

AG	d mm	GL mm	D mm	H mm	 mm	fits to Snapflex	Number
M 16 x 1,5	9,5	6	25,6	29,5	25	16	1.515.1681.50
M 20 x 1,5	12,5	6	31	33	30	20	1.515.2081.50
M 25 x 1,5	17	6,5	40,2	36,5	39	25	1.515.2581.50
M 32 x 1,5	22,5	8	47,5	38,5	47,5	32	1.515.3281.50
M 40 x 1,5	29	8	56,5	41	55	40	1.515.4081.50
M 50 x 1,5	36,5	10	67	43	65	50	1.515.5081.50

Snapflex Industrie Standard metrisch

Snapturn 90°

Metr.




Material Polyamide

Operating Temperature -20 °C – 80 °C

Protection IP 42

Colors black (RAL 9005)

Advice:
- International certificat under development



AG	d mm	GL mm	H mm	L mm	 mm	fits to Snapflex	Number
M 16 x 1,5	9,5	9,5	30	57	12	16	1.525.1601.50
M 20 x 1,5	12,5	9,5	35,5	64	16	20	1.525.2001.50
M 25 x 1,5	17	10	45	71,5	20	25	1.525.2501.50
M 32 x 1,5	22,5	13	51	87,5	27	32	1.525.3201.50
M 40 x 1,5	29	13	65,4	97,2	32	40	1.525.4001.50
M 50 x 1,5	36,5	13,5	72	106,5	41	50	1.525.5001.50

Snapturn-M 90°

Metr.




Material Polyamide, Brass

Operating Temperature -20 °C – 80 °C

Protection IP 42

Colors black (RAL 9005)

Advice:
- International certificat under development
- NPT on request




AG	d mm	GL mm	H mm	L mm	 mm	fits to Snapflex	Number
M 16 x 1,5	9,5	6	33,5	57	12	16	1.525.1681.50
M 20 x 1,5	12,5	6	39	64	16	20	1.525.2081.50
M 25 x 1,5	17	6,5	48,5	71,5	20	25	1.525.2581.50
M 32 x 1,5	22,5	8	54,5	87,5	27	32	1.525.3281.50
M 40 x 1,5	29	8	68,5	97,2	32	40	1.525.4081.50
M 50 x 1,5	36,5	9	75,5	106,5	41	50	1.525.5081.50

Snapflex Industrie Standard metrisch

Snapturn 135°

Metr.




Material Polyamide

Operating Temperature -20 °C – 80 °C

Protection IP 42

Colors black (RAL 9005)


Advice:
- International certificat under development



AG	d mm	GL mm	H mm	L mm	mm	fits to Snapflex	Number
M 16 x 1,5	9,5	9,5	38,9	40,4	12	16	1.526.1601.50
M 20 x 1,5	12,5	9,5	44,7	48,2	16	20	1.526.2001.50
M 25 x 1,5	17	10	53,9	57,4	20	25	1.526.2501.50
M 32 x 1,5	22,5	13	60,8	68,8	27	32	1.526.3201.50
M 40 x 1,5	29	13	69,5	79,5	32	40	1.526.4001.50
M 50 x 1,5	36,5	13,5	78,5	89,5	41	50	1.526.5001.50

Snapturn-M 135°

Metr.



Material Polyamide, Brass

Operating Temperature -20 °C – 80 °C

Protection IP 42

Colors black (RAL 9005)

Advice:
- International certificat under development
- NPT on request



AG	d mm	GL mm	H mm	L mm	mm	fits to Snapflex	Number
M 16 x 1,5	9,5	6	42,4	41,4	12	16	1.526.1681.50
M 20 x 1,5	12,5	6	48,2	48,2	16	20	1.526.2081.50
M 25 x 1,5	17	6,5	57,4	57,9	20	25	1.526.2581.50
M 32 x 1,5	22,5	8	64,3	68,8	27	32	1.526.3281.50
M 40 x 1,5	29	8	73	79,5	32	40	1.526.4081.50
M 50 x 1,5	36,5	9	82	89,5	41	50	1.526.5081.50

Snapflex Industry standard metric

Snapclic-DUO-PA


Metr.

Material Polyamide

Seal NBR

RoHS
Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors black (RAL 9005)

Advice:
 - NPT and elongated thread upon request


AG	Ø mm	GL mm	H mm	D mm	Ø mm	fits to Snapflex	Number
M 16 x 1,5	5-10	8	42	25	22	16	1.542.1601.50
M 16 x 1,5	3-7	8	42	25	22	16	1.542.1601.51
M 20 x 1,5	10-14	10	46	30	27	20	1.542.2001.50
M 20 x 1,5	7-12	10	46	30	27	20	1.542.2001.51
M 25 x 1,5	13-18	11	50	35	33	25	1.542.2501.50
M 25 x 1,5	9-16	11	50	35	33	25	1.542.2501.51
M 32 x 1,5	18-24	11	60	42	42	32	1.542.3201.50
M 32 x 1,5	13-20	11	60	42	42	32	1.542.3201.51
M 40 x 1,5	22-31	13	60	50	53	40	1.542.4001.50
M 40 x 1,5	20-26	13	60	50	53	40	1.542.4001.51

Snapclic-DUO-PA


PG

Material Polyamide

RoHS
Seal NBR

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Colors black (RAL 9005)

Advice:
 - NPT and elongated thread upon request


AG	Ø mm	GL mm	H mm	D mm	Ø mm	fits to Snapflex	Number
PG 11	5-10	8	42	25	22	16	1.543.1116.14
PG 11	3-7	8	42	25	22	16	1.543.1116.15
PG 16	10-14	10	46	30	27	20	1.543.1620.14
PG 16	7-12	10	46	30	27	20	1.543.1620.15
PG 21	13-16	11	50	35	33	25	1.543.2125.14
PG 21	9-16	11	50	35	33	25	1.543.2125.15
PG 29	18-22	11	60	42	42	32	1.543.2932.14
PG 29	13-20	11	60	42	42	32	1.543.2932.15
PG 36	22-31	13	60	50	53	40	1.543.3640.14
PG 36	20-26	13	60	50	53	40	1.543.3640.15

Snapflex Industry standard metric

Snapclic-DUO-MS

Metr.

Material

Nickel plated brass

Clamping insert

Polyamide

Seal

NBR

Operating Temperature

-40 °C – 100 °C (-40 °F – 212 °F)

Advice:

- NPT and elongated thread upon request
- Also available as EMC version!
- DN Corrugated Conduit upon request!

AG	$\varnothing$ mm	GL mm	H mm	D mm	$\varnothing$ mm	fits to Snapflex	Number
M 16 x 1,5	5–10	6	38,5	25	24/20	16	1.547.1601.50
M 16 x 1,5	3–7	6	38,5	25	24/20	16	1.547.1601.51
M 20 x 1,5	10–14	6	41,5	30	28/24	20	1.547.2001.50
M 20 x 1,5	7–12	6	41,5	30	28/24	20	1.547.2001.51
M 25 x 1,5	13–18	7	44,5	35	34/30	25	1.547.2501.50
M 25 x 1,5	9–16	7	44,5	35	34/30	25	1.547.2501.51
M 32 x 1,5	18–24	8	52,5	42	40	32	1.547.3201.50
M 32 x 1,5	13–20	8	52,5	42	40	32	1.547.3201.51
M 40 x 1,5	22–31	8	59	50	50	40	1.547.4001.50
M 40 x 1,5	20–26	8	59	50	50	40	1.547.4001.51

Snapclic-DUO-MS

PG

Material

Nickel plated brass

Clamping insert

Polyamide

Seal

NBR

Operating Temperature

-40 °C – 100 °C (-40 °F – 212 °F)


Advice:

- NPT and elongated thread upon request
- Also available as EMC version!
- DN Corrugated Conduit upon request!

AG	$\varnothing$ mm	GL mm	H mm	D mm	$\varnothing$ mm	fits to Snapflex	Number
PG 11	5 – 10	6	38,5	25	24/20	16	1.548.1116.01
PG 11	3 – 7	6	38,5	25	24/20	16	1.548.1116.15
PG 16	10 – 14	6	41,5	30	28/24	20	1.548.1620.01
PG 16	7 – 12	6	41,5	30	28/24	20	1.548.1620.15
PG 21	13 – 16	7	44,5	35	34/30	25	1.548.2125.01
PG 21	9 – 16	7	44,5	35	34/30	25	1.548.2125.15
PG 29	18 – 22	8	52,5	42	40	32	1.548.2932.01
PG 29	13 – 20	8	52,5	42	40	32	1.548.2932.15
PG 36	22 – 28	8	59	50	50	40	1.548.3640.01
PG 36	20 – 26	8	59	50	50	40	1.548.3640.15


Snapflex Industry standard metric

Snapclic-PA-W




Material	Polyamide
O-Ring	NBR
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F)
Colors	black (RAL 9005)

Advice:
- NPT thread on request




AG	GL mm	H mm	L mm	D mm	 mm	fits to Snapflex	Number
M 25 x 1,5	11	40	53	30	33	20	1.552.2520.50
M 25 x 1,5	11	40	53	35	33	25	1.552.2525.50
M 32 x 1,5	11	51,5	64,5	42	42	32	1.552.3200.50

Snapclic-PA-W



Material	Polyamide
O-Ring	NBR
Operating Temperature	-40 °C – 100 °C (-40 °F – 212 °F)
Colors	black (RAL 9005)


Advice:
- NPT thread on request



AG	GL mm	H mm	L mm	D mm	 mm	fits to Snapflex	Number
PG 16	10	32,5	41,5	25	27	16	1.552.1616.14
PG 21	11	40	53	30	33	20	1.552.2120.14
PG 21	11	40	53,5	35	33	25	1.552.2125.14
PG 29	11	51,5	64,5	42	42	32	1.552.2932.14
NPT 3/4"	13	40	53	30	33	20	1.552.3420.70
NPT 3/4"	13	40	53,5	35	33	25	1.552.3425.70
NPT 1"	19	51,5	64,5	42	42	32	1.552.1032.70

Snapflex Industry standard metric

Snapclip



Material Polyamide




RoHS

Operating Temperature -30 °C – 100 °C (-22 °F – 212 °F)


Colors grey (RAL 7031), black (RAL 9005)

Advice:
- PP on request



fits to Snapflex	H mm	H1 mm	L mm	L1 mm	D mm	d mm	Number grey	Number black
16	27	29,5	21	27	10	5,3	1.730.1600.50	1.730.1601.50
20	31	33,5	28	31	10	5,3	1.730.2000.50	1.730.2001.50
25	36	36	34	37	10	5,3	1.730.2500.50	1.730.2501.50
32	43	45,5	42	42,5	10	5,3	1.730.3200.50	1.730.3201.50
40	51	53,5	51	52	10	5,3	1.730.4000.50	1.730.4001.50
50	61	63,5	62	65	10	5,3	1.730.5000.50	1.730.5001.50
63	73	77	76	78	10	5,3	1.730.6300.50	1.730.6301.50


Snapform



Material Special steel



RoHS



fits to Snapflex	H mm	L mm	B mm	Number
16	50	66	30	1.318.1600.04
20	60	75	34	1.318.2000.04
25	65	80	39	1.318.2500.04
32	75	90	46	1.318.3200.04
40	95	105	55	1.318.4000.04
50	115	125	66	1.318.5000.04
63	145	165	82	1.318.6300.04

Corrugated conduit systems

Snapflex-Ex metric


Conduits of the Snapflex-Ex series are based on metric dimensions. They were designed for standard applications in hazardous locations type "e" according to EN 60079-0 and EN 60079-7.



You can find in this chapter:

- ATEX certified conduits
- ATEX certified combined conduit/cable glands

Snapflex-Ex



Material Polyamide



Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)


Colors black (RAL 9005)

Advice:
- For the international certificates
please see page 176 or our homepage
www.hummel.com



Size D	d mm	D mm	Number black
16	10,7	16	1.560.1601.50
20	14,1	20	1.560.2001.50
25	18,3	25	1.560.2501.50
32	24,3	32	1.560.3201.50
40	31,2	40	1.560.4001.50

Snapclip-Ex




Material Polyamide



Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)

Colors black (RAL 9005)

Advice:
- For the international certificates
please see page 176 or our homepage
www.hummel.com



Size D	H mm	H1 mm	L mm	L1 mm	D mm	d mm	Number black
16	27	29,5	21	27	10	5,3	1.731.1601.50
20	31	33,5	28	37	10	5,3	1.731.2001.50
25	36	36	34	37	10	5,3	1.731.2501.50
32	43	45,5	42	42,5	10	5,3	1.731.3201.50
40	51	53,5	51	52	10	5,3	1.731.4001.50

Snapcllic-DUO-MS-Ex

Metr.



II 2G 1D

Material Nickel plated brass


Clamping insert Polyamide

Seal NBR

Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)

Advice:

- NPT and elongated thread on request
- For the international certificates please see page 176 or our homepage www.hummel.com



AG	mm	GL mm	H mm	D mm	mm	fits to Snapflex-Ex	Number
M 16 x 1,5	5 – 10	6	38,5	25	24/20	16	1.566.1601.50
M 16 x 1,5	3 – 7	6	38,5	25	24/20	16	1.566.1601.51
M 20 x 1,5	10 – 14	6	41,5	30	28/24	20	1.566.2001.50
M 20 x 1,5	7 – 12	6	41,5	30	28/24	20	1.566.2001.51
M 25 x 1,5	13 – 18	7	44,5	35	34/30	25	1.566.2501.50
M 25 x 1,5	9 – 16	7	44,5	35	34/30	25	1.566.2501.51
M 32 x 1,5	18 – 24	8	52,5	42	40	32	1.566.3201.50
M 32 x 1,5	13 – 20	8	52,5	42	40	32	1.566.3201.51
M 40 x 1,5	22 – 31	8	59	50	50	40	1.566.4001.50
M 40 x 1,5	20 – 26	8	59	50	50	40	1.566.4001.51

Snapclic-DUO-MS-Ex

PG



Material Nickel plated brass

Clamping insert Polyamide

Seal NBR


Operating Temperature -20 °C – 95 °C (-4 °F – 203 °F)

Advice:

- NPT and elongated thread on request
- For the international certificates please see page 176 or our homepage www.hummel.com



II 2G 1D



AG	$\varnothing$ mm	GL mm	H mm	D mm	mm	fits to Snapflex-Ex	Number
PG 11	5-10	6	38,5	25	24/20	16	1.567.1116.01
PG 11	3-7	6	38,5	25	24/20	16	1.567.1116.15
PG 16	10-14	6	41,5	30	28/24	20	1.567.1620.01
PG 16	7-12	6	41,5	30	28/24	20	1.567.1620.15
PG 21	13-16	7	44,5	35	34/30	25	1.567.2125.01
PG 21	9-16	7	44,5	35	34/30	25	1.567.2125.15
PG 29	18-22	8	52,5	42	40	32	1.567.2932.01
PG 29	13-20	8	52,5	42	40	32	1.567.2932.15
PG 36	22-28	8	59	50	50	40	1.567.3640.01
PG 36	20-26	8	59	50	50	40	1.567.3640.15

Corrugated conduit systems

DN conduits


You can find in this chapter:

- DN conduit made of polyamide
- SM fittings for fast mounting of DN conduit
- snap elbow systems for DN conduit



SM-WS-PA

DN



Material Polyamide



RoHS


Operating Temperature -40 °C – 110 °C (-40 °F – 230 °F)

Colors grey (RAL 7031), black (RAL 9005)



Size DN	Typ	d mm	D mm	Number grey	Number black
10	PA	10	13	1.510.0900.14	1.510.0901.14
12	PA	12	15,5	1.510.1100.14	1.510.1101.14
14	PA	14	18,5	1.510.1300.14	1.510.1301.14
17	PA	16,5	21	1.510.1600.14	1.510.1601.14
23	PA	22,5	28,5	1.510.2100.14	1.510.2101.14
29	PA	28,5	34,5	1.510.2900.14	1.510.2901.14
37	PA	36	42	1.510.3600.14	1.510.3601.14
50	PA	47,5	54	1.510.4800.14	1.510.4801.14

Metr., PG, NPT




AG	GL mm	H mm	D mm	 mm	DN	Number grey	Number black
M 16 x 1,5	8	23	20	17	10	1.511.1600.50	1.511.1601.50
M 20 x 1,5	9	28	26,5	24	14	1.511.2000.50	1.511.2001.50
M 25 x 1,5	11	32	38,5	35	23	1.511.2500.50	1.511.2501.50
M 32 x 1,5	11	35	46	42	29	1.511.3200.50	1.511.3201.50
PG 9	8	23	19	17	10	1.511.0900.14	1.511.0901.14
PG 11	8	25	23	21	12	1.511.1100.14	1.511.1101.14
PG 13,5	9	28	26,5	24	14	1.511.1300.14	1.511.1301.14
PG 16	10	29	30	27	17	1.511.1600.14	1.511.1601.14
PG 21	11	32	38,5	35	23	1.511.2100.14	1.511.2101.14
PG 29	11	35	46	42	29	1.511.2900.14	1.511.2901.14
PG 36	13	41	54,5	50	37	1.511.3600.14	1.511.3601.14
PG 48	14	46	70	64	50	1.511.4800.14	1.511.4801.14
NPT 3/8"	15	23	19	17	10	1.511.3800.70	1.511.3801.70
NPT 1/2"	13	29	30	27	17	1.511.1216.70	1.511.1217.70
NPT 3/4"	13	32	38,5	35	23	1.511.3400.70	1.511.3401.70
NPT 1"	15	35	46	42	29	1.511.1000.70	1.511.1001.70

SM-W

Metr., PG, NPT



Material	Polyamide
O-Ring	NBR
Protection	IP 54 with fixed conduit mounting IP 65
Operating Temperature	-20 °C – 80 °C (-4 °F – 176 °F)
Colors	black (RAL 9005)




AG	GL mm	H mm	L mm	 mm	D mm	fits to SM-Conduit DN	Number
M 16 x 1,5	8	23	43	19	20	10	1.513.1601.50
M 20 x 1,5	9	30,5	52	24	26,5	14	1.513.2001.50
M 25 x 1,5	11	40	70	33	38,5	23	1.513.2501.50
M 32 x 1,5	11	51,5	83	42	46	29	1.513.3201.50
PG 9	8	23	43	19	19	10	1.513.0901.14
PG 11	8	27	48	22	23	12	1.513.1101.14
PG 13,5	9	30,5	52	24	26,5	14	1.513.1301.14
PG 16	10	32,5	56	27	30	17	1.513.1601.14
PG 21	11	40	70	33	38,5	23	1.513.2101.14
PG 29	11	51,5	83	42	46	29	1.513.2901.14
NPT 3/8"	15	23	43	19	19	10	1.513.3801.70
NPT 1/2"	13	32,5	56	27	30	17	1.513.1217.70
NPT 3/4"	13	40	70	33	38,5	23	1.513.3401.70
NPT 1"	15	51,5	83	42	46	29	1.513.1001.70

DN



RoHS



Size DN	Flange	Ø mm	A mm	B mm	C mm	D mm	F mm	H mm	Number grey	Number black
12	1	4,3	49	47	37	15,5	29	35	1.312.1100.15	1.312.1101.15
17	1	4,3	49	47	37	15,5	29	35	1.312.1600.15	1.312.1601.15
23	1	6,0	69	65	51,5	21,5	41,5	44	1.312.2100.15	1.312.2101.15
29	2	6,5	90	78	64,5	9,5	64,5	55	1.312.2900.15	1.312.2901.15
37	2	6,5	99	94	79,5	10,5	79,5	66	1.312.3600.15	1.312.3601.15
50	2	6,5	116	101	87,5	12,5	87,5	76	1.312.4800.15	1.312.4801.15

Technical Information

Other International Ex-Certifications



Ukraine

No. 1100



Russia

PPC 00-27485

POCC-DE-RG05-B03140, POCC-RU-0001-11TB05



China

CQST CNEx06.1147U

CQST CNEx06.1148U



Brazil

INMETRO MC AEX-4665-X

INMETRO MC AEX-5233-X

INMETRO MC AEX-5234-X

INMETRO MC AEX-5235-X

INMETRO MC AEX-8528

INMETRO MC AEX-6203-X

INMETRO MC AEX-6410-X

INMETRO MC AEX-6411-X

INMETRO MC AEX-6412-X

INMETRO MC AEX-8822-X

Installation Instructions

Multi hole inserts:

Cable diameter should not be less than 20% of hole diameter and the difference between cable diameter and hole should never exceed 1 mm (.04").

Flat cable inserts:

The clamping range of the cable used may not deviate from the manufacturer-specified minimum values by more than 1 mm in length and 1 mm in width. The geometries of the cable and the insert hole must be compatible (semicircular or straight at the sides).



IECEX BVS 07.0019X

IECEX BVS 07.0021

IECEX BVS 07.0020X

IECEX BVS 07.0022X

IECEX BVS 10.0078X

IECEX KEM 06.0056

IECEX KEM 07.0012

IECEX KEM 07.0014X

IECEX KEM 07.0013X

Approvals for HSK Strain Relief Fittings / Licence Number 40012033

Page	Article	Number	Temperature Range	Approval G (Gas)	Approval D (Dust)	EC-Type Examination Certificate
148	RSD-MS-Ex	1.078.*	-20 °C – 95 °C	x	x	DMT 03 ATEX E 049
148	RSD-MS-Ex	1.079.*	-60 °C – 180 °C	x	x	DMT 03 ATEX E 049
152	RSD-INOX-Ex	1.098.*	-20 °C – 180 °C	x	x	DMT 03 ATEX E 049
152	RSD-INOX-Ex	1.099.*	-60 °C – 180 °C	x	x	DMT 03 ATEX E 049
151	V-INOX-Ex	1.192.*	-20 °C – 95 °C	x	x	DMT 03 ATEX E 049
151	V-INOX-FPM-Ex	1.193.*	-20 °C – 180 °C	x	x	DMT 03 ATEX E 049
151	V-INOX-VMQ-Ex	1.194.*	-60 °C – 180 °C	x	x	DMT 03 ATEX E 049
147	V-MS-Ex	1.197.*	-20 °C – 95 °C	x	x	DMT 03 ATEX E 049
147	V-MS-FPM-Ex	1.198.*	-20 °C – 180 °C	x	x	DMT 03 ATEX E 049
147	V-MS-VMQ-Ex	1.199.*	-60 °C – 180 °C	x	x	DMT 03 ATEX E 049
134	HSK-K-MZ-Ex	1.215.*	-20 °C – 70 °C	x	x	KEMA 99 ATEX 6971 X
112–116	HSK-K-Ex	1.291.*	-20 °C – 95 °C	x	x	DMT 02 ATEX E 047 X
112, 113	HSK-K-Ex	1.295.*	-20 °C – 95 °C	x	x	DMT 02 ATEX E 047 X
146	HSK-V-Ex / Mz-V-Ex	1.296.*	-20 °C – 95 °C	x	x	BVS 03 ATEX E 298
144, 145	V-Ex	1.297.*	-20 °C – 90 °C	x	x	DMT 03 ATEX E 049
169, 170	Snapclix-Duo-MS-Ex	1.566.* / 1.567.*	-20 °C – 95 °C	x	x	BVS 06 ATEX E 069 X
168	Snapflex-Ex	1.560.*	-20 °C – 95 °C	x	x	BVS 06 ATEX E 069 X
133	HSK-K-FLAKA-Ex	1.589.*	-20 °C – 95 °C	x	x	DMT 02 ATEX E 047 X
136	HSK-M-FLAKA-Ex	1.689.*	-20 °C – 95 °C	x	x	DMT 03 ATEX E 051 X
132	HSK-K-Multi-Ex	1.599.*	-20 °C – 95 °C	x	x	DMT 02 ATEX E 047 X
106, 107	EXIOS Barrier	1.606.*	-60 °C – 85 °C	x	x	Sira-11-ATEX-1110-X
104, 105	EXIOS Standard	1.605.*	-60 °C – 105 °C	x	x	BVS 10 ATEX E 062 X
117–120, 126, 127	HSK-M/EMV-Ex	1.610.* / 1.616.*	-20 °C – 95 °C	x	x	DMT 03 ATEX E 051 X
128–130, 137, 138	HSK-MZ/EMV-Ex	1.611.* / 1.617.*	-20 °C – 95 °C	x	x	DMT 03 ATEX E 051 X
121, 122	HSK-INOX-Ex	1.612.*	-20 °C – 95 °C	x	x	DMT 03 ATEX E 051 X
140	HSK-M-Ex-d	1.622.*	-60 °C – 105 °C	x	x	KEMA 99 ATEX 6968 X
141	HSK-MZ-Ex-d	1.628.*	-60 °C – 105 °C	x	x	KEMA 99 ATEX 6968 X
142	HSK-INOX-Ex-d	1.632.*	-60 °C – 105 °C	x	x	KEMA 99 ATEX 6968 X
142	HSK-INOX-PVDF-Ex-d	1.633.*	-20 °C – 130 °C	x	x	KEMA 99 ATEX 6968 X
140	HSK-M-PVDF-Ex-d	1.634.*	-20 °C – 130 °C	x	x	KEMA 99 ATEX 6968 X
124, 125	HSK-M-EMV-D-Ex	1.636.*	-20 °C – 95 °C	x	x	DMT 03 ATEX E 051 X
124, 125	HSK-M-EMV-D-Ex	1.637.*	-60 °C – 95 °C	x	x	KEMA 99 ATEX 6971 X
117–120, 126, 127	HSK-M/EMV-Ex	1.640.* / 1.646.*	-60 °C – 95 °C	x	x	KEMA 99 ATEX 6971 X
128–130	HSK-MZ/EMV-Ex	1.647.*	-60 °C – 95 °C	x	x	KEMA 99 ATEX 6971 X
121, 122	HSK-INOX-Ex	1.642.*	-60 °C – 95 °C	x	x	KEMA 99 ATEX 6971 X
117–120	HSK-M-PVDF-Ex	1.660.*	-20 °C – 130 °C	x	x	KEMA 99 ATEX 6971 X
137, 138	HSK-MZ-PVDF-Ex	1.661.*	-20 °C – 130 °C	x	x	KEMA 99 ATEX 6971 X
121, 122	HSK-INOX-PVDF-Ex	1.662.*	-20 °C – 130 °C	x	x	KEMA 99 ATEX 6971 X
127	HSK-M-EMV-PVDF-Ex	1.666.*	-20 °C – 130 °C	x	x	KEMA 99 ATEX 6971 X
129, 130	HSK-MZ-EMV-PVDF-Ex	1.667.*	-20 °C – 130 °C	x	x	KEMA 99 ATEX 6971 X
135	HSK-M-Multi-Ex	1.687.*	-20 °C – 95 °C	x	x	DMT 03 ATEX E 051 X
168	Snapclip-Ex	1.731.*	-20 °C – 95 °C	x	x	BVS 06 ATEX E 069 X
149, 153	V-MS-/INOX-Ex-d	1.875.* / 1.895.*	-20 °C – 95 °C	x	x	KEMA 06 ATEX 0024
149, 153	V-MS-/INOX-FPM-Ex-d	1.876.* / 1.896.*	-20 °C – 180 °C	x	x	KEMA 06 ATEX 0024
149, 153	V-MS-/INOX-VMQ-Ex-d	1.877.* / 1.897.*	-60 °C – 180 °C	x	x	KEMA 06 ATEX 0024
150, 154	RSD-MS-/INOX-Ex-d	1.878.* / 1.898.*	-20 °C – 95 °C	x	x	KEMA 06 ATEX 0024
150, 154	RSD-MS-/INOX-Ex-d	1.879.* / 1.899.*	-60 °C – 180 °C	x	x	KEMA 06 ATEX 0024

International Protection, EN 60529


1. Code		2. Code	Penetration of water	Non-protected	protection against dripping water	Protected against vertically falling water drops when device is tilted up to 15°	Water sprayed at an angle up to 60° on either side of the vertical shall have no harmful effects	Water splashed from any direction shall have no harmful effects	Water projected in jets from any direction shall have no harmful effects	Water projected in powerful jets from any direction shall have no harmful effects	protection against temporary submersion	protection against permanent submersion
Protection against human access to hazardous parts	Protection of equipment against penetration of solid foreign objects			IP x0	IP x1	IP x2	IP x3	IP x4	IP x5	IP x6	IP x7	IP x8
Non-protected	Non-protected	IP 0x		IP 00								
Protected against access to hazardous parts with the back of the hand	Protected against solid foreign objects larger in diameter than 50mm	IP 1x		IP 10	IP 11	IP 12						
Protected against access to hazardous parts with a finger	Protected against solid foreign object larger in diameter than 12,5mm	IP 2x		IP 20	IP 21	IP 22	IP 23					
Protected against access to hazardous parts with a tool larger in diameter than 25mm	Protected against solid foreign objects larger in diameter than 2,5mm	IP 3x		IP 30	IP 31	IP 32	IP 33	IP 34				
Protected against access to hazardous parts with a wire larger in diameter than 1,0mm	Protected against solid foreign objects larger in diameter than 1mm	IP 4x		IP 40	IP 41	IP 42	IP 43	IP 44				
Protected against access to hazardous parts with a wire larger in diameter than 1,0mm	Prevents penetration of dust sufficient to cause damage inside the equipment.	IP 5x		IP 50				IP 54	IP 55			
Protected against access to hazardous parts with a wire larger in diameter than 1,0mm	Dust proof	IP 6x		IP 60					IP 65	IP 66	IP 67	IP 68

Product Material Abbreviations

CR	Chloroprene rubber	PP	Polypropylene
FPM	Fluorelastomer	PVC	Polyvinylchloride
Ms	Nickel plated brass	PVDF	Polyvinylidenfluoride
NBR	Buna-N	SB	Styrene Butadiene
PA	Polyamide	VMQ	Silicone
PE	Polyethylene		


Technical Information

Metric ISO Thread Specifications




Size	Pitch mm	Outside-Ø D1 mm	Inside-Ø D2 mm	Thru- hole mm
M 12 x 1,5	1,5	12	10,38	12,2
M 16 x 1,5	1,5	16	14,38	16,2
M 20 x 1,5	1,5	20	18,38	20,2
M 25 x 1,5	1,5	25	23,38	25,2
M 32 x 1,5	1,5	32	30,38	32,2
M 40 x 1,5	1,5	40	38,38	40,2
M 50 x 1,5	1,5	50	48,38	50,2
M 63 x 1,5	1,5	63	61,38	63,2

PG Thread Specifications




Size	Pitch mm	Outside-Ø D1 mm	Inside-Ø D2 mm	Thru- hole mm
PG 7	1,270	12,5	11,28	12,7
PG 9	1,410	15,2	13,86	15,4
PG 11	1,410	18,6	17,26	18,8
PG 13,5	1,410	20,4	19,06	20,7
PG 16	1,410	22,5	21,16	22,8
PG 21	1,588	28,3	26,78	28,6
PG 29	1,588	37,0	35,48	37,4
PG 36	1,588	47,0	45,48	47,5
PG 42	1,588	54,0	52,48	54,5
PG 48	1,588	59,3	57,78	59,8

NPT Thread Specifications



Size	Pitch mm	Outside-Ø mm	Number of pitches n
1/4" NPT	1,411	13,716	18
3/8" NPT	1,411	17,145	18
1/2" NPT	1,814	21,336	14
3/4" NPT	1,814	26,67	14
1" NPT	2,208	33,4	11 1/2
1 1/4" NPT	2,208	42,164	11 1/2
1 1/2" NPT	2,208	48,26	11 1/2
2" NPT	2,208	60,325	11 1/2
2 1/2" NPT	3,175	73,025	8
3" NPT	3,175	88,9	8
3 1/2" NPT	3,175	101,6	8

British G Thread Specifications



Size	Pitch mm	Outside-Ø D1 mm	Inside-Ø D2 mm	Thru- hole mm
G 1/4"	1,337	13,157	11,445	13,4
G 3/8"	1,337	16,662	14,950	17,0
G 1/2"	1,814	20,955	18,631	21,3
G 5/8"	1,814	26,441	24,117	26,8
G 1"	2,309	33,249	30,291	33,7
G 1 1/4"	2,309	41,910	38,952	42,4
G 1 1/2"	2,309	47,803	44,845	48,3
G 2"	2,309	59,614	56,656	60,2
G 2 1/2"	2,309	75,184	72,226	75,7
G 3"	2,309	87,884	84,926	88,5
G 3 1/2"	2,309	100,330	97,372	101,0
G 4"	2,309	113,030	110,072	114,0

Snapturn

High strain relief on corrugated conduit!

1. Screw Snapturn into mounting hole
2. Insert Snapflex into Snapturn
3. Hold Snapturn against the housing and tighten the nut – finished!



finished

Snapturn

the efficient way of
corrugated conduit
mounting

HSK-M-EMV / METRICA-M-EMV




Step 1



- + Strip cable
- + Expose braided shield

Step 2

- + Feed cable through dome nut and clamping insert
- + Fold braided shield over clamping insert
- + Make sure that braided shield overlaps the O-Ring by 3/32" (2 mm)



Step 3




- + Push clamping insert into body and tighten dome nut
- + Assemble into housing
- + Finished!

HSK-M-EMV-D

Option 1

Feed-through of cable and shield (braided or foil)


- + Expose shield approximately 7/16" (10 mm)
- + Insert cable into fitting until the shield reaches the contact position
- + Tighten dome nut



Option 2

Feed-through of shield (braided or foil)


- + Remove cable jacket to expose the shield as required
- + Insert cable into fitting until the shield reaches the contact position
- + Tighten dome nut



Option 3

Termination of the braided shield in the fitting

- + Strip cable jacket and braided shield to different lengths
- + For small diameter cables fold the braided shield back over the cable jacket
- + Insert cable into fitting until the shield reaches the contact position
- + Tighten dome nut





www.hummel.com

[illegible]

Europe

HUMMEL France

HUMMEL s.a.r.l.
4, rue des fleurs
68190 Ungersheim / France

Tel. +33 (0) 3 89 / 55 37 20
Fax +33 (0) 3 89 / 53 80 27
E-Mail info.fr@hummel.com
www.hummel.com

HUMMEL UK

HUMMEL UK Limited
Office 3, Momentum House
Enterprise Way, Lowton St Marys,
Warrington, Cheshire, WA3 2BP
United Kingdom

Tel. +44 (0) 19 42 / 60 56 95
Fax +44 (0) 19 42 / 26 93 24
E-Mail info.uk@hummel.com
www.hummel.com

HUMMEL Italy

HUMMEL s.r.l.
Via Valdellatorre 182
10091 Alpignano (Torino) / Italy

Tel. +39 / (0) 11 / 9 68 26 38
Fax +39 / (0) 11 / 9 78 55 50
E-Mail info.it@hummel.com
www.hummel.com

HUMMEL Poland

HUMMEL Sales Office Poland
Al. 23 Stycznia 26 lok. 20
86-300 Grudziadz / Polen

Tel. +48 (662) 38 27 99
Fax +48 (56) 643 00 11
E-Mail info.pl@hummel.com
www.hummel.com

HUMMEL Russia

OOO HUMMEL
Retschnikow 21, Strojenije 1
115142 Moskau / Russia

Tel. +7 / 499 / 7 82-40 75
Fax +7 / 499 / 6 14-67 40
E-Mail info@hummel-russia.ru
www.hummel-russia.ru

HUMMEL Skandivavia

HUMMEL Connector Systems AB
Oxtorgsgatan 3
55317 Jönköping / Sweden

Tel. +46 (0) 73 / 800 12 00
E-Mail info.se@hummel.com
www.hummel.com

HUMMEL Hungary

HUMMEL Ungarn Kft.
Ko' rösü út 49.
2360 Gyál / Hungary

Tel. +36 / 29 54 06 33
Fax +36 / 29 54 06 35
E-Mail info.hcs.hu@hummel.com
www.hummel.com

Asia

HUMMEL Azerbaijan

HUMMEL Sales Office Azerbaijan
Jafar Khandan str. 3, ap. 25
AZ 1130 Baku / Azerbaijan

Tel. +994 12 569 15 75
Mobil +994 50 349 63 90
E-Mail info.az@hummel.com
www.hummel.com

HUMMEL China

HUMMEL Connector Systems (Shanghai) Co., Ltd.
Room 1701 Central Plaza
No.227 Huang Pi (N) Road
200003 Shanghai / P.R. China

Tel. +86 / 21 63 75 85-51
Fax +86 / 21 63 75 85-53
E-Mail info.hcs.cn@hummel.com
www.hummel.com

HUMMEL India

HUMMEL Connector Systems Pvt. Ltd.
1211, Surya Kiran Building, 19,
Kasturba Gandhi Marg
110001 New Delhi / India

Tel. +91 / 11 / 430075-21 / - 23
Fax +91 / 11 / 430075-22
E-Mail info.in@hummel.com
www.hummel.com

HUMMEL Kazakhstan

HUMMEL Sales Office Kasachstan
Turksibskij rayon, Mikrorayon Zhuldyz-1,
dom 6, kwartira 19
050049 Almaty / Kasachstan

Tel. +7 701 7262004
E-Mail info.kz@hummel.com
www.hummel.com

HUMMEL South Korea

HUMMEL AG Korea Branch
#628 Ssangyong Platinum River,
432-10 Cheonho-dong, Gangdong-gu,
Seoul, 134-020 Korea

Tel. +82 (0) 2 470 27 62
Fax +82 (0) 2 470 27 63
E-Mail info.kr@hummel.com
www.hummel.com

South America

HUMMEL Brazil

HUMMEL Connector Systems Ltda.
Rua Derville Gabriel Pereira, 280
Barro Preto – Centro Empresarial Tatui I
CEP 18280-614 - Tatui / SP / Brazil

Tel. +55 (15) 33 22-70 00
Fax +55 (15) 33 22-70 26
E-Mail vendas@hummel.com.br
www.hummel.com.br

HUMMEL Divisions

Electro Technology

Touchpanels - Solutions - Custom fabrication of Enclosures
Industrial Enclosures - Cable Glands - Cable Protection - Circular Connectors



Electronic

Operator Panels - Frontsheets and Keyboards - Battery Chargers
Cable Assembly - Sensors - Controls - Systems Solutions - Temperature Controllers



Heating Equipment

Solar Heating - Valves and Fittings - Compression Fittings
Heat Pumps - Thermostatic Heads



Customised

Parts made of Metal and Nylon



www.hummel.com

HUMMEL AG

Division ET
Lise-Meitner-Straße 2
79211 Denzlingen
Germany

Tel. +49 (0)76 66 / 9 11 10-0
Fax +49 (0)76 66 / 9 11 10-20
E-Mail info.et@hummel.com

HUMMEL AG

Lise-Meitner-Straße 2
79211 Denzlingen
Germany
www.hummel.com

