

## Weller Hot Air Rework Station With Internal Pump, 120 V



◀◀ previous print close next ▶▶

### Product Details

<b>Catalog No.</b>	<b>WHA900</b>
<b>UPC Code</b>	<b>037103222282</b>
<b>Wattage</b>	<b>650 W</b>
<b>Desoldering Pencil(s)</b>	<b>None</b>
<b>Temperature Range</b>	<b>122° F to 1022° F</b>
<b>Voltage</b>	<b>120 V/24 V</b>
<b>Supplied Tip(s)</b>	<b>None</b>
<b>Air Flow Volume</b>	<b>5 l/min - 50 l/min</b>
<b>Pump Type</b>	<b>Turbine</b>
<b>Packaging</b>	<b>Industrial Box/ Carton</b>
<b>Literature</b>	<b><a href="#">550582.pdf</a></b>
<b>Low Res. Image</b>	<b><a href="#">WHA900_100.jpg</a></b>
<b>High Res. Image</b>	<b><a href="#">WHA900_300.jpg</a></b>
<b>Operating Ins.</b>	<b><a href="#">WHA900_USA_Manual.pdf</a></b>
<b>Stock Item</b>	<b>Normal Stock Item</b>

### Package Details (Dimensions)

Email this Page

#### Product Features:

- For reworking SMT components
- Compact design maximizes workspace efficiency
- Controlled output maintains set temp regardless of air flow setting
- Temperature and air flow are controlled independently
- Standby button allows you to power down to low settings when not in use
- Includes a rest support for the hand piece
- Nozzles sold separately