

## General Information

Extended Product Type:	JB5-3
Product ID:	1SNK905303R0000
EAN:	3472599097568
Catalog Description:	JB5-3 Jumper Bar - Orange
Long Description:	Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking, - Perfectly adapted to low level electrical contact (20mA, 50mV).

## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

## Ordering

Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010
Color:	Orange

## Dimensions

Product Net Height:	13.4 mm
Product Net Length:	26.8 mm
Product Net Depth:	26.8 mm
Product Net Weight:	2 g
Product Net Width:	5.2 mm

## Technical

Spacing:	5.2 mm
Function:	Jumper Bars
Rated Current ( $I_n$ ):	Main Circuit 32 A
Rated Short-time Withstand Current ( $I_{cw}$ ):	for 1 s 480 A
Rated Voltage ( $U_r$ ):	1000 V
Rated Impulse Withstand Voltage ( $U_{imp}$ ):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	1 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	ZDK2.5-22 ZDP2.5-11 ZDP2.5-22 ZDP2.5-D1 ZDP2.5-D2 ZDS4-22 ZK2.5 ZK2.5-3P ZK2.5-4P ZK2.5-CH-4P ZK2.5-D1 ZK2.5-D1-PE ZK2.5-D2 ZK2.5-D2-PE ZK2.5-D-CH ZK2.5-PE ZK2.5-PE-3P ZK2.5-PE-4P ZK2.5-S ZK2.5-S-4P ZK2.5-SF ZK2.5-SF-R ZK2.5-SP ZK2.5-SP-4P ZK2.5-S-R1 ZP2.5 ZP2.5-3P ZP2.5-4P ZP2.5-D1

ZP2.5-D2  
ZP2.5-PE  
ZP2.5-PE-3P  
ZP2.5-PE-4P  
ZS4  
ZS4-D1  
ZS4-D2  
ZS4-D2-S  
ZS4-D2-S-T  
ZS4-D-CH  
ZS4-T3

## Technical UL/CSA

<b>Flammability According to UL94:</b>	V0
<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V

## Environmental

<b>Resistance to Vibrations acc. to IEC 60068-2-6:</b>	Compliant
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C

## Certificates and Declarations (Document Number)

<b>Instructions and Manuals:</b>	1SNK160027C0201
<b>ATEX Certificate:</b>	1SND162004A1706
<b>CB Certificate:</b>	1SND161017A0202
<b>Data Sheet, Technical Information:</b>	1SNK160027D0201
<b>RoHS Information:</b>	1SND230499F0202

## Classifications

<b>E-nummer:</b>	2925367
<b>ETIM 4:</b>	EC000489 - Cross-connector for terminal block
<b>ETIM 5:</b>	EC000489 - Cross-connector for terminal block
<b>ETIM 6:</b>	EC000489 - Cross-connector for terminal block
<b>Object Classification Code:</b>	X

## Container Information

<b>Package Level 1 Width:</b>	50 mm
<b>Package Level 1 Length:</b>	117 mm
<b>Package Level 1 Height:</b>	50 mm
<b>Package Level 1 Gross Weight:</b>	0.1 kg
<b>Package Level 1 EAN:</b>	3472599097568
<b>Package Level 2 Units:</b>	1500 piece
<b>Package Level 3 Units:</b>	144000 piece
<b>Package Level 1 Units:</b>	50 piece

