

RoHS Compliant

### Features

- Miniature ceramic package
- Highly reliable with seam welding
- CMOS output
- Supply voltage  $V_{CC}=3.3V$
- $\pm 25 \times 10^{-6}$  available

Table 1

| Freq. Tol. Code | Tolerance $\times 10^{-6}$ | Operating Temperature Range (°C) | Note                          |
|-----------------|----------------------------|----------------------------------|-------------------------------|
| 0               | $\pm 50$                   | -10 to +70                       | Standard specifications       |
| S               | $\pm 30$                   |                                  |                               |
| U               | $\pm 25$                   |                                  |                               |
| F               | $\pm 100$                  | -40 to +85                       | With only certain frequencies |
| G               | $\pm 50$                   |                                  |                               |
| 6               | $\pm 50$                   | -40 to +105                      |                               |

### How to Order

KC3225A 25.0000 C 3 0 E 00  
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Type (3.2x2.5mm SMD)
- ② Output Frequency
- ③ Output Type (CMOS)
- ④ Supply Voltage (3.3V)
- ⑤ Frequency Tolerance (See Table 1)
- ⑥ Symmetry/ INH Function (45/ 55%, Stand-by)
- ⑦ Customer Special Model Suffix (STD Specification is "00")

Packaging (Tape & Reel 2000 pcs./ reel)


### Specifications

| Item  | Symbol      | Conditions  | Min.  | Max.         | Units   |                  |
|---|-------------|---|---|--------------|---------|------------------|
| Output Frequency Range  | $f_o$       |   | 1.5   | 125          | MHz     |                  |
| Frequency Tolerance   | $f_{tol}$   | Initial tolerance, Operating temperature range, Rated power supply voltage change, Load change, Aging (1 year @25°C), Shock and vibration | Op. Temp.: -40 to +85°C                                 | -100         | +100    | $\times 10^{-6}$ |
|   |             |   | Op. Temp.: -10 to +70°C/<br>-40 to +85°C/ -40 to +105°C | -50          | +50     |                  |
|   |             |   | Op. Temp.: -10 to +70°C                                 | -30          | +30     |                  |
|   |             |   | Op. Temp.: -10 to +70°C                                 | -25          | +25     |                  |
| Storage Temperature Range                                     | $T_{stg}$   |   | -55   | +125         | °C      |                  |
| Operating Temperature Range                                   | $T_{use}$   | Standard Specifications   | -10   | +70          | °C      |                  |
|   |             | Extend (Option)   | -40   | +105         |         |                  |
| Max. Supply Voltage   | —           |   | -0.5  | +7.0         | V       |                  |
| Supply Voltage  | $V_{CC}$    | Freq. Tol.Code: 0, S, F   | +2.97   | +3.63        | V       |                  |
|   |             | Freq. Tol.Code: U, G, 6   | +3.14   | +3.46        |         |                  |
| Current Consumption (Maximum Loaded)                          | $I_{CC}$    | 1.5 $\leq f_o \leq 26$ MHz  | —   | 6            | mA      |                  |
|   |             | 26 $< f_o \leq 50$ MHz  | —   | 8            |         |                  |
|   |             | 50 $< f_o \leq 67.5$ MHz  | —   | 12           |         |                  |
|   |             | 67.5 $< f_o \leq 95$ MHz  | —   | 20           |         |                  |
|   |             | 95 $< f_o \leq 125$ MHz   | —   | 25           |         |                  |
| Stand-by Current  | $I_{std}$   |   | —   | 10           | $\mu A$ |                  |
| Symmetry  | SYM         | @50% $V_{CC}$   | 45  | 55           | %       |                  |
| Rise/ Fall Time (10% $V_{CC}$ to 90% $V_{CC}$ Maximum Loaded) | $t_r / t_f$ | 1.5 $\leq f_o \leq 67.5$ MHz  | —   | 5            | ns      |                  |
|   |             | 67.5 $< f_o \leq 125$ MHz   | —   | 3            |         |                  |
| Low Level Output Voltage                                      | $V_{OL}$    | $I_{OL}=4$ mA   | —   | 10% $V_{CC}$ | V       |                  |
| High Level Output Voltage                                     | $V_{OH}$    | $I_{OH}=-4$ mA  | 90% $V_{CC}$  | —            | V       |                  |
| CMOS Load   | $L_{CMOS}$  | CMOS Output   | —   | 15           | pF      |                  |
| Input Voltage Range   | $V_{IN}$    |   | 0   | $V_{CC}$     | V       |                  |
| Low Level Input Voltage                                       | $V_{IL}$    |   | —   | 30% $V_{CC}$ | V       |                  |
| High Level Input Voltage                                      | $V_{IH}$    |   | 70% $V_{CC}$  | —            | V       |                  |
| Disable Time  | $t_{dis}$   |   | —   | 150          | ns      |                  |
| Enable Time   | $t_{ena}$   |   | —   | 5            | ms      |                  |
| Start-up Time   | $t_{str}$   | @Minimum operating voltage to be 0 sec.   | —   | 10           | ms      |                  |
| 1 Sigma Jitter  | $J_{Sigma}$ | Measured with Wavecrest SIA-3000  | 1.5 $\leq f_o \leq 60$ MHz                              | —            | 8       | ps               |
|   |             |   | 60 $< f_o \leq 125$ MHz                                 | —            | 5       |                  |
| Peak to Peak Jitter   | $J_{PK-PK}$ | Measured with Wavecrest SIA-3000  | 1.5 $\leq f_o \leq 60$ MHz                              | —            | 80      | ps               |
|   |             |   | 60 $< f_o \leq 125$ MHz                                 | —            | 40      |                  |

Note: All electrical characteristics are defined at the maximum load and operating temperature range.  
 Please contact us for inquiry about operating temperature range, available frequencies and other conditions.

### Dimensions

(Unit: mm)



### Recommended Land Pattern

(Unit: mm)

