

SL7 and SL4 signal towers

Product Range Catalog

Clearly brighter, louder und faster



EATON

Powering Business Worldwide



Eaton Online Catalog – find product details quickly and efficiently!

You can find comprehensive up-to-date product information at <http://de.ecat.moeller.net>

Lookup

You can search by keywords, product names, article numbers, technical data: The search understands everything and takes you straight to the product you're looking for.

Graphical navigation

Graphical representation of the fields of application and product groups.

Selection aids

Tailored to the typical expert's approach, this search aid helps you quickly find the product you need.


Data sheets

For every article the catalog can generate a technical data sheet, which you can convert to a PDF file for printing or saving with a single click.

Parts lists

From your search results you can create a parts list that you can then send to your Eaton sales partner as a query.

You can find comprehensive up-to-date information about Eaton's automation products and switchgear in our Online Catalog.



HTML data sheet; can be saved as PDF file.

Item	Qty.	Photo	AVDCH ID	Part no.	Short Text
<input type="checkbox"/>	1		111917	ES4P-221-DMX01	Safety control relay, 24 V DC, 10 A
<input type="checkbox"/>	1		228758	FAK-CONBRULATOR	Complete unit
<input type="checkbox"/>	1		284823	M225-00LM-GR-3110D	Double ext. illum. flat, off-button ext.
<input type="checkbox"/>	1		250090	DLR15-R1 (110V/50HZ, 120V/60HZ)	Contactor 7.5kW/400V AC-operated
<input type="checkbox"/>	1		138516	PKB55X10-85	PKE55 - trip block Standard 8-65A

Parts list, e.g. for queries to Eaton Sales.



Signal towers SL7



System overview	6
Ordering	8
Complete devices	8
Customised complete unit	8
Card with LED	8
Continuous light	8
Flashing light	9
Strobe light	10
Card with high-output LED	11
Continuous light	11
Flashing light	11
Strobe light	11
Card for filament lamp	11
Continuous light	11
Acoustic modules	12
Basic modules	13
Mounting brackets	14
Including mounting bracket M20 cable gland	14
Tool for replacing filament lamp	14
Filament bulbs	14

Technical data	15
----------------	----

Dimensions	17
------------	----

Complete devices	17
Light modules	17
Acoustic modules	17
Basic modules	18
Base module for connecting to SmartWire-DT®	20
Accessories	20

Signal towers SL4



System overview	22
Ordering	24
Complete devices	24
Customised complete unit	24
Card with LED	24
Continuous light	24
Flashing light	25
Strobe light	26
Multistrobe light	26
Card for filament lamp	27
Continuous light	27
Acoustic modules	27
Basic modules	28
Mounting brackets	29
Including mounting bracket M20 cable gland	29
Tool for replacing filament lamp	29
Filament bulbs	29
Technical data	30

Dimensions	32
------------	----

Complete devices	32
Light modules	32
Acoustic modules	32
Basic modules	33
Base module for connecting to SmartWire-DT®	35
Accessories	35



Energizing a world that demands more.

Discover today's Eaton.

Powering business worldwide

As a global diversified power management company, we help customers worldwide manage the power needed for buildings, aircraft, trucks, cars, machinery and businesses.

Eaton's innovative technologies help customers manage electrical, hydraulic and mechanical power more reliably, efficiently, safely and sustainably.



EATON

Powering Business Worldwide



We deliver:

- **Electrical solutions** that use less energy, improve power reliability and make the places we live and work safer and more comfortable
- **Hydraulic and electrical solutions** that enable machines to deliver more productivity without wasting power
- **Aerospace solutions** that make aircraft lighter, safer and less costly to operate, and help airports operate more efficiently
- **Vehicle drivetrain and powertrain solutions** that deliver more power to cars, trucks and buses, while reducing fuel consumption and emissions

We provide integrated solutions that help make energy, in all its forms, more practical and accessible.

With 2012 sales of \$16.3 billion, Eaton has approximately 103,000 employees around the world and sells products in more than 175 countries.



Eaton's electrical business

Eaton is a global leader with expertise in:

- Power distribution and circuit protection
- Backup power protection
- Solutions for harsh and hazardous environments
- Lighting and security
- Structural solutions and wiring devices
- Control and automation
- Engineering services

Eaton is positioned through its global solutions to answer today's most critical electrical power management challenges. With 100 years of electrical experience behind us, we're energized by the challenge of powering up a world that demands twice as much energy as today. We're anticipating needs, engineering products, and creating solutions to energize our markets today and in the future.

We are dedicated to ensuring that reliable, efficient and safe power is available when it's needed most.

www.eaton.eu

Clearly Eaton!


Eaton has the entire machine in view – from the control panel to the peripherals. Its optimized signal towers can now guarantee even better control over all key processes and with it increased availability for your machines.



Clearly MORE EFFICIENT!

An essential part of Eaton's Lean Solution approach, SmartWire-DT is a technology designed to reduce electrical engineering costs for machines by up to 30%. Signal towers are an important component of this technology, since the advance warning function provides information that help the operator avoid potential standstills and increase availability. Potential failures are not just detected in advance by intelligent switchgear, but in fact are also signaled by signal towers with SmartWire-DT.

Example: Savings in every step of the life cycle



Clearly LOVELIER!

An engaging design with smooth curves enhances the appeal of our new signal towers and, together with the control and signal units in the RMQ-Titan range of products, creates a standardized look for machines and systems.



Clearly LOUDER!

Acoustic modules with up to 8 selectable signals, as well as adjustable volume levels (up to 100 dB), make it possible to adapt perfectly to any environment.

Clearly BRIGHTER!



Signal towers indicate machine states by means of visual and acoustic signals. Accordingly, they must be easy to see from a distance, and the information they provide must be clear from the get-go. Orange has been added to the colors shown in order to comply with international standards. More importantly, Eaton has improved its signal towers exactly where it counts. High-performance LEDs provide a level of brightness that will be reliably seen even under extremely adverse conditions. Benefit from better attention-getting power, stronger brightness and higher volumes as well as multiple tone variants to identify faults unambiguously or even help prevent them from occurring at all.

Clearly MORE COMPACT!



Eaton signal towers have been designed with flexibility in mind so that they can be used regardless of adverse installation conditions, such as the lack of ceiling clearance and situations that require different signals on the right or left-hand side. Both signal tower sizes can also be installed vertically with up to 5 elements per side.

Clearly MORE FLEXIBLE!



Our new signal towers can be flexibly installed in any of 9 different ways. In addition to the option of mounting them on the side, there are various options for mounting the cup-shaped base directly, as well as a variety of tube mounting options. In addition, tubes with lengths of 100, 250, and 400 mm make mounting even more flexible.

Clearly STURDIER!

With a high IP66 degree of protection, our signal towers provide perfect protection even against water jets from all directions. These signal towers are meant for worldwide use. Type approvals and certifications for Europe and North American have already been obtained, and ship classifications and CCC are currently pending.



Mounting and dismantling of protruding signal towers can be a major effort, particularly when transporting machines. The new rapid-mount system speeds up that process by up to 50%.

The transportation cover protects cables and terminals.

Card for filament lamp, continuous light	1	Card with LED	4a	Base module	6
Without light element (filament lamp with BA15d socket)		with LED		Easy mounting with bayonet mount	
Easy mounting with bayonet mount		Flashing frequency 1.4 Hz		Degree of protection IP66	
Modules can be arranged in any order		→ page 10		Including cover plate	
Degree of protection IP66		Card with high-output LED	4b	With spring-cage terminals	
Max. 2 x 5 modules that can be actuated individually (two with base module SL7-CB-D only)		with High Performance LED		Base for mounting on both sides	6a
Operating mode: 100 % DF (duty factor)		Flashing frequency 1.4 Hz		→ page 14	
→ page 11		→ page 11		Base with aluminium tube and plastic foot	6b
Card with LED, continuous light	2	Card with high-output LED	4c	Aluminium tube 100 mm, 250 mm or 400 mm	
Easy mounting with bayonet mount		with High Performance LED with various strobe sequences		→ page 13	
Modules can be arranged in any order		Flashing frequency 1 - 2.6 Hz		Base with aluminum tube and banjo bolt	6c
Degree of protection IP66		→ page 11		Aluminium tube 100 mm, 250 mm or 400 mm	
Max. 2 x 5 modules that can be actuated individually (two with base module SL7-CB-D only)		Acoustic module	5	→ page 13	
Operating mode: 100 % DF (duty factor)		Easy mounting with bayonet mount		Base with external fixing holes	6 d
→ page 11		Set up as topmost module		→ page 13	
Card with LED	2a	Max. 2 x 1 modules that can be actuated separately (two with base module SL7-CB-D only)		One-sided base with bracket	6e
with LED		Permanently integrated cover plate		→ page 14	
→ page 8		Degree of protection IP66		Base with internal (on the inside) fixing holes	6f
Card with high-output LED	2b	Operating mode: 100 % DF (duty factor)		→ page 13	
with High Performance LED		sound pressure 100 db, adjustable with internal potentiometer		Base with built-in (pre-assembled) fixing screws	6g
→ page 11		Acoustic module	5a	→ page 13	
Card with LED, flashing light	3	Continuous tone or pulsed tone, adjustable with internal dip switches		Base with base adapter for slipping onto place (rapid mounting and wiring system)	6h
with LED		Frequency: 2800 Hz		Aluminium tube 100 mm, 250 mm or 400 mm	
Easy mounting with bayonet mount		→ page 12		→ page 13	
Modules can be arranged in any order		Acoustic module	5b	Base with base adapter for slipping onto place (rapid mounting and wiring system) and SmartWire-DT connection	6i
Degree of protection IP66		Multi-tone (8 tones) adjustable with internal dip switch		Aluminium tube 100 mm	
Max. 2 x 5 modules that can be actuated individually (two with base module SL7-CB-D only)		Frequency 500 - 2700 Hz		→ page 13	
Operating mode: 100 % DF (duty factor)		→ page 12		Base with base adapter for slipping onto place (rapid mounting and wiring system) and SmartWire-DT connection	6i
Flashing frequency 2 Hz		Acoustic module	5c	Aluminium tube 100 mm	
→ page 9		Continuous tone or pulsed tone; can be actuated externally; takes up 2 inputs (2 modules)		→ page 13	
Card with LED, strobe light	4	Frequency: 2800 Hz		Accessory Considerations	7
Easy mounting with bayonet mount		→ page 12		Mounting brackets	
Modules can be arranged in any order		Card with LED, continuous light	1	Including mounting bracket M20 cable gland	
Degree of protection IP66		Without light element (filament lamp with BA15d socket)		Tool for replacing filament lamp	
Max. 2 x 5 modules that can be actuated individually (two with base module SL7-CB-D only)		Easy mounting with bayonet mount		Filament lamp	
Operating mode: 100 % DF (duty factor)		Modules can be arranged in any order		→ page 14	
		Degree of protection IP66			
		Max. 2 x 5 modules that can be actuated individually (two with base module SL7-CB-D only)			
		Operating mode: 100 % DF (duty factor)			
		→ page 11			

Ordering

	Rated operational voltage U_e V	Number of modules	Colour	Function	Part no. Article no.	Price see price list	Std. pack
Complete devices							
	24 V AC/DC	2			SL7-100-L-RG-24LED 171424		1 off 
		3			SL7-100-L-RYG-24LED 171425		
Customised complete unit							
Order on request, * = Freely selectable customer identification or stock no., Maximum 10 characters					SL7-COMBINATION-* 171386		1 off

	Rated operational voltage U_e V	Colour	Function	Part no. Article no.	Price see price list	Std. pack	
	Continuous light IP66	24 V AC/DC			SL7-L24-B 171461		1 off 
					SL7-L24-G 171462		
					SL7-L24-R 171463		
					SL7-L24-W 171464		
					SL7-L24-Y 171465		
					SL7-L24-A 171466		
		110/120 V AC			SL7-L120-B 171467		
					SL7-L120-G 171468		
					SL7-L120-R 171469		
					SL7-L120-W 171470		
					SL7-L120-Y 171471		
					SL7-L120-A 171472		
	230/240 V AC		SL7-L230-B 171473				
			SL7-L230-G 171474				
			SL7-L230-R 171475				
			SL7-L230-W 171476				
			SL7-L230-Y 171477				
			SL7-L230-A 171426				

Notes

Information relevant for export to North America 

Product Standards IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
 UL File No. E29184
 UL CCN NKCR

CSA File No.
 CSA Class No.
 NA Certification
 Degree of Protection


UL report applies to both US and Canada
 NKCR7
 UL listed, certified by UL for use in Canada
 UL Type 4, 4X, 13

		Rated operational voltage U_e V	Colour	Function	Part no. Article no.	Price see price list	Std. pack
	Flashing light IP66 2 Hz	24 V AC/DC		  	SL7-BL24-B 171439		1 off  
					SL7-BL24-G 171440		
					SL7-BL24-R 171441		
					SL7-BL24-W 171442		
					SL7-BL24-Y 171388		
					SL7-BL24-A 171389		
		110/120 V AC		SL7-BL120-B 171390			
				SL7-BL120-G 171391			
				SL7-BL120-R 171392			
				SL7-BL120-W 171393			
				SL7-BL120-Y 171394			
				SL7-BL120-A 171395			
		230/240 V AC		SL7-BL230-B 171396			
				SL7-BL230-G 171397			
				SL7-BL230-R 171398			
				SL7-BL230-W 171399			
				SL7-BL230-Y 171400			
				SL7-BL230-A 171401			

Notes

Information relevant for export to North America

 	
Product Standards	IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	UL report applies to both US and Canada
CSA Class No.	NKCR7
NA Certification	UL listed, certified by UL for use in Canada
Degree of Protection	UL Type 4, 4X, 13

		Rated operational voltage U _e V	Colour	Function	Part no. Article no.	Price see price list	Std. pack
Card with LED							
 <p>Strobe light IP66 1.4 Hz</p>	24 V AC/DC			SL7-FL24-B 171402		1 off  	
				SL7-FL24-G 171403			
				SL7-FL24-R 171404			
				SL7-FL24-W 171405			
				SL7-FL24-Y 171406			
				SL7-FL24-A 171407			
		110/120 V AC			SL7-FL120-B 171408		
					SL7-FL120-G 171409		
					SL7-FL120-R 171410		
					SL7-FL120-W 171411		
					SL7-FL120-Y 171412		
					SL7-FL120-A 171413		
		230/240 V AC			SL7-FL230-B 171414		
					SL7-FL230-G 171415		
					SL7-FL230-R 171416		
					SL7-FL230-W 171417		
					SL7-FL230-Y 171418		
					SL7-FL230-A 171419		

Notes

Information relevant for export to North America



Product Standards	IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	UL report applies to both US and Canada
CSA Class No.	NKCR7
NA Certification	UL listed, certified by UL for use in Canada
Degree of Protection	UL Type 4, 4X, 13

	Rated operational voltage U_e V	Colour	Function	Part no. Article no.	Price see price list	Std. pack
Card with high-output LED						
	Continuous light IP66 High-performance LED for maximum signaling effect High Performance LED	24 V AC/DC			SL7-L24-B-HP 171427	1 off  
					SL7-L24-G-HP 171428	
					SL7-L24-R-HP 171429	
					SL7-L24-W-HP 171430	
					SL7-L24-Y-HP 171431	
					SL7-L24-A-HP 171432	
	Strobe light IP66 High-performance LED for maximum signaling effect High Performance LED 1.4 Hz	24 V AC/DC			SL7-FL24-B-HP 171420	
					SL7-FL24-G-HP 171421	
					SL7-FL24-R-HP 171422	
					SL7-FL24-W-HP 171423	
					SL7-FL24-Y-HP 171273	
					SL7-FL24-A-HP 171274	
	Multistrobe light IP66 High-performance LED for maximum signaling effect High Performance LED 1 - 2.6 Hz	24 V AC/DC			SL7-FL24-B-HPM 171275	
					SL7-FL24-G-HPM 171276	
					SL7-FL24-R-HPM 171277	
					SL7-FL24-W-HPM 171278	
					SL7-FL24-Y-HPM 171279	
					SL7-FL24-A-HPM 171280	
Card for filament lamp						
	Continuous light IP66 without light elements Filament lamp max. 7 W Filament bulbs → page 14	< 250 V AC/DC			SL7-L-B 171433	1 off  
					SL7-L-G 171434	
					SL7-L-R 171435	
					SL7-L-W 171436	
					SL7-L-Y 171437	
					SL7-L-A 171438	

Notes





Information relevant for export to North America

 	Product Standards	IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
	UL File No.	E29184
	UL CCN	NKCR
	CSA File No.	UL report applies to both US and Canada
	CSA Class No.	NKCR7
	NA Certification	UL listed, certified by UL for use in Canada
	Degree of Protection	UL Type 4, 4X, 13

	Rated operational voltage U_e V	Rated operational current I_e mA	Colour	Function	Sound type	Part no. Article no.	Price see price list	Std. pack
Acoustic modules								
Continuous tone or pulsed tone, adjustable with internal dip switches. Sound pressure 100 db, adjustable with internal potentiometer. $f = 2800$ Hz Place only at the highest position on a pole IP66								
	24 V AC/DC	max. 92				SL7-AP24 171281		1 off 
	110/120 V AC	max. 41				SL7-AP120 171282		
	230/240 V AC	max. 43				SL7-AP230 171283		
Continuous tone or pulsed tone, external actuation. Assigned two inputs (2 modules). Sound pressure 100 db, adjustable with internal potentiometer. $f = 2800$ Hz Place only at the highest position on a pole IP66								
	24 V AC/DC	max. 92				SL7-AP24-E 171284		1 off 
	110/120 V AC	max. 41				SL7-AP120-E 171285		
	230/240 V AC	max. 43				SL7-AP230-E 171286		
Multi-tone; 8 tones, adjustable with internal dip switch. Sound pressure 100 db, adjustable with internal potentiometer. $f = 500 - 2700$ Hz Place only at the highest position on a pole IP66								
	24 V AC/DC	max. 115				SL7-AP24-M 171287		1 off 
	110/120 V AC	max. 45				SL7-AP120-M 171288		
	230/240 V AC	max. 43				SL7-AP230-M 171289		

Notes**Information relevant for export to North America**

Product Standards	IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	UL report applies to both US and Canada
CSA Class No.	NKCR7
NA Certification	UL listed, certified by UL for use in Canada
Degree of Protection	UL Type 4, 4X, 13

	Tube length	Colour	For use with	Part no. Article no.	Price see price list	Std. pack
Basic modules						
for horizontal mounting including cover max. 5 modules						
	Base with aluminium tube and plastic foot Spring-loaded terminals	100 mm	black Aluminum color tube	SL7-L-... SL7-BL-... SL7-FL-... SL7-AP-...	SL7-CB-100 171443	1 off  
		250 mm			SL7-CB-250 171444	
		400 mm			SL7-CB-400 171445	
	Base with aluminum tube and banjo bolt Spring-loaded terminals	100 mm			SL7-CB-T-100 171452	
		250 mm			SL7-CB-T-250 171453	
		400 mm			SL7-CB-T-400 171454	
	Base with internal (on the inside) fixing holes Spring-loaded terminals	-	black		SL7-CB-IMH¹⁾ 171447	
	Base with built-in (pre-assembled) fixing screws Spring-loaded terminals	-			SL7-CB-IMS 171448	
	Base with external fixing holes Spring-loaded terminals	-			SL7-CB-EMH 171449	
	Base with base adapter for slipping onto place (rapid mounting and wiring system) Screw terminals	100 mm	black Aluminum color tube		SL7-FMS-100 171456	
		250 mm			SL7-FMS-250 171457	
		400 mm			SL7-FMS-400 171458	
	Base with base adapter for slipping onto place (rapid mounting and wiring system) Blade terminal SWD4-8MF2 max. 0.3 A per module External power supply connectable (24 V DC) Configurable with SWD-Assist (planning and ordering help)	100 mm			SL7-SWD²⁾ 171459	

Notes

Information relevant for export to North America



Product Standards IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No. E29184
UL CCN NKCR
CSA File No. UL report applies to both US and Canada
CSA Class No. NKCR7
NA Certification UL listed, certified by UL for use in Canada
Degree of Protection UL Type 4, 4X, 13

¹⁾ Product Standards

IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No. E29184
UL CCN NKCR
CSA File No. UL report applies to both US and Canada
CSA Class No. NKCR7
NA Certification UL listed, certified by UL for use in Canada
Degree of Protection UL Type 1

²⁾ Product Standards

IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
Request filed for UL and CSA
Degree of Protection UL Type 4, 4X, 13

	Colour	For use with	Part no. Article no.	Price see price list	Std. pack	
Basic modules						
for vertical mounting, including cover, max. 5 modules						
	One-sided base with bracket Spring-loaded terminals	black	SL7-L-... SL7-BL-... SL7-FL-... SL7-AP-...	SL7-CB-FW 171450	1 off  	
for vertical mounting on both sides, including cover, max. 2 x 5 modules						
	Base with external fixing holes Spring-loaded terminals	black	SL7-L-... SL7-BL-... SL7-FL-... SL7-AP-...	SL7-CB-D 171451	1 off  	
Mounting brackets						
for vertical mounting, Plastic						
	-	-	SL4-PIB-... SL7-CB-...	SL7/4-FW 171446	1 off  	
Including mounting bracket M20 cable gland						
for vertical mounting, Metal						
	-	-	SL4-PIB-T-... SL7-CB-T-...	SL7/4-FW-T 171455	1 off  	
Tool for replacing filament lamp						
	-	-	-	SL7/4-BET 171294	1 off	
Filament bulbs						
Mounting: Ba15d						
	> 3000	12 V	5 W	SL7-L-...	SL7-L12 171290	1 off
		24 V	6.5 W		SL7-L24 171291	
		120 V	7 W		SL7-L120 171292	
		230 V	6.5 W		SL7-L230 171293	

Notes**Information relevant for export to North America**

Product Standards	IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	UL report applies to both US and Canada
CSA Class No.	NKCR7
NA Certification	UL listed, certified by UL for use in Canada
Degree of Protection	UL Type 4, 4X, 13

Technical data

			SL7-...
General			
Standards			IEC/EN 60947-5-1
Climatic proofing			Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60069-2-30
Mounting position			As required
Mechanical shock resistance		g	> 15 according to IEC 60068-2-27 Shock duration 11 ms Sinusoidal
IEC degree of protection			IP66 IEC/EN 60529
Protection type UL			Type 4, 4X, 13
Material			Enclosure: Polycarbonate (PC), black Cap: Polycarbonate (PC)
Cap colour			blue, green, red, clear, yellow, orange
Ambient temperature		°C	-30 - +60
Number of signal elements			Max. 5 with standard base Max. 10 with base for mounting on both sides
Terminal capacity			
Solid or flexible conductor		mm ²	0.13 - 2.5
Flexible with ferrule with plastic collar		mm ²	0.25 - 1.5
			AWG 24 - AWG 14
Contacts			
Rated impulse withstand voltage		U_{imp} V AC	4000
Rated insulation voltage		U_i V	250
Overvoltage category/pollution degree			III/3

		SL7-L-....	SL7-BL-....	SL7-FL-....	SL7-L24-....-HP	SL7-FL24-....-HP	SL7-FL24-....-HPM	SL7-L-....
Module								
Type of light		Continuous light	Flashing light	Strobe light	Continuous light	Strobe light	Multistrobe light	Continuous light
Light elements		LED			High Performance LED			Filament lamp max. 7 W
Mounting		-	-	-	-	-	-	Ba15d
Flashing/strobe frequency		-	2 Hz	1.4 Hz	-	1.4 Hz	1 - 2.6 Hz	-
Transmission angle		360°						
Leakage current	A	< 0.003						
Current-/power consumption								
24 V AC/DC	A	0.049 - 0.054	0.058	0.130 - 0.135	0.170 - 0.200	0.260 - 0.265	0.260 - 0.265	-
110/120 V AC	A	0.028 - 0.031	0.028 - 0.030	0.010	-	-	-	-
230/240V AC	A	0.027 - 0.028	0.030 - 0.031	0.010	-	-	-	-
Power consumption		-	-	-	-	-	-	Max. 7 W with the specified voltages
Voltage levels		24 V AC/DC ± 10 % 110/120 V AC ± 10 % 230/240 V AC ± 10 %			18-30 V DC/18-26 V AC			up to 250 V AC/DC
lifespan	h	> 100000			> 50000			> 3000
Weight	g	80						

			SL7-AP...	SL7-AP...-E	SL7-AP...-M
Acoustic modules					
Type of tone			Continuous or pulsed tone	Continuous or pulsed tone	Continuous or pulsed tone 8 types of sound
Types of sound			2 versions, table of sound types	2 versions, table of sound types	8 versions, table of sound types
Sound setting			Internal; 1 pole DIP	can be externally actuated	Internal; 3 pole DIP
Sound pressure		dB	100	100	100
Sound pressure level adjustment			Built-in, potentiometer	Built-in, potentiometer	Built-in, potentiometer
Sound_pressure_can_be_lowered_to_a_minimum_of			88 dB	88 dB	88 dB
Transmission angle			360°	360°	360°
Current-/power consumption					
24 V AC/DC		A	0.092	0.092	0.115
110 /120 V AC		A	0.041	0.041	0.045
230 /240V AC		A	0.043	0.043	0.043
Voltage levels			24 V AC/DC ± 10 % 110/120 V AC ± 10 % 230/240 V AC ± 10 %	24 V AC/DC ± 10 % 110/120 V AC ± 10 % 230/240 V AC ± 10 %	24 V AC/DC ± 10 % 110/120 V AC ± 10 % 230/240 V AC ± 10 %
Weight		g	102	102	102


Table of sound types

	Sound type	Frequency Hz	Diagram	Repeat rate	Special application	Max. volume dB
SL7-AP...	Continuous tone	approx. 2800		-	-	100
	Pulsed tone	approx. 2800		approx. 2 Hz	-	100
SL7-AP...-E	Continuous tone	approx. 2800		-	-	100
	Pulsed tone	approx. 2800		approx. 2 Hz	-	100
SL7-AP...-M	Continuous tone	2700		-	-	100
	Continuous tone	1350		-	-	100
	Pulsed tone	2700		250 ms on, 250 ms off	-	100
	Pulsed tone	1350		250 ms on, 250 ms off	-	100
	falling	1200 - 500		1 Hz	Evacuation, Germany, DIN 3304-3	98
	Rising	500 - 1200		Rising 3 s, 0.5 s off	Netherlands NEN 2575:2000	98
	Alternating	800 - 1000		2 Hz		94
	rising/falling	500 - 1500		10 Hz		94


Dimensions

Complete devices

SL7-100-L-RG-24LED




SL7-100-L-RYG-24LED




Light modules

SL7-(B)(F)L ...




Acoustic modules

SL7-AP...




Basic modules


SL7-CB-...



Part no.	a mm (inch)
SL7-CB-100	171 (6.73)
SL7-CB-250	321 (12.64)
SL7-CB-400	471 (18.54)





SL7-CB-T-...





Part no.	a mm (inch)
SL7-CB-T-100	190 (7.48)
SL7-CB-T-250	340 (13.38)
SL7-CB-T-400	490 (19.29)

SL7-CB-D




SL7-CB-EMH




Basic modules


SL7-CB-FW




SL7-CB-IMH




SL7-CB-IMS



SL7-FMS-...




Part no.	a mm (inch)
SL7-FMS-100	192 (7.55)
SL7-FMS-250	342 (13.46)
SL7-FMS-400	492 (19.37)




Base module for connecting to SmartWire-DT®

SL7-SWD




Mounting brackets

SL7/4-FW




SL7/4-FW-T




Filament bulbs

SL7-L12



Tool for replacing filament lamp

SL7/4-BET



Card for filament lamp, continuous light	1	Acoustic module	5	Base with base adapter for slipping onto place (rapid mounting and wiring system) and SmartWire-DT connection	6i
Without light element (filament lamp with BA15d socket)		Continuous tone or pulsed tone, adjustable with internal dip switches		Aluminium tube 100 mm	
Easy mounting with bayonet mount		Sound pressure 80 dB, adjustable with internal potentiometer, frequency 4000 Hz		→ page 28	
Modules can be arranged in any order		Easy mounting with bayonet mount			
Degree of protection IP66		Set up as topmost module			
Max. 2 x 5 modules that can be actuated individually (two with base module SL7-CB-D only)		Max. 2 x 1 modules that can be individually actuated (two with base module SL7-CB-D only)		Accessory Considerations	7
Operating mode: 100 % DF (duty factor)		Permanently integrated cover plate		Mounting brackets	
→ page 27		Degree of protection IP66		Including mounting bracket M20 cable gland	
		Operating mode: 100 % DF (duty factor)		Tool for replacing filament lamp	
		→ page 27		Filament lamp	
				→ page 29	
Card with LED, continuous light	2	Base module	6		
with LED		Easy mounting with bayonet mount			
Easy mounting with bayonet mount		Degree of protection IP66			
Modules can be arranged in any order		Including cover plate			
Degree of protection IP66		with Push in terminals			
Max. 2 x 5 modules that can be actuated individually (two with base module SL7-CB-D only)				Base for mounting on both sides	6a
Operating mode: 100 % DF (duty factor)				→ page 29	
→ page 24					
				Base with aluminium tube and plastic foot	6b
				Aluminium tube 100 mm, 250 mm or 400 mm	
				→ page 28	
				Base with aluminum tube and banjo bolt	6c
				Aluminium tube 100 mm, 250 mm or 400 mm	
				→ page 28	
				Base with external fixing holes	6 d
				→ page 28	
				One-sided base with bracket	6e
				→ page 29	
				Base with internal (on the inside) fixing holes	6f
				→ page 28	
				Base with built-in (pre-assembled) fixing screws	6g
				→ page 28	
				Base with base adapter for slipping onto place (rapid mounting and wiring system)	6h
				Aluminium tube 100 mm, 250 mm or 400 mm	
				→ page 28	
Card with LED, flashing light	3				
with LED					
Easy mounting with bayonet mount					
Modules can be arranged in any order					
Degree of protection IP66					
Max. 2 x 5 modules that can be actuated individually (two with base module SL7-CB-D only)					
Operating mode: 100 % DF (duty factor)					
Flashing frequency 2 Hz					
→ page 25					
Card with LED, strobe light	4				
Easy mounting with bayonet mount					
Modules can be arranged in any order					
Degree of protection IP66					
Max. 2 x 5 modules that can be actuated individually (two with base module SL7-CB-D only)					
Operating mode: 100 % DF (duty factor)					
Card with LED	4a				
with LED					
Flashing frequency 1.4 Hz					
→ page 26					
Card with LED	4b				
With LED for effective signaling effect with various flashing sequences					
Flashing frequency approx. 1 -2.6 Hz					
→ page 26					

Ordering

	Rated operational voltage U _e V	Number of modules	Colour	Function	Part no. Article no.	Price see price list	Std. pack
Complete devices							
	24 V AC/DC	2			SL4-100-L-RG-24LED 171295		1 off 
		3			SL4-100-L-RYG-24LED 171296		
Customised complete unit							
Order on request, * = Freely selectable customer identification or stock no., Maximum 10 characters					SL4-COMBINATION-* 171387		1 off

	Rated operational voltage U _e V	Colour	Function	Part no. Article no.	Price see price list	Std. pack	
Card with LED							
	24 V AC/DC			SL4-L24-B 171313		1 off 	
				SL4-L24-G 171314			
				SL4-L24-R 171315			
				SL4-L24-W 171316			
				SL4-L24-Y 171317			
				SL4-L24-A 171318			
		110/120 V AC					SL4-L120-B 171319
							SL4-L120-G 171320
							SL4-L120-R 171321
				SL4-L120-W 171322			
				SL4-L120-Y 171323			
				SL4-L120-A 171324			
	230/240 V AC			SL4-L230-B 171325			
				SL4-L230-G 171326			
				SL4-L230-R 171327			
				SL4-L230-W 171328			
				SL4-L230-Y 171329			
				SL4-L230-A 171330			

Notes


Information relevant for export to North America



Product Standards IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
 UL File No. E29184
 UL CCN NKCR

CSA File No.
 CSA Class No.
 NA Certification
 Degree of Protection

UL report applies to both US and Canada
 NKCR7
 UL listed, certified by UL for use in Canada
 UL Type 4, 4X, 13

		Rated operational voltage U_e V	Colour	Function	Part no. Article no.	Price see price list	Std. pack
	Flashing light IP66 2 Hz	24 V AC/DC			SL4-BL24-B 171337		1 off  
					SL4-BL24-G 171338		
					SL4-BL24-R 171339		
					SL4-BL24-W 171340		
					SL4-BL24-Y 171341		
					SL4-BL24-A 171342		
			110/120 V AC			SL4-BL120-B 171343	
				SL4-BL120-G 171344			
				SL4-BL120-R 171345			
				SL4-BL120-W 171346			
				SL4-BL120-Y 171347			
				SL4-BL120-A 171348			
		230/240 V AC			SL4-BL230-B 171349		
				SL4-BL230-G 171350			
				SL4-BL230-R 171351			
				SL4-BL230-W 171352			
				SL4-BL230-Y 171353			
				SL4-BL230-A 171354			

Notes

Information relevant for export to North America



Product Standards	IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	UL report applies to both US and Canada
CSA Class No.	NKCR7
NA Certification	UL listed, certified by UL for use in Canada
Degree of Protection	UL Type 4, 4X, 13

		Rated operational voltage U _e V	Colour	Function	Part no. Article no.	Price see price list	Std. pack			
Card with LED										
	Strobe light IP66 1.4 Hz	24 V AC/DC			SL4-FL24-B 171355		1 off 			
					SL4-FL24-G 171356					
					SL4-FL24-R 171357					
					SL4-FL24-W 171358					
					SL4-FL24-Y 171359					
					SL4-FL24-A 171360					
			110/120 V AC			SL4-FL120-B 171361				
				SL4-FL120-G 171362						
				SL4-FL120-R 171363						
				SL4-FL120-W 171364						
				SL4-FL120-Y 171365						
				SL4-FL120-A 171366						
		230/240 V AC			SL4-FL230-B 171367					
				SL4-FL230-G 171368						
				SL4-FL230-R 171369						
				SL4-FL230-W 171370						
				SL4-FL230-Y 171371						
				SL4-FL230-A 171372						
				Multistrobe light IP66 LED for effective signaling effect With various strobe sequences 1 - 2.6 Hz	24 V AC/DC				SL4-FL24-B-M 171373	
						SL4-FL24-G-M 171374				
						SL4-FL24-R-M 171375				
	SL4-FL24-W-M 171376									
	SL4-FL24-Y-M 171377									
	SL4-FL24-A-M 171378									

Notes

Information relevant for export to North America






Product Standards	IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	UL report applies to both US and Canada
CSA Class No.	NKCR7
NA Certification	UL listed, certified by UL for use in Canada
Degree of Protection	UL Type 4, 4X, 13

		Rated operational voltage U_e V	Colour	Function	Part no. Article no.	Price see price list	Std. pack
Card for filament lamp							
	Continuous light IP66 without light elements Filament lamp max. 4 W Filament bulbs → page 29	< 250 V AC/DC			SL4-L-B 171331		1 off 
					SL4-L-G 171332		
					SL4-L-R 171333		
					SL4-L-W 171334		
					SL4-L-Y 171335		
					SL4-L-A 171336		

	Rated operational voltage U_e V	Rated operational current I_e mA	Colour	Function	Sound type	Part no. Article no.	Price see price list	Std. pack
Acoustic modules								
Continuous tone or pulsed tone, adjustable with internal dip switches. Sound pressure 80 db, adjustable with internal potentiometer. $f = 4000$ Hz Place only at the highest position on a pole IP66								
	24 V AC/DC	max. 39				SL4-AP24 171379		1 off 
	110/120 V AC	max. 21				SL4-AP120 171380		
	230/240 V AC	max. 21				SL4-AP230 171381		

Notes**Information relevant for export to North America**

	Product Standards	IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
	UL File No.	E29184
	UL CCN	NKCR
	CSA File No.	UL report applies to both US and Canada
	CSA Class No.	NKCR7
	NA Certification	UL listed, certified by UL for use in Canada
	Degree of Protection	UL Type 4, 4X, 13

		Tube length	Colour	For use with	Part no. Article no.	Price see price list	Std. pack
Basic modules							
for horizontal mounting including cover max. 5 modules							
	Base with aluminium tube and plastic foot Push in terminals	100 mm	black Aluminum color tube	SL4-L-... SL4-BL-... SL4-FL-... SL4-AP-...	SL4-PIB-100 171297		1 off  
		250 mm			SL4-PIB-250 171298		
		400 mm			SL4-PIB-400 171299		
	Base with aluminum tube and banjo bolt Push in terminals	100 mm			SL4-PIB-T-100 171305		
		250 mm			SL4-PIB-T-250 171306		
		400 mm			SL4-PIB-T-400 171307		
	Base with external fixing holes Push in terminals	-	black		SL4-PIB-EMH 171302		
	Base with internal (on the inside) fixing holes - Push in terminals	-			SL4-PIB-IMH¹⁾ 171300		
	Base with built-in (pre-assembled) fixing screws Push in terminals	-			SL4-PIB-IMS 171301		
	Base with base adapter for slipping onto place (rapid mounting and wiring system) Screw terminals	100 mm	black Aluminum color tube		SL4-FMS-100 171308		
		250 mm			SL4-FMS-250 171309		
		400 mm			SL4-FMS-400 171310		
	Base with base adapter for slipping onto place (rapid mounting and wiring system) Blade terminal SWD4-8MF2 max. 0.3 A per module External power supply connectable (24 V DC) Configurable with SWD-Assist (planning and ordering help)	100 mm			SL4-SWD²⁾ 171311		

Notes

Information relevant for export to North America



Product Standards IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
 UL File No. E29184
 UL CCN NKCR
 CSA File No. UL report applies to both US and Canada
 CSA Class No. NKCR7
 NA Certification UL listed, certified by UL for use in Canada
 Degree of Protection UL Type 4, 4X, 13

¹⁾ Product Standards IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
 UL File No. E29184
 UL CCN NKCR
 CSA File No. UL report applies to both US and Canada
 CSA Class No. NKCR7
 NA Certification UL listed, certified by UL for use in Canada
 Degree of Protection UL Type 1

²⁾ Product Standards IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
 NA Certification Request filed for UL and CSA
 Degree of Protection UL Type 4, 4X, 13

	Colour	For use with	Part no. Article no.	Price see price list	Std. pack
Basic modules					
for vertical mounting including cover					
	One-sided base with bracket Push in terminals max. 5 modules	black	SL4-L-... SL4-BL-... SL4-FL-... SL4-AP-...	SL4-PIB-FW 171303	1 off  
for vertical mounting on both sides including cover					
	Base with external fixing holes Push in terminals max. 2 x 5 modules	black	SL4-L-... SL4-BL-... SL4-FL-... SL4-AP-...	SL4-PIB-D 171304	1 off  
Mounting brackets					
for vertical mounting, Plastic					
	-	-	SL4-PIB-... SL7-CB-...	SL7/4-FW 171446	1 off  
Including mounting bracket M20 cable gland					
for vertical mounting, Metal					
	-	-	SL4-PIB-T... SL7-CB-T...	SL7/4-FW-T 171455	1 off  
Tool for replacing filament lamp					
	-	-	-	SL7/4-BET 171294	1 off
Filament bulbs					
Mounting: Ba15d					
	> 3000	12 V 24 V 120 V 230 V	4 W SL4-L-...	SL4-L12 171382 SL4-L24 171383 SL4-L120 171384 SL4-L230 171385	1 off

Notes**Information relevant for export to North America**

Product Standards	IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	UL report applies to both US and Canada
CSA Class No.	NKCR7
NA Certification	UL listed, certified by UL for use in Canada
Degree of Protection	UL Type 4, 4X, 13

Technical data

			SL4-...
General			
Standards			IEC/EN 60947-5-1
Climatic proofing			Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60069-2-30
Mounting position			As required
Mechanical shock resistance		g	> 15 according to IEC 60068-2-27 Shock duration 11 ms Sinusoidal
IEC degree of protection			IP66 IEC/EN 60529
Protection type UL			Type 4, 4X, 13
Material			Enclosure: Polycarbonate (PC), black Cap: Polycarbonate (PC)
Cap colour			blue, green, red, clear, yellow, orange
Ambient temperature		°C	-30 - +60
Number of signal elements			Max. 5 with standard base Max. 10 with base for mounting on both sides
Terminal capacity			
Solid or flexible conductor		mm ²	0.2 - 1.5
Solid or flexible conductor, with ferrule		mm ²	0.25 - 1.5
Flexible with ferrule with plastic collar		mm ²	0.25 - 0.75
			AWG 24 - AWG 16
Contacts			
Rated impulse withstand voltage		U _{imp}	V AC
			4000
Rated insulation voltage		U _i	V
			250
Overvoltage category/pollution degree			III/3

			SL4-L...-...	SL4-BL...-...	SL4-FL...-...	SL4-FL24...-M	SL4-L...
Light modules							
Type of light			Continuous light	Flashing light	Strobe light	Multistrobe light	Continuous light
Light elements			LED				Filament lamp max. 4 W
Mounting			-	-	-	-	Ba15d
Flashing/strobe frequency			-	2 Hz	1.4 Hz	1 - 2.6 Hz	-
Transmission angle			360°				
Leakage current		A	< 0.003				
Current-/power consumption							
24 V AC/DC		A	0.022 - 0.033	0.028 - 0.036	0.035 - 0.065	0.048 - 0.068	-
110 /120 V AC		A	0.030	0.030	0.10	-	-
230 /240V AC		A	0.030	0.030	0.10	-	-
Power consumption			-	-	-	-	Max. 4 W with the specified voltages
Voltage levels			24 V AC/DC ± 10 % 110/120 V AC ± 10 % 230/240 V AC ± 10 %			24 V AC/DC ± 10 %	up to 250 V AC/DC
lifespan		h	> 100000				
Weight		g	45				

			SL4-AP...
Acoustic modules			
Type of tone			Continuous or pulsed tone
Types of sound			2 versions, table of sound types
Sound setting			Internal; 1 pole DIP
Sound pressure		dB	80
Sound pressure level adjustment			-
Sound_pressure_can_be_lowered_t o_a_minimum_of			-
Transmission angle			360°
Current-/power consumption			
24 V AC/DC		A	0.039
110 /120 V AC		A	0.021
230 /240V AC		A	0.021
Voltage levels			
			24 V AC/DC \pm 10 % 110/120 V AC \pm 10 % 230/240 V AC \pm 10 %
Weight		g	43


Table of sound types

	Sound type	Frequency Hz	Diagram	Repeat rate	Special application	Max. volume dB
SL4-AP...	Continuous tone	approx. 4000	_____	-	-	80
	Pulsed tone	approx. 4000	— — —	approx. 2 Hz	-	80


Dimensions

Complete devices

SL4-100-L-RG-24LED




SL4-100-L-RYG-24LED




Light modules

SL4-(B)(F)L ...




Acoustic modules

SL4-AP...




Basic modules


SL4-PIB-...



Part no.	a mm (inch)
SL4-PIB-100	136 (3.53)
SL4-PIB-250	286 (11.26)
SL4-PIB-400	436 (17.16)





SL4-PIB-T-...





Part no.	a mm (inch)
SL4-PIB-T-100	150 (5.90)
SL4-PIB-T-250	300 (11.81)
SL4-PIB-T-400	450 (17.72)

SL4-PIB-D




SL4-PIB-EMH




Basic modules


SL4-PIB-FW




SL4-PIB-IMH




SL4-PIB-IMS



SL4-FMS-...




Part no.	a mm (inch)
SL4-FMS-100	157 (6.18)
SL4-FMS-250	307 (12.09)
SL4-FMS-400	457 (17.99)




Base module for connecting to SmartWire-DT®

SL4-SWD




Mounting brackets

SL7/4-FW




SL7/4-FW-T




Filament bulbs

SL7-L12



Tool for replacing filament lamp

SL7/4-BET



CUTLER-HAMMER COOPER
 BUSSMANN POWERWARE
 MEM BILL
 CROUSE-HINDS MOELLER
 SANTAK HOLEC
 WESTINGHOUSE MGE OFFICE PROTECTION SYSTEMS B-LINE

EAT•N

Powering Business Worldwide

The power of fusion.



EAT•N

Powering Business Worldwide

There's a certain energy at Eaton. It's the power of uniting some of the world's most respected names to build a brand you can trust to meet your every power management need.

Eaton is dedicated to ensuring that reliable, efficient and safe power is available when it's needed most. Building on over 100 years of experience in electrical power management, the experts at Eaton deliver customized, integrated solutions to solve your most critical challenges. To learn more visit www.eaton.eu/electrical.

All of the above are trademarks of Eaton or its affiliates. • Eaton has a license to use the Westinghouse brand name in Asia Pacific. ©2013 Eaton.

Eaton is dedicated to ensuring that reliable, efficient and safe power is available when it's needed most. With unparalleled knowledge of electrical power management across industries, experts at Eaton deliver customized, integrated solutions to solve our customers' most critical challenges.

Our focus is on delivering the right solution for the application. But, decision makers demand more than just innovative products. They turn to Eaton for an unwavering commitment to personal support that makes customer success a top priority. For more information, **visit www.eaton.eu/electrical**.

To contact an Eaton salesperson or local distributor/agent, please visit www.eaton.eu/electrical/customersupport

Changes to the products, to the information contained in this document, and to prices are reserved; so are errors and omissions. Only order confirmations and technical documentation by Eaton is binding. Photos and pictures also do not warrant a specific layout or functionality. Their use in whatever form is subject to prior approval by Eaton. The same applies to Trademarks (especially Eaton, Moeller, Cutler-Hammer). The Terms and Conditions of Eaton apply, as referenced on Eaton internet pages and Eaton order confirmations.

Eaton Industries GmbH
Hein-Moeller-Str. 7-11
D-53115 Bonn/Germany

© 2013 by Eaton Corporation
All rights reserved
Printed in Germany 05/13
Publication No.: CA047002EN-INT
Doku/DHW/bb/dfs 04/13
Article No.: 171892



Eaton is a registered trademark of Eaton Corporation.

All other trademarks are property of their respective owners.

SmartWire-DT® is a registered trademark of Eaton Corporation.