



# Low resistance chip resistors (long-side terminal)

## ■ PRL / RL series

### Features

- Innovative structure that takes consideration of heat dissipation suppresses the surface temperature enabling the small sizes, reduction of the influence on surrounding components, excellent temperature cycle resistance, low ESL and low noise.

### Applications

- PC power sources, inverters, automotive electronics, adopters, industrial machines


### ◆ Part numbering system

<b>PRL</b>	<b>1220</b>	<b>- R010 - D - T5</b>	Packaging quantity: T5(5,000pcs)	<b>RL</b>	<b>3720W</b>	<b>T - R10 - F</b>	Temperature coefficient of resistance
Series code			Resistance tolerance	Series code		Resistance tolerance	Nominal resistance value
Size: PRL0816, PRL1220, PRL1632, PRL3264						Size: RL3720W, RL7520W	

### ◆ Electrical Specification

Type	Power ratings	Temperature coefficient of resistance (ppm/°C)	Resistance range(Ω) Resistance tolerance				Maximum voltage	Resistance value series	Operating temperature	Packaging quantity
<b>PRL0816</b>	1/3W	±50	75m≤R≤100m		-			E-24	-55°C ~ 125°C	T5
		±100	43m≤R≤68m							
		0 ~ +200	—	33m≤R≤39m						
		0 ~ +350	—	18m≤R≤27m						
<b>PRL1220</b>	2/3W	—	10m≤R≤15m		-			E-24 1m step (7m ~ 10m)	-55°C ~ 125°C	T5
		±50	56m≤R≤100m							
		±100	47m≤R≤51m							
		0 ~ +200	—	20m≤R≤43m						
<b>PRL1632</b>	1W	0 ~ +350	—	10m≤R≤18m		-		E-24 1m step (5m ~ 10m)	-55°C ~ 125°C	T5
		±50	56m≤R≤100m							
		±100	20m≤R≤51m							
		0 ~ +200	—	10m≤R≤18m						
<b>PRL3264</b>	2W	0 ~ +350	—	5m≤R≤9m		-	√(P · R)	E-24 1m step (3m ~ 10m)	-55°C ~ 125°C	T5
		±50	56m≤R≤100m							
		±100	47m≤R≤51m							
		0 ~ +200	—	20m≤R≤43m						
<b>RL3720W</b>	1W	0 ~ +350	—	10m≤R≤18m		-		E-24 1m step (1m ~ 10m)	-55°C ~ 125°C	T5
		±50(Q)	—	5m≤R≤91m						
		±100(R)	—	1m≤R≤4m						
		0 ~ +200(S)	—	100m≤R≤1						
<b>RL7520W</b>	2W	0 ~ +350(T)	—	5m≤R≤9m		-		E-24 1m step (1m ~ 10m)	-55°C ~ 125°C	T5
		±50(Q)	—	100m≤R≤470m						
		±100(R)	—	10m≤R≤91m						
		0 ~ +200(S)	—	100m≤R≤470m						
4,000pcs										


### ◆ Dimensions



Type	Size (inch)	L	W	a	b	t
<b>PRL0816</b>	0603	0.80±0.20	1.60±0.20	—	0.20±0.10	0.40±0.10
<b>PRL1220</b>	0805	1.25±0.20	2.00±0.20	—	0.35±0.15	0.50±0.10
<b>PRL1632</b>	1206	1.60±0.20	3.20±0.20	—	0.45±0.15	0.50±0.10
<b>PRL3264</b>	2512	3.20±0.20	6.40±0.20	—	0.90±0.15	0.50±0.10
<b>RL3720W</b>	1508	2.00±0.20	3.75±0.30	0.40±0.20	0.40±0.20	0.50±0.20
<b>RL7520W</b>	3008	2.00±0.20	7.50±0.30	0.40±0.20	0.40±0.20	0.50±0.20


(unit : mm)

## ◆ESL (Equivalent series inductance)






## ◆Surface temperature data


### ○ The high power type land pattern and surface temperature




These high-power low resistance chip resistors are designed to dissipate heat efficiently through the land patterns on circuit boards. The actual temperature of the surface of the resistor is dependent upon the dimensions and the shape of the land patterns.



## ◆Derating Curve




RL3720W



RL7520W

## ◆Resistance to power pulse



### Test procedure

Voltage pulse is applied to the test samples mounted on the test board. After each pulse, resistance drift is measured. Pulse voltage is increased until the drift exceeds +/- 0.5%. The power at that voltage is defined as the maximum pulse power.