## S1A, S1B, S1D, S1G, S1J, S1K, S1M

Vishay General Semiconductor

RoHS

### **Surface Mount Glass Passivated Rectifier**



**DO-214AC (SMA)** 

PRIMARY CHARACTERISTICS								
I <sub>F(AV)</sub>	1.0 A							
$V_{RRM}$	50 V, 100 V, 200 V, 400 V, 600 V, 800 V, 1000 V							
I <sub>FSM</sub>	40 A, 30 A							
E <sub>AS</sub>	5 mJ							
I <sub>R</sub>	1.0 μΑ, 5.0 μΑ							
$V_{F}$	1.1 V							
T <sub>J</sub> max.	150 °C							
Package	DO-214AC (SMA)							
Diode variations	Single die							

#### **FEATURES**

- Low profile package
- · Ideal for automated placement
- · Glass passivated pellet chip junction
- Low forward voltage drop
- · Low leakage current
- · High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see <a href="https://www.vishav.com/doc?99912"><u>www.vishav.com/doc?99912</u></a>

#### **TYPICAL APPLICATIONS**

For use in general purpose rectification of power supplies, inverters, converters and freewheeling diodes for consumer, automotive, and telecommunication.

#### **MECHANICAL DATA**

Case: DO-214AC (SMA)

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHSp-compliant, commercial grade Base P/NHE3\_X - RoHS-compliant and AEC-Q101 qualified ("\_X" denotes revision code e.g. A, B,.....)

**Terminals:** Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 2 whisker test, HE3 suffix meets JESD 201 class 2 whisker test

Polarity: Color band denotes cathode end

MAXIMUM RATINGS (T <sub>A</sub> = 25 °C unless otherwise noted)									
PARAMETER	SYMBOL	S1A	S1B	S1D	S1G	S1J	S1K	S1M	UNIT
Device marking code		SA	SB	SD	SG	SJ	SK	SM	
Maximum recurrent peak reverse voltage	V <sub>RRM</sub>	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V <sub>RMS</sub>	35 70 140 280 420		420	560	700	V		
Maximum DC blocking voltage	$V_{DC}$	50	100	200	400	600	800	1000	V
Maximum average forward rectified current (fig. 1)	I <sub>F(AV)</sub>	1.0					Α		
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	40 30					80	Α	
Non-repetitive peak reverse avalanche energy at 25 °C, I <sub>AS</sub> = 1 A, L = 10 mH	E <sub>AS</sub>	5					mJ		
Operating junction and storage temperature range	T <sub>J</sub> , T <sub>STG</sub>	-55 to +150						°C	

# S1A, S1B, S1D, S1G, S1J, S1K, S1M

### Vishay General Semiconductor

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>A</sub> = 25 °C unless otherwise noted)										
PARAMETER	TEST CONDITIONS	SYMBOL	S1A	S1B	S1D	S1G	S1J	S1K	S1M	UNIT
Maximum instantaneous forward voltage	1.0 A	V <sub>F</sub>	1.1					V		
Maximum DC reverse current at rated DC blocking voltage	$T_A = 25 ^{\circ}\text{C}$ $T_A = 125 ^{\circ}\text{C}$	I <sub>R</sub>	1.0 5.0 50				.0	μΑ		
Typical reverse recovery time	I <sub>F</sub> = 0.5 A, I <sub>R</sub> = 1.0 A, I <sub>rr</sub> = 0.25 A	t <sub>rr</sub>	1.8			1.8			μs	
Typical junction capacitance	4.0 V, 1 MHz	CJ	12					pF		

THERMAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)									
PARAMETER	SYMBOL S1A S1B S1D S1G S1J S1K S1M UN					UNIT			
Typical thermal resistance (1)	$R_{\theta JA}$	75					85		°C/W
Typical thermal resistance (*)	$R_{\theta JL}$	27				30		C/VV	

#### Note

<sup>(1)</sup> Thermal resistance from junction to ambient and from junction to lead mounted on PCB with 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pad areas

ORDERING INFORMATION (Example)									
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE					
S1J-E3/61T	0.064	61T	1800	7" diameter plastic tape and reel					
S1J-E3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel					
S1JHE3_A/H (1)	0.064	Н	1800	7" diameter plastic tape and reel					
S1JHE3_A/I (1)	0.064	I	7500	13" diameter plastic tape and reel					

#### Note

### RATINGS AND CHARACTERISTICS CURVES (T<sub>A</sub> = 25 °C unless otherwise noted)




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current

<sup>(1)</sup> AEC-Q101 qualified

### Vishay General Semiconductor





Fig. 3 - Typical Instantaneous Forward Characteristics






Fig. 4 - Typical Reverse Leakage Characteristics






Fig. 6 - Typical Transient Thermal Impedance

### PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

#### **DO-214AC (SMA)**



#### **Mounting Pad Layout**





### **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Revision: 13-Jun-16 1 Document Number: 91000