

## WSU-24M - Wrap-Strip-Unwrap Tool, 24 AWG - Data Sheet

Each WSU wire wrapping tool wraps, unwraps and even strips the appropriate wire diameter with a unique built-in stripper blade. Ideal for bench use or tool kit in all service and repair applications. In addition to versatility, convenience, and reliability, the WSU Series offers exceptional value. Modified Wrap, Gauge 24 AWG, Terminal Hole Diameter 0.075 inches, Terminal Hole Depth 1.5 inches, Outside Diameter 0.213 inches, Square Post 0.045 inches. Unwrap side: Terminal Hole Depth, 1.5 inches, Outside Diameter 0.119 inches.



Specifications	
Wrap Type	Modified
Wire Gauge	24 AWG (0.5 mm)
Maximum Insulation Diameter	0.036" (0.91 mm)
Terminal Hole Dia.	0.075" (1.9 mm)
Terminal Hole Depth	1.50" (38.1 mm)
Outside Diameter	.213" (5.4mm)
Wrap Post Size	0.045" (1.14 mm)
Functions	Wrap, Unwrap, and Strip
Features	Provides 1.5 to 2 turns of insulation
Color	Red Handle
Weight	0.106 lbs
UPC No	811490013667