



DA7217

DA7217 is a high-performance, low-power audio codec optimized for use in headsets or wearable devices. It has differential headphone outputs for use inside headset devices, offering excellent left to right channel separation and common mode noise rejection. DA7217 also has a stereo DAC to headphone output path and ultra-low power operating modes to support always-on audio detect applications.

DA7217 contains two analog microphone input paths, or up to four digital microphone input paths, or a combination of both. The other chip in this family, the DA7218, has single-ended headphone outputs, and has been designed with headphone detect for use in accessories.



32 ball WLCSP package, 0.5 mm pitch

Features

- ► High performance stereo DAC to headphone playback path with 110 dB dynamic range
- ► 4 mW stereo playback power consumption
- ► DAC digital filters with audio and voice mode options, five-band equalizer and five programmable biquad stages
- Dedicated low-latency digital sideband filter with three programmable biquad stages
- ► High performance microphone to ADC record path with 105 dB dynamic range
- ► 2.5 mW stereo record power consumption
- ► ADC digital filters with audio and voice mode options
- 500 μW always-on record mode with automatic level detection
- Hybrid analog / digital automatic level control to dynamically control the record level
- Shutdown mode offering current consumption during standby of 2.5 μA
- Two low-noise microphone bias regulators with programmable output voltage and ultralow power mode
- ► A high efficiency two-level, true-ground charge pump for generating class-G headphone supplies
- ► Voice mode filtering up to 32 kHz


- Flexible digital mixing from all seven inputs to all six outputs with independent gain on each mixer path
- ► Ability to run the ADCs at a different sample rate to the DACs on a single I²S interface
- Digital tone generator with built-in support for DTMF
- System controller for simplified, pop-free startup and shutdown
- Phase-locked loop with sample rate tracking supporting MCLK frequencies from 2 MHz to 54 MHz
- ► Automatic tuning of on-chip reference oscillator for clock-free operation in low-power modes
- 4-wire digital audio interface with support for l²S, four-channel l²S, TDM and other audio formats
- ► 2-wire I²C compatible control interface with support for High Speed mode up to 3.4 MHz
- ► 24-bit data at up to 96 kHz sample rate
- The headphone amplifier can be run directly from the supply, thus eliminating the need for charge pump capacitors



Applications

- ► Hearables
- ► Wireless and wired headphones
- ► Wireless and wired headsets

Block Diagram



Feature highlights


- Superior hi-fidelity audio performance for immersive record and playback
- ► Sub 500 µW always-on power extends battery life for audio activity detection
- ► Flexible programming filtering (sideband, voice) enhances voice and audio playback
- Mixed sample rate support for wideband applications
- Supports the latest generation of low power analog and digital microphones
- Small package footprint with an optimized ballout conducive to low cost PCB manufacturing







Audio System diagram



Dialog Semiconductor Worldwide Sales Offices - www.dialog-semiconductor.com email: info@diasemi.com

United Kingdom Phone: +44 1793 757700

The Netherlands Phone: +31 73 640 88 22

Phone: +81 3 5425 4567

Singapore Phone: +65 648 499 29

Phone: +82 2 3469 8200 China (Shenzhen)

Germany Phone: +49 7021 805-0

North America Phone: +1 408 845 8500

Taiwan Phone: +886 281 786 222 Hong Kong Phone: +852 3769 5200 Phone: +86 755 2981 3669

China (Shanghai) Phone: +86 21 5424 9058

This publication is issued to provide outline information only, which unless agreed by Dialog Semiconductor may not be used, applied, or reproduced for any purpose or be regarded as a representation relating to products. All use of Dialog Semiconductor products, software and applications referred to in this document are subject to Dialog Semiconductor's <u>Standard Terms and Conditions of Sale</u>, available on the company website (<u>www.dialog-semiconductor.com</u>) unless otherwise stated.

Dialog and the Dialog logo are trademarks of Dialog Semiconductor plc or its subsidiaries. All other product or service names are the property of their

© Copyright 2016 Dialog Semiconductor. All rights reserved.