


HEALTH & SAFETY PRODUCT DATA SHEET

SECTION 1: Identification of the substance / Preparation and Company

1.1. Identification of the product

Name of the product:
Packaging :

 SNOW FLUID (code 160578 & 160579)
Can of 1L, 5L

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1 Relevant identified uses

Spec. Industrial / professional use: For professional use

Application of the substance / preparation: Liquid formulation used to produce an artificial snow effect for show & party's

1.2.2. unsuitable uses

No additional information available

1.3. Details of the Company:

AVSL GROUP LTD

Containerbase, Barton Dock Road
Manchester , M41 7BQ - United Kingdom
Website : www.avslgroup.com

1.4. Emergency call number

Country	Company	Emergency Number
France	ORFILA	+33 (0) 1 45 42 59 59

SECTION 2: Hazard Identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP] Show CLP + DPD classification information in section 2.1

Skin Irrit. 2 H315
Eye Dam. 1 H318
Full text of H-phrases: see section 16

Classification according to Directive 67/548 / EEC [DSD] or 1999/45 / EC [DPD]

Xi; R41
Full text of R-phrases: see section 16

Adverse physicochemical, human health and the environment

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP): GHS05

Signal word (CLP): Danger

Hazardous ingredients:

SODIUM SULFATE LAURETH

Hazard statements (CLP):

H315 - Causes skin irritation

H318 - Causes serious eye damage

Precautionary statements (CLP): P264 - Wash hands thoroughly after handling

P280 - Wear protective gloves

P302 + P352 - IF ON SKIN:

Wash with plenty of soap and water

P305 + P351 + P338 - IF IN EYES

Rinse cautiously with water for several minutes.

Remove contact lenses if the victim does and if they can be easily removed. Continue rinsing

P310 - Call a physician immediately

P332 + P313 - If skin irritation occurs: Get medical advice

P362 + P364 - Take off contaminated clothing and wash before reuse



2.3. Other hazards

No additional information available

SECTION 3: Composition/informations on ingredients

3.1. Substance Not applicable
3.2. Mixture

Name	Product identifier	%	Classification according to Directive 67/548 / EEC
SODIUM LAURETH SULFATE	(CAS n° : 68891-38-3) (CE n° : 500 -234-8	10 à 15 %	Xi; R38 Xi; R41

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
SODIUM LAURETH SULFATE	(CAS n°) 68891-38-3 (CE n°) 500-234-8	10 - 15 %	Skin Irrit. 2, H315 Eye Dam. 1, H318

Text of R and H phrases: see section 16

SECTION 4: First Aid

4.1. Description of the first aid :

General First Aid: Never give anything by mouth to an unconscious person. If you feel unwell consult a doctor (if possible show the label).

First aid for inhalation: Fresh air. Allow the victim to rest.
First aid for skin contact: Wash thoroughly with soap and water. Wash contaminated clothing before re use.
If skin irritation occurs: Get medical attention. See a doctor. Specific treatment (see ... on this label).
First aid after eye contact: Rinse cautiously with water for several minutes.
Remove contact lenses if the victim wears them and if they can be easily removed.
Continue rinsing.
Call a POISON CENTER or physician.

First aid after swallowing: Rinse mouth. DO NOT induce vomiting. Obtain emergency medical attention.

4.2. Important symptoms and effects, both acute and delayed

Symptoms / injuries after skin contact: Causes skin irritation.
Symptoms / injuries after eye contact: Causes serious eye damage.

4.3. Indication of immediate medical attention and special treatment needed

Symptomatic treatment.

SECTION 5: Measures against fire

5.1. Extinguishing Media

Suitable extinguishing media: Foam. Dry powder. Carbon dioxide. Water spray. Sable.
Unsuitable extinguishing media: Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

No additional information available

5.3. Advice for firefighters

Instructions fight against fire: Cool exposed containers by water spray or fog.
Exercise caution when fighting any chemical fire.
Avoid wastewater struggle against fire contaminate the environment.

Protection in the event of fire: Do not enter fire area without proper protective equipment, including protection breathing.

SECTION 6: Measures in case of Accidental Release

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non rescuers

Emergency procedures: Evacuate unnecessary personnel.

6.1.2. For rescuers

Protective equipment: Provide adequate protection to cleaning teams.
Emergency procedures: Ventilate the area.

6.2. Precautions for environmental protection

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and materials for containment and cleaning

Methods for cleaning: Absorb spilled as quickly as possible with inert solids such as clay or diatomaceous earth.
Collect spillage. Store away from other materials.

6.4. Reference to other sections

See Section 8. Exposure controls / personal protection.

SECTION 7: Handling & Storage

7.1. Precautions for safe handling

Precautions for safe handling: Wash hands and other exposed areas with mild soap and water before eating, drinking, smoking and when leaving work.

Hygiene measures:

Ensure good ventilation of the work area to avoid vapor formation.

Wash hands thoroughly after handling.

7.2. Conditions for safe storage, including any incompatibilities

Storage: Keep only in the original container in a cool, well ventilated place away
Keep containers closed when not in use.

Incompatible products: Strong bases. Strong acids.

Incompatible materials: Ignition sources. Direct sunlight.

7.3. Use (s) Final (s) specific (s)

No additional information available

SECTION 8: Exposure controls / personal protection

8.1. Control parameters No additional information available

8.2. Exposure controls

Personal protective equipment: Avoid all unnecessary exposure.

Hand protection: Wear protective gloves

Eye Protection: Splash goggles or safety glasses

Skin and body: Wear suitable protective clothing

Respiratory protection: Wear a suitable mask

Other information: Do not eat, do not drink and do not smoke while use.

SECTION 9: Physical and chemical properties

9.1. Basic physical and chemical properties Information

Physical State: Liquid
Color: Colorless.
Odour: Characteristic.
Odour threshold: No data available
pH: No data available

Relative evaporation rate (butylacetate = 1): No data available

Melting point: No data available

Freezing point: No data available

Boiling point: 100 ° C

Flash point: 98 ° C

Auto-ignition temperature: No data available

Decomposition temperature: No data available

Flammability (solid, gas): Non flammable

Vapour pressure: 23 hPa at 20°C

Relative vapor density at 20 ° C: No data available

Relative density: No data available

Solubility: Miscible in water

Log Pow: No data available

Viscosity, kinematic: No data available

Viscosity, dynamic: No data available

Explosive properties: No data available

Oxidizing properties: No data available

Explosive limits: No data available

9.2. other information

No additional information available

SECTION 10: Stability & Reactivity

SECTION 13: Disposal considerations

13.1. Waste treatment methods Recommendations for waste disposal
Dispose of according to local safety regulations / national regulations.
Ecology - waste materials: Avoid release to the environment.

SECTION 14: Transport information

Pursuant to the requirements of ADR / RID / IMDG / IATA / DNA

14.1. UN number

Not regulated for transport

14.2. UN shipping name

Shipping name (ADR): Not applicable
Shipping name (IMDG): Not applicable
Shipping name (IATA): Not applicable
Shipping Name (ADN): Not applicable
Shipping Name (RID): Not applicable

14.3. Class (es) hazard ADR transportation

Class (es) of danger for transport (ADR): Not applicable

IMDG

Class (es) of danger for transport (IMDG): Not applicable

IATA

Class (es) of danger for transport (IATA): Not applicable

DNA

Class (es) of danger for transport (ADN): Not applicable

RID

Class (es) of Transport hazard (RID): Not applicable

14.4. Packing group

Packing Group (ADR): Not applicable
Packing Group (IMDG): Not applicable
Packing Group (IATA): Not applicable
Packing Group (ADN): Not applicable
Packing group (RID): Not applicable

14.5. Environmental hazards

Dangerous for the environment: No
Marine pollutant: No
Other information: No supplementary information available

14.6. Special precautions for user

14.6.1. Road transport

14.6.2. Maritime transport

14.6.3. Air transport

14.6.4. Waterway transportation

Not subject to ADN: No

14.6.5. Rail transport

Prohibited transport (RID): No

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1. Regulations / legislation specific for the substance or mixture Safety, health and environment

15.1.1. EU regulations

Does not contain substances subject to restrictions of Annex XVII
Does not contain substances of the REACH candidate list
Does not contain substances listed in Annex XIV of REACH

15.1.2. National regulations

No additional information available

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out

SECTION 16: Others informations

Data sources: REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labeling and packaging of substances and mixtures, amending and repealing Directives 67/548 / EEC and 1999/45 / EC and amending Regulation (EC) No 1907/2006.

Other information: None (e).

Textes des phrases R-,H- et EUH:

Eye Dam. 1	Serious eye damage / eye irritation, Category 1
Skin Irrit. 2	Corrosive / irritating to the skin, category 2
H315	Causes skin irritation
H318	Causes serious eye damage
R38	Irritating to the skin
R41	Risk of eye damage
Xi	Irritant

Classification and procedure used to determine the classification of mixtures in accordance with regulation (EC) 1272/2008 [CLP]

Skin Irrit. 2	H315	Calculation method
Eye Dam. 1	H318	Calculation method