


**KEMET Part Number: T350E106M025AT7301**  
(T350E106M025ATTR)

Tantalum, MnO2 Tantalum, Commercial Grade, T350, 10 uF, 20%, 25 V, Radial, Solid Tantalum, Conformal, Dipped, Lead Spacing = 2.54mm



General Information	
<b>Dielectric:</b>	MnO2 Tantalum
<b>Style:</b>	Radial
<b>Series:</b>	T350
<b>Description:</b>	Radial, Solid Tantalum, Conformal, Dipped
<b>Features:</b>	Low Leakage
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Notes:</b>	Longest Lead Is Positive

Dimensions	
<b>D</b>	5.5mm
<b>H</b>	8.9mm
<b>S</b>	2.54mm +/-0.38mm
<b>LL</b>	12.7mm +/-1.26mm
<b>F</b>	0.5mm +/-0.05mm

Specifications	
<b>Capacitance:</b>	10 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	25 VDC (85C), 21 VDC (125C Surge), 0.25 V (125C Reverse)
<b>Temperature Range:</b>	-55/+125C
<b>Dissipation Factor:</b>	6%
<b>Leakage Current:</b>	2 uAmps

Packaging Specifications	
<b>Packaging:</b>	T&R, 305mm
<b>Packaging Quantity:</b>	1000