

EADI250D

Air Duster

EADI250D utilises HFC152A propellant which offers a lower degree of flammability in use when compared to standard hydrocarbon propellants. It has been designed for the removal of dust and airborne contamination from very delicate or inaccessible areas of electrical and electronic equipment. EADI250D is an invertible product, which is particularly useful for very intricate equipment or items which cannot be moved for cleaning or maintenance.

- Inert, pure compressed gas for dust removal
- Ideal for removing particulates from inaccessible areas on delicate equipment
- Non-VOC according to US regulations
- Low global warming potential

Typical Properties

Colour	Colourless
Flash Point (°C)	<50°C
GWP	140

<u>Description</u>	<u>Packaging</u>	<u>Order Code</u>	<u>Shelf Life</u>
<u>Invertible Airduster</u>	250ml Aerosol	EADI250D	48 months

Directions for Use

EADI250D can be used in any direction and should be sprayed in short sharp blasts. Although this product has a lower flammability level than other flammable solvents, it is still not advised to spray directly onto live equipment.

Caution: Do not use EADI250D for prolonged blasts as the surface of the can will form frost.

Revision 0: April 2017

Copyright Electrolube 2013

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification.

Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.

Ashby Park, Coalfield Way,
Ashby de la Zouch,
Leicestershire LE65 1JR
T +44 (0)1530 419 600
F +44 (0)1530 416 640
BS EN ISO 9001:2008
Certificate No. FM 32082