

HAKKO 951·952 ESD SAFE

SOLDERING GUN



- Available for your Hakko 701, 702B, 928, 936, or 937.
- ESD safe by design.
- Compact design and light weight.
- Easy positioning for the solder feeding.
- A variety of tip type.

Specifications


Model No.	951	952
Type	M	L
Power Consumption	AC 24V/50W	
Standard Tip	900M-T-S10	900L-T-B
Temperature Range	200-480°C	
Tip to Ground Resistance	< 2Ω	
Tip to Ground Potential	< 2mV (Typ. 0.6mV)	
Heating Element	Ceramic Heater	
Standard Guide Nozzle	ø1.0 (B2654)	
Usable Solder Dia.	ø0.6, 0.8, 1.0, 1.2, 1.6	
Outer Dimensions	170(W) x 180(H)mm	
Weight (w/o cord)	177g	187g

Optional Parts


Part No.	Name/Description
B2652	Guide Nozzle for ø 0.6mm/ESD
B2653	Guide Nozzle for ø 0.8mm/ESD
B2654	Guide Nozzle for ø 1.0mm/ESD
B2655	Guide Nozzle for ø 1.2mm/ESD
B2656	Guide Nozzle for ø 1.6mm/ESD
A1321	Heating Element
C1437	Iron Holder

Replacement Tips

Medium For 951



Large For 952



Unit : mm

Tip Out Dia ø8.5mm
* For heavy duty soldering Hakko recommends the 952 gun with heavier tips.

CAUTION

Use only genuine replacement tips for Hakko 951, 952. The tips for Hakko Dash are not available to use.
* These tips are tinned flat only.

Tip Out Dia ø6.5mm