

2.0Megapixel 1080P HDCVI PIR Style Hidden Camera



Features

- ''' 1/2.8" 2.0Megapixel CMOS
- ''' 25/30fps@1080P, 25/30/50/60fps@720P
- ''' High speed, long distance real-time transmission
- ''' HD definition
- ''' OSD Menu, DVR control as default, coaxial control optional''''
- ''' Day/Night (ICR), AWB, AGC, BLC, 2D-DNR
- ''' 3.7mm pinhole lens
- ''' DC12V

Technical Specifications

Model	82-20320
Camera	
Image Sensor	1/2.8" 2Megapixel CMOS
Effective Pixels	1920(H)×1080(V)
Electronic Shutter	1/60s~1/60,000s
Video Frame Rate	25/30fps@1080P, 25/30/50/60fps@720P
Synchronization	Internal
Min. Illumination	0.01Lux@F1.2(AGC ON)
Video Output	1-channel BNC HDCVI high definition video output/ CVBS 960H definition video output (Can switch)
Camera Features	
Max. IR LEDs Length	N/A
Day/Night	Auto / Color / B/W
Noise Reduction	2D
OSD Menu	Support
Lens	
Focal Length	3.7mm pinhole lens
General	
Power Supply	DC12V±10%
Power Consumption	Max 8W
Working Environment	-20°C~+60°C / Less than 95%RH (no condensation)
Transmission Distance	Over 500m via 75-3 coaxial cable
Ingress Protection	N/A
Dimensions	Φ120mm×60mm
Weight	0.18kg

Dimensions (mm)

