

89740 Multi-Conductor - Audio, Control and Instrumentation Cable

For more Information
please call

1-800-Belden1



General Description:

18 AWG stranded (19x30) tinned copper conductors, plenum, FEP insulation, twisted pair, FEP jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	18	19x30	TC - Tinned Copper

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
FEP - Fluorinated Ethylene Propylene	.007

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (in.)
Teflon®	FEP - Fluorinated Ethylene Propylene	.009

Overall Cable

Overall Nominal Diameter: 0.132 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Bulk Cable Weight: 15 lbs/1000 ft.

Max. Recommended Pulling Tension: 49 lbs.

Min. Bend Radius/Minor Axis: 1.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CL3P, CMP

CEC/C(UL) Specification: CMP

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MIL Order #39 (China RoHS): Yes

Flame Test

89740 Multi-Conductor - Audio, Control and Instrumentation Cable

UL Flame Test: NI-PA 262

CSA Flame Test: FT6

Plenum/Non-Plenum

Plenum (Y/N): Yes

Non-Plenum Number: 9740

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

72

Nom. Inductance:

Inductance (µH/ft)

0.14

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

20

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

5.5

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

5.4 Amps per conductor @ 25°C

Notes (Overall)

Notes: For use in indoor plenum environments but also suitable for outdoor and underground applications. Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
89740 002100	100 FT	3,000 LB	RED	C	2#18 FEP FEP
89740 0021000	1,000 FT	16,000 LB	RED	C	2#18 FEP FEP
89740 0023000	3,000 FT	48,000 LB	RED	C Z	2#18 FEP FEP
89740 002500	500 FT	9,000 LB	RED	C	2#18 FEP FEP
89740 0025000	5,000 FT	80,000 LB	RED	C Z	2#18 FEP FEP

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 2 Revision Date: 09-20-2012

© 2016 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).