

Inductors

VHF chokes

Series/Type: B82111B Date: June 2012

© EPCOS AG 2015. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.



VHF chokes

B82111B

Rated voltage 500 V AC/DC Rated current 2 ... 10 A Rated inductance 3 ... 25 µH

Construction

- Ferrite cylinder core
- Winding: single-layer, enamel copper wire, winding ends brought out as leads
- Polyester insulating sleeve

Features

- High resonant frequency
- High rated current
- Suitable for wave soldering
- RoHS-compatible
- ENEC10 approval 400

Applications

- RF blocking and filtering
- Interference suppression in small appliances

Terminals

- Central axial leads
- Base material Cu
- Hot-dip tinned with pure tin


Marking

L_B and I_B in clear text and approval mark

Delivery mode

Bulk

Dimensional drawing



Dimensions in mm

Please read *Cautions and warnings* and *Important notes* at the end of this document.



VHF chokes

Technical data and measuring conditions

Test voltage V _{test}	2500 V AC, 1 min					
Rated inductance L _R	$ \begin{array}{llllllllllllllllllllllllllllllllllll$					
Inductance tolerance	±20%					
Rated temperature T _R	+60 °C					
Rated current I _R	Maximum permissible DC current at rated temperature					
DC resistance R _{typ}	Measured at +20 °C, tolerance ±20%, typical values					
Resonance frequency fres	Measured with Agilent 4294A or 8753ES, +20 $^\circ\text{C}$ tolerance $\pm30\%$					
Solderability (lead-free)	Sn95.5Ag3.8Cu0.7: +(245 \pm 5) °C, (3 \pm 0.3) s Wetting of soldering area \geq 90% (to IEC 60068-2-20, test Ta)					
Resistance to soldering heat (wave soldering)	+(260 ±5) °C, 10 s (to IEC 60068-2-20, test Tb)					
Tensile strength of leads	≥ 30 N (to IEC 60068-2-21, test Ua)					
Climatic category	55/125/56 (to IEC 60068-1)					
Storage conditions	Mounted: -55 °C +125 °C Packaged: -25 °C +40 °C, ≤ 75% RH					
Approvals	EN 60938					

▲ Mounting information

When bending the leads, take care that the bending point is **at least 3 mm** apart from the face ends of the core and that the start-of-winding areas are not subjected to any mechanical stress.

②TDK

VHF chokes

B82111B

I _R	L _R	R _{typ}	f _{res}	Dimensions (mm)				Approx. weight	Ordering code	Approvals
	μH	Ω	MHz	I _{1-1.5}	I ₂₋₃	d _{1 max.}	d ₂	g		10
2	17	0.063	100	18.3	24	7.0	0.45	3.0	B82111B0000C014	×
3	8	0.025	145	18.3	24	7.0	0.63	3.0	B82111B0000C013	×
3	13	0.024	170	24.5	29	6.5	0.67	3.5	B82111B0000C019	×
3	20	0.054	125	24.5	29	6.0	0.5	3.5	B82111B0000C020	×
3	25	0.046	85	28.5	34	8.5	0.63	6.0	B82111B0000C024	×
4	6	0.017	170	18.3	24	7.5	0.75	3.0	B82111B0000C012	×
4	11	0.020	150	24.5	29	6.5	0.71	6.0	B82111B0000C018	×
4	15	0.024	120	28.5	34	8.5	0.75	7.0	B82111B0000C023	×
6	4	0.014	205	18.3	24	7.5	0.8	4.0	B82111B0000C011	×
6	6	0.010	200	24.5	29	7.0	0.95	5.0	B82111B0000C017	×
6	9	0.012	150	28.5	34	9.0	0.95	8.0	B82111B0000C022	×
9	3	0.006	220	24.5	29	7.5	1.2	5.0	B82111B0000C016	×
10	5	0.005	175	28.5	34	9.5	1.3	10.0	B82111B0000C021	×


Characteristics and ordering codes

 \times = approval granted


Impedance |Z| versus frequency f

measured with impedance analyzer Agilent 4294A or S-parameter network analyzer Agilent 8753ES, typical values at +20 $^\circ\text{C}$

B82111B0000C011...C014



B82111B0000C016...C020



Please read *Cautions and warnings* and *Important notes* at the end of this document.


Λ



Impedance |Z| versus frequency f


measured with impedance analyzer Agilent 4294A or S-parameter network analyzer Agilent 8753ES, typical values at +20 °C

B82111B0000C021...C024



Current derating I_{op}/I_R versus ambient temperature T_A

(rated temperature $T_{R} = +60 \ ^{\circ}C$)





Cautions and warnings

- Please note the recommendations in our Inductors data book (latest edition) and in the data sheets.
 - Particular attention should be paid to the derating curves given there.
 - The soldering conditions should also be observed. Temperatures quoted in relation to wave soldering refer to the pin, not the housing.
- If the components are to be washed varnished it is necessary to check whether the washing varnish agent that is used has a negative effect on the wire insulation, any plastics that are used, or on glued joints. In particular, it is possible for washing varnish agent residues to have a negative effect in the long-term on wire insulation.

Washing processes may damage the product due to the possible static or cyclic mechanical loads (e.g. ultrasonic cleaning). They may cause cracks to develop on the product and its parts, which might lead to reduced reliability or lifetime.

- The following points must be observed if the components are potted in customer applications:
 - Many potting materials shrink as they harden. They therefore exert a pressure on the plastic housing or core. This pressure can have a deleterious effect on electrical properties, and in extreme cases can damage the core or plastic housing mechanically.
 - It is necessary to check whether the potting material used attacks or destroys the wire insulation, plastics or glue.
 - The effect of the potting material can change the high-frequency behaviour of the components.
- Ferrites are sensitive to direct impact. This can cause the core material to flake, or lead to breakage of the core.
- Even for customer-specific products, conclusive validation of the component in the circuit can only be carried out by the customer.



The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.

We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

- 6. Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI).
- 7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CeraLink, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, FilterCap, FormFit, MiniBlue, MiniCell, MKD, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.