# **Product datasheet** Characteristics

# NSYS3D10830P

Spacial S3D plain door with mount.plate. H1000xW800xD300 IP66 IK10 RAL7035.



### Main

Spacial
Spacial S3D
Multi-purpose
Compact enclosure
1000 mm
800 mm
300 mm
Plain
Plain
Standard
Wall-mounting
Body 1 Cable gland plate 2 Mounting plate 1 Door with lock 1

### Complementary

Main		
Range	Spacial	
Product name	Spacial S3D	
Device application	Multi-purpose	
Product or component type	Compact enclosure	
Enclosure nominal height	1000 mm	
Enclosure nominal width	800 mm	
Enclosure nominal depth	300 mm	
Door type	Plain	
Mounting plate description	Plain	
Type of gland plate	Standard	
Installation accessory type	Wall-mounting	
Device composition	Body 1 Cable gland plate 2 Mounting plate 1 Door with lock 1	
Complementary		
Variant particularity	Gutter-shaped front rail double sheet thickness Single piece body	
Number of doors	1 front face	
Door opening	Reversible 120 °	
Lock type	3 points lock, 3 mm double-bar	
Accessibility for operation	Front	
Removable parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element	
Material	Galvanised steel for mounting plate	
	Steel for enclosure	

Colour	Grey RAL 7035 enclosure :
Standards	IEC 62208
Product certifications	GL CUL DNV BV UL LR

## Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

## Offer Sustainability

Sustainable offer status	Green Premium product	
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity	
	Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	
	Reference not containing SVHC above the threshold	
Product environmental profile	Available	
	Product environmental	
Product end of life instructions	Need no specific recycling operations	-
	Product environmental	

#### Contractual warranty

Contractual warranty		
Warranty period	18 months	