



For more Information
please call

1-800-Belden1



General Description:

18 AWG solid .040" bare copper-covered steel conductor, foam FEP insulation, Duofoil® (100% coverage) plus a tinned copper braid shield (95% coverage), FEP jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	18	Solid	BCCS - Bare Copper Covered Steel	.040

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
FFEP - Foam Fluorinated Ethylene Propylene	.170

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
FEP - Fluorinated Ethylene Propylene

Overall Cable

Overall Nominal Diameter: 0.234 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-70°C To +200°C
Bulk Cable Weight:	43 lbs/1000 ft.
Max. Recommended Pulling Tension:	141 lbs.
Min. Bend Radius/Minor Axis:	2.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CATVP, CMP
CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes
Series Type:	Series 6

Flame Test

UL Flame Test: NFPA 262

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

89120 Coax - CATV Cable

CSA Flame Test: FT6

Plenum/Non-Plenum

Plenum (Y/N): Yes

Plenum Number: 87120, 82120

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/ft)

.09

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

16.5

Nominal Velocity of Propagation:

VP (%)

82

Nominal Delay:

Delay (ns/ft)

1.24

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

28.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

1.7

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	.3
10	.66
50	1.6
100	2.2
200	3.0
400	4.6
700	6.6
900	7.7
1000	8.2

Max. Operating Voltage - UL:

Voltage

300 V RMS

Minimum Structural Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
		5	400	20

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
89120 0101000	1,000 FT	46.000 LB	BLACK	C	#18 FFEP SH FEP
89120 010500	500 FT	23.000 LB	BLACK	C	#18 FFEP SH FEP

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 08-28-2012

© 2016 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the



product.