


7988P Multi-Conductor - 4-Pair UTP Cable for RGB Video



For more Information
please call

1-800-Belden1

**General Description:**

Category 5e, 24 AWG bonded pairs solid bare copper conductors, plenum, FEP Teflon insulation, skew 9.0ns/100m nominal, rip cord, Flamarrest® jacket.

Usage (Overall)

Suitable Applications:

Category 5e, UTP Based Video Applications, and KVM

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

Total Number of Conductors:

8

Insulation

Insulation Material:

Insulation Material
FEP - Fluorinated Ethylene Propylene

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride

Outer Jacket Ripcord:

Yes

Overall Cable

Overall Nominal Diameter:

0.193 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range:

-20°C To +75°C

Bulk Cable Weight:

21 lbs/1000 ft.

Max. Recommended Pulling Tension:

40 lbs.

Min. Bend Radius/Minor Axis:

2 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:

CMP

CEC/C(UL) Specification:

CMP

EU Directive 2011/65/EU (RoHS II):

Yes

EU CE Mark:

Yes

EU Directive 2000/53/EC (ELV):

Yes

EU Directive 2002/95/EC (RoHS):

Yes

7988P Multi-Conductor - 4-Pair UTP Cable for RGB Video

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes
Other Specification:	NEMA WC-63.1 Category 5e, UL Verified to Category 5e

Applicable Patents:

Country
www.belden.com/p

Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	7988R

Electrical Characteristics (Overall)

Maximum Capacitance Unbalance (pF/100 m):	66
---	----

Nominal Velocity of Propagation:

VP (%)
72

Typical Delay Skew:

Delay Skew (ns/ft)
0.027

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)
1	2.0	65.3	65.3	60.3	60.3	20.0
4	4.1	56.3	53.3	49.2	49.2	23.0
8	5.8	51.8	48.8	43.0	43.0	24.5
10	6.5	50.3	47.3	40.8	40.8	25.0
16	8.2	47.3	44.3	36.0	36.0	25.0
20	9.3	45.8	42.8	33.5	33.5	25.0
25	10.4	44.3	41.3	30.9	30.9	24.3
31.25	11.7	42.9	39.9	28.2	28.2	23.6
62.5	17.0	38.4	35.4	18.4	18.4	21.5
100	22.0	35.3	32.3	10.3	10.3	20.1
155	28.1	32.5	29.54	2.0	2.0	15.8
200	32.4	30.8	27.8	1.0	1.0	15.0

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	100 ± 15	63.8	60.8
4	100 ± 15	100 ± 15	51.7	48.7
8	100 ± 15	100 ± 15	45.7	42.7
10	100 ± 15	100 ± 15	43.8	40.8
16	100 ± 15	100 ± 15	39.7	36.7
20	100 ± 15	100 ± 15	37.7	34.7
25	100 ± 15	100 ± 15	35.8	32.8
31.25	100 ± 15	100 ± 15	33.9	30.9
62.5	100 ± 15	100 ± 15	27.8	24.8
100	100 ± 15	100 ± 15	23.8	20.8
155	100 ± 25	100 ± 15	19.9	16.9

7988P Multi-Conductor - 4-Pair UTP Cable for RGB Video

200	100 ± 25	100 ± 15	17.7	14.7
-----	----------	----------	------	------

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft. intervals. Electricals are preliminary, final data is pending.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7988P N3UU1000	1,000 FT	23.000 LB	GREEN, MIL		4 PR #24 FEP PVC

Revision Number: 3 Revision Date: 03-11-2014

© 2016 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).