


## FEATURES

### EDLC (Electric Double Layer Capacitor)

- High Power Density (Low ESR)
- Over 500,000 cycle life (semi-permanent)
- Higher energy density compared with 2.7V caps
- RoHS compliant



## Drawing



D (Φ)	8
d (Φ)	0.6
P (mm)	3.5

## SPECIFICATION

ITEM		CHARACTERISTICS	
Product series		EDLC	
Rated Voltage ( $V_R$ )		3.0V	
Operating Temperature		-40 ~ +65 °C	
Capacitance Tolerance		-10 ~ +30%	
High Temperature Load Life		After 1,000 hours at $V_R$ loaded under +65 °C, capacitors meet the following criteria.	
		Capacitance Change	≤ 30% of initial value
		ESR	≤ 2 times of specified value
		85°C Higher Temperature	Max. 2.4V
Cycle Life Characteristics	Cycle	Over 500,000	
	$\Delta C$	≤ 30% of initial value	
	ESR	≤ 2 times of specified value	
	Method	Cycle of Charge/discharge from $V_R$ to $1/2V_R$	
Shelf Life		2 Years No Electrical Charge, Temperature below 70 °C ( $\Delta C$ : ≤ 10% of initial value / $\Delta ESR$ : ≤ 50% of specified value)	

Part Number	Rated Voltage (V)	Capacitance (F)	ESR (mΩ)		Max. Current (A)	Leakage Current (mA, 72hr)	Weight (g)	Volume (ml)
			AC(1kHz)	DC				
VEC 3R0 105 QG	3.0	1	145	220	1.0	0.003	1.1	0.7

\* Max. Current : 1 sec. discharge to  $1/2V_R$