



For more Information
please call

1-800-Belden1



General Description:

4-conductor SO oil-resistant rubber jacket, 600V, 90°C, paper tape separator, smooth jacket, UL/CSA listed, color code: black, white, green, red.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
4	14	41x30	BC - Bare Copper

Total Number of Conductors: 4

Type of Cordage: SO

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
EPDM - Ethylene Propylene Diene Monomer Rubber	0.048

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
Rubber	.087

Overall Cable

Overall Cabling Fillers: Jute

Overall Cabling Color Code Chart:

Color
Black
White
Green
Red

Overall Cabling Separator Material: Paper Tape

Overall Nominal Diameter: 0.603 in.

Mechanical Characteristics (Overall)

Bulk Cable Weight: 202 lbs/1000 ft.

Min. Bend Radius/Minor Axis: 6.250 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC(UL) Specification: SO

CSA Specification: SO

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

19217 Portable Cordage - UL/CSA Types: SVT, SO

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

CSA Flame Test:	FT2
-----------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Surface Printing (Overall)**Electrical Characteristics (Overall)****Max. Operating Voltage - UL:****Voltage**

600 V RMS

Max. Recommended Current:**Current**

15 Amps per conductor @ 25°C

10 Amps per conductor @ 25°C (over 50 ft.)

Dielectric Withstand Voltage:	3000 V AC Applied for 1 Min.
-------------------------------	------------------------------

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
19217 010200	200 FT	43.600 LB	BLACK	C	4 #14 EPDM CPE TYPE SO
19217 01050	50 FT	11.800 LB	BLACK	C	4 #14 EPDM CPE TYPE SO

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 10-16-2012

© 2016 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).